

Definitions of Historic Events for SG6800

Table 1. Event Categories and Codes

Category Name	Category Code
DAT	1
BAT	2
DNP	3
LOG	4
SUM	5
CMD	8
CFM	11
FLT	12
SWX	13
FPX	14
ACW	15
WFC	16
IIM	22
WFM	23
UTL	24
NET	27
PGE	28
SER	29
EVT	30
RTL	31

Table 2. Types of Additional Data Items for Historic Events (175 items)

Data Type Name	Represented As	Type Information																																				
Action	UINT16	<p>Action in action path</p> <table border="1"> <thead> <tr> <th colspan="3">Enumeration</th> </tr> <tr> <th>Binary</th> <th>Value</th> <th>Description</th> </tr> </thead> <tbody> <tr> <td>4</td> <td>CloseForXfer</td> <td>Close for xfer</td> </tr> <tr> <td>20</td> <td>ContractRequest</td> <td>Contract request</td> </tr> <tr> <td>21</td> <td>ContractTerminate</td> <td>Contract Terminate</td> </tr> <tr> <td>30</td> <td>BlockRecloser</td> <td>Block recloser</td> </tr> <tr> <td>31</td> <td>UnblockRecloser</td> <td>Unblock recloser</td> </tr> <tr> <td>33</td> <td>BlockGroundTrip</td> <td>Block ground trip</td> </tr> <tr> <td>34</td> <td>UnblockGroundTrip</td> <td>Unblock ground trip</td> </tr> <tr> <td>36</td> <td>AlternateSettings</td> <td>Alternate settings</td> </tr> <tr> <td>37</td> <td>Normal</td> <td>Normal</td> </tr> <tr> <td>200</td> <td>ActionPathDone</td> <td>Action path done</td> </tr> </tbody> </table>	Enumeration			Binary	Value	Description	4	CloseForXfer	Close for xfer	20	ContractRequest	Contract request	21	ContractTerminate	Contract Terminate	30	BlockRecloser	Block recloser	31	UnblockRecloser	Unblock recloser	33	BlockGroundTrip	Block ground trip	34	UnblockGroundTrip	Unblock ground trip	36	AlternateSettings	Alternate settings	37	Normal	Normal	200	ActionPathDone	Action path done
Enumeration																																						
Binary	Value	Description																																				
4	CloseForXfer	Close for xfer																																				
20	ContractRequest	Contract request																																				
21	ContractTerminate	Contract Terminate																																				
30	BlockRecloser	Block recloser																																				
31	UnblockRecloser	Unblock recloser																																				
33	BlockGroundTrip	Block ground trip																																				
34	UnblockGroundTrip	Unblock ground trip																																				
36	AlternateSettings	Alternate settings																																				
37	Normal	Normal																																				
200	ActionPathDone	Action path done																																				
ActiveURBEClassMask	UINT16	<p>Active URBE Class Mask</p> <table border="1"> <thead> <tr> <th colspan="3">Enumeration</th> </tr> <tr> <th>Binary</th> <th>Value</th> <th>Description</th> </tr> </thead> <tbody> <tr> <td>0</td> <td>None</td> <td>No URBE</td> </tr> <tr> <td>2</td> <td>Class1</td> <td>Class 1 active</td> </tr> <tr> <td>4</td> <td>Class2</td> <td>Class 1 active</td> </tr> <tr> <td>6</td> <td>Class12</td> <td>Class 1 and 2 active</td> </tr> <tr> <td>8</td> <td>Class3</td> <td>Class 3 active</td> </tr> <tr> <td>10</td> <td>Class13</td> <td>Class 1 and 3 active</td> </tr> <tr> <td>12</td> <td>Class23</td> <td>Class 2 and 3 active</td> </tr> </tbody> </table>	Enumeration			Binary	Value	Description	0	None	No URBE	2	Class1	Class 1 active	4	Class2	Class 1 active	6	Class12	Class 1 and 2 active	8	Class3	Class 3 active	10	Class13	Class 1 and 3 active	12	Class23	Class 2 and 3 active									
Enumeration																																						
Binary	Value	Description																																				
0	None	No URBE																																				
2	Class1	Class 1 active																																				
4	Class2	Class 1 active																																				
6	Class12	Class 1 and 2 active																																				
8	Class3	Class 3 active																																				
10	Class13	Class 1 and 3 active																																				
12	Class23	Class 2 and 3 active																																				



Definitions of Historic Events

		14 Class123 Class 1 and 2 and 3 active																																	
Agent	UINT16	<p>Numeric Type, Range: 0-65535</p> <table border="1" style="margin-left: auto; margin-right: auto;"> <thead> <tr> <th>Action</th><th>Value</th></tr> </thead> <tbody> <tr> <td>Multiplier</td><td>1</td></tr> <tr> <td>Adder</td><td>0</td></tr> </tbody> </table>	Action	Value	Multiplier	1	Adder	0																											
Action	Value																																		
Multiplier	1																																		
Adder	0																																		
AnyPhaseLoss	UINT16	<p>Pole X Phase Loss</p> <p>Numeric Type, Range: 0-15</p> <table border="1" style="margin-left: auto; margin-right: auto;"> <thead> <tr> <th>Action</th><th>Value</th></tr> </thead> <tbody> <tr> <td>Multiplier</td><td>1</td></tr> <tr> <td>Adder</td><td>0</td></tr> </tbody> </table>	Action	Value	Multiplier	1	Adder	0																											
Action	Value																																		
Multiplier	1																																		
Adder	0																																		
AverageLoad	UINT16	<p>Averaged Load</p> <p>Numeric Type, Range: 0-65535</p> <table border="1" style="margin-left: auto; margin-right: auto;"> <thead> <tr> <th>Action</th><th>Value</th></tr> </thead> <tbody> <tr> <td>Multiplier</td><td>1</td></tr> <tr> <td>Adder</td><td>0</td></tr> </tbody> </table>	Action	Value	Multiplier	1	Adder	0																											
Action	Value																																		
Multiplier	1																																		
Adder	0																																		
BMMRESULT	UINT16	<p>BMM RESULT</p> <p>Enumeration</p> <table border="1" style="margin-left: auto; margin-right: auto;"> <thead> <tr> <th>Binary</th><th>Value</th><th>Description</th></tr> </thead> <tbody> <tr> <td>0</td><td>BMMRESSUCS</td><td>BMM Result is Successful</td></tr> <tr> <td>1</td><td>BMMRESBADREQ</td><td>BMM Result is bad</td></tr> <tr> <td>2</td><td>BMMRESBUSY</td><td>BMM Result is busy</td></tr> <tr> <td>3</td><td>BMMRESBMMUNAVA</td><td>BMM Result is unavailable</td></tr> <tr> <td>4</td><td>BMMRESBMMREADFAIL</td><td>BMM Result failed to read</td></tr> <tr> <td>5</td><td>BMMRESBMMWRITEFAIL</td><td>BMM Result failed to write</td></tr> <tr> <td>6</td><td>BMMRESRENMATCO</td><td>BMM Result Read but not matching copy</td></tr> <tr> <td>7</td><td>BMMRESOVERFLOW</td><td>BMM Result has overflowed</td></tr> <tr> <td>8</td><td>BMMRESBADRECORD</td><td>BMM Result has a bad record</td></tr> <tr> <td>9</td><td>BMMRESNOFON</td><td>BMM Result is not found</td></tr> </tbody> </table>	Binary	Value	Description	0	BMMRESSUCS	BMM Result is Successful	1	BMMRESBADREQ	BMM Result is bad	2	BMMRESBUSY	BMM Result is busy	3	BMMRESBMMUNAVA	BMM Result is unavailable	4	BMMRESBMMREADFAIL	BMM Result failed to read	5	BMMRESBMMWRITEFAIL	BMM Result failed to write	6	BMMRESRENMATCO	BMM Result Read but not matching copy	7	BMMRESOVERFLOW	BMM Result has overflowed	8	BMMRESBADRECORD	BMM Result has a bad record	9	BMMRESNOFON	BMM Result is not found
Binary	Value	Description																																	
0	BMMRESSUCS	BMM Result is Successful																																	
1	BMMRESBADREQ	BMM Result is bad																																	
2	BMMRESBUSY	BMM Result is busy																																	
3	BMMRESBMMUNAVA	BMM Result is unavailable																																	
4	BMMRESBMMREADFAIL	BMM Result failed to read																																	
5	BMMRESBMMWRITEFAIL	BMM Result failed to write																																	
6	BMMRESRENMATCO	BMM Result Read but not matching copy																																	
7	BMMRESOVERFLOW	BMM Result has overflowed																																	
8	BMMRESBADRECORD	BMM Result has a bad record																																	
9	BMMRESNOFON	BMM Result is not found																																	
BMMSTATE	UINT16	<p>BMM STATE</p> <p>Enumeration</p> <table border="1" style="margin-left: auto; margin-right: auto;"> <thead> <tr> <th>Binary</th><th>Value</th><th>Description</th></tr> </thead> <tbody> <tr> <td>0</td><td>BMM_STATE_READY</td><td>BMM is ready to process API calls</td></tr> <tr> <td>1</td><td>BMM_STATE_BUSY</td><td>BMM is busy processing an API call or with maintenance</td></tr> <tr> <td>2</td><td>BMM_STATE_INIT</td><td>BMM is initializing</td></tr> <tr> <td>3</td><td>BMMSTATNOTDETECTED</td><td>BMM hardware is not accessible</td></tr> <tr> <td>4</td><td>BMM_STATE_ERROR</td><td>A fatal run-time error encountered during operation</td></tr> </tbody> </table>	Binary	Value	Description	0	BMM_STATE_READY	BMM is ready to process API calls	1	BMM_STATE_BUSY	BMM is busy processing an API call or with maintenance	2	BMM_STATE_INIT	BMM is initializing	3	BMMSTATNOTDETECTED	BMM hardware is not accessible	4	BMM_STATE_ERROR	A fatal run-time error encountered during operation															
Binary	Value	Description																																	
0	BMM_STATE_READY	BMM is ready to process API calls																																	
1	BMM_STATE_BUSY	BMM is busy processing an API call or with maintenance																																	
2	BMM_STATE_INIT	BMM is initializing																																	
3	BMMSTATNOTDETECTED	BMM hardware is not accessible																																	
4	BMM_STATE_ERROR	A fatal run-time error encountered during operation																																	
BooleanTrueFalse	UINT16	<p>Enumeration</p> <table border="1" style="margin-left: auto; margin-right: auto;"> <thead> <tr> <th>Binary</th><th>Value</th><th>Description</th></tr> </thead> <tbody> <tr> <td>0</td><td>false</td><td>false</td></tr> <tr> <td>1</td><td>true</td><td>true</td></tr> </tbody> </table>	Binary	Value	Description	0	false	false	1	true	true																								
Binary	Value	Description																																	
0	false	false																																	
1	true	true																																	
bufsiz	UINT16	<p>Numeric Type, Range: 0-65535</p> <table border="1" style="margin-left: auto; margin-right: auto;"> <thead> <tr> <th>Action</th><th>Value</th></tr> </thead> <tbody> <tr> <td>Multiplier</td><td>1</td></tr> <tr> <td>Adder</td><td>0</td></tr> </tbody> </table>	Action	Value	Multiplier	1	Adder	0																											
Action	Value																																		
Multiplier	1																																		
Adder	0																																		
CallbackStatus	UINT16	<p>Callback Status</p> <p>Enumeration</p> <table border="1" style="margin-left: auto; margin-right: auto;"> <thead> <tr> <th>Binary</th><th>Value</th><th>Description</th></tr> </thead> <tbody> <tr> <td>0</td><td>0</td><td>Normal</td></tr> <tr> <td>1</td><td>1</td><td>Warning</td></tr> <tr> <td>2</td><td>2</td><td>Error</td></tr> </tbody> </table>	Binary	Value	Description	0	0	Normal	1	1	Warning	2	2	Error																					
Binary	Value	Description																																	
0	0	Normal																																	
1	1	Warning																																	
2	2	Error																																	

		<table border="1"> <thead> <tr> <th>Binary</th><th>Value</th><th>Description</th></tr> </thead> <tbody> <tr> <td>0</td><td>ResponseReceived</td><td>Message response received successfully</td></tr> <tr> <td>1</td><td>NoResponse</td><td>Message received no response</td></tr> <tr> <td>2</td><td>ExpiredOnXmitList</td><td>Message expired on the transmit list</td></tr> <tr> <td>3</td><td>ResponseDataError</td><td>Message response data contained an error</td></tr> <tr> <td>4</td><td>NoAssocPeerDevice</td><td>Message had no associated peer device</td></tr> </tbody> </table>	Binary	Value	Description	0	ResponseReceived	Message response received successfully	1	NoResponse	Message received no response	2	ExpiredOnXmitList	Message expired on the transmit list	3	ResponseDataError	Message response data contained an error	4	NoAssocPeerDevice	Message had no associated peer device																																																																																							
Binary	Value	Description																																																																																																									
0	ResponseReceived	Message response received successfully																																																																																																									
1	NoResponse	Message received no response																																																																																																									
2	ExpiredOnXmitList	Message expired on the transmit list																																																																																																									
3	ResponseDataError	Message response data contained an error																																																																																																									
4	NoAssocPeerDevice	Message had no associated peer device																																																																																																									
ClearPRBlocker	UINT16	<table border="1"> <thead> <tr> <th colspan="3">Enumeration</th></tr> <tr> <th>Binary</th><th>Value</th><th>Description</th></tr> </thead> <tbody> <tr> <td>0</td><td>MasterBlks</td><td>Master Blocks</td></tr> <tr> <td>1</td><td>SetptBlks</td><td>Setpoint Blocks</td></tr> </tbody> </table>	Enumeration			Binary	Value	Description	0	MasterBlks	Master Blocks	1	SetptBlks	Setpoint Blocks																																																																																													
Enumeration																																																																																																											
Binary	Value	Description																																																																																																									
0	MasterBlks	Master Blocks																																																																																																									
1	SetptBlks	Setpoint Blocks																																																																																																									
CoachRejectionCode	UINT16	<p>Coach Rejection Code</p> <table border="1"> <thead> <tr> <th colspan="3">Enumeration</th></tr> <tr> <th>Binary</th><th>Value</th><th>Description</th></tr> </thead> <tbody> <tr> <td>1</td><td>Old</td><td></td></tr> <tr> <td>2</td><td>Duplicate</td><td></td></tr> <tr> <td>3</td><td>CRCBad</td><td></td></tr> </tbody> </table>	Enumeration			Binary	Value	Description	1	Old		2	Duplicate		3	CRCBad																																																																																											
Enumeration																																																																																																											
Binary	Value	Description																																																																																																									
1	Old																																																																																																										
2	Duplicate																																																																																																										
3	CRCBad																																																																																																										
CommandCode	UINT16	<table border="1"> <thead> <tr> <th colspan="3">Enumeration</th></tr> <tr> <th>Binary</th><th>Value</th><th>Description</th></tr> </thead> <tbody> <tr> <td>1</td><td>OpenSw1</td><td>Open Sw1</td></tr> <tr> <td>2</td><td>OpenSw2</td><td>Open Sw2</td></tr> <tr> <td>3</td><td>OpenSw3</td><td>Open Sw3</td></tr> <tr> <td>4</td><td>CloseSw1</td><td>Close Sw1</td></tr> <tr> <td>5</td><td>CloseSw2</td><td>Close Sw2</td></tr> <tr> <td>6</td><td>CloseSw3</td><td>Close Sw3</td></tr> <tr> <td>7</td><td>BATTTest</td><td>Start Bat.Test</td></tr> <tr> <td>8</td><td>STLSw1</td><td>Shots to Lockout SW1</td></tr> <tr> <td>9</td><td>STLSw2</td><td>Shots to Lockout SW2</td></tr> <tr> <td>10</td><td>ClearOC</td><td>Clear Overcurrent</td></tr> <tr> <td>11</td><td>FailOvDis</td><td>Failure Override Disable</td></tr> <tr> <td>12</td><td>FailOvEna</td><td>Failure Override Enable</td></tr> <tr> <td>13</td><td>AutoDis</td><td>Auto Op Disable</td></tr> <tr> <td>14</td><td>AutoEna</td><td>Auto Op Enable</td></tr> <tr> <td>15</td><td>Auto1Dis</td><td>Auto Op Sw1 Disable</td></tr> <tr> <td>16</td><td>Auto1Ena</td><td>Auto Op Sw1 Enable</td></tr> <tr> <td>17</td><td>Auto2Dis</td><td>Auto Op Sw2 Disable</td></tr> <tr> <td>18</td><td>Auto2Ena</td><td>Auto Op Sw2 Enable</td></tr> <tr> <td>19</td><td>HLTDis</td><td>HLT Disable</td></tr> <tr> <td>20</td><td>HLTEna</td><td>HLT Enable</td></tr> <tr> <td>21</td><td>HLT1Dis</td><td>HLT Sw1 Disable</td></tr> <tr> <td>22</td><td>HLT1Ena</td><td>HLT Sw1 Enable</td></tr> <tr> <td>23</td><td>HLT2Dis</td><td>HLT Sw2 Disable</td></tr> <tr> <td>24</td><td>HLT2Ena</td><td>HLT Sw2 Enable</td></tr> <tr> <td>25</td><td>HLT3Dis</td><td>HLT Sw3 Disable</td></tr> <tr> <td>26</td><td>HLT3Ena</td><td>HLT Sw3 Enable</td></tr> <tr> <td>27</td><td>USER</td><td>User-defined</td></tr> <tr> <td>28</td><td>ClrMan</td><td>Clear Manual Op</td></tr> <tr> <td>29</td><td>SRBlock</td><td>SCADA+Restoration Block</td></tr> <tr> <td>30</td><td>SREna</td><td>SCADA+Restoration Enable</td></tr> <tr> <td>31</td><td>SABlock</td><td>SCADA+Auto Op Block</td></tr> <tr> <td>32</td><td>SAEna</td><td>SCADA+Auto Op Enable</td></tr> <tr> <td>33</td><td>RegCnt</td><td>Set Regular Reclose Count</td></tr> </tbody> </table>	Enumeration			Binary	Value	Description	1	OpenSw1	Open Sw1	2	OpenSw2	Open Sw2	3	OpenSw3	Open Sw3	4	CloseSw1	Close Sw1	5	CloseSw2	Close Sw2	6	CloseSw3	Close Sw3	7	BATTTest	Start Bat.Test	8	STLSw1	Shots to Lockout SW1	9	STLSw2	Shots to Lockout SW2	10	ClearOC	Clear Overcurrent	11	FailOvDis	Failure Override Disable	12	FailOvEna	Failure Override Enable	13	AutoDis	Auto Op Disable	14	AutoEna	Auto Op Enable	15	Auto1Dis	Auto Op Sw1 Disable	16	Auto1Ena	Auto Op Sw1 Enable	17	Auto2Dis	Auto Op Sw2 Disable	18	Auto2Ena	Auto Op Sw2 Enable	19	HLTDis	HLT Disable	20	HLTEna	HLT Enable	21	HLT1Dis	HLT Sw1 Disable	22	HLT1Ena	HLT Sw1 Enable	23	HLT2Dis	HLT Sw2 Disable	24	HLT2Ena	HLT Sw2 Enable	25	HLT3Dis	HLT Sw3 Disable	26	HLT3Ena	HLT Sw3 Enable	27	USER	User-defined	28	ClrMan	Clear Manual Op	29	SRBlock	SCADA+Restoration Block	30	SREna	SCADA+Restoration Enable	31	SABlock	SCADA+Auto Op Block	32	SAEna	SCADA+Auto Op Enable	33	RegCnt	Set Regular Reclose Count
Enumeration																																																																																																											
Binary	Value	Description																																																																																																									
1	OpenSw1	Open Sw1																																																																																																									
2	OpenSw2	Open Sw2																																																																																																									
3	OpenSw3	Open Sw3																																																																																																									
4	CloseSw1	Close Sw1																																																																																																									
5	CloseSw2	Close Sw2																																																																																																									
6	CloseSw3	Close Sw3																																																																																																									
7	BATTTest	Start Bat.Test																																																																																																									
8	STLSw1	Shots to Lockout SW1																																																																																																									
9	STLSw2	Shots to Lockout SW2																																																																																																									
10	ClearOC	Clear Overcurrent																																																																																																									
11	FailOvDis	Failure Override Disable																																																																																																									
12	FailOvEna	Failure Override Enable																																																																																																									
13	AutoDis	Auto Op Disable																																																																																																									
14	AutoEna	Auto Op Enable																																																																																																									
15	Auto1Dis	Auto Op Sw1 Disable																																																																																																									
16	Auto1Ena	Auto Op Sw1 Enable																																																																																																									
17	Auto2Dis	Auto Op Sw2 Disable																																																																																																									
18	Auto2Ena	Auto Op Sw2 Enable																																																																																																									
19	HLTDis	HLT Disable																																																																																																									
20	HLTEna	HLT Enable																																																																																																									
21	HLT1Dis	HLT Sw1 Disable																																																																																																									
22	HLT1Ena	HLT Sw1 Enable																																																																																																									
23	HLT2Dis	HLT Sw2 Disable																																																																																																									
24	HLT2Ena	HLT Sw2 Enable																																																																																																									
25	HLT3Dis	HLT Sw3 Disable																																																																																																									
26	HLT3Ena	HLT Sw3 Enable																																																																																																									
27	USER	User-defined																																																																																																									
28	ClrMan	Clear Manual Op																																																																																																									
29	SRBlock	SCADA+Restoration Block																																																																																																									
30	SREna	SCADA+Restoration Enable																																																																																																									
31	SABlock	SCADA+Auto Op Block																																																																																																									
32	SAEna	SCADA+Auto Op Enable																																																																																																									
33	RegCnt	Set Regular Reclose Count																																																																																																									

Definitions of Historic Events

		<table border="1"> <tr><td>34</td><td>AltCnt</td><td>Set Alternate Reclose Count</td></tr> <tr><td>35</td><td>BlkRest</td><td>Broadcast Prohibit Restore</td></tr> <tr><td>36</td><td>AckADI1</td><td>Ack ADI 1</td></tr> <tr><td>37</td><td>AckADI2</td><td>Ack ADI 2</td></tr> <tr><td>38</td><td>AckADI3</td><td>Ack ADI 3</td></tr> </table>	34	AltCnt	Set Alternate Reclose Count	35	BlkRest	Broadcast Prohibit Restore	36	AckADI1	Ack ADI 1	37	AckADI2	Ack ADI 2	38	AckADI3	Ack ADI 3																																																																		
34	AltCnt	Set Alternate Reclose Count																																																																																	
35	BlkRest	Broadcast Prohibit Restore																																																																																	
36	AckADI1	Ack ADI 1																																																																																	
37	AckADI2	Ack ADI 2																																																																																	
38	AckADI3	Ack ADI 3																																																																																	
CommandSource	UINT16	<table border="1"> <thead> <tr><th colspan="3">Enumeration</th></tr> <tr> <th>Binary</th> <th>Value</th> <th>Description</th> </tr> </thead> <tbody> <tr><td>0</td><td>Undef</td><td>Undefined</td></tr> <tr><td>1</td><td>AutoOp</td><td>Automatic Operations</td></tr> <tr><td>2</td><td>SCADA</td><td>Remote Operations</td></tr> <tr><td>3</td><td>ILink</td><td>WiFi or other</td></tr> <tr><td>4</td><td>FP</td><td>Faceplate</td></tr> </tbody> </table>	Enumeration			Binary	Value	Description	0	Undef	Undefined	1	AutoOp	Automatic Operations	2	SCADA	Remote Operations	3	ILink	WiFi or other	4	FP	Faceplate																																																												
Enumeration																																																																																			
Binary	Value	Description																																																																																	
0	Undef	Undefined																																																																																	
1	AutoOp	Automatic Operations																																																																																	
2	SCADA	Remote Operations																																																																																	
3	ILink	WiFi or other																																																																																	
4	FP	Faceplate																																																																																	
CommErrorCode	UINT16	<p>Communications error code</p> <table border="1"> <thead> <tr><th colspan="2">Numeric Type, Range: 0-65535</th></tr> <tr> <th>Action</th> <th>Value</th> </tr> </thead> <tbody> <tr><td>Multiplier</td><td>1</td></tr> <tr><td>Adder</td><td>0</td></tr> </tbody> </table>	Numeric Type, Range: 0-65535		Action	Value	Multiplier	1	Adder	0																																																																									
Numeric Type, Range: 0-65535																																																																																			
Action	Value																																																																																		
Multiplier	1																																																																																		
Adder	0																																																																																		
connectID	UINT16	<p>Connection ID</p> <table border="1"> <thead> <tr><th colspan="2">Numeric Type, Range: 0-65535</th></tr> <tr> <th>Action</th> <th>Value</th> </tr> </thead> <tbody> <tr><td>Multiplier</td><td>1</td></tr> <tr><td>Adder</td><td>0</td></tr> </tbody> </table>	Numeric Type, Range: 0-65535		Action	Value	Multiplier	1	Adder	0																																																																									
Numeric Type, Range: 0-65535																																																																																			
Action	Value																																																																																		
Multiplier	1																																																																																		
Adder	0																																																																																		
ConnectionID	UINT16	<p>ConnectionID</p> <table border="1"> <thead> <tr><th colspan="3">Enumeration</th></tr> <tr> <th>Binary</th> <th>Value</th> <th>Description</th> </tr> </thead> <tbody> <tr><td>0</td><td>CIDUndefined</td><td>CID Undefined</td></tr> <tr><td>1</td><td>CIDGeneral</td><td>CID General</td></tr> <tr><td>2</td><td>CIDIInternalDNP</td><td>CID IInternal DNP</td></tr> <tr><td>3</td><td>CIDCoach</td><td>CID Coach</td></tr> <tr><td>4</td><td>CIDRunner</td><td>CID Runner</td></tr> <tr><td>5</td><td>CIDContractAgt</td><td>CID Contract Agent</td></tr> <tr><td>6</td><td>CIDNetlistXfer</td><td>CID Netlist Xfer</td></tr> <tr><td>7</td><td>CIDCoraAlleyOop</td><td>CID CoraAlley Oop</td></tr> <tr><td>8</td><td>CIDIT2Events</td><td>CID IT2 Events</td></tr> <tr><td>9</td><td>CIDProtection</td><td>CID Protection</td></tr> <tr><td>10</td><td>CIDDATLoadMgmt</td><td>CID DAT Load Mgmt</td></tr> <tr><td>11</td><td>CIDCECSignal</td><td>CID CEC Signal</td></tr> <tr><td>12</td><td>CIDD1ag</td><td>CID Diag</td></tr> <tr><td>13</td><td>CIDRemoteXmit</td><td>CID Remote Xmit</td></tr> <tr><td>16</td><td>CIDNETObjMgmt</td><td>CID NET Object Mgmt</td></tr> <tr><td>17</td><td>CIDNETRunner0</td><td>CID NET Runner 0</td></tr> <tr><td>18</td><td>CIDNETRunner1</td><td>CID NET Runner 1</td></tr> <tr><td>19</td><td>CIDNETRunner2</td><td>CID NET Runner 2</td></tr> <tr><td>20</td><td>CIDNETRunner3</td><td>CID NET Runner 3</td></tr> <tr><td>21</td><td>CIDNETRunner4</td><td>CID NET Runner 4</td></tr> <tr><td>22</td><td>CIDNETRunner5</td><td>CID NET Runner 5</td></tr> <tr><td>23</td><td>CIDNETRunner6</td><td>CID NET Runner 6</td></tr> <tr><td>24</td><td>CIDNETRunner7</td><td>CID NET Runner 7</td></tr> <tr><td>25</td><td>CIDNETRunner8</td><td>CID NET Runner 8</td></tr> <tr><td>26</td><td>CIDNETRunner9</td><td>CID NET Runner 9</td></tr> </tbody> </table>	Enumeration			Binary	Value	Description	0	CIDUndefined	CID Undefined	1	CIDGeneral	CID General	2	CIDIInternalDNP	CID IInternal DNP	3	CIDCoach	CID Coach	4	CIDRunner	CID Runner	5	CIDContractAgt	CID Contract Agent	6	CIDNetlistXfer	CID Netlist Xfer	7	CIDCoraAlleyOop	CID CoraAlley Oop	8	CIDIT2Events	CID IT2 Events	9	CIDProtection	CID Protection	10	CIDDATLoadMgmt	CID DAT Load Mgmt	11	CIDCECSignal	CID CEC Signal	12	CIDD1ag	CID Diag	13	CIDRemoteXmit	CID Remote Xmit	16	CIDNETObjMgmt	CID NET Object Mgmt	17	CIDNETRunner0	CID NET Runner 0	18	CIDNETRunner1	CID NET Runner 1	19	CIDNETRunner2	CID NET Runner 2	20	CIDNETRunner3	CID NET Runner 3	21	CIDNETRunner4	CID NET Runner 4	22	CIDNETRunner5	CID NET Runner 5	23	CIDNETRunner6	CID NET Runner 6	24	CIDNETRunner7	CID NET Runner 7	25	CIDNETRunner8	CID NET Runner 8	26	CIDNETRunner9	CID NET Runner 9
Enumeration																																																																																			
Binary	Value	Description																																																																																	
0	CIDUndefined	CID Undefined																																																																																	
1	CIDGeneral	CID General																																																																																	
2	CIDIInternalDNP	CID IInternal DNP																																																																																	
3	CIDCoach	CID Coach																																																																																	
4	CIDRunner	CID Runner																																																																																	
5	CIDContractAgt	CID Contract Agent																																																																																	
6	CIDNetlistXfer	CID Netlist Xfer																																																																																	
7	CIDCoraAlleyOop	CID CoraAlley Oop																																																																																	
8	CIDIT2Events	CID IT2 Events																																																																																	
9	CIDProtection	CID Protection																																																																																	
10	CIDDATLoadMgmt	CID DAT Load Mgmt																																																																																	
11	CIDCECSignal	CID CEC Signal																																																																																	
12	CIDD1ag	CID Diag																																																																																	
13	CIDRemoteXmit	CID Remote Xmit																																																																																	
16	CIDNETObjMgmt	CID NET Object Mgmt																																																																																	
17	CIDNETRunner0	CID NET Runner 0																																																																																	
18	CIDNETRunner1	CID NET Runner 1																																																																																	
19	CIDNETRunner2	CID NET Runner 2																																																																																	
20	CIDNETRunner3	CID NET Runner 3																																																																																	
21	CIDNETRunner4	CID NET Runner 4																																																																																	
22	CIDNETRunner5	CID NET Runner 5																																																																																	
23	CIDNETRunner6	CID NET Runner 6																																																																																	
24	CIDNETRunner7	CID NET Runner 7																																																																																	
25	CIDNETRunner8	CID NET Runner 8																																																																																	
26	CIDNETRunner9	CID NET Runner 9																																																																																	

		<table border="1"> <tr><td>27</td><td>CIDNETRunner10</td><td>CID NET Runner 10</td></tr> <tr><td>28</td><td>CIDNETRunner11</td><td>CID NET Runner 11</td></tr> <tr><td>29</td><td>CIDNETRunner12</td><td>CID NET Runner 12</td></tr> <tr><td>30</td><td>CIDNETRunner13</td><td>CID NET Runner 13</td></tr> <tr><td>31</td><td>CIDNETRunner14</td><td>CID NET Runner 14</td></tr> <tr><td>32</td><td>CIDNETRunner15</td><td>CID NET Runner 15</td></tr> </table>	27	CIDNETRunner10	CID NET Runner 10	28	CIDNETRunner11	CID NET Runner 11	29	CIDNETRunner12	CID NET Runner 12	30	CIDNETRunner13	CID NET Runner 13	31	CIDNETRunner14	CID NET Runner 14	32	CIDNETRunner15	CID NET Runner 15																																													
27	CIDNETRunner10	CID NET Runner 10																																																															
28	CIDNETRunner11	CID NET Runner 11																																																															
29	CIDNETRunner12	CID NET Runner 12																																																															
30	CIDNETRunner13	CID NET Runner 13																																																															
31	CIDNETRunner14	CID NET Runner 14																																																															
32	CIDNETRunner15	CID NET Runner 15																																																															
ContractState	UINT16	<p>Contract State.</p> <table border="1"> <thead> <tr><th colspan="3">Enumeration</th></tr> <tr> <th>Binary</th><th>Value</th><th>Description</th></tr> </thead> <tbody> <tr><td>1</td><td>CActive</td><td>Contract state active</td></tr> <tr><td>2</td><td>CReqPend</td><td>Contract state request pending</td></tr> <tr><td>3</td><td>CReqUnsent</td><td>Contract state request unsent</td></tr> <tr><td>4</td><td>CReqTrav</td><td>Contract state request traveling</td></tr> <tr><td>5</td><td>CReqAccept</td><td>Contract state request accepted</td></tr> <tr><td>6</td><td>CReqDecline</td><td>Contract state request declined</td></tr> <tr><td>7</td><td>CReqDeclContd</td><td>Contract state request decline continuing</td></tr> <tr><td>8</td><td>CDsIveStart</td><td>Contract state dissolve start</td></tr> <tr><td>9</td><td>CDsIveContd</td><td>Contract state dissolve continue</td></tr> <tr><td>10</td><td>CMaintStart</td><td>Contract state maintenance start</td></tr> <tr><td>11</td><td>CMaintTickl</td><td>Contract state maintenance tickle</td></tr> <tr><td>12</td><td>CMaintTrav</td><td>Contract state maintenance travel</td></tr> <tr><td>13</td><td>CMTravNoFind</td><td>Contract state maintenance travel not found</td></tr> <tr><td>14</td><td>CMTrRetNoFnd</td><td>Contract state maint travel return not found</td></tr> <tr><td>15</td><td>CMTicklNoFind</td><td>Contract state maintenance tickle not found</td></tr> <tr><td>16</td><td>CMTiRetNoFnd</td><td>Contract state maint tickle return not found</td></tr> <tr><td>17</td><td>CMaintReact</td><td>Contract state maintenance reactivate contract</td></tr> <tr><td>18</td><td>CMNoReact</td><td>Contract state maint don't reactivate here - continue</td></tr> <tr><td>19</td><td>CChk2ndFld</td><td>Contract state request - check 2nd field</td></tr> </tbody> </table>	Enumeration			Binary	Value	Description	1	CActive	Contract state active	2	CReqPend	Contract state request pending	3	CReqUnsent	Contract state request unsent	4	CReqTrav	Contract state request traveling	5	CReqAccept	Contract state request accepted	6	CReqDecline	Contract state request declined	7	CReqDeclContd	Contract state request decline continuing	8	CDsIveStart	Contract state dissolve start	9	CDsIveContd	Contract state dissolve continue	10	CMaintStart	Contract state maintenance start	11	CMaintTickl	Contract state maintenance tickle	12	CMaintTrav	Contract state maintenance travel	13	CMTravNoFind	Contract state maintenance travel not found	14	CMTrRetNoFnd	Contract state maint travel return not found	15	CMTicklNoFind	Contract state maintenance tickle not found	16	CMTiRetNoFnd	Contract state maint tickle return not found	17	CMaintReact	Contract state maintenance reactivate contract	18	CMNoReact	Contract state maint don't reactivate here - continue	19	CChk2ndFld	Contract state request - check 2nd field
Enumeration																																																																	
Binary	Value	Description																																																															
1	CActive	Contract state active																																																															
2	CReqPend	Contract state request pending																																																															
3	CReqUnsent	Contract state request unsent																																																															
4	CReqTrav	Contract state request traveling																																																															
5	CReqAccept	Contract state request accepted																																																															
6	CReqDecline	Contract state request declined																																																															
7	CReqDeclContd	Contract state request decline continuing																																																															
8	CDsIveStart	Contract state dissolve start																																																															
9	CDsIveContd	Contract state dissolve continue																																																															
10	CMaintStart	Contract state maintenance start																																																															
11	CMaintTickl	Contract state maintenance tickle																																																															
12	CMaintTrav	Contract state maintenance travel																																																															
13	CMTravNoFind	Contract state maintenance travel not found																																																															
14	CMTrRetNoFnd	Contract state maint travel return not found																																																															
15	CMTicklNoFind	Contract state maintenance tickle not found																																																															
16	CMTiRetNoFnd	Contract state maint tickle return not found																																																															
17	CMaintReact	Contract state maintenance reactivate contract																																																															
18	CMNoReact	Contract state maint don't reactivate here - continue																																																															
19	CChk2ndFld	Contract state request - check 2nd field																																																															
ControlCode	UINT16	<p>Control Number</p> <table border="1"> <thead> <tr><th colspan="2">Numeric Type, Range: 0-15</th></tr> <tr> <th>Action</th><th>Value</th></tr> </thead> <tbody> <tr><td>Multiplier</td><td>1</td></tr> <tr><td>Adder</td><td>0</td></tr> </tbody> </table>	Numeric Type, Range: 0-15		Action	Value	Multiplier	1	Adder	0																																																							
Numeric Type, Range: 0-15																																																																	
Action	Value																																																																
Multiplier	1																																																																
Adder	0																																																																
CycleNumber	UINT16	<p>Cycle number</p> <table border="1"> <thead> <tr><th colspan="2">Numeric Type, Range: 0-65535</th></tr> <tr> <th>Action</th><th>Value</th></tr> </thead> <tbody> <tr><td>Multiplier</td><td>1</td></tr> <tr><td>Adder</td><td>0</td></tr> </tbody> </table>	Numeric Type, Range: 0-65535		Action	Value	Multiplier	1	Adder	0																																																							
Numeric Type, Range: 0-65535																																																																	
Action	Value																																																																
Multiplier	1																																																																
Adder	0																																																																
DataLength	UINT16	<p>Length of the data</p> <table border="1"> <thead> <tr><th colspan="2">Numeric Type, Range: 0-65535</th></tr> <tr> <th>Action</th><th>Value</th></tr> </thead> <tbody> <tr><td>Multiplier</td><td>1</td></tr> <tr><td>Adder</td><td>0</td></tr> </tbody> </table>	Numeric Type, Range: 0-65535		Action	Value	Multiplier	1	Adder	0																																																							
Numeric Type, Range: 0-65535																																																																	
Action	Value																																																																
Multiplier	1																																																																
Adder	0																																																																
DATARNR	UINT16	<p>Data runnes working within the time limits</p> <table border="1"> <thead> <tr><th colspan="3">Enumeration</th></tr> <tr> <th>Binary</th><th>Value</th><th>Description</th></tr> </thead> <tbody> <tr><td>1</td><td>NETXDATRNR</td><td>Runners are working within timeouts when set</td></tr> </tbody> </table>	Enumeration			Binary	Value	Description	1	NETXDATRNR	Runners are working within timeouts when set																																																						
Enumeration																																																																	
Binary	Value	Description																																																															
1	NETXDATRNR	Runners are working within timeouts when set																																																															
dctsiz	UINT16	<p>Data Length</p>																																																															

Definitions of Historic Events

		<table border="1"> <thead> <tr> <th colspan="2">Numeric Type, Range: 0-65535</th> </tr> <tr> <th>Action</th><th>Value</th></tr> </thead> <tbody> <tr> <td>Multiplier</td><td>1</td></tr> <tr> <td>Adder</td><td>0</td></tr> </tbody> </table>	Numeric Type, Range: 0-65535		Action	Value	Multiplier	1	Adder	0				
Numeric Type, Range: 0-65535														
Action	Value													
Multiplier	1													
Adder	0													
DestinationIndex	UINT16	<p>Destination Index</p> <table border="1"> <thead> <tr> <th colspan="2">Numeric Type, Range: 0-65535</th> </tr> <tr> <th>Action</th><th>Value</th></tr> </thead> <tbody> <tr> <td>Multiplier</td><td>1</td></tr> <tr> <td>Adder</td><td>0</td></tr> </tbody> </table>	Numeric Type, Range: 0-65535		Action	Value	Multiplier	1	Adder	0				
Numeric Type, Range: 0-65535														
Action	Value													
Multiplier	1													
Adder	0													
DestNodeID	UINT16	<p>NET Destination Node ID</p> <table border="1"> <thead> <tr> <th colspan="2">Numeric Type, Range: 0-65535</th> </tr> <tr> <th>Action</th><th>Value</th></tr> </thead> <tbody> <tr> <td>Multiplier</td><td>1</td></tr> <tr> <td>Adder</td><td>0</td></tr> </tbody> </table>	Numeric Type, Range: 0-65535		Action	Value	Multiplier	1	Adder	0				
Numeric Type, Range: 0-65535														
Action	Value													
Multiplier	1													
Adder	0													
dev	UINT16	<p>Device Type, either a substation or not a substation</p> <table border="1"> <thead> <tr> <th colspan="2">Numeric Type, Range: 0-65535</th> </tr> <tr> <th>Action</th><th>Value</th></tr> </thead> <tbody> <tr> <td>Multiplier</td><td>1</td></tr> <tr> <td>Adder</td><td>0</td></tr> </tbody> </table>	Numeric Type, Range: 0-65535		Action	Value	Multiplier	1	Adder	0				
Numeric Type, Range: 0-65535														
Action	Value													
Multiplier	1													
Adder	0													
DeviceIndex	UINT16	<p>local device number of the FN Runner Source Device</p> <table border="1"> <thead> <tr> <th colspan="2">Numeric Type, Range: 0-65535</th> </tr> <tr> <th>Action</th><th>Value</th></tr> </thead> <tbody> <tr> <td>Multiplier</td><td>1</td></tr> <tr> <td>Adder</td><td>0</td></tr> </tbody> </table>	Numeric Type, Range: 0-65535		Action	Value	Multiplier	1	Adder	0				
Numeric Type, Range: 0-65535														
Action	Value													
Multiplier	1													
Adder	0													
DeviceNumber	UINT16	<p>Working runner source list in the Runner Source Control</p> <table border="1"> <thead> <tr> <th colspan="2">Numeric Type, Range: 0-65535</th> </tr> <tr> <th>Action</th><th>Value</th></tr> </thead> <tbody> <tr> <td>Multiplier</td><td>1</td></tr> <tr> <td>Adder</td><td>0</td></tr> </tbody> </table>	Numeric Type, Range: 0-65535		Action	Value	Multiplier	1	Adder	0				
Numeric Type, Range: 0-65535														
Action	Value													
Multiplier	1													
Adder	0													
DeviceWirepairs	UINT16	<p>Number of Device-Wire pairs from prep function</p> <table border="1"> <thead> <tr> <th colspan="2">Numeric Type, Range: 0-65535</th> </tr> <tr> <th>Action</th><th>Value</th></tr> </thead> <tbody> <tr> <td>Multiplier</td><td>1</td></tr> <tr> <td>Adder</td><td>0</td></tr> </tbody> </table>	Numeric Type, Range: 0-65535		Action	Value	Multiplier	1	Adder	0				
Numeric Type, Range: 0-65535														
Action	Value													
Multiplier	1													
Adder	0													
DiagTestType	UINT16	<p>Type of diagnostic test</p> <table border="1"> <thead> <tr> <th colspan="3">Enumeration</th> </tr> <tr> <th>Binary</th><th>Value</th><th>Description</th></tr> </thead> <tbody> <tr> <td>0</td><td>Scheduled</td><td>Scheduled</td></tr> <tr> <td>1</td><td>Quick</td><td>Quick</td></tr> </tbody> </table>	Enumeration			Binary	Value	Description	0	Scheduled	Scheduled	1	Quick	Quick
Enumeration														
Binary	Value	Description												
0	Scheduled	Scheduled												
1	Quick	Quick												
Direction	UINT16	<p>Direction</p> <table border="1"> <thead> <tr> <th colspan="3">Enumeration</th> </tr> <tr> <th>Binary</th><th>Value</th><th>Description</th></tr> </thead> <tbody> <tr> <td>1</td><td>Forward</td><td>Forward</td></tr> <tr> <td>2</td><td>Reverse</td><td>Reverse</td></tr> </tbody> </table>	Enumeration			Binary	Value	Description	1	Forward	Forward	2	Reverse	Reverse
Enumeration														
Binary	Value	Description												
1	Forward	Forward												
2	Reverse	Reverse												
DivBy10	UINT16	<p>Divide by 10</p> <table border="1"> <thead> <tr> <th colspan="2">Numeric Type, Range: 0-65535</th> </tr> </thead> </table>	Numeric Type, Range: 0-65535											
Numeric Type, Range: 0-65535														

		<table border="1"> <thead> <tr> <th>Action</th><th>Value</th></tr> </thead> <tbody> <tr> <td>Multiplier</td><td>0.1</td></tr> <tr> <td>Adder</td><td>0</td></tr> </tbody> </table>	Action	Value	Multiplier	0.1	Adder	0						
Action	Value													
Multiplier	0.1													
Adder	0													
DNPAddress	UINT16	<p>Values represented in hexadecimal code</p> <p>Numeric Type, Range: 1-65519</p> <table border="1"> <thead> <tr> <th>Action</th><th>Value</th></tr> </thead> <tbody> <tr> <td>Multiplier</td><td>1</td></tr> <tr> <td>Adder</td><td>0</td></tr> </tbody> </table> <p>Presentation</p> <table border="1"> <thead> <tr> <th>Binary</th><th>{0:X2}</th></tr> </thead> </table>	Action	Value	Multiplier	1	Adder	0	Binary	{0:X2}				
Action	Value													
Multiplier	1													
Adder	0													
Binary	{0:X2}													
DNPApControl	UINT16	<p>DNP application control byte</p> <p>Numeric Type, Range: 0-255</p> <table border="1"> <thead> <tr> <th>Action</th><th>Value</th></tr> </thead> <tbody> <tr> <td>Multiplier</td><td>1</td></tr> <tr> <td>Adder</td><td>0</td></tr> </tbody> </table>	Action	Value	Multiplier	1	Adder	0						
Action	Value													
Multiplier	1													
Adder	0													
DNPApFunctionCode	UINT16	<p>DNP Application Function Code</p> <p>Numeric Type, Range: 0-255</p> <table border="1"> <thead> <tr> <th>Action</th><th>Value</th></tr> </thead> <tbody> <tr> <td>Multiplier</td><td>1</td></tr> <tr> <td>Adder</td><td>0</td></tr> </tbody> </table>	Action	Value	Multiplier	1	Adder	0						
Action	Value													
Multiplier	1													
Adder	0													
DNPDLAction	UINT16	<p>DNP DL Action</p> <p>Enumeration</p> <table border="1"> <thead> <tr> <th>Binary</th><th>Value</th><th>Description</th></tr> </thead> <tbody> <tr> <td>1</td><td>RecordReinit</td><td>record reinit</td></tr> <tr> <td>2</td><td>ResetSeqNumOnly</td><td>reset seq num only</td></tr> <tr> <td>3</td><td>NewPeerAdded</td><td>new peer added</td></tr> </tbody> </table>	Binary	Value	Description	1	RecordReinit	record reinit	2	ResetSeqNumOnly	reset seq num only	3	NewPeerAdded	new peer added
Binary	Value	Description												
1	RecordReinit	record reinit												
2	ResetSeqNumOnly	reset seq num only												
3	NewPeerAdded	new peer added												
DNPObjectType	UINT16	<p>DNP Object Type</p> <p>Numeric Type, Range: 0-255</p> <table border="1"> <thead> <tr> <th>Action</th><th>Value</th></tr> </thead> <tbody> <tr> <td>Multiplier</td><td>1</td></tr> <tr> <td>Adder</td><td>0</td></tr> </tbody> </table>	Action	Value	Multiplier	1	Adder	0						
Action	Value													
Multiplier	1													
Adder	0													
DNPObjectVariation	UINT16	<p>DNP Object Variation</p> <p>Numeric Type, Range: 0-255</p> <table border="1"> <thead> <tr> <th>Action</th><th>Value</th></tr> </thead> <tbody> <tr> <td>Multiplier</td><td>1</td></tr> <tr> <td>Adder</td><td>0</td></tr> </tbody> </table>	Action	Value	Multiplier	1	Adder	0						
Action	Value													
Multiplier	1													
Adder	0													
DNPOutputBlockStatusCode	UINT16	<p>DNP Output Block Status Code</p> <p>Numeric Type, Range: 0-255</p> <table border="1"> <thead> <tr> <th>Action</th><th>Value</th></tr> </thead> <tbody> <tr> <td>Multiplier</td><td>1</td></tr> <tr> <td>Adder</td><td>0</td></tr> </tbody> </table>	Action	Value	Multiplier	1	Adder	0						
Action	Value													
Multiplier	1													
Adder	0													
DNPPointCode	UINT16	<p>Internal DNP point code</p> <p>Numeric Type, Range: 0-65535</p> <table border="1"> <thead> <tr> <th>Action</th><th>Value</th></tr> </thead> <tbody> <tr> <td>Multiplier</td><td>1</td></tr> <tr> <td>Adder</td><td>0</td></tr> </tbody> </table>	Action	Value	Multiplier	1	Adder	0						
Action	Value													
Multiplier	1													
Adder	0													

Definitions of Historic Events

DNPPointType	UINT16	DNP Point Type <table border="1"> <thead> <tr> <th colspan="3">Enumeration</th> </tr> <tr> <th>Binary</th><th>Value</th><th>Description</th></tr> </thead> <tbody> <tr> <td>1</td><td>Binary</td><td>binary</td></tr> <tr> <td>2</td><td>Analog</td><td>analog</td></tr> <tr> <td>3</td><td>Counter</td><td>counter</td></tr> </tbody> </table>	Enumeration			Binary	Value	Description	1	Binary	binary	2	Analog	analog	3	Counter	counter																								
Enumeration																																									
Binary	Value	Description																																							
1	Binary	binary																																							
2	Analog	analog																																							
3	Counter	counter																																							
DNPTranspFunctionCode	UINT16	DNP transport function code <table border="1"> <thead> <tr> <th colspan="2">Numeric Type, Range: 0-255</th> </tr> <tr> <th>Action</th><th>Value</th></tr> </thead> <tbody> <tr> <td>Multiplier</td><td>1</td></tr> <tr> <td>Adder</td><td>0</td></tr> </tbody> </table>	Numeric Type, Range: 0-255		Action	Value	Multiplier	1	Adder	0																															
Numeric Type, Range: 0-255																																									
Action	Value																																								
Multiplier	1																																								
Adder	0																																								
DNPTransportHeader	UINT16	DNP transport header byte <table border="1"> <thead> <tr> <th colspan="2">Numeric Type, Range: 0-255</th> </tr> <tr> <th>Action</th><th>Value</th></tr> </thead> <tbody> <tr> <td>Multiplier</td><td>1</td></tr> <tr> <td>Adder</td><td>0</td></tr> </tbody> </table>	Numeric Type, Range: 0-255		Action	Value	Multiplier	1	Adder	0																															
Numeric Type, Range: 0-255																																									
Action	Value																																								
Multiplier	1																																								
Adder	0																																								
EnabDisab	UINT16	<table border="1"> <thead> <tr> <th colspan="3">Enumeration</th> </tr> <tr> <th>Binary</th><th>Value</th><th>Description</th></tr> </thead> <tbody> <tr> <td>1</td><td>Enabled</td><td>Enabled</td></tr> <tr> <td>0</td><td>Disabled</td><td>Disabled</td></tr> </tbody> </table>	Enumeration			Binary	Value	Description	1	Enabled	Enabled	0	Disabled	Disabled																											
Enumeration																																									
Binary	Value	Description																																							
1	Enabled	Enabled																																							
0	Disabled	Disabled																																							
EntryPointDevice	UINT16	Indication that this control is the Entry Point Device <table border="1"> <thead> <tr> <th colspan="2">Numeric Type, Range: 0-65535</th> </tr> <tr> <th>Action</th><th>Value</th></tr> </thead> <tbody> <tr> <td>Multiplier</td><td>1</td></tr> <tr> <td>Adder</td><td>0</td></tr> </tbody> </table>	Numeric Type, Range: 0-65535		Action	Value	Multiplier	1	Adder	0																															
Numeric Type, Range: 0-65535																																									
Action	Value																																								
Multiplier	1																																								
Adder	0																																								
ErrorCodeNETX	UINT16	Error code for the Netx system <table border="1"> <thead> <tr> <th colspan="3">Enumeration</th> </tr> <tr> <th>Binary</th><th>Value</th><th>Description</th></tr> </thead> <tbody> <tr> <td>0</td><td>NETX_SUCCESS</td><td>Netx is successful</td></tr> <tr> <td>32</td><td>NETX_BAD_VER</td><td>Netx has a bad version</td></tr> <tr> <td>64</td><td>NETX_NO_NETVW</td><td>Netx has no Net view</td></tr> <tr> <td>128</td><td>NETX_NO_RTU</td><td>No RTU was found for NETX</td></tr> <tr> <td>256</td><td>NETX_BAD_NETVW</td><td>Netx has a bad Net view</td></tr> <tr> <td>512</td><td>NETX_OBJ_FAIL</td><td>Netx object has failed</td></tr> <tr> <td>1024</td><td>NETX_FAIL</td><td>Netx has failed</td></tr> <tr> <td>2048</td><td>NETX_OBJ_QUED</td><td>Netx object has been qued</td></tr> <tr> <td>4096</td><td>NETX_NOT_RSD</td><td>Netx has not RSD</td></tr> <tr> <td>8192</td><td>NETX_BAD_CRC</td><td>Netx has a bad CRC</td></tr> <tr> <td>16384</td><td>NETX_NOTACTV</td><td>Netx is not active</td></tr> </tbody> </table>	Enumeration			Binary	Value	Description	0	NETX_SUCCESS	Netx is successful	32	NETX_BAD_VER	Netx has a bad version	64	NETX_NO_NETVW	Netx has no Net view	128	NETX_NO_RTU	No RTU was found for NETX	256	NETX_BAD_NETVW	Netx has a bad Net view	512	NETX_OBJ_FAIL	Netx object has failed	1024	NETX_FAIL	Netx has failed	2048	NETX_OBJ_QUED	Netx object has been qued	4096	NETX_NOT_RSD	Netx has not RSD	8192	NETX_BAD_CRC	Netx has a bad CRC	16384	NETX_NOTACTV	Netx is not active
Enumeration																																									
Binary	Value	Description																																							
0	NETX_SUCCESS	Netx is successful																																							
32	NETX_BAD_VER	Netx has a bad version																																							
64	NETX_NO_NETVW	Netx has no Net view																																							
128	NETX_NO_RTU	No RTU was found for NETX																																							
256	NETX_BAD_NETVW	Netx has a bad Net view																																							
512	NETX_OBJ_FAIL	Netx object has failed																																							
1024	NETX_FAIL	Netx has failed																																							
2048	NETX_OBJ_QUED	Netx object has been qued																																							
4096	NETX_NOT_RSD	Netx has not RSD																																							
8192	NETX_BAD_CRC	Netx has a bad CRC																																							
16384	NETX_NOTACTV	Netx is not active																																							
ExcessLoad	UINT16	<table border="1"> <thead> <tr> <th colspan="3">Enumeration</th> </tr> <tr> <th>Binary</th><th>Value</th><th>Description</th></tr> </thead> <tbody> <tr> <td>0</td><td>ExcessLoad</td><td>Excess Load</td></tr> </tbody> </table>	Enumeration			Binary	Value	Description	0	ExcessLoad	Excess Load																														
Enumeration																																									
Binary	Value	Description																																							
0	ExcessLoad	Excess Load																																							
ExpressNetViewRow	UINT16	Number of entries in row, one for device,one for wire <table border="1"> <thead> <tr> <th colspan="2">Numeric Type, Range: 0-65535</th> </tr> <tr> <th>Action</th><th>Value</th></tr> </thead> <tbody> <tr> <td>Multiplier</td><td>1</td></tr> <tr> <td>Adder</td><td>0</td></tr> </tbody> </table>	Numeric Type, Range: 0-65535		Action	Value	Multiplier	1	Adder	0																															
Numeric Type, Range: 0-65535																																									
Action	Value																																								
Multiplier	1																																								
Adder	0																																								

FaultBits	UINT16	Fault Bits Numeric Type, Range: 0-65535 <table border="1"> <thead> <tr> <th>Action</th><th>Value</th></tr> </thead> <tbody> <tr> <td>Multiplier</td><td>1</td></tr> <tr> <td>Adder</td><td>0</td></tr> </tbody> </table>	Action	Value	Multiplier	1	Adder	0																								
Action	Value																															
Multiplier	1																															
Adder	0																															
FeederNetCRC	UINT16	CRC of this Feeder Net Numeric Type, Range: 0-65535 <table border="1"> <thead> <tr> <th>Action</th><th>Value</th></tr> </thead> <tbody> <tr> <td>Multiplier</td><td>1</td></tr> <tr> <td>Adder</td><td>0</td></tr> </tbody> </table>	Action	Value	Multiplier	1	Adder	0																								
Action	Value																															
Multiplier	1																															
Adder	0																															
FeederNetID	UINT16	Feeder Net ID Numeric Type, Range: 0-65535 <table border="1"> <thead> <tr> <th>Action</th><th>Value</th></tr> </thead> <tbody> <tr> <td>Multiplier</td><td>1</td></tr> <tr> <td>Adder</td><td>0</td></tr> </tbody> </table>	Action	Value	Multiplier	1	Adder	0																								
Action	Value																															
Multiplier	1																															
Adder	0																															
FeederNetIndex	UINT16	Feeder Net Index Numeric Type, Range: 0-65535 <table border="1"> <thead> <tr> <th>Action</th><th>Value</th></tr> </thead> <tbody> <tr> <td>Multiplier</td><td>1</td></tr> <tr> <td>Adder</td><td>0</td></tr> </tbody> </table>	Action	Value	Multiplier	1	Adder	0																								
Action	Value																															
Multiplier	1																															
Adder	0																															
FeederNetObjectFlags	UINT16	Incoming Feeder Net Flags from ITD Numeric Type, Range: 0-65535 <table border="1"> <thead> <tr> <th>Action</th><th>Value</th></tr> </thead> <tbody> <tr> <td>Multiplier</td><td>1</td></tr> <tr> <td>Adder</td><td>0</td></tr> </tbody> </table>	Action	Value	Multiplier	1	Adder	0																								
Action	Value																															
Multiplier	1																															
Adder	0																															
FeederNetObjType	UINT16	Type of netlist distribution Numeric Type, Range: 0-65535 <table border="1"> <thead> <tr> <th>Action</th><th>Value</th></tr> </thead> <tbody> <tr> <td>Multiplier</td><td>1</td></tr> <tr> <td>Adder</td><td>0</td></tr> </tbody> </table>	Action	Value	Multiplier	1	Adder	0																								
Action	Value																															
Multiplier	1																															
Adder	0																															
FixQuality	UINT16	Enumeration <table border="1"> <thead> <tr> <th>Binary</th><th>Value</th><th>Description</th></tr> </thead> <tbody> <tr> <td>0</td><td>NoSignal</td><td>No Signal</td></tr> <tr> <td>1</td><td>GPS</td><td>GPS</td></tr> <tr> <td>2</td><td>DGPS</td><td>DGPS</td></tr> <tr> <td>3</td><td>PPS</td><td>PPS</td></tr> <tr> <td>4</td><td>RealTmKinematic</td><td>Real Time Kinematic</td></tr> <tr> <td>5</td><td>FloatRTK</td><td>Float RTK</td></tr> <tr> <td>6</td><td>Estimated</td><td>Estimated</td></tr> <tr> <td>7</td><td>MnlInputMode</td><td>Manual Input Mode</td></tr> <tr> <td>8</td><td>SimulatMode</td><td>Simulation Mode</td></tr> </tbody> </table>	Binary	Value	Description	0	NoSignal	No Signal	1	GPS	GPS	2	DGPS	DGPS	3	PPS	PPS	4	RealTmKinematic	Real Time Kinematic	5	FloatRTK	Float RTK	6	Estimated	Estimated	7	MnlInputMode	Manual Input Mode	8	SimulatMode	Simulation Mode
Binary	Value	Description																														
0	NoSignal	No Signal																														
1	GPS	GPS																														
2	DGPS	DGPS																														
3	PPS	PPS																														
4	RealTmKinematic	Real Time Kinematic																														
5	FloatRTK	Float RTK																														
6	Estimated	Estimated																														
7	MnlInputMode	Manual Input Mode																														
8	SimulatMode	Simulation Mode																														
FreqTrip	UINT16	Enumeration <table border="1"> <thead> <tr> <th>Binary</th><th>Value</th><th>Description</th></tr> </thead> <tbody> <tr> <td>0</td><td>NoTrip</td><td>No Trip</td></tr> <tr> <td>1</td><td>FreqTrip</td><td>Freq Trip</td></tr> </tbody> </table>	Binary	Value	Description	0	NoTrip	No Trip	1	FreqTrip	Freq Trip																					
Binary	Value	Description																														
0	NoTrip	No Trip																														
1	FreqTrip	Freq Trip																														
FreqTripType	UINT16	Over Under Freq. Trip Numeric Type, Range: 1-2																														

Definitions of Historic Events

		<table border="1"> <thead> <tr> <th>Action</th><th>Value</th></tr> </thead> <tbody> <tr> <td>Multiplier</td><td>1</td></tr> <tr> <td>Adder</td><td>0</td></tr> </tbody> </table>	Action	Value	Multiplier	1	Adder	0																												
Action	Value																																			
Multiplier	1																																			
Adder	0																																			
GPSStatus	UINT16	<table border="1"> <thead> <tr> <th colspan="3">Enumeration</th></tr> <tr> <th>Binary</th><th>Value</th><th>Description</th></tr> </thead> <tbody> <tr> <td>0</td><td>TimePosOK</td><td>Time Position OK</td></tr> <tr> <td>1</td><td>TPosOKPendStab</td><td>Time Position OK Pending Stability</td></tr> <tr> <td>2</td><td>TPosOKNoPulse</td><td>Time Position OK No Pulse Signal</td></tr> <tr> <td>3</td><td>TimePosInvalid</td><td>Time Position Invalid</td></tr> <tr> <td>4</td><td>DInvalidSLineOdd</td><td>Data Invalid Serial Line Anomaly</td></tr> <tr> <td>5</td><td>DInvalidSLineErr</td><td>Data Invalid Serial Line Error</td></tr> <tr> <td>6</td><td>DInvalidSLineSil</td><td>Data Invalid Serial Line Silence</td></tr> <tr> <td>7</td><td>DisabledByUser</td><td>Disabled By User</td></tr> <tr> <td>255</td><td>NotInitialized</td><td>Not Initialized</td></tr> </tbody> </table>	Enumeration			Binary	Value	Description	0	TimePosOK	Time Position OK	1	TPosOKPendStab	Time Position OK Pending Stability	2	TPosOKNoPulse	Time Position OK No Pulse Signal	3	TimePosInvalid	Time Position Invalid	4	DInvalidSLineOdd	Data Invalid Serial Line Anomaly	5	DInvalidSLineErr	Data Invalid Serial Line Error	6	DInvalidSLineSil	Data Invalid Serial Line Silence	7	DisabledByUser	Disabled By User	255	NotInitialized	Not Initialized	
Enumeration																																				
Binary	Value	Description																																		
0	TimePosOK	Time Position OK																																		
1	TPosOKPendStab	Time Position OK Pending Stability																																		
2	TPosOKNoPulse	Time Position OK No Pulse Signal																																		
3	TimePosInvalid	Time Position Invalid																																		
4	DInvalidSLineOdd	Data Invalid Serial Line Anomaly																																		
5	DInvalidSLineErr	Data Invalid Serial Line Error																																		
6	DInvalidSLineSil	Data Invalid Serial Line Silence																																		
7	DisabledByUser	Disabled By User																																		
255	NotInitialized	Not Initialized																																		
HealingType	UINT16	<table border="1"> <thead> <tr> <th colspan="3">Enumeration</th></tr> <tr> <th>Binary</th><th>Value</th><th>Description</th></tr> </thead> <tbody> <tr> <td>1</td><td>ITII</td><td>IT-II</td></tr> <tr> <td>2</td><td>RSH</td><td>RSH</td></tr> </tbody> </table>	Enumeration			Binary	Value	Description	1	ITII	IT-II	2	RSH	RSH																						
Enumeration																																				
Binary	Value	Description																																		
1	ITII	IT-II																																		
2	RSH	RSH																																		
Hexushort	UINT16	<p>Values represented in hexadecimal code</p> <table border="1"> <thead> <tr> <th colspan="3">Numeric Type, Range: 0-65535</th></tr> <tr> <th>Action</th><th>Value</th><th></th></tr> </thead> <tbody> <tr> <td>Multiplier</td><td>1</td><td></td></tr> <tr> <td>Adder</td><td>0</td><td></td></tr> </tbody> </table> <table border="1"> <thead> <tr> <th colspan="3">Presentation</th></tr> <tr> <th>Binary</th><th colspan="2">{0:X2}</th></tr> </thead> </table>	Numeric Type, Range: 0-65535			Action	Value		Multiplier	1		Adder	0		Presentation			Binary	{0:X2}																	
Numeric Type, Range: 0-65535																																				
Action	Value																																			
Multiplier	1																																			
Adder	0																																			
Presentation																																				
Binary	{0:X2}																																			
HLT1	UINT16	<table border="1"> <thead> <tr> <th colspan="3">Enumeration</th></tr> <tr> <th>Binary</th><th>Value</th><th>Description</th></tr> </thead> <tbody> <tr> <td>0</td><td>HLTSW1Inactive</td><td>HLT Inactive</td></tr> <tr> <td>1</td><td>HLTSW1Active</td><td>HLT Active</td></tr> </tbody> </table>	Enumeration			Binary	Value	Description	0	HLTSW1Inactive	HLT Inactive	1	HLTSW1Active	HLT Active																						
Enumeration																																				
Binary	Value	Description																																		
0	HLTSW1Inactive	HLT Inactive																																		
1	HLTSW1Active	HLT Active																																		
HLT2	UINT16	<table border="1"> <thead> <tr> <th colspan="3">Enumeration</th></tr> <tr> <th>Binary</th><th>Value</th><th>Description</th></tr> </thead> <tbody> <tr> <td>0</td><td>HLTSW2Inactive</td><td>HLT Inactive</td></tr> <tr> <td>1</td><td>HLTSW2Active</td><td>HLT Active</td></tr> </tbody> </table>	Enumeration			Binary	Value	Description	0	HLTSW2Inactive	HLT Inactive	1	HLTSW2Active	HLT Active																						
Enumeration																																				
Binary	Value	Description																																		
0	HLTSW2Inactive	HLT Inactive																																		
1	HLTSW2Active	HLT Active																																		
INCNUMTEAM	UINT16	<p>FEEDERNET incoming team array number of teams</p> <table border="1"> <thead> <tr> <th colspan="3">Numeric Type, Range: 0-65535</th></tr> <tr> <th>Action</th><th>Value</th><th></th></tr> </thead> <tbody> <tr> <td>Multiplier</td><td>1</td><td></td></tr> <tr> <td>Adder</td><td>0</td><td></td></tr> </tbody> </table>	Numeric Type, Range: 0-65535			Action	Value		Multiplier	1		Adder	0																							
Numeric Type, Range: 0-65535																																				
Action	Value																																			
Multiplier	1																																			
Adder	0																																			
IndexMngTable	UINT16	<p>Find this node in the NLTA arrays</p> <table border="1"> <thead> <tr> <th colspan="3">Numeric Type, Range: 0-65535</th></tr> <tr> <th>Action</th><th>Value</th><th></th></tr> </thead> <tbody> <tr> <td>Multiplier</td><td>1</td><td></td></tr> <tr> <td>Adder</td><td>0</td><td></td></tr> </tbody> </table>	Numeric Type, Range: 0-65535			Action	Value		Multiplier	1		Adder	0																							
Numeric Type, Range: 0-65535																																				
Action	Value																																			
Multiplier	1																																			
Adder	0																																			
Instance	UINT16	<p>Instance: The value is used for debugging purposes and does not yield any benefit</p> <table border="1"> <thead> <tr> <th colspan="3">Numeric Type, Range: 0-65535</th></tr> <tr> <th>Action</th><th>Value</th><th></th></tr> </thead> <tbody> <tr> <td>Multiplier</td><td>1</td><td></td></tr> <tr> <td>Adder</td><td>0</td><td></td></tr> </tbody> </table>	Numeric Type, Range: 0-65535			Action	Value		Multiplier	1		Adder	0																							
Numeric Type, Range: 0-65535																																				
Action	Value																																			
Multiplier	1																																			
Adder	0																																			

		Internal event-specific code																											
InternalCode	UINT16	<table border="1"> <thead> <tr> <th colspan="3">Enumeration</th> </tr> <tr> <th>Binary</th><th>Value</th><th>Description</th></tr> </thead> <tbody> <tr> <td>1</td><td>CCircRsrcOK</td><td>Contract circuit resources are adequate</td></tr> <tr> <td>2</td><td>CLineSegReqHi</td><td>Contract line segment request above limit</td></tr> <tr> <td>3</td><td>CLoadCapReqHi</td><td>Contract load capacity request above limit</td></tr> <tr> <td>4</td><td>SrcSubSwVloss</td><td>SourceSub Switch has detected voltage loss</td></tr> </tbody> </table>	Enumeration			Binary	Value	Description	1	CCircRsrcOK	Contract circuit resources are adequate	2	CLineSegReqHi	Contract line segment request above limit	3	CLoadCapReqHi	Contract load capacity request above limit	4	SrcSubSwVloss	SourceSub Switch has detected voltage loss									
Enumeration																													
Binary	Value	Description																											
1	CCircRsrcOK	Contract circuit resources are adequate																											
2	CLineSegReqHi	Contract line segment request above limit																											
3	CLoadCapReqHi	Contract load capacity request above limit																											
4	SrcSubSwVloss	SourceSub Switch has detected voltage loss																											
LineSegLimit	UINT16	<table border="1"> <thead> <tr> <th colspan="3">Enumeration</th> </tr> <tr> <th>Binary</th><th>Value</th><th>Description</th></tr> </thead> <tbody> <tr> <td>0</td><td>LineSegLimit</td><td>Line Seg Limit</td></tr> </tbody> </table>	Enumeration			Binary	Value	Description	0	LineSegLimit	Line Seg Limit																		
Enumeration																													
Binary	Value	Description																											
0	LineSegLimit	Line Seg Limit																											
LoadingCurrent	UINT16	<p>1 amperes per count</p> <table border="1"> <thead> <tr> <th colspan="3">Numeric Type, Range: 0-655350</th> </tr> <tr> <th>Action</th><th>Value</th><th></th></tr> </thead> <tbody> <tr> <td>Multiplier</td><td>1</td><td></td></tr> <tr> <td>Adder</td><td>0</td><td></td></tr> </tbody> </table>	Numeric Type, Range: 0-655350			Action	Value		Multiplier	1		Adder	0																
Numeric Type, Range: 0-655350																													
Action	Value																												
Multiplier	1																												
Adder	0																												
LOGDiagType	UINT16	<p>LOG Diagnos Type</p> <table border="1"> <thead> <tr> <th colspan="3">Enumeration</th> </tr> <tr> <th>Binary</th><th>Value</th><th>Description</th></tr> </thead> <tbody> <tr> <td>1</td><td>Alarm</td><td>Alarm</td></tr> <tr> <td>2</td><td>Warning</td><td>Warning</td></tr> <tr> <td>4</td><td>Error</td><td>Error</td></tr> </tbody> </table>	Enumeration			Binary	Value	Description	1	Alarm	Alarm	2	Warning	Warning	4	Error	Error												
Enumeration																													
Binary	Value	Description																											
1	Alarm	Alarm																											
2	Warning	Warning																											
4	Error	Error																											
ManualOp	UINT16	<table border="1"> <thead> <tr> <th colspan="3">Enumeration</th> </tr> <tr> <th>Binary</th><th>Value</th><th>Description</th></tr> </thead> <tbody> <tr> <td>0</td><td>ManOpInactive</td><td>Man Op Inactive</td></tr> <tr> <td>1</td><td>ManOpActive</td><td>Man Op Active</td></tr> </tbody> </table>	Enumeration			Binary	Value	Description	0	ManOpInactive	Man Op Inactive	1	ManOpActive	Man Op Active															
Enumeration																													
Binary	Value	Description																											
0	ManOpInactive	Man Op Inactive																											
1	ManOpActive	Man Op Active																											
MapNumber	UINT16	<p>MapNumber</p> <table border="1"> <thead> <tr> <th colspan="3">Enumeration</th> </tr> <tr> <th>Binary</th><th>Value</th><th>Description</th></tr> </thead> <tbody> <tr> <td>0</td><td>BinaryInput</td><td>binary input</td></tr> <tr> <td>1</td><td>AnalogInput</td><td>analog input</td></tr> <tr> <td>2</td><td>Counter</td><td>counter</td></tr> <tr> <td>3</td><td>Control</td><td>control</td></tr> <tr> <td>4</td><td>AnalogOutput</td><td>analog output</td></tr> <tr> <td>5</td><td>DblBinaryInput</td><td>double binary output</td></tr> </tbody> </table>	Enumeration			Binary	Value	Description	0	BinaryInput	binary input	1	AnalogInput	analog input	2	Counter	counter	3	Control	control	4	AnalogOutput	analog output	5	DblBinaryInput	double binary output			
Enumeration																													
Binary	Value	Description																											
0	BinaryInput	binary input																											
1	AnalogInput	analog input																											
2	Counter	counter																											
3	Control	control																											
4	AnalogOutput	analog output																											
5	DblBinaryInput	double binary output																											
Master	UINT16	<table border="1"> <thead> <tr> <th colspan="3">Enumeration</th> </tr> <tr> <th>Binary</th><th>Value</th><th>Description</th></tr> </thead> <tbody> <tr> <td>1</td><td>Master1</td><td>Master 1</td></tr> <tr> <td>2</td><td>Master2</td><td>Master 2</td></tr> <tr> <td>3</td><td>Master3</td><td>Master 3</td></tr> <tr> <td>4</td><td>Master4</td><td>Master 4</td></tr> <tr> <td>5</td><td>Master5</td><td>Master 5</td></tr> <tr> <td>6</td><td>Master6</td><td>Master 6</td></tr> <tr> <td>255</td><td>NoMaster</td><td>No Master</td></tr> </tbody> </table>	Enumeration			Binary	Value	Description	1	Master1	Master 1	2	Master2	Master 2	3	Master3	Master 3	4	Master4	Master 4	5	Master5	Master 5	6	Master6	Master 6	255	NoMaster	No Master
Enumeration																													
Binary	Value	Description																											
1	Master1	Master 1																											
2	Master2	Master 2																											
3	Master3	Master 3																											
4	Master4	Master 4																											
5	Master5	Master 5																											
6	Master6	Master 6																											
255	NoMaster	No Master																											
MasterRecAddError	UINT16	<table border="1"> <thead> <tr> <th colspan="3">Enumeration</th> </tr> <tr> <th>Binary</th><th>Value</th><th>Description</th></tr> </thead> <tbody> <tr> <td>0</td><td>Good</td><td>good</td></tr> <tr> <td>1</td><td>Error</td><td>error</td></tr> <tr> <td>2</td><td>AlrdyInList</td><td>already in list</td></tr> </tbody> </table>	Enumeration			Binary	Value	Description	0	Good	good	1	Error	error	2	AlrdyInList	already in list												
Enumeration																													
Binary	Value	Description																											
0	Good	good																											
1	Error	error																											
2	AlrdyInList	already in list																											

Definitions of Historic Events

		<table border="1"> <tr><td>3</td><td>ListFull</td><td>list full</td></tr> <tr><td>4</td><td>NotOnList</td><td>not on list</td></tr> </table>	3	ListFull	list full	4	NotOnList	not on list																														
3	ListFull	list full																																				
4	NotOnList	not on list																																				
MaxPeersWhen	UINT16	<p>Max Peers Occur During This</p> <table border="1"> <thead> <tr> <th colspan="3">Enumeration</th> </tr> <tr> <th>Binary</th><th>Value</th><th>Description</th></tr> </thead> <tbody> <tr><td>0</td><td>WhenTestInit</td><td>WhenTestInit</td></tr> <tr><td>1</td><td>WhenTestStats</td><td>WhenTestStats</td></tr> </tbody> </table>	Enumeration			Binary	Value	Description	0	WhenTestInit	WhenTestInit	1	WhenTestStats	WhenTestStats																								
Enumeration																																						
Binary	Value	Description																																				
0	WhenTestInit	WhenTestInit																																				
1	WhenTestStats	WhenTestStats																																				
MemberWithDoneAndEOL	UINT16	<table border="1"> <thead> <tr> <th colspan="3">Enumeration</th> </tr> <tr> <th>Binary</th><th>Value</th><th>Description</th></tr> </thead> <tbody> <tr><td>1</td><td>Member1</td><td>Member 1</td></tr> <tr><td>2</td><td>Member2</td><td>Member 2</td></tr> <tr><td>3</td><td>Member3</td><td>Member 3</td></tr> <tr><td>4</td><td>Member4</td><td>Member 4</td></tr> <tr><td>5</td><td>Member5</td><td>Member 5</td></tr> <tr><td>6</td><td>Member6</td><td>Member 6</td></tr> <tr><td>7</td><td>Member7</td><td>Member 7</td></tr> <tr><td>8</td><td>Member8</td><td>Member 8</td></tr> <tr><td>254</td><td>EndofList</td><td>EndofList</td></tr> <tr><td>256</td><td>Done</td><td>Done</td></tr> </tbody> </table>	Enumeration			Binary	Value	Description	1	Member1	Member 1	2	Member2	Member 2	3	Member3	Member 3	4	Member4	Member 4	5	Member5	Member 5	6	Member6	Member 6	7	Member7	Member 7	8	Member8	Member 8	254	EndofList	EndofList	256	Done	Done
Enumeration																																						
Binary	Value	Description																																				
1	Member1	Member 1																																				
2	Member2	Member 2																																				
3	Member3	Member 3																																				
4	Member4	Member 4																																				
5	Member5	Member 5																																				
6	Member6	Member 6																																				
7	Member7	Member 7																																				
8	Member8	Member 8																																				
254	EndofList	EndofList																																				
256	Done	Done																																				
MoreThanOneDiffFound	UINT16	<table border="1"> <thead> <tr> <th colspan="3">Enumeration</th> </tr> <tr> <th>Binary</th><th>Value</th><th>Description</th></tr> </thead> <tbody> <tr><td>0</td><td>OneDiffFound</td><td>Only OneDiff Found</td></tr> <tr><td>1</td><td>TwoOrMoreDiffs</td><td>Two Or More Diffs</td></tr> </tbody> </table>	Enumeration			Binary	Value	Description	0	OneDiffFound	Only OneDiff Found	1	TwoOrMoreDiffs	Two Or More Diffs																								
Enumeration																																						
Binary	Value	Description																																				
0	OneDiffFound	Only OneDiff Found																																				
1	TwoOrMoreDiffs	Two Or More Diffs																																				
netfragID	UINT16	<p>Net Fragment ID</p> <table border="1"> <thead> <tr> <th colspan="2">Numeric Type, Range: 0-65535</th> </tr> <tr> <th>Action</th><th>Value</th></tr> </thead> <tbody> <tr><td>Multiplier</td><td>1</td></tr> <tr><td>Adder</td><td>0</td></tr> </tbody> </table>	Numeric Type, Range: 0-65535		Action	Value	Multiplier	1	Adder	0																												
Numeric Type, Range: 0-65535																																						
Action	Value																																					
Multiplier	1																																					
Adder	0																																					
NETLISTRNR	UINT16	<p>Number of NETLIST runners in RunnerSource</p> <table border="1"> <thead> <tr> <th colspan="2">Numeric Type, Range: 0-65535</th> </tr> <tr> <th>Action</th><th>Value</th></tr> </thead> <tbody> <tr><td>Multiplier</td><td>1</td></tr> <tr><td>Adder</td><td>0</td></tr> </tbody> </table>	Numeric Type, Range: 0-65535		Action	Value	Multiplier	1	Adder	0																												
Numeric Type, Range: 0-65535																																						
Action	Value																																					
Multiplier	1																																					
Adder	0																																					
netobuffFree	UINT16	<p>Cumulative free buffer space</p> <table border="1"> <thead> <tr> <th colspan="2">Numeric Type, Range: 0-65535</th> </tr> <tr> <th>Action</th><th>Value</th></tr> </thead> <tbody> <tr><td>Multiplier</td><td>1</td></tr> <tr><td>Adder</td><td>0</td></tr> </tbody> </table>	Numeric Type, Range: 0-65535		Action	Value	Multiplier	1	Adder	0																												
Numeric Type, Range: 0-65535																																						
Action	Value																																					
Multiplier	1																																					
Adder	0																																					
NETSTE	UINT16	<p>Net state E</p> <table border="1"> <thead> <tr> <th colspan="3">Enumeration</th> </tr> <tr> <th>Binary</th><th>Value</th><th>Description</th></tr> </thead> <tbody> <tr><td>1</td><td>BACKIDLE</td><td>Go back to idle</td></tr> <tr><td>8</td><td>RESENDRNR</td><td>Go re-send the runner objects since some failed</td></tr> <tr><td>4</td><td>WAITRT</td><td>Go wait for returns</td></tr> </tbody> </table>	Enumeration			Binary	Value	Description	1	BACKIDLE	Go back to idle	8	RESENDRNR	Go re-send the runner objects since some failed	4	WAITRT	Go wait for returns																					
Enumeration																																						
Binary	Value	Description																																				
1	BACKIDLE	Go back to idle																																				
8	RESENDRNR	Go re-send the runner objects since some failed																																				
4	WAITRT	Go wait for returns																																				
NetViewAnalyzer	UINT16	<table border="1"> <thead> <tr> <th colspan="3">Enumeration</th> </tr> <tr> <th>Binary</th><th>Value</th><th>Description</th></tr> </thead> <tbody> <tr><td>0</td><td>NETVIEWNOTVALID</td><td>Net view is not valid</td></tr> </tbody> </table>	Enumeration			Binary	Value	Description	0	NETVIEWNOTVALID	Net view is not valid																											
Enumeration																																						
Binary	Value	Description																																				
0	NETVIEWNOTVALID	Net view is not valid																																				

		<table border="1" style="width: 100%; border-collapse: collapse;"> <tr><td style="width: 20px;">2</td><td style="width: 100px;">NETVIEWVALID</td><td>Net view is valid</td></tr> </table>	2	NETVIEWVALID	Net view is valid															
2	NETVIEWVALID	Net view is valid																		
NETViewLength	UINT16	<p>The Normal State NetView Length of each row table</p> <table border="1" style="width: 100%; border-collapse: collapse; text-align: center;"> <tr><th colspan="2">Numeric Type, Range: 0-65535</th></tr> <tr><th>Action</th><th>Value</th></tr> <tr><td>Multiplier</td><td>1</td></tr> <tr><td>Adder</td><td>0</td></tr> </table>	Numeric Type, Range: 0-65535		Action	Value	Multiplier	1	Adder	0										
Numeric Type, Range: 0-65535																				
Action	Value																			
Multiplier	1																			
Adder	0																			
NetViewRowNum	UINT16	<p>Runner source row number in nnet</p> <table border="1" style="width: 100%; border-collapse: collapse; text-align: center;"> <tr><th colspan="2">Numeric Type, Range: 0-65535</th></tr> <tr><th>Action</th><th>Value</th></tr> <tr><td>Multiplier</td><td>1</td></tr> <tr><td>Adder</td><td>0</td></tr> </table>	Numeric Type, Range: 0-65535		Action	Value	Multiplier	1	Adder	0										
Numeric Type, Range: 0-65535																				
Action	Value																			
Multiplier	1																			
Adder	0																			
NETVSRC	UINT16	<table border="1" style="width: 100%; border-collapse: collapse; text-align: center;"> <thead> <tr><th colspan="3">Enumeration</th></tr> <tr><th>Binary</th><th>Value</th><th>Description</th></tr> </thead> <tbody> <tr><td>1</td><td>NETVSRC_NORMAL</td><td>NETV source is normal</td></tr> <tr><td>2</td><td>NETVSRC_ALTERNATE</td><td>NETV source is alternate</td></tr> <tr><td>3</td><td>NETVFDR_NOTNORMAL</td><td>NETV source is not normal</td></tr> <tr><td>255</td><td>NETVSRC_UNDEFINED</td><td>NETV source is undefined</td></tr> </tbody> </table>	Enumeration			Binary	Value	Description	1	NETVSRC_NORMAL	NETV source is normal	2	NETVSRC_ALTERNATE	NETV source is alternate	3	NETVFDR_NOTNORMAL	NETV source is not normal	255	NETVSRC_UNDEFINED	NETV source is undefined
Enumeration																				
Binary	Value	Description																		
1	NETVSRC_NORMAL	NETV source is normal																		
2	NETVSRC_ALTERNATE	NETV source is alternate																		
3	NETVFDR_NOTNORMAL	NETV source is not normal																		
255	NETVSRC_UNDEFINED	NETV source is undefined																		
NodeCount	UINT16	<p>Number of appearances in this runner</p> <table border="1" style="width: 100%; border-collapse: collapse; text-align: center;"> <tr><th colspan="2">Numeric Type, Range: 0-65535</th></tr> <tr><th>Action</th><th>Value</th></tr> <tr><td>Multiplier</td><td>1</td></tr> <tr><td>Adder</td><td>0</td></tr> </table>	Numeric Type, Range: 0-65535		Action	Value	Multiplier	1	Adder	0										
Numeric Type, Range: 0-65535																				
Action	Value																			
Multiplier	1																			
Adder	0																			
NodeIndex	UINT16	<p>Our position in the Node Index table</p> <table border="1" style="width: 100%; border-collapse: collapse; text-align: center;"> <tr><th colspan="2">Numeric Type, Range: 0-65535</th></tr> <tr><th>Action</th><th>Value</th></tr> <tr><td>Multiplier</td><td>1</td></tr> <tr><td>Adder</td><td>0</td></tr> </table>	Numeric Type, Range: 0-65535		Action	Value	Multiplier	1	Adder	0										
Numeric Type, Range: 0-65535																				
Action	Value																			
Multiplier	1																			
Adder	0																			
Nodelists	UINT16	<p>Runner node lists</p> <table border="1" style="width: 100%; border-collapse: collapse; text-align: center;"> <tr><th colspan="2">Numeric Type, Range: 0-65535</th></tr> <tr><th>Action</th><th>Value</th></tr> <tr><td>Multiplier</td><td>1</td></tr> <tr><td>Adder</td><td>0</td></tr> </table>	Numeric Type, Range: 0-65535		Action	Value	Multiplier	1	Adder	0										
Numeric Type, Range: 0-65535																				
Action	Value																			
Multiplier	1																			
Adder	0																			
NoMaster	UINT16	<table border="1" style="width: 100%; border-collapse: collapse; text-align: center;"> <thead> <tr><th colspan="3">Enumeration</th></tr> <tr><th>Binary</th><th>Value</th><th>Description</th></tr> </thead> <tbody> <tr><td>0</td><td>MasterExists</td><td>MasterExists</td></tr> <tr><td>1</td><td>NoMaster</td><td>No Master</td></tr> </tbody> </table>	Enumeration			Binary	Value	Description	0	MasterExists	MasterExists	1	NoMaster	No Master						
Enumeration																				
Binary	Value	Description																		
0	MasterExists	MasterExists																		
1	NoMaster	No Master																		
NoPeersWhen	UINT16	<p>Max Peers Occur During This</p> <table border="1" style="width: 100%; border-collapse: collapse; text-align: center;"> <tr><th colspan="3">Enumeration</th></tr> <tr><th>Binary</th><th>Value</th><th>Description</th></tr> <tr><td>0</td><td>SchedTest</td><td>SchedTest</td></tr> <tr><td>1</td><td>QuickTest</td><td>QuickTest</td></tr> <tr><td>2</td><td>KeepAlive</td><td>KeepAlive</td></tr> <tr><td>3</td><td>KwikKeepAlive</td><td>KwikKeepAlive</td></tr> </table>	Enumeration			Binary	Value	Description	0	SchedTest	SchedTest	1	QuickTest	QuickTest	2	KeepAlive	KeepAlive	3	KwikKeepAlive	KwikKeepAlive
Enumeration																				
Binary	Value	Description																		
0	SchedTest	SchedTest																		
1	QuickTest	QuickTest																		
2	KeepAlive	KeepAlive																		
3	KwikKeepAlive	KwikKeepAlive																		
nsnlg	UINT16	<p>number of device connections present, counter, list len</p> <table border="1" style="width: 100%; border-collapse: collapse; text-align: center;"> <tr><th colspan="2">Numeric Type, Range: 0-65535</th></tr> <tr><th>Action</th><th>Value</th></tr> <tr><td>Multiplier</td><td>1</td></tr> </table>	Numeric Type, Range: 0-65535		Action	Value	Multiplier	1												
Numeric Type, Range: 0-65535																				
Action	Value																			
Multiplier	1																			

Definitions of Historic Events

		Adder 0								
nt	UINT16	<p>Number of team records</p> <table border="1"> <thead> <tr> <th colspan="2">Numeric Type, Range: 0-65535</th> </tr> <tr> <th>Action</th> <th>Value</th> </tr> </thead> <tbody> <tr> <td>Multiplier</td> <td>1</td> </tr> <tr> <td>Adder</td> <td>0</td> </tr> </tbody> </table>	Numeric Type, Range: 0-65535		Action	Value	Multiplier	1	Adder	0
Numeric Type, Range: 0-65535										
Action	Value									
Multiplier	1									
Adder	0									
NumberFrames	UINT16	<p>Number frames have been currently written on CF</p> <table border="1"> <thead> <tr> <th colspan="2">Numeric Type, Range: 0-3600</th> </tr> <tr> <th>Action</th> <th>Value</th> </tr> </thead> <tbody> <tr> <td>Multiplier</td> <td>1</td> </tr> <tr> <td>Adder</td> <td>0</td> </tr> </tbody> </table>	Numeric Type, Range: 0-3600		Action	Value	Multiplier	1	Adder	0
Numeric Type, Range: 0-3600										
Action	Value									
Multiplier	1									
Adder	0									
NumDataElements	UINT16	<p>Actual number of data elements in DLV</p> <table border="1"> <thead> <tr> <th colspan="2">Numeric Type, Range: 0-65535</th> </tr> <tr> <th>Action</th> <th>Value</th> </tr> </thead> <tbody> <tr> <td>Multiplier</td> <td>1</td> </tr> <tr> <td>Adder</td> <td>0</td> </tr> </tbody> </table>	Numeric Type, Range: 0-65535		Action	Value	Multiplier	1	Adder	0
Numeric Type, Range: 0-65535										
Action	Value									
Multiplier	1									
Adder	0									
NumDevicesinFN	UINT16	<p>Number of devices in the Feeder Net</p> <table border="1"> <thead> <tr> <th colspan="2">Numeric Type, Range: 0-65535</th> </tr> <tr> <th>Action</th> <th>Value</th> </tr> </thead> <tbody> <tr> <td>Multiplier</td> <td>1</td> </tr> <tr> <td>Adder</td> <td>0</td> </tr> </tbody> </table>	Numeric Type, Range: 0-65535		Action	Value	Multiplier	1	Adder	0
Numeric Type, Range: 0-65535										
Action	Value									
Multiplier	1									
Adder	0									
NumNodeID	UINT16	<p>Number of Node IDs in the list</p> <table border="1"> <thead> <tr> <th colspan="2">Numeric Type, Range: 0-65535</th> </tr> <tr> <th>Action</th> <th>Value</th> </tr> </thead> <tbody> <tr> <td>Multiplier</td> <td>1</td> </tr> <tr> <td>Adder</td> <td>0</td> </tr> </tbody> </table>	Numeric Type, Range: 0-65535		Action	Value	Multiplier	1	Adder	0
Numeric Type, Range: 0-65535										
Action	Value									
Multiplier	1									
Adder	0									
NumNodeIndex	UINT16	<p>Number of indexes in the Node table</p> <table border="1"> <thead> <tr> <th colspan="2">Numeric Type, Range: 0-65535</th> </tr> <tr> <th>Action</th> <th>Value</th> </tr> </thead> <tbody> <tr> <td>Multiplier</td> <td>1</td> </tr> <tr> <td>Adder</td> <td>0</td> </tr> </tbody> </table>	Numeric Type, Range: 0-65535		Action	Value	Multiplier	1	Adder	0
Numeric Type, Range: 0-65535										
Action	Value									
Multiplier	1									
Adder	0									
NumOfDevices	UINT16	<p>Netview number of devices/switches in DivisionNet</p> <table border="1"> <thead> <tr> <th colspan="2">Numeric Type, Range: 0-65535</th> </tr> <tr> <th>Action</th> <th>Value</th> </tr> </thead> <tbody> <tr> <td>Multiplier</td> <td>1</td> </tr> <tr> <td>Adder</td> <td>0</td> </tr> </tbody> </table>	Numeric Type, Range: 0-65535		Action	Value	Multiplier	1	Adder	0
Numeric Type, Range: 0-65535										
Action	Value									
Multiplier	1									
Adder	0									
NumOfPowSrc	UINT16	<p>Number of power sources in DivisionNet</p> <table border="1"> <thead> <tr> <th colspan="2">Numeric Type, Range: 0-65535</th> </tr> <tr> <th>Action</th> <th>Value</th> </tr> </thead> <tbody> <tr> <td>Multiplier</td> <td>1</td> </tr> <tr> <td>Adder</td> <td>0</td> </tr> </tbody> </table>	Numeric Type, Range: 0-65535		Action	Value	Multiplier	1	Adder	0
Numeric Type, Range: 0-65535										
Action	Value									
Multiplier	1									
Adder	0									
NumOfRows	UINT16	<p>Net Present NetView number of rows in table for DivisionNet</p> <table border="1"> <thead> <tr> <th colspan="2">Numeric Type, Range: 0-65535</th> </tr> <tr> <th>Action</th> <th>Value</th> </tr> </thead> <tbody> <tr> <td>Multiplier</td> <td>1</td> </tr> <tr> <td>Adder</td> <td>0</td> </tr> </tbody> </table>	Numeric Type, Range: 0-65535		Action	Value	Multiplier	1	Adder	0
Numeric Type, Range: 0-65535										
Action	Value									
Multiplier	1									
Adder	0									

NumOfTeams	UINT16	<p>Number of teams</p> <table border="1" style="margin-left: auto; margin-right: auto;"> <thead> <tr><th colspan="2">Numeric Type, Range: 0-65535</th></tr> <tr><th>Action</th><th>Value</th></tr> </thead> <tbody> <tr><td>Multiplier</td><td>1</td></tr> <tr><td>Adder</td><td>0</td></tr> </tbody> </table>	Numeric Type, Range: 0-65535		Action	Value	Multiplier	1	Adder	0																												
Numeric Type, Range: 0-65535																																						
Action	Value																																					
Multiplier	1																																					
Adder	0																																					
NumOfWirePairs	UINT16	<p>Number of entries in the D-W (Device-Wire) tables</p> <table border="1" style="margin-left: auto; margin-right: auto;"> <thead> <tr><th colspan="2">Numeric Type, Range: 0-65535</th></tr> <tr><th>Action</th><th>Value</th></tr> </thead> <tbody> <tr><td>Multiplier</td><td>1</td></tr> <tr><td>Adder</td><td>0</td></tr> </tbody> </table>	Numeric Type, Range: 0-65535		Action	Value	Multiplier	1	Adder	0																												
Numeric Type, Range: 0-65535																																						
Action	Value																																					
Multiplier	1																																					
Adder	0																																					
NumPaths	UINT16	<p>Number of paths in this particular Feeder Net</p> <table border="1" style="margin-left: auto; margin-right: auto;"> <thead> <tr><th colspan="2">Numeric Type, Range: 0-65535</th></tr> <tr><th>Action</th><th>Value</th></tr> </thead> <tbody> <tr><td>Multiplier</td><td>1</td></tr> <tr><td>Adder</td><td>0</td></tr> </tbody> </table>	Numeric Type, Range: 0-65535		Action	Value	Multiplier	1	Adder	0																												
Numeric Type, Range: 0-65535																																						
Action	Value																																					
Multiplier	1																																					
Adder	0																																					
NumPayLoad	UINT16	<p>Quantity of associated payload elements</p> <table border="1" style="margin-left: auto; margin-right: auto;"> <thead> <tr><th colspan="2">Numeric Type, Range: 0-65535</th></tr> <tr><th>Action</th><th>Value</th></tr> </thead> <tbody> <tr><td>Multiplier</td><td>1</td></tr> <tr><td>Adder</td><td>0</td></tr> </tbody> </table>	Numeric Type, Range: 0-65535		Action	Value	Multiplier	1	Adder	0																												
Numeric Type, Range: 0-65535																																						
Action	Value																																					
Multiplier	1																																					
Adder	0																																					
NumRunners	UINT16	<p>Number of runners</p> <table border="1" style="margin-left: auto; margin-right: auto;"> <thead> <tr><th colspan="2">Numeric Type, Range: 0-65535</th></tr> <tr><th>Action</th><th>Value</th></tr> </thead> <tbody> <tr><td>Multiplier</td><td>1</td></tr> <tr><td>Adder</td><td>0</td></tr> </tbody> </table>	Numeric Type, Range: 0-65535		Action	Value	Multiplier	1	Adder	0																												
Numeric Type, Range: 0-65535																																						
Action	Value																																					
Multiplier	1																																					
Adder	0																																					
ObjectLength	UINT16	<table border="1" style="margin-left: auto; margin-right: auto;"> <thead> <tr><th colspan="2">Numeric Type, Range: 0-65535</th></tr> <tr><th>Action</th><th>Value</th></tr> </thead> <tbody> <tr><td>Multiplier</td><td>1</td></tr> <tr><td>Adder</td><td>0</td></tr> </tbody> </table>	Numeric Type, Range: 0-65535		Action	Value	Multiplier	1	Adder	0																												
Numeric Type, Range: 0-65535																																						
Action	Value																																					
Multiplier	1																																					
Adder	0																																					
ObjID	UINT16	<p>Object ID</p> <table border="1" style="margin-left: auto; margin-right: auto;"> <thead> <tr><th colspan="2">Numeric Type, Range: 0-65535</th></tr> <tr><th>Action</th><th>Value</th></tr> </thead> <tbody> <tr><td>Multiplier</td><td>1</td></tr> <tr><td>Adder</td><td>0</td></tr> </tbody> </table>	Numeric Type, Range: 0-65535		Action	Value	Multiplier	1	Adder	0																												
Numeric Type, Range: 0-65535																																						
Action	Value																																					
Multiplier	1																																					
Adder	0																																					
ObjState	UINT16	<p style="text-align: center;">Enumeration</p> <table border="1" style="margin-left: auto; margin-right: auto;"> <thead> <tr><th>Binary</th><th>Value</th><th>Description</th></tr> </thead> <tbody> <tr><td>0</td><td>NETOBJSTATENONE</td><td>No net object state</td></tr> <tr><td>1</td><td>NETOBJSTATEREADY</td><td>Net object state is ready</td></tr> <tr><td>2</td><td>NETOBJSEBUFFERED</td><td>Net object state is buffered</td></tr> <tr><td>3</td><td>NETOBJSTATEACKEXEC</td><td>Net object state positive ack</td></tr> <tr><td>4</td><td>NETOBJNACKEXEC</td><td>Net object state negative ack</td></tr> <tr><td>5</td><td>NETOBJSTATEHOLD</td><td>Net object state is on hold</td></tr> <tr><td>6</td><td>NETOBJSTATESEND</td><td>Net object state sent</td></tr> <tr><td>7</td><td>NETOBJSENDWAIT</td><td>Net object state is waiting to be sent</td></tr> <tr><td>8</td><td>NETOBJSENDCONTINUE</td><td>Net object state is continued to be sent</td></tr> <tr><td>9</td><td>NETOBJSTATEREMOVE</td><td>Net object state is removed</td></tr> <tr><td>10</td><td>NETOBJRECEIVED</td><td>Net object state is received</td></tr> </tbody> </table>	Binary	Value	Description	0	NETOBJSTATENONE	No net object state	1	NETOBJSTATEREADY	Net object state is ready	2	NETOBJSEBUFFERED	Net object state is buffered	3	NETOBJSTATEACKEXEC	Net object state positive ack	4	NETOBJNACKEXEC	Net object state negative ack	5	NETOBJSTATEHOLD	Net object state is on hold	6	NETOBJSTATESEND	Net object state sent	7	NETOBJSENDWAIT	Net object state is waiting to be sent	8	NETOBJSENDCONTINUE	Net object state is continued to be sent	9	NETOBJSTATEREMOVE	Net object state is removed	10	NETOBJRECEIVED	Net object state is received
Binary	Value	Description																																				
0	NETOBJSTATENONE	No net object state																																				
1	NETOBJSTATEREADY	Net object state is ready																																				
2	NETOBJSEBUFFERED	Net object state is buffered																																				
3	NETOBJSTATEACKEXEC	Net object state positive ack																																				
4	NETOBJNACKEXEC	Net object state negative ack																																				
5	NETOBJSTATEHOLD	Net object state is on hold																																				
6	NETOBJSTATESEND	Net object state sent																																				
7	NETOBJSENDWAIT	Net object state is waiting to be sent																																				
8	NETOBJSENDCONTINUE	Net object state is continued to be sent																																				
9	NETOBJSTATEREMOVE	Net object state is removed																																				
10	NETOBJRECEIVED	Net object state is received																																				

Definitions of Historic Events

		<table border="1"> <tr> <td>11</td><td>NETOBJSENDDELAY</td><td>Net object state is delayed</td></tr> </table>	11	NETOBJSENDDELAY	Net object state is delayed																																																																																				
11	NETOBJSENDDELAY	Net object state is delayed																																																																																							
OneHexByte	UINT16	<p>Values represented in hexadecimal code</p> <table border="1"> <tr> <td colspan="2">Numeric Type, Range: 0-255</td> </tr> <tr> <td>Action</td> <td>Value</td> </tr> <tr> <td>Multiplier</td> <td>1</td> </tr> <tr> <td>Adder</td> <td>0</td> </tr> <tr> <td colspan="2">Presentation</td> </tr> <tr> <td>Binary</td> <td>{0:X2}</td> </tr> </table>	Numeric Type, Range: 0-255		Action	Value	Multiplier	1	Adder	0	Presentation		Binary	{0:X2}																																																																											
Numeric Type, Range: 0-255																																																																																									
Action	Value																																																																																								
Multiplier	1																																																																																								
Adder	0																																																																																								
Presentation																																																																																									
Binary	{0:X2}																																																																																								
Point	UINT16	<table border="1"> <tr> <td colspan="3">Enumeration</td> </tr> <tr> <th>Binary</th> <th>Value</th> <th>Description</th> </tr> <tr> <td>1</td> <td>OperateIR</td> <td>Point to operate IR</td> </tr> <tr> <td>2</td> <td>BlockReclosing</td> <td>Point to block reclosing</td> </tr> <tr> <td>3</td> <td>BlockGroundTrip</td> <td>Point to block ground trip</td> </tr> <tr> <td>4</td> <td>ChangeProfile</td> <td>Point to change profile.</td> </tr> </table>	Enumeration			Binary	Value	Description	1	OperateIR	Point to operate IR	2	BlockReclosing	Point to block reclosing	3	BlockGroundTrip	Point to block ground trip	4	ChangeProfile	Point to change profile.																																																																					
Enumeration																																																																																									
Binary	Value	Description																																																																																							
1	OperateIR	Point to operate IR																																																																																							
2	BlockReclosing	Point to block reclosing																																																																																							
3	BlockGroundTrip	Point to block ground trip																																																																																							
4	ChangeProfile	Point to change profile.																																																																																							
PointType	UINT16	<table border="1"> <tr> <td colspan="3">Enumeration</td> </tr> <tr> <th>Binary</th> <th>Value</th> <th>Description</th> </tr> <tr> <td>0</td> <td>OpenPoint</td> <td>Open Point</td> </tr> <tr> <td>1</td> <td>ClosedPoint</td> <td>Closed Point</td> </tr> <tr> <td>2</td> <td>InconsistPt</td> <td>Inconsistent Point</td> </tr> </table>	Enumeration			Binary	Value	Description	0	OpenPoint	Open Point	1	ClosedPoint	Closed Point	2	InconsistPt	Inconsistent Point																																																																								
Enumeration																																																																																									
Binary	Value	Description																																																																																							
0	OpenPoint	Open Point																																																																																							
1	ClosedPoint	Closed Point																																																																																							
2	InconsistPt	Inconsistent Point																																																																																							
PortCode	UINT16	<p>Communication port code.</p> <table border="1"> <tr> <td colspan="3">Enumeration</td> </tr> <tr> <th>Binary</th> <th>Value</th> <th>Description</th> </tr> <tr> <td>0</td> <td>UDP</td> <td>UDP</td> </tr> <tr> <td>1</td> <td>PortA</td> <td>portA</td> </tr> <tr> <td>2</td> <td>PortB</td> <td>portB</td> </tr> <tr> <td>3</td> <td>PortC</td> <td>portC</td> </tr> <tr> <td>4</td> <td>PortD</td> <td>portD</td> </tr> <tr> <td>6</td> <td>TCPV6</td> <td>TCP Virtual Port 6</td> </tr> <tr> <td>7</td> <td>TCPV7</td> <td>TCP Virtual Port 7</td> </tr> <tr> <td>8</td> <td>TCPV8</td> <td>TCP Virtual Port 8</td> </tr> <tr> <td>9</td> <td>TCPV9</td> <td>TCP Virtual Port 9</td> </tr> <tr> <td>10</td> <td>TCPV10</td> <td>TCP Virtual Port 10</td> </tr> <tr> <td>11</td> <td>TCPV11</td> <td>TCP Virtual Port 11</td> </tr> <tr> <td>12</td> <td>TCPV12</td> <td>TCP Virtual Port 12</td> </tr> <tr> <td>13</td> <td>TCPV13</td> <td>TCP Virtual Port 13</td> </tr> <tr> <td>14</td> <td>TCPV14</td> <td>TCP Virtual Port 14</td> </tr> <tr> <td>15</td> <td>TCPV15</td> <td>TCP Virtual Port 15</td> </tr> <tr> <td>16</td> <td>TCPV16</td> <td>TCP Virtual Port 16</td> </tr> <tr> <td>17</td> <td>TCPV17</td> <td>TCP Virtual Port 17</td> </tr> <tr> <td>18</td> <td>TCPV18</td> <td>TCP Virtual Port 18</td> </tr> <tr> <td>19</td> <td>TCPV19</td> <td>TCP Virtual Port 19</td> </tr> <tr> <td>20</td> <td>TCPV20</td> <td>TCP Virtual Port 20</td> </tr> <tr> <td>21</td> <td>TCPV21</td> <td>TCP Virtual Port 21</td> </tr> <tr> <td>22</td> <td>TCPV22</td> <td>TCP Virtual Port 22</td> </tr> <tr> <td>23</td> <td>TCPV23</td> <td>TCP Virtual Port 23</td> </tr> <tr> <td>24</td> <td>TCPV24</td> <td>TCP Virtual Port 24</td> </tr> <tr> <td>25</td> <td>TCPV25</td> <td>TCP Virtual Port 25</td> </tr> <tr> <td>26</td> <td>TCPV26</td> <td>TCP Virtual Port 26</td> </tr> <tr> <td>27</td> <td>TCPV27</td> <td>TCP Virtual Port 27</td> </tr> </table>	Enumeration			Binary	Value	Description	0	UDP	UDP	1	PortA	portA	2	PortB	portB	3	PortC	portC	4	PortD	portD	6	TCPV6	TCP Virtual Port 6	7	TCPV7	TCP Virtual Port 7	8	TCPV8	TCP Virtual Port 8	9	TCPV9	TCP Virtual Port 9	10	TCPV10	TCP Virtual Port 10	11	TCPV11	TCP Virtual Port 11	12	TCPV12	TCP Virtual Port 12	13	TCPV13	TCP Virtual Port 13	14	TCPV14	TCP Virtual Port 14	15	TCPV15	TCP Virtual Port 15	16	TCPV16	TCP Virtual Port 16	17	TCPV17	TCP Virtual Port 17	18	TCPV18	TCP Virtual Port 18	19	TCPV19	TCP Virtual Port 19	20	TCPV20	TCP Virtual Port 20	21	TCPV21	TCP Virtual Port 21	22	TCPV22	TCP Virtual Port 22	23	TCPV23	TCP Virtual Port 23	24	TCPV24	TCP Virtual Port 24	25	TCPV25	TCP Virtual Port 25	26	TCPV26	TCP Virtual Port 26	27	TCPV27	TCP Virtual Port 27
Enumeration																																																																																									
Binary	Value	Description																																																																																							
0	UDP	UDP																																																																																							
1	PortA	portA																																																																																							
2	PortB	portB																																																																																							
3	PortC	portC																																																																																							
4	PortD	portD																																																																																							
6	TCPV6	TCP Virtual Port 6																																																																																							
7	TCPV7	TCP Virtual Port 7																																																																																							
8	TCPV8	TCP Virtual Port 8																																																																																							
9	TCPV9	TCP Virtual Port 9																																																																																							
10	TCPV10	TCP Virtual Port 10																																																																																							
11	TCPV11	TCP Virtual Port 11																																																																																							
12	TCPV12	TCP Virtual Port 12																																																																																							
13	TCPV13	TCP Virtual Port 13																																																																																							
14	TCPV14	TCP Virtual Port 14																																																																																							
15	TCPV15	TCP Virtual Port 15																																																																																							
16	TCPV16	TCP Virtual Port 16																																																																																							
17	TCPV17	TCP Virtual Port 17																																																																																							
18	TCPV18	TCP Virtual Port 18																																																																																							
19	TCPV19	TCP Virtual Port 19																																																																																							
20	TCPV20	TCP Virtual Port 20																																																																																							
21	TCPV21	TCP Virtual Port 21																																																																																							
22	TCPV22	TCP Virtual Port 22																																																																																							
23	TCPV23	TCP Virtual Port 23																																																																																							
24	TCPV24	TCP Virtual Port 24																																																																																							
25	TCPV25	TCP Virtual Port 25																																																																																							
26	TCPV26	TCP Virtual Port 26																																																																																							
27	TCPV27	TCP Virtual Port 27																																																																																							

		<table border="1"> <tr><td>28</td><td>TCPV28</td><td>TCP Virtual Port 28</td></tr> <tr><td>29</td><td>TCPV29</td><td>TCP Virtual Port 29</td></tr> <tr><td>30</td><td>TCPV30</td><td>TCP Virtual Port 30</td></tr> <tr><td>31</td><td>TCPV31</td><td>TCP Virtual Port 31</td></tr> <tr><td>32</td><td>TCPV32</td><td>TCP Virtual Port 32</td></tr> <tr><td>33</td><td>TCPV33</td><td>TCP Virtual Port 33</td></tr> <tr><td>34</td><td>TCPV34</td><td>TCP Virtual Port 34</td></tr> <tr><td>35</td><td>TCPV35</td><td>TCP Virtual Port 35</td></tr> <tr><td>36</td><td>TCPV36</td><td>TCP Virtual Port 36</td></tr> <tr><td>37</td><td>TCPV37</td><td>TCP Virtual Port 37</td></tr> <tr><td>38</td><td>TCPV38</td><td>TCP Virtual Port 38</td></tr> <tr><td>255</td><td>Undefined</td><td>Undefined</td></tr> <tr><td>20000</td><td>P20000</td><td>20000</td></tr> <tr><td>20001</td><td>P20001</td><td>20001</td></tr> </table>	28	TCPV28	TCP Virtual Port 28	29	TCPV29	TCP Virtual Port 29	30	TCPV30	TCP Virtual Port 30	31	TCPV31	TCP Virtual Port 31	32	TCPV32	TCP Virtual Port 32	33	TCPV33	TCP Virtual Port 33	34	TCPV34	TCP Virtual Port 34	35	TCPV35	TCP Virtual Port 35	36	TCPV36	TCP Virtual Port 36	37	TCPV37	TCP Virtual Port 37	38	TCPV38	TCP Virtual Port 38	255	Undefined	Undefined	20000	P20000	20000	20001	P20001	20001
28	TCPV28	TCP Virtual Port 28																																										
29	TCPV29	TCP Virtual Port 29																																										
30	TCPV30	TCP Virtual Port 30																																										
31	TCPV31	TCP Virtual Port 31																																										
32	TCPV32	TCP Virtual Port 32																																										
33	TCPV33	TCP Virtual Port 33																																										
34	TCPV34	TCP Virtual Port 34																																										
35	TCPV35	TCP Virtual Port 35																																										
36	TCPV36	TCP Virtual Port 36																																										
37	TCPV37	TCP Virtual Port 37																																										
38	TCPV38	TCP Virtual Port 38																																										
255	Undefined	Undefined																																										
20000	P20000	20000																																										
20001	P20001	20001																																										
PRReason	UINT16	<table border="1"> <thead> <tr> <th colspan="3">Enumeration</th> </tr> <tr> <th>Binary</th><th>Value</th><th>Description</th></tr> </thead> <tbody> <tr><td>1</td><td>UnderFrequency</td><td>Under Frequency</td></tr> <tr><td>2</td><td>HotLineTag</td><td>Hot Line Tag</td></tr> <tr><td>3</td><td>ManualOperation</td><td>Manual Operation</td></tr> <tr><td>4</td><td>LocalCommand</td><td>Local Command</td></tr> <tr><td>5</td><td>AuxInput</td><td>Aux Input</td></tr> <tr><td>6</td><td>StateMismatch</td><td>State Mismatch</td></tr> <tr><td>7</td><td>SCADAMaster</td><td>SCADA Master</td></tr> </tbody> </table>	Enumeration			Binary	Value	Description	1	UnderFrequency	Under Frequency	2	HotLineTag	Hot Line Tag	3	ManualOperation	Manual Operation	4	LocalCommand	Local Command	5	AuxInput	Aux Input	6	StateMismatch	State Mismatch	7	SCADAMaster	SCADA Master															
Enumeration																																												
Binary	Value	Description																																										
1	UnderFrequency	Under Frequency																																										
2	HotLineTag	Hot Line Tag																																										
3	ManualOperation	Manual Operation																																										
4	LocalCommand	Local Command																																										
5	AuxInput	Aux Input																																										
6	StateMismatch	State Mismatch																																										
7	SCADAMaster	SCADA Master																																										
RegistrationStatus	UINT16	<table border="1"> <thead> <tr> <th colspan="3">Enumeration</th> </tr> <tr> <th>Binary</th><th>Value</th><th>Description</th></tr> </thead> <tbody> <tr><td>0</td><td>DNPRETURNGOOD</td><td>DNP return is good</td></tr> <tr><td>1</td><td>DNPRETURNERROR</td><td>DNP return error</td></tr> <tr><td>2</td><td>DNPRTNERRONLIST</td><td>DNP return error already on the list</td></tr> <tr><td>3</td><td>DNPRTNERRLISTFULL</td><td>DNP return error is full</td></tr> <tr><td>4</td><td>DNPRTNOTONLIST</td><td>DNP return error not on list</td></tr> <tr><td>5</td><td>DNPRTNERRNOTP2P</td><td>DNP return error not P2P</td></tr> <tr><td>6</td><td>DNPRTNDELAY</td><td>DNP return delayed before retry</td></tr> <tr><td>7</td><td>DNPRTNACTIVEPOINT</td><td>DNP return active on point</td></tr> <tr><td>8</td><td>DNPRETURNCOMPLETE</td><td>DNP return is complete</td></tr> <tr><td>9</td><td>DNPRTNINPROGRESS</td><td>DNP return in progress</td></tr> <tr><td>10</td><td>DNPRRNOTMASTER</td><td>DNP return not a master</td></tr> </tbody> </table>	Enumeration			Binary	Value	Description	0	DNPRETURNGOOD	DNP return is good	1	DNPRETURNERROR	DNP return error	2	DNPRTNERRONLIST	DNP return error already on the list	3	DNPRTNERRLISTFULL	DNP return error is full	4	DNPRTNOTONLIST	DNP return error not on list	5	DNPRTNERRNOTP2P	DNP return error not P2P	6	DNPRTNDELAY	DNP return delayed before retry	7	DNPRTNACTIVEPOINT	DNP return active on point	8	DNPRETURNCOMPLETE	DNP return is complete	9	DNPRTNINPROGRESS	DNP return in progress	10	DNPRRNOTMASTER	DNP return not a master			
Enumeration																																												
Binary	Value	Description																																										
0	DNPRETURNGOOD	DNP return is good																																										
1	DNPRETURNERROR	DNP return error																																										
2	DNPRTNERRONLIST	DNP return error already on the list																																										
3	DNPRTNERRLISTFULL	DNP return error is full																																										
4	DNPRTNOTONLIST	DNP return error not on list																																										
5	DNPRTNERRNOTP2P	DNP return error not P2P																																										
6	DNPRTNDELAY	DNP return delayed before retry																																										
7	DNPRTNACTIVEPOINT	DNP return active on point																																										
8	DNPRETURNCOMPLETE	DNP return is complete																																										
9	DNPRTNINPROGRESS	DNP return in progress																																										
10	DNPRRNOTMASTER	DNP return not a master																																										
RegType	UINT16	<table border="1"> <thead> <tr> <th colspan="3">Enumeration</th> </tr> <tr> <th>Binary</th><th>Value</th><th>Description</th></tr> </thead> <tbody> <tr><td>0</td><td>ToUI</td><td>To UI</td></tr> <tr><td>1</td><td>ToMapping</td><td>To Mapping</td></tr> </tbody> </table>	Enumeration			Binary	Value	Description	0	ToUI	To UI	1	ToMapping	To Mapping																														
Enumeration																																												
Binary	Value	Description																																										
0	ToUI	To UI																																										
1	ToMapping	To Mapping																																										
RestoreConditionTestResult	UINT16	<p>Restore Condition Test Result</p> <table border="1"> <thead> <tr> <th colspan="3">Enumeration</th> </tr> <tr> <th>Binary</th><th>Value</th><th>Description</th></tr> </thead> <tbody> <tr><td>0</td><td>NoResult</td><td>NO RESULT</td></tr> <tr><td>1</td><td>CloseSwOK</td><td>CLOSE SW OK</td></tr> <tr><td>2</td><td>Isolated</td><td>ISOLATED</td></tr> <tr><td>3</td><td>ExcessLoad</td><td>EXCESSIVE LOAD</td></tr> <tr><td>4</td><td>CloseOnly</td><td>CLOSE ONLY</td></tr> <tr><td>5</td><td>OpenOnly</td><td>OPEN ONLY</td></tr> <tr><td>6</td><td>LineSegLimit</td><td>LINE SEGMENT LIMIT</td></tr> <tr><td>7</td><td>NbrProblem</td><td>NEIGHBOR ERROR</td></tr> </tbody> </table>	Enumeration			Binary	Value	Description	0	NoResult	NO RESULT	1	CloseSwOK	CLOSE SW OK	2	Isolated	ISOLATED	3	ExcessLoad	EXCESSIVE LOAD	4	CloseOnly	CLOSE ONLY	5	OpenOnly	OPEN ONLY	6	LineSegLimit	LINE SEGMENT LIMIT	7	NbrProblem	NEIGHBOR ERROR												
Enumeration																																												
Binary	Value	Description																																										
0	NoResult	NO RESULT																																										
1	CloseSwOK	CLOSE SW OK																																										
2	Isolated	ISOLATED																																										
3	ExcessLoad	EXCESSIVE LOAD																																										
4	CloseOnly	CLOSE ONLY																																										
5	OpenOnly	OPEN ONLY																																										
6	LineSegLimit	LINE SEGMENT LIMIT																																										
7	NbrProblem	NEIGHBOR ERROR																																										

Definitions of Historic Events

		<table border="1"> <tr><td>8</td><td>PhaseLoss</td><td>PHASE LOSS</td></tr> <tr><td>9</td><td>SrcBrkIsol</td><td>SRC BREAK ISOLATED</td></tr> <tr><td>10</td><td>LoadShed</td><td>LOAD SHED</td></tr> <tr><td>11</td><td>Short2Srces</td><td>SHORT TWO SOURCES</td></tr> <tr><td>100</td><td>CoordProblem</td><td>COORD ERROR</td></tr> <tr><td>101</td><td>PrevBadV</td><td>PREV BAD VOLT</td></tr> </table>	8	PhaseLoss	PHASE LOSS	9	SrcBrkIsol	SRC BREAK ISOLATED	10	LoadShed	LOAD SHED	11	Short2Srces	SHORT TWO SOURCES	100	CoordProblem	COORD ERROR	101	PrevBadV	PREV BAD VOLT
8	PhaseLoss	PHASE LOSS																		
9	SrcBrkIsol	SRC BREAK ISOLATED																		
10	LoadShed	LOAD SHED																		
11	Short2Srces	SHORT TWO SOURCES																		
100	CoordProblem	COORD ERROR																		
101	PrevBadV	PREV BAD VOLT																		
RouteEntryError	UINT16	<p>Route Entry Error</p> <table border="1"> <thead> <tr> <th colspan="3">Enumeration</th> </tr> <tr> <th>Binary</th> <th>Value</th> <th>Description</th> </tr> </thead> <tbody> <tr><td>1</td><td>BroadcastAddrInvalid</td><td>broadcast addresses invalid in routing tables</td></tr> <tr><td>2</td><td>IPAddrPortInvalid</td><td>IP address and port indication must be mutually exclusive</td></tr> </tbody> </table>	Enumeration			Binary	Value	Description	1	BroadcastAddrInvalid	broadcast addresses invalid in routing tables	2	IPAddrPortInvalid	IP address and port indication must be mutually exclusive						
Enumeration																				
Binary	Value	Description																		
1	BroadcastAddrInvalid	broadcast addresses invalid in routing tables																		
2	IPAddrPortInvalid	IP address and port indication must be mutually exclusive																		
RSD	UINT16	<p>Runner Source Device</p> <table border="1"> <thead> <tr> <th colspan="2">Numeric Type, Range: 0-65535</th> </tr> <tr> <th>Action</th> <th>Value</th> </tr> </thead> <tbody> <tr><td>Multiplier</td><td>1</td></tr> <tr><td>Adder</td><td>0</td></tr> </tbody> </table>	Numeric Type, Range: 0-65535		Action	Value	Multiplier	1	Adder	0										
Numeric Type, Range: 0-65535																				
Action	Value																			
Multiplier	1																			
Adder	0																			
RTUAddress	UINT16	<p>DNP address</p> <table border="1"> <thead> <tr> <th colspan="2">Numeric Type, Range: 0-65535</th> </tr> <tr> <th>Action</th> <th>Value</th> </tr> </thead> <tbody> <tr><td>Multiplier</td><td>1</td></tr> <tr><td>Adder</td><td>0</td></tr> </tbody> </table>	Numeric Type, Range: 0-65535		Action	Value	Multiplier	1	Adder	0										
Numeric Type, Range: 0-65535																				
Action	Value																			
Multiplier	1																			
Adder	0																			
RTULists	UINT16	<p>Runner RTU lists</p> <table border="1"> <thead> <tr> <th colspan="2">Numeric Type, Range: 0-65535</th> </tr> <tr> <th>Action</th> <th>Value</th> </tr> </thead> <tbody> <tr><td>Multiplier</td><td>1</td></tr> <tr><td>Adder</td><td>0</td></tr> </tbody> </table>	Numeric Type, Range: 0-65535		Action	Value	Multiplier	1	Adder	0										
Numeric Type, Range: 0-65535																				
Action	Value																			
Multiplier	1																			
Adder	0																			
RunnerIndex	UINT16	<p>Local runner index number</p> <table border="1"> <thead> <tr> <th colspan="2">Numeric Type, Range: 0-65535</th> </tr> <tr> <th>Action</th> <th>Value</th> </tr> </thead> <tbody> <tr><td>Multiplier</td><td>1</td></tr> <tr><td>Adder</td><td>0</td></tr> </tbody> </table>	Numeric Type, Range: 0-65535		Action	Value	Multiplier	1	Adder	0										
Numeric Type, Range: 0-65535																				
Action	Value																			
Multiplier	1																			
Adder	0																			
RunnerNumber	UINT16	<p>Runner Number</p> <table border="1"> <thead> <tr> <th colspan="2">Numeric Type, Range: 0-65535</th> </tr> <tr> <th>Action</th> <th>Value</th> </tr> </thead> <tbody> <tr><td>Multiplier</td><td>1</td></tr> <tr><td>Adder</td><td>0</td></tr> </tbody> </table>	Numeric Type, Range: 0-65535		Action	Value	Multiplier	1	Adder	0										
Numeric Type, Range: 0-65535																				
Action	Value																			
Multiplier	1																			
Adder	0																			
RunnerQuantity	UINT16	<p>Next data collection runner's quantity</p> <table border="1"> <thead> <tr> <th colspan="2">Numeric Type, Range: 0-65535</th> </tr> <tr> <th>Action</th> <th>Value</th> </tr> </thead> <tbody> <tr><td>Multiplier</td><td>1</td></tr> <tr><td>Adder</td><td>0</td></tr> </tbody> </table>	Numeric Type, Range: 0-65535		Action	Value	Multiplier	1	Adder	0										
Numeric Type, Range: 0-65535																				
Action	Value																			
Multiplier	1																			
Adder	0																			
RunnerSize	UINT16	<p>Size of received runner in BYTES</p> <table border="1"> <thead> <tr> <th colspan="2">Numeric Type, Range: 0-65535</th> </tr> <tr> <th>Action</th> <th>Value</th> </tr> </thead> <tbody> <tr><td>Multiplier</td><td>1</td></tr> <tr><td>Adder</td><td>0</td></tr> </tbody> </table>	Numeric Type, Range: 0-65535		Action	Value	Multiplier	1	Adder	0										
Numeric Type, Range: 0-65535																				
Action	Value																			
Multiplier	1																			
Adder	0																			

Enumeration								
	Binary	Value	Description					
RunnerType	UINT16	0	NETOBJTYPEUNDEF					
		1	NETOBJTYPEACKMESG					
		2	NETOBJTYPENACKMESG					
		3	NETOBJTYPENETLIST					
		4	NETOBJTYPERAWPUSH					
		16	NETxCMMCKRSP					
		19	NETxNLRQST					
		21	NETxNPRIrsp					
		22	NETxACTPNL					
		23	NETxNADJNLND					
		24	NETxDATCLCT					
		25	NETxDATDLV					
		27	NETxADJNLRPT					
		28	NETxADJDBRPT					
		29	NETxADJDBDLV					
		30	NETxPEERCHK					
		160	NETxNETLRPT					
			Active Netlist reporter					
SBOTimerValue	UINT16	Timer value for Select-Before-Operate. Unit = 0.1 sec.						
		Numeric Type, Range: 0-65535						
		<table border="1"> <thead> <tr> <th>Action</th> <th>Value</th> </tr> </thead> <tbody> <tr> <td>Multiplier</td> <td>1</td> </tr> <tr> <td>Adder</td> <td>0</td> </tr> </tbody> </table>			Action	Value	Multiplier	1
Action	Value							
Multiplier	1							
Adder	0							
SCACACCommand	UINT16	Enumeration						
		Binary	Value	Description				
		0	None	None				
		1	PulseOn	PULSE ON				
		2	PulseOff	PULSE OFF				
		3	LatchOn	LATCH ON				
		4	LatchOff	LATCH OFF				
		65	Close	CLOSE				
		129	Trip	TRIP				
		Enumeration						
		Binary	Value	Description				
SCACACCommandCode	UINT16	8192	BATTTest	Start Battery Test				
		8464	OperateSw1	Operate Sw1				
		8465	OperateSw2	Operate Sw2				
		8466	OperateSw3	Operate Sw3				
		8704	STLSw1	Shots to Lockout SW1				
		8705	STLSw2	Shots to Lockout SW2				
		8706	ClearOC	Clear Overcurrent				
		8960	FailOvEnaorDis	Failure Override Enable/Disable				
		8962	AutoEnaorDis	Auto Op Enable/Disable				
		8964	Auto1EnaorDis	Auto Op Sw1 Enable/Disable				
		8966	Auto2EnaorDis	Auto Op Sw2 Enable/Disable				
		8968	HLTEnaorDis	HLT Disable				
		8970	HLT1EnaorDis	HLT Sw1 Enable/Disable				
		8972	HLT2EnaorDis	HLT Sw2 Enable/Disable				
		8974	HLT3EnaorDis	HLT Sw3 Enable/Disable				
		8976	AckADI1	Ack ADI 1				

Definitions of Historic Events

		<table border="1"> <tr><td>8978</td><td>AckADI2</td><td>Ack ADI 2</td></tr> <tr><td>8980</td><td>AckADI3</td><td>Ack ADI 3</td></tr> <tr><td>9472</td><td>ClrErrors</td><td>Clear Errors</td></tr> <tr><td>9474</td><td>ClrWarnings</td><td>Clear Warnings</td></tr> <tr><td>9476</td><td>ClrAlarms</td><td>Clear Alarms</td></tr> </table>	8978	AckADI2	Ack ADI 2	8980	AckADI3	Ack ADI 3	9472	ClrErrors	Clear Errors	9474	ClrWarnings	Clear Warnings	9476	ClrAlarms	Clear Alarms
8978	AckADI2	Ack ADI 2															
8980	AckADI3	Ack ADI 3															
9472	ClrErrors	Clear Errors															
9474	ClrWarnings	Clear Warnings															
9476	ClrAlarms	Clear Alarms															
SecondaryEvent	UINT16	<p>Secondary Event Flag for WFC capture</p> <table border="1"> <tr><th colspan="2">Numeric Type, Range: 0-1</th></tr> <tr><th>Action</th><th>Value</th></tr> <tr><td>Multiplier</td><td>1</td></tr> <tr><td>Adder</td><td>0</td></tr> </table>	Numeric Type, Range: 0-1		Action	Value	Multiplier	1	Adder	0							
Numeric Type, Range: 0-1																	
Action	Value																
Multiplier	1																
Adder	0																
short	INT16	<p>INT16</p> <table border="1"> <tr><th colspan="2">Numeric Type, Range: -32768-32767</th></tr> <tr><th>Action</th><th>Value</th></tr> <tr><td>Multiplier</td><td>1</td></tr> <tr><td>Adder</td><td>0</td></tr> </table>	Numeric Type, Range: -32768-32767		Action	Value	Multiplier	1	Adder	0							
Numeric Type, Range: -32768-32767																	
Action	Value																
Multiplier	1																
Adder	0																
SideInfo	UINT16	<p>Enumeration</p> <table border="1"> <thead> <tr><th>Binary</th><th>Value</th><th>Description</th></tr> </thead> <tbody> <tr><td>0</td><td>SIDEUNKOWN</td><td>Side information is unkown</td></tr> <tr><td>1</td><td>SIDE1</td><td>This team member is on side 1 of the switch</td></tr> <tr><td>2</td><td>SIDE2</td><td>This team member is on side of the switch</td></tr> </tbody> </table>	Binary	Value	Description	0	SIDEUNKOWN	Side information is unkown	1	SIDE1	This team member is on side 1 of the switch	2	SIDE2	This team member is on side of the switch			
Binary	Value	Description															
0	SIDEUNKOWN	Side information is unkown															
1	SIDE1	This team member is on side 1 of the switch															
2	SIDE2	This team member is on side of the switch															
SizeOfObject	UINT16	<p>Size of the arriving object in bytes, also a flag/signal of arrival to State machine A</p> <table border="1"> <tr><th colspan="2">Numeric Type, Range: 0-65535</th></tr> <tr><th>Action</th><th>Value</th></tr> <tr><td>Multiplier</td><td>1</td></tr> <tr><td>Adder</td><td>0</td></tr> </table>	Numeric Type, Range: 0-65535		Action	Value	Multiplier	1	Adder	0							
Numeric Type, Range: 0-65535																	
Action	Value																
Multiplier	1																
Adder	0																
SrcNodeID	UINT16	<p>NET Source Node ID</p> <table border="1"> <tr><th colspan="2">Numeric Type, Range: 0-65535</th></tr> <tr><th>Action</th><th>Value</th></tr> <tr><td>Multiplier</td><td>1</td></tr> <tr><td>Adder</td><td>0</td></tr> </table>	Numeric Type, Range: 0-65535		Action	Value	Multiplier	1	Adder	0							
Numeric Type, Range: 0-65535																	
Action	Value																
Multiplier	1																
Adder	0																
State	UINT16	<p>State of the transition</p> <table border="1"> <tr><th colspan="3">Enumeration</th></tr> <tr><th>Binary</th><th>Value</th><th>Description</th></tr> <tr><td>1</td><td>TransON</td><td>Transition to On</td></tr> <tr><td>2</td><td>TransOFF</td><td>Transition to Off</td></tr> </table>	Enumeration			Binary	Value	Description	1	TransON	Transition to On	2	TransOFF	Transition to Off			
Enumeration																	
Binary	Value	Description															
1	TransON	Transition to On															
2	TransOFF	Transition to Off															
StatusFeedbackArea	UINT16	<p>Netx status feedback area, Data 1 is current state while Data 2 is the previous state</p> <table border="1"> <tr><th colspan="2">Numeric Type, Range: 0-65536</th></tr> <tr><th>Action</th><th>Value</th></tr> <tr><td>Multiplier</td><td>1</td></tr> <tr><td>Adder</td><td>0</td></tr> </table>	Numeric Type, Range: 0-65536		Action	Value	Multiplier	1	Adder	0							
Numeric Type, Range: 0-65536																	
Action	Value																
Multiplier	1																
Adder	0																
Substation	UINT16	<p>Present Substation</p> <table border="1"> <tr><th colspan="2">Numeric Type, Range: 0-65535</th></tr> <tr><th>Action</th><th>Value</th></tr> <tr><td>Multiplier</td><td>1</td></tr> <tr><td>Adder</td><td>0</td></tr> </table>	Numeric Type, Range: 0-65535		Action	Value	Multiplier	1	Adder	0							
Numeric Type, Range: 0-65535																	
Action	Value																
Multiplier	1																
Adder	0																
SUMSessionEndReason	UINT16	<p>SUM Session End Reason</p>															

		Enumeration <table border="1"> <thead> <tr> <th>Binary</th><th>Value</th><th>Description</th></tr> </thead> <tbody> <tr> <td>0</td><td>DeviceStartup</td><td>Device Startup</td></tr> <tr> <td>1</td><td>Logoff</td><td>Logoff</td></tr> <tr> <td>2</td><td>Timeout</td><td>Timeout</td></tr> <tr> <td>3</td><td>Preempted</td><td>Preempted</td></tr> </tbody> </table>	Binary	Value	Description	0	DeviceStartup	Device Startup	1	Logoff	Logoff	2	Timeout	Timeout	3	Preempted	Preempted												
Binary	Value	Description																											
0	DeviceStartup	Device Startup																											
1	Logoff	Logoff																											
2	Timeout	Timeout																											
3	Preempted	Preempted																											
SW1LostPhases	UINT16	Enumeration <table border="1"> <thead> <tr> <th>Binary</th><th>Value</th><th>Description</th></tr> </thead> <tbody> <tr> <td>0</td><td>None</td><td>None</td></tr> <tr> <td>2</td><td>A</td><td>A</td></tr> <tr> <td>4</td><td>B</td><td>B</td></tr> <tr> <td>6</td><td>AB</td><td>A and B</td></tr> <tr> <td>8</td><td>C</td><td>C</td></tr> <tr> <td>10</td><td>AC</td><td>A and C</td></tr> <tr> <td>12</td><td>BC</td><td>B and C</td></tr> <tr> <td>14</td><td>ABC</td><td>A and B and C</td></tr> </tbody> </table>	Binary	Value	Description	0	None	None	2	A	A	4	B	B	6	AB	A and B	8	C	C	10	AC	A and C	12	BC	B and C	14	ABC	A and B and C
Binary	Value	Description																											
0	None	None																											
2	A	A																											
4	B	B																											
6	AB	A and B																											
8	C	C																											
10	AC	A and C																											
12	BC	B and C																											
14	ABC	A and B and C																											
SW1Or2	UINT16	Enumeration <table border="1"> <thead> <tr> <th>Binary</th><th>Value</th><th>Description</th></tr> </thead> <tbody> <tr> <td>1</td><td>SW1</td><td>SW1</td></tr> <tr> <td>2</td><td>SW2</td><td>SW2</td></tr> </tbody> </table>	Binary	Value	Description	1	SW1	SW1	2	SW2	SW2																		
Binary	Value	Description																											
1	SW1	SW1																											
2	SW2	SW2																											
SW2LostPhases	UINT16	Enumeration <table border="1"> <thead> <tr> <th>Binary</th><th>Value</th><th>Description</th></tr> </thead> <tbody> <tr> <td>0</td><td>None</td><td>None</td></tr> <tr> <td>2</td><td>D</td><td>D</td></tr> <tr> <td>4</td><td>E</td><td>E</td></tr> <tr> <td>6</td><td>DE</td><td>D and E</td></tr> <tr> <td>8</td><td>F</td><td>F</td></tr> <tr> <td>10</td><td>DF</td><td>D and F</td></tr> <tr> <td>12</td><td>EF</td><td>E and F</td></tr> <tr> <td>14</td><td>DEF</td><td>D and E and F</td></tr> </tbody> </table>	Binary	Value	Description	0	None	None	2	D	D	4	E	E	6	DE	D and E	8	F	F	10	DF	D and F	12	EF	E and F	14	DEF	D and E and F
Binary	Value	Description																											
0	None	None																											
2	D	D																											
4	E	E																											
6	DE	D and E																											
8	F	F																											
10	DF	D and F																											
12	EF	E and F																											
14	DEF	D and E and F																											
SWDisabledType	UINT16	Enumeration <table border="1"> <thead> <tr> <th>Binary</th><th>Value</th><th>Description</th></tr> </thead> <tbody> <tr> <td>1</td><td>BatBad</td><td>Battery Bad</td></tr> <tr> <td>2</td><td>ExtLocal</td><td>External Local</td></tr> <tr> <td>4</td><td>LowPress</td><td>Low Pressure</td></tr> <tr> <td>8</td><td>Grounded</td><td>Grounded</td></tr> <tr> <td>16</td><td>VisualDis</td><td>Visible Disconnect</td></tr> <tr> <td>32</td><td>NoOverride</td><td>Override Failed</td></tr> <tr> <td>64</td><td>Other</td><td>Other</td></tr> <tr> <td>128</td><td>HLT</td><td>Hot Line Tag</td></tr> </tbody> </table>	Binary	Value	Description	1	BatBad	Battery Bad	2	ExtLocal	External Local	4	LowPress	Low Pressure	8	Grounded	Grounded	16	VisualDis	Visible Disconnect	32	NoOverride	Override Failed	64	Other	Other	128	HLT	Hot Line Tag
Binary	Value	Description																											
1	BatBad	Battery Bad																											
2	ExtLocal	External Local																											
4	LowPress	Low Pressure																											
8	Grounded	Grounded																											
16	VisualDis	Visible Disconnect																											
32	NoOverride	Override Failed																											
64	Other	Other																											
128	HLT	Hot Line Tag																											
SwitchBlockedInput	UINT16	Enumeration <table border="1"> <thead> <tr> <th>Binary</th><th>Value</th><th>Description</th></tr> </thead> <tbody> <tr> <td>1</td><td>ADI1</td><td>User Input 1</td></tr> <tr> <td>2</td><td>ADI2</td><td>User Input 2</td></tr> <tr> <td>3</td><td>ADI3</td><td>User Input 3</td></tr> </tbody> </table>	Binary	Value	Description	1	ADI1	User Input 1	2	ADI2	User Input 2	3	ADI3	User Input 3															
Binary	Value	Description																											
1	ADI1	User Input 1																											
2	ADI2	User Input 2																											
3	ADI3	User Input 3																											
SwitchBlockedType	UINT16	Enumeration <table border="1"> <thead> <tr> <th>Binary</th><th>Value</th><th>Description</th></tr> </thead> <tbody> <tr> <td>4</td><td>CloseOp</td><td>Close Op</td></tr> <tr> <td>8</td><td>OpenOp</td><td>Open Op</td></tr> </tbody> </table>	Binary	Value	Description	4	CloseOp	Close Op	8	OpenOp	Open Op																		
Binary	Value	Description																											
4	CloseOp	Close Op																											
8	OpenOp	Open Op																											
SwitchNum	UINT16	Enumeration <table border="1"> <thead> <tr> <th>Binary</th><th>Value</th><th>Description</th></tr> </thead> </table>	Binary	Value	Description																								
Binary	Value	Description																											

Definitions of Historic Events

		<table border="1"> <thead> <tr> <th>Binary</th><th>Value</th><th>Description</th></tr> </thead> <tbody> <tr> <td>1</td><td>Switch1</td><td>Switch 1</td></tr> <tr> <td>2</td><td>Switch2</td><td>Switch 2</td></tr> <tr> <td>3</td><td>Switch3</td><td>Switch 3</td></tr> </tbody> </table>	Binary	Value	Description	1	Switch1	Switch 1	2	Switch2	Switch 2	3	Switch3	Switch 3																																													
Binary	Value	Description																																																									
1	Switch1	Switch 1																																																									
2	Switch2	Switch 2																																																									
3	Switch3	Switch 3																																																									
SwitchOperationResult	UINT16	<p>Switch Operation Result</p> <table border="1"> <thead> <tr> <th colspan="3">Enumeration</th></tr> <tr> <th>Binary</th><th>Value</th><th>Description</th></tr> </thead> <tbody> <tr> <td>0</td><td>SOKNoRes</td><td>SW OK (no result yet)</td></tr> <tr> <td>1</td><td>ClsVerif</td><td>SW CLOSE VERIFIED</td></tr> <tr> <td>2</td><td>ClVerErr</td><td>SW CLOSE VERIFY FAIL</td></tr> <tr> <td>3</td><td>ClVerErrTr</td><td>SW CLOSE VERIFY FAIL TRIP</td></tr> <tr> <td>4</td><td>BadSwNum</td><td>BAD SW NUM</td></tr> <tr> <td>5</td><td>SwNotAuto</td><td>SW NOT AUTO</td></tr> <tr> <td>6</td><td>SBadDir</td><td>SW BAD DIRECTION</td></tr> <tr> <td>7</td><td>SwWasCls</td><td>SW WAS CLOSED</td></tr> <tr> <td>8</td><td>OpnVerif</td><td>SW OPEN VERIFIED</td></tr> <tr> <td>9</td><td>OpnVerErr</td><td>SW OPEN VERIFY FAIL</td></tr> <tr> <td>10</td><td>OpnXcesLd</td><td>SW OPEN EXCESS LOAD</td></tr> <tr> <td>11</td><td>SwWasOpen</td><td>SW WAS OPEN</td></tr> <tr> <td>12</td><td>CmdVerif</td><td>COMMAND VERIFIED</td></tr> <tr> <td>13</td><td>CmdRedun</td><td>COMMAND REDUNDANT</td></tr> <tr> <td>14</td><td>CmdVerErr</td><td>COMMAND VERIFY FAIL</td></tr> <tr> <td>15</td><td>BadCtlPt</td><td>BAD CTRL PT</td></tr> <tr> <td>16</td><td>ClsErrV</td><td>SW CLOSE FAIL VOLT</td></tr> </tbody> </table>	Enumeration			Binary	Value	Description	0	SOKNoRes	SW OK (no result yet)	1	ClsVerif	SW CLOSE VERIFIED	2	ClVerErr	SW CLOSE VERIFY FAIL	3	ClVerErrTr	SW CLOSE VERIFY FAIL TRIP	4	BadSwNum	BAD SW NUM	5	SwNotAuto	SW NOT AUTO	6	SBadDir	SW BAD DIRECTION	7	SwWasCls	SW WAS CLOSED	8	OpnVerif	SW OPEN VERIFIED	9	OpnVerErr	SW OPEN VERIFY FAIL	10	OpnXcesLd	SW OPEN EXCESS LOAD	11	SwWasOpen	SW WAS OPEN	12	CmdVerif	COMMAND VERIFIED	13	CmdRedun	COMMAND REDUNDANT	14	CmdVerErr	COMMAND VERIFY FAIL	15	BadCtlPt	BAD CTRL PT	16	ClsErrV	SW CLOSE FAIL VOLT
Enumeration																																																											
Binary	Value	Description																																																									
0	SOKNoRes	SW OK (no result yet)																																																									
1	ClsVerif	SW CLOSE VERIFIED																																																									
2	ClVerErr	SW CLOSE VERIFY FAIL																																																									
3	ClVerErrTr	SW CLOSE VERIFY FAIL TRIP																																																									
4	BadSwNum	BAD SW NUM																																																									
5	SwNotAuto	SW NOT AUTO																																																									
6	SBadDir	SW BAD DIRECTION																																																									
7	SwWasCls	SW WAS CLOSED																																																									
8	OpnVerif	SW OPEN VERIFIED																																																									
9	OpnVerErr	SW OPEN VERIFY FAIL																																																									
10	OpnXcesLd	SW OPEN EXCESS LOAD																																																									
11	SwWasOpen	SW WAS OPEN																																																									
12	CmdVerif	COMMAND VERIFIED																																																									
13	CmdRedun	COMMAND REDUNDANT																																																									
14	CmdVerErr	COMMAND VERIFY FAIL																																																									
15	BadCtlPt	BAD CTRL PT																																																									
16	ClsErrV	SW CLOSE FAIL VOLT																																																									
SwitchPosition	UINT16	<p>Switch position</p> <table border="1"> <thead> <tr> <th colspan="2">Numeric Type, Range: 1-8</th></tr> <tr> <th>Action</th><th>Value</th></tr> </thead> <tbody> <tr> <td>Multiplier</td><td>1</td></tr> <tr> <td>Adder</td><td>0</td></tr> </tbody> </table>	Numeric Type, Range: 1-8		Action	Value	Multiplier	1	Adder	0																																																	
Numeric Type, Range: 1-8																																																											
Action	Value																																																										
Multiplier	1																																																										
Adder	0																																																										
SwitchRecord	UINT16	<table border="1"> <thead> <tr> <th colspan="2">Numeric Type, Range: 0-8</th></tr> <tr> <th>Action</th><th>Value</th></tr> </thead> <tbody> <tr> <td>Multiplier</td><td>1</td></tr> <tr> <td>Adder</td><td>0</td></tr> </tbody> </table>	Numeric Type, Range: 0-8		Action	Value	Multiplier	1	Adder	0																																																	
Numeric Type, Range: 0-8																																																											
Action	Value																																																										
Multiplier	1																																																										
Adder	0																																																										
SwitchState	UINT16	<p>Switch State</p> <table border="1"> <thead> <tr> <th colspan="3">Enumeration</th></tr> <tr> <th>Binary</th><th>Value</th><th>Description</th></tr> </thead> <tbody> <tr> <td>0</td><td>DATUSWSTAT_UNKOWN</td><td>Switch State is unknown</td></tr> <tr> <td>1</td><td>DATUSWSTAT_CLOSED</td><td>Switch State is closed</td></tr> <tr> <td>2</td><td>DATUSWSTAT_OPEN</td><td>Switch State is open</td></tr> <tr> <td>3</td><td>DATUSWSTAT_TRANS</td><td>Switch State is in transition</td></tr> <tr> <td>4</td><td>DATUSWSTAT_UNDEF</td><td>Switch State is undefined</td></tr> </tbody> </table>	Enumeration			Binary	Value	Description	0	DATUSWSTAT_UNKOWN	Switch State is unknown	1	DATUSWSTAT_CLOSED	Switch State is closed	2	DATUSWSTAT_OPEN	Switch State is open	3	DATUSWSTAT_TRANS	Switch State is in transition	4	DATUSWSTAT_UNDEF	Switch State is undefined																																				
Enumeration																																																											
Binary	Value	Description																																																									
0	DATUSWSTAT_UNKOWN	Switch State is unknown																																																									
1	DATUSWSTAT_CLOSED	Switch State is closed																																																									
2	DATUSWSTAT_OPEN	Switch State is open																																																									
3	DATUSWSTAT_TRANS	Switch State is in transition																																																									
4	DATUSWSTAT_UNDEF	Switch State is undefined																																																									
SWnum	UINT16	<table border="1"> <thead> <tr> <th colspan="3">Enumeration</th></tr> <tr> <th>Binary</th><th>Value</th><th>Description</th></tr> </thead> <tbody> <tr> <td>0</td><td>SW1</td><td>SW1</td></tr> <tr> <td>1</td><td>SW2</td><td>SW2</td></tr> <tr> <td>2</td><td>SW3</td><td>SW3</td></tr> </tbody> </table>	Enumeration			Binary	Value	Description	0	SW1	SW1	1	SW2	SW2	2	SW3	SW3																																										
Enumeration																																																											
Binary	Value	Description																																																									
0	SW1	SW1																																																									
1	SW2	SW2																																																									
2	SW3	SW3																																																									
SWOp	UINT16	<table border="1"> <thead> <tr> <th colspan="3">Enumeration</th></tr> <tr> <th>Binary</th><th>Value</th><th>Description</th></tr> </thead> </table>	Enumeration			Binary	Value	Description																																																			
Enumeration																																																											
Binary	Value	Description																																																									

		<table border="1"> <tr><td>1</td><td>Close</td><td>Close</td></tr> <tr><td>2</td><td>Open</td><td>Open</td></tr> </table>	1	Close	Close	2	Open	Open																																	
1	Close	Close																																							
2	Open	Open																																							
SWPos	UINT16	<table border="1"> <thead> <tr> <th colspan="3">Enumeration</th> </tr> <tr> <th>Binary</th><th>Value</th><th>Description</th></tr> </thead> <tbody> <tr><td>1</td><td>SW1</td><td>SW1</td></tr> <tr><td>2</td><td>SW2</td><td>SW2</td></tr> <tr><td>3</td><td>SW3</td><td>SW3</td></tr> <tr><td>4</td><td>SW4</td><td>SW4</td></tr> <tr><td>5</td><td>SW5</td><td>SW5</td></tr> <tr><td>6</td><td>SW6</td><td>SW6</td></tr> <tr><td>7</td><td>SW7</td><td>SW7</td></tr> <tr><td>8</td><td>SW8</td><td>SW8</td></tr> </tbody> </table>	Enumeration			Binary	Value	Description	1	SW1	SW1	2	SW2	SW2	3	SW3	SW3	4	SW4	SW4	5	SW5	SW5	6	SW6	SW6	7	SW7	SW7	8	SW8	SW8									
Enumeration																																									
Binary	Value	Description																																							
1	SW1	SW1																																							
2	SW2	SW2																																							
3	SW3	SW3																																							
4	SW4	SW4																																							
5	SW5	SW5																																							
6	SW6	SW6																																							
7	SW7	SW7																																							
8	SW8	SW8																																							
SWSWOp	UINT16	<table border="1"> <thead> <tr> <th colspan="3">Enumeration</th> </tr> <tr> <th>Binary</th><th>Value</th><th>Description</th></tr> </thead> <tbody> <tr><td>1</td><td>SwClose</td><td>SwClose</td></tr> <tr><td>2</td><td>SwOpen</td><td>SwOpen</td></tr> </tbody> </table>	Enumeration			Binary	Value	Description	1	SwClose	SwClose	2	SwOpen	SwOpen																											
Enumeration																																									
Binary	Value	Description																																							
1	SwClose	SwClose																																							
2	SwOpen	SwOpen																																							
SWXCommandSource	UINT16	<table border="1"> <thead> <tr> <th colspan="3">Enumeration</th> </tr> <tr> <th>Binary</th><th>Value</th><th>Description</th></tr> </thead> <tbody> <tr><td>0</td><td>Undef</td><td>Undefined</td></tr> <tr><td>64</td><td>AutoOp</td><td>Automatic Operations</td></tr> <tr><td>32</td><td>SCADA</td><td>Remote Operations</td></tr> <tr><td>16</td><td>FP</td><td>Faceplate</td></tr> <tr><td>128</td><td>ILink</td><td>WiFi or other</td></tr> <tr><td>144</td><td>Grounded</td><td>Grounded</td></tr> </tbody> </table>	Enumeration			Binary	Value	Description	0	Undef	Undefined	64	AutoOp	Automatic Operations	32	SCADA	Remote Operations	16	FP	Faceplate	128	ILink	WiFi or other	144	Grounded	Grounded															
Enumeration																																									
Binary	Value	Description																																							
0	Undef	Undefined																																							
64	AutoOp	Automatic Operations																																							
32	SCADA	Remote Operations																																							
16	FP	Faceplate																																							
128	ILink	WiFi or other																																							
144	Grounded	Grounded																																							
SWXnum	UINT16	<table border="1"> <thead> <tr> <th colspan="3">Enumeration</th> </tr> <tr> <th>Binary</th><th>Value</th><th>Description</th></tr> </thead> <tbody> <tr><td>0</td><td>SWX1</td><td>SWX1</td></tr> <tr><td>1</td><td>SWX2</td><td>SWX2</td></tr> <tr><td>2</td><td>SWX3</td><td>SWX3</td></tr> </tbody> </table>	Enumeration			Binary	Value	Description	0	SWX1	SWX1	1	SWX2	SWX2	2	SWX3	SWX3																								
Enumeration																																									
Binary	Value	Description																																							
0	SWX1	SWX1																																							
1	SWX2	SWX2																																							
2	SWX3	SWX3																																							
syncstat	UINT16	<table border="1"> <thead> <tr> <th colspan="3">Enumeration</th> </tr> <tr> <th>Binary</th><th>Value</th><th>Description</th></tr> </thead> <tbody> <tr><td>0</td><td>DATASYNCHSUCCESS</td><td>Operation was successful</td></tr> <tr><td>1</td><td>DATASYNCHBADSTATE</td><td>Present States of Local Switches do not match Normal states</td></tr> <tr><td>2</td><td>DATASYNCHNOTQUIET</td><td>IntelliTEAM is not 'quiet' (in the process of transferring)</td></tr> <tr><td>3</td><td>DATASYNCHNETBADDATA</td><td>Netlist data is somehow invalid (e.g. no local teams)</td></tr> <tr><td>4</td><td>DATASYNCHNINPROCESS</td><td>Presently processing a new netlist</td></tr> <tr><td>5</td><td>DATASYNCHNORTUADDR</td><td>Device is not configured with an RTU address</td></tr> </tbody> </table>	Enumeration			Binary	Value	Description	0	DATASYNCHSUCCESS	Operation was successful	1	DATASYNCHBADSTATE	Present States of Local Switches do not match Normal states	2	DATASYNCHNOTQUIET	IntelliTEAM is not 'quiet' (in the process of transferring)	3	DATASYNCHNETBADDATA	Netlist data is somehow invalid (e.g. no local teams)	4	DATASYNCHNINPROCESS	Presently processing a new netlist	5	DATASYNCHNORTUADDR	Device is not configured with an RTU address															
Enumeration																																									
Binary	Value	Description																																							
0	DATASYNCHSUCCESS	Operation was successful																																							
1	DATASYNCHBADSTATE	Present States of Local Switches do not match Normal states																																							
2	DATASYNCHNOTQUIET	IntelliTEAM is not 'quiet' (in the process of transferring)																																							
3	DATASYNCHNETBADDATA	Netlist data is somehow invalid (e.g. no local teams)																																							
4	DATASYNCHNINPROCESS	Presently processing a new netlist																																							
5	DATASYNCHNORTUADDR	Device is not configured with an RTU address																																							
SystemVoltage	UINT16	<table border="1"> <thead> <tr> <th colspan="3">Enumeration</th> </tr> <tr> <th>Binary</th><th>Value</th><th>Description</th></tr> </thead> <tbody> <tr><td>1</td><td>V69000</td><td>69000</td></tr> <tr><td>2</td><td>V46000</td><td>46000</td></tr> <tr><td>3</td><td>V44000</td><td>44000</td></tr> <tr><td>4</td><td>V40600</td><td>40600</td></tr> <tr><td>5</td><td>V36000</td><td>36000</td></tr> <tr><td>6</td><td>V34500</td><td>34500</td></tr> <tr><td>7</td><td>V27600</td><td>27600</td></tr> <tr><td>8</td><td>V26400</td><td>26400</td></tr> <tr><td>9</td><td>V24900</td><td>24900</td></tr> <tr><td>10</td><td>V23900</td><td>23900</td></tr> <tr><td>11</td><td>V22900</td><td>22900</td></tr> </tbody> </table>	Enumeration			Binary	Value	Description	1	V69000	69000	2	V46000	46000	3	V44000	44000	4	V40600	40600	5	V36000	36000	6	V34500	34500	7	V27600	27600	8	V26400	26400	9	V24900	24900	10	V23900	23900	11	V22900	22900
Enumeration																																									
Binary	Value	Description																																							
1	V69000	69000																																							
2	V46000	46000																																							
3	V44000	44000																																							
4	V40600	40600																																							
5	V36000	36000																																							
6	V34500	34500																																							
7	V27600	27600																																							
8	V26400	26400																																							
9	V24900	24900																																							
10	V23900	23900																																							
11	V22900	22900																																							

Definitions of Historic Events

		<table border="1"> <tr><td>12</td><td>V20800</td><td>20800</td></tr> <tr><td>13</td><td>V14400</td><td>14400</td></tr> <tr><td>14</td><td>V13800</td><td>13800</td></tr> <tr><td>15</td><td>V13200</td><td>13200</td></tr> <tr><td>16</td><td>V12470</td><td>12470</td></tr> <tr><td>17</td><td>V12000</td><td>12000</td></tr> <tr><td>18</td><td>V8320</td><td>8320</td></tr> <tr><td>19</td><td>V7200</td><td>7200</td></tr> <tr><td>20</td><td>V4800</td><td>4800</td></tr> <tr><td>21</td><td>V4160</td><td>4160</td></tr> <tr><td>22</td><td>V33000</td><td>33000</td></tr> <tr><td>23</td><td>V22000</td><td>22000</td></tr> <tr><td>24</td><td>V20000</td><td>20000</td></tr> <tr><td>25</td><td>V11000</td><td>11000</td></tr> <tr><td>26</td><td>V10000</td><td>10000</td></tr> </table>	12	V20800	20800	13	V14400	14400	14	V13800	13800	15	V13200	13200	16	V12470	12470	17	V12000	12000	18	V8320	8320	19	V7200	7200	20	V4800	4800	21	V4160	4160	22	V33000	33000	23	V22000	22000	24	V20000	20000	25	V11000	11000	26	V10000	10000
12	V20800	20800																																													
13	V14400	14400																																													
14	V13800	13800																																													
15	V13200	13200																																													
16	V12470	12470																																													
17	V12000	12000																																													
18	V8320	8320																																													
19	V7200	7200																																													
20	V4800	4800																																													
21	V4160	4160																																													
22	V33000	33000																																													
23	V22000	22000																																													
24	V20000	20000																																													
25	V11000	11000																																													
26	V10000	10000																																													
Task	UINT16	<table border="1"> <tr><th colspan="3">Numeric Type, Range: 0-65535</th></tr> <tr> <th>Action</th><th colspan="2">Value</th></tr> <tr><td>Multiplier</td><td colspan="2">1</td></tr> <tr><td>Adder</td><td colspan="2">0</td></tr> </table>	Numeric Type, Range: 0-65535			Action	Value		Multiplier	1		Adder	0																																		
Numeric Type, Range: 0-65535																																															
Action	Value																																														
Multiplier	1																																														
Adder	0																																														
TCPPortActiveState	UINT16	<table border="1"> <tr><th colspan="3">Enumeration</th></tr> <tr> <th>Binary</th><th>Value</th><th>Description</th></tr> <tr><td>0</td><td>Undefined</td><td>Undefined</td></tr> <tr><td>1</td><td>Unused</td><td>Unused</td></tr> <tr><td>2</td><td>Active</td><td>Active</td></tr> <tr><td>3</td><td>Connect</td><td>Connect</td></tr> <tr><td>4</td><td>Disconnect</td><td>Disconnect</td></tr> <tr><td>5</td><td>Reconnect</td><td>Reconnect</td></tr> <tr><td>6</td><td>Error</td><td>Error</td></tr> <tr><td>7</td><td>Blocking</td><td>Blocking</td></tr> <tr><td>8</td><td>KpAliveSend</td><td>Send Keep Alive</td></tr> </table>	Enumeration			Binary	Value	Description	0	Undefined	Undefined	1	Unused	Unused	2	Active	Active	3	Connect	Connect	4	Disconnect	Disconnect	5	Reconnect	Reconnect	6	Error	Error	7	Blocking	Blocking	8	KpAliveSend	Send Keep Alive												
Enumeration																																															
Binary	Value	Description																																													
0	Undefined	Undefined																																													
1	Unused	Unused																																													
2	Active	Active																																													
3	Connect	Connect																																													
4	Disconnect	Disconnect																																													
5	Reconnect	Reconnect																																													
6	Error	Error																																													
7	Blocking	Blocking																																													
8	KpAliveSend	Send Keep Alive																																													
TCPPortConnectState	UINT16	<table border="1"> <tr><th colspan="3">Enumeration</th></tr> <tr> <th>Binary</th><th>Value</th><th>Description</th></tr> <tr><td>1</td><td>Removed</td><td>Removed</td></tr> <tr><td>2</td><td>Disconnecting</td><td>Disconnecting</td></tr> <tr><td>3</td><td>Connecting</td><td>Connecting</td></tr> <tr><td>4</td><td>Changed</td><td>Changed</td></tr> <tr><td>5</td><td>Badstate</td><td>Bad state</td></tr> <tr><td>6</td><td>KpAliveSent</td><td>Keep Alive Sent</td></tr> <tr><td>7</td><td>KpAliveBad</td><td>Keep Alive Bad</td></tr> </table>	Enumeration			Binary	Value	Description	1	Removed	Removed	2	Disconnecting	Disconnecting	3	Connecting	Connecting	4	Changed	Changed	5	Badstate	Bad state	6	KpAliveSent	Keep Alive Sent	7	KpAliveBad	Keep Alive Bad																		
Enumeration																																															
Binary	Value	Description																																													
1	Removed	Removed																																													
2	Disconnecting	Disconnecting																																													
3	Connecting	Connecting																																													
4	Changed	Changed																																													
5	Badstate	Bad state																																													
6	KpAliveSent	Keep Alive Sent																																													
7	KpAliveBad	Keep Alive Bad																																													
Team	UINT16	<p>Team number</p> <table border="1"> <tr><th colspan="3">Numeric Type, Range: 1-8</th></tr> <tr> <th>Action</th><th colspan="2">Value</th></tr> <tr><td>Multiplier</td><td colspan="2">1</td></tr> <tr><td>Adder</td><td colspan="2">0</td></tr> </table>	Numeric Type, Range: 1-8			Action	Value		Multiplier	1		Adder	0																																		
Numeric Type, Range: 1-8																																															
Action	Value																																														
Multiplier	1																																														
Adder	0																																														
TeamNumber	UINT16	<table border="1"> <tr><th colspan="3">Enumeration</th></tr> <tr> <th>Binary</th><th>Value</th><th>Description</th></tr> <tr><td>1</td><td>Team1</td><td>Team 1</td></tr> <tr><td>2</td><td>Team2</td><td>Team 2</td></tr> <tr><td>3</td><td>Team3</td><td>Team 3</td></tr> </table>	Enumeration			Binary	Value	Description	1	Team1	Team 1	2	Team2	Team 2	3	Team3	Team 3																														
Enumeration																																															
Binary	Value	Description																																													
1	Team1	Team 1																																													
2	Team2	Team 2																																													
3	Team3	Team 3																																													

		<table border="1"> <tr><td>4</td><td>Team4</td><td>Team 4</td></tr> <tr><td>5</td><td>Team5</td><td>Team 5</td></tr> <tr><td>6</td><td>Team6</td><td>Team 6</td></tr> <tr><td>7</td><td>Team7</td><td>Team 7</td></tr> <tr><td>8</td><td>Team8</td><td>Team 8</td></tr> </table>	4	Team4	Team 4	5	Team5	Team 5	6	Team6	Team 6	7	Team7	Team 7	8	Team8	Team 8																					
4	Team4	Team 4																																				
5	Team5	Team 5																																				
6	Team6	Team 6																																				
7	Team7	Team 7																																				
8	Team8	Team 8																																				
TeamNumberWithUnknown	UINT16	<table border="1"> <thead> <tr> <th colspan="3">Enumeration</th> </tr> <tr> <th>Binary</th><th>Value</th><th>Description</th></tr> </thead> <tbody> <tr><td>0</td><td>DirUnknown</td><td>Dir Unknown</td></tr> <tr><td>1</td><td>Team1</td><td>Team 1</td></tr> <tr><td>2</td><td>Team2</td><td>Team 2</td></tr> <tr><td>3</td><td>Team3</td><td>Team 3</td></tr> <tr><td>4</td><td>Team4</td><td>Team 4</td></tr> <tr><td>5</td><td>Team5</td><td>Team 5</td></tr> <tr><td>6</td><td>Team6</td><td>Team 6</td></tr> <tr><td>7</td><td>Team7</td><td>Team 7</td></tr> <tr><td>8</td><td>Team8</td><td>Team 8</td></tr> <tr><td>9</td><td>TeamIsVirtual</td><td>Team is virtual</td></tr> </tbody> </table>	Enumeration			Binary	Value	Description	0	DirUnknown	Dir Unknown	1	Team1	Team 1	2	Team2	Team 2	3	Team3	Team 3	4	Team4	Team 4	5	Team5	Team 5	6	Team6	Team 6	7	Team7	Team 7	8	Team8	Team 8	9	TeamIsVirtual	Team is virtual
Enumeration																																						
Binary	Value	Description																																				
0	DirUnknown	Dir Unknown																																				
1	Team1	Team 1																																				
2	Team2	Team 2																																				
3	Team3	Team 3																																				
4	Team4	Team 4																																				
5	Team5	Team 5																																				
6	Team6	Team 6																																				
7	Team7	Team 7																																				
8	Team8	Team 8																																				
9	TeamIsVirtual	Team is virtual																																				
TeamRecord	UINT16	<p>Team record</p> <table border="1"> <thead> <tr> <th colspan="2">Numeric Type, Range: 0-8</th> </tr> <tr> <th>Action</th><th>Value</th></tr> </thead> <tbody> <tr><td>Multiplier</td><td>1</td></tr> <tr><td>Adder</td><td>0</td></tr> </tbody> </table>	Numeric Type, Range: 0-8		Action	Value	Multiplier	1	Adder	0																												
Numeric Type, Range: 0-8																																						
Action	Value																																					
Multiplier	1																																					
Adder	0																																					
TeamWithDone	UINT16	<table border="1"> <thead> <tr> <th colspan="3">Enumeration</th> </tr> <tr> <th>Binary</th><th>Value</th><th>Description</th></tr> </thead> <tbody> <tr><td>1</td><td>Member1</td><td>Member 1</td></tr> <tr><td>2</td><td>Member2</td><td>Member 2</td></tr> <tr><td>3</td><td>Member3</td><td>Member 3</td></tr> <tr><td>4</td><td>Member4</td><td>Member 4</td></tr> <tr><td>5</td><td>Member5</td><td>Member 5</td></tr> <tr><td>6</td><td>Member6</td><td>Member 6</td></tr> <tr><td>7</td><td>Member7</td><td>Member 7</td></tr> <tr><td>8</td><td>Member8</td><td>Member 8</td></tr> <tr><td>256</td><td>Done</td><td>Done</td></tr> </tbody> </table>	Enumeration			Binary	Value	Description	1	Member1	Member 1	2	Member2	Member 2	3	Member3	Member 3	4	Member4	Member 4	5	Member5	Member 5	6	Member6	Member 6	7	Member7	Member 7	8	Member8	Member 8	256	Done	Done			
Enumeration																																						
Binary	Value	Description																																				
1	Member1	Member 1																																				
2	Member2	Member 2																																				
3	Member3	Member 3																																				
4	Member4	Member 4																																				
5	Member5	Member 5																																				
6	Member6	Member 6																																				
7	Member7	Member 7																																				
8	Member8	Member 8																																				
256	Done	Done																																				
TimeSource	UINT16	<table border="1"> <thead> <tr> <th colspan="3">Enumeration</th> </tr> <tr> <th>Binary</th><th>Value</th><th>Description</th></tr> </thead> <tbody> <tr><td>1</td><td>MCUInternal</td><td>MCU internal oscillator</td></tr> <tr><td>2</td><td>RTC</td><td>MCU RTC</td></tr> <tr><td>3</td><td>GPS</td><td>MCU GPS</td></tr> </tbody> </table>	Enumeration			Binary	Value	Description	1	MCUInternal	MCU internal oscillator	2	RTC	MCU RTC	3	GPS	MCU GPS																					
Enumeration																																						
Binary	Value	Description																																				
1	MCUInternal	MCU internal oscillator																																				
2	RTC	MCU RTC																																				
3	GPS	MCU GPS																																				
totallen	UINT16	<p>Total Length</p> <table border="1"> <thead> <tr> <th colspan="2">Numeric Type, Range: 0-65535</th> </tr> <tr> <th>Action</th><th>Value</th></tr> </thead> <tbody> <tr><td>Multiplier</td><td>1</td></tr> <tr><td>Adder</td><td>0</td></tr> </tbody> </table>	Numeric Type, Range: 0-65535		Action	Value	Multiplier	1	Adder	0																												
Numeric Type, Range: 0-65535																																						
Action	Value																																					
Multiplier	1																																					
Adder	0																																					
TransferState	UINT16	<table border="1"> <thead> <tr> <th colspan="3">Enumeration</th> </tr> <tr> <th>Binary</th><th>Value</th><th>Description</th></tr> </thead> <tbody> <tr><td>0</td><td>IDLE</td><td>IDLE</td></tr> <tr><td>1</td><td>INIT</td><td>INIT</td></tr> <tr><td>2</td><td>RQST</td><td>RQST</td></tr> <tr><td>3</td><td>GRNT</td><td>GRNT</td></tr> <tr><td>4</td><td>RTN0</td><td>RTN0</td></tr> </tbody> </table>	Enumeration			Binary	Value	Description	0	IDLE	IDLE	1	INIT	INIT	2	RQST	RQST	3	GRNT	GRNT	4	RTN0	RTN0															
Enumeration																																						
Binary	Value	Description																																				
0	IDLE	IDLE																																				
1	INIT	INIT																																				
2	RQST	RQST																																				
3	GRNT	GRNT																																				
4	RTN0	RTN0																																				

Definitions of Historic Events

		<table border="1"> <tr><td>5</td><td>RTN1</td><td>RTN1</td></tr> <tr><td>6</td><td>RTN2</td><td>RTN2</td></tr> <tr><td>7</td><td>RTN3</td><td>RTN3</td></tr> <tr><td>8</td><td>WAIT</td><td>WAIT</td></tr> <tr><td>9</td><td>STOP</td><td>STOP</td></tr> <tr><td>10</td><td>FAULT</td><td>FAULT</td></tr> <tr><td>11</td><td>HOLD</td><td>HOLD</td></tr> <tr><td>12</td><td>CORA</td><td>CORA</td></tr> <tr><td>13</td><td>PLI</td><td>PLI</td></tr> <tr><td>14</td><td>PLIDONE</td><td>PLIDONE</td></tr> <tr><td>15</td><td>PLIWAIT</td><td>PLIWAIT</td></tr> <tr><td>16</td><td>PLIWAIT2</td><td>PLIWAIT2</td></tr> <tr><td>255</td><td>UNDEF</td><td>UNDEF</td></tr> </table>	5	RTN1	RTN1	6	RTN2	RTN2	7	RTN3	RTN3	8	WAIT	WAIT	9	STOP	STOP	10	FAULT	FAULT	11	HOLD	HOLD	12	CORA	CORA	13	PLI	PLI	14	PLIDONE	PLIDONE	15	PLIWAIT	PLIWAIT	16	PLIWAIT2	PLIWAIT2	255	UNDEF	UNDEF
5	RTN1	RTN1																																							
6	RTN2	RTN2																																							
7	RTN3	RTN3																																							
8	WAIT	WAIT																																							
9	STOP	STOP																																							
10	FAULT	FAULT																																							
11	HOLD	HOLD																																							
12	CORA	CORA																																							
13	PLI	PLI																																							
14	PLIDONE	PLIDONE																																							
15	PLIWAIT	PLIWAIT																																							
16	PLIWAIT2	PLIWAIT2																																							
255	UNDEF	UNDEF																																							
URBESStatus	UINT16	<p>URBE Status</p> <table border="1"> <thead> <tr> <th colspan="3">Enumeration</th> </tr> <tr> <th>Binary</th><th>Value</th><th>Description</th></tr> </thead> <tbody> <tr><td>1</td><td>Enabled</td><td>enabled</td></tr> <tr><td>0</td><td>Disabled</td><td>disabled</td></tr> </tbody> </table>	Enumeration			Binary	Value	Description	1	Enabled	enabled	0	Disabled	disabled																											
Enumeration																																									
Binary	Value	Description																																							
1	Enabled	enabled																																							
0	Disabled	disabled																																							
ushort	UINT16	<p>UINT16</p> <table border="1"> <thead> <tr> <th colspan="2">Numeric Type, Range: 0-65535</th> </tr> <tr> <th>Action</th><th>Value</th></tr> </thead> <tbody> <tr><td>Multiplier</td><td>1</td></tr> <tr><td>Adder</td><td>0</td></tr> </tbody> </table>	Numeric Type, Range: 0-65535		Action	Value	Multiplier	1	Adder	0																															
Numeric Type, Range: 0-65535																																									
Action	Value																																								
Multiplier	1																																								
Adder	0																																								
VAddr16	UINT16	<p>16-bit virtual memory address</p> <table border="1"> <thead> <tr> <th colspan="2">Numeric Type, Range: 0-65535</th> </tr> <tr> <th>Action</th><th>Value</th></tr> </thead> <tbody> <tr><td>Multiplier</td><td>1</td></tr> <tr><td>Adder</td><td>0</td></tr> </tbody> </table>	Numeric Type, Range: 0-65535		Action	Value	Multiplier	1	Adder	0																															
Numeric Type, Range: 0-65535																																									
Action	Value																																								
Multiplier	1																																								
Adder	0																																								
VMAccessAction	UINT16	<p>VM Access Action</p> <table border="1"> <thead> <tr> <th colspan="3">Enumeration</th> </tr> <tr> <th>Binary</th><th>Value</th><th>Description</th></tr> </thead> <tbody> <tr><td>0</td><td>ReadSpcl</td><td>ReadSpcl</td></tr> <tr><td>1</td><td>Read</td><td>Read</td></tr> <tr><td>2</td><td>Read1</td><td>Read</td></tr> <tr><td>3</td><td>Write</td><td>Write</td></tr> <tr><td>4</td><td>Write1</td><td>Write</td></tr> <tr><td>5</td><td>WriteSpcl</td><td>WriteSpcl</td></tr> </tbody> </table>	Enumeration			Binary	Value	Description	0	ReadSpcl	ReadSpcl	1	Read	Read	2	Read1	Read	3	Write	Write	4	Write1	Write	5	WriteSpcl	WriteSpcl															
Enumeration																																									
Binary	Value	Description																																							
0	ReadSpcl	ReadSpcl																																							
1	Read	Read																																							
2	Read1	Read																																							
3	Write	Write																																							
4	Write1	Write																																							
5	WriteSpcl	WriteSpcl																																							
VMFunctionCode	UINT16	<table border="1"> <thead> <tr> <th colspan="3">Enumeration</th> </tr> <tr> <th>Binary</th><th>Value</th><th>Description</th></tr> </thead> <tbody> <tr><td>1</td><td>Read</td><td>read</td></tr> <tr><td>2</td><td>Write</td><td>write</td></tr> </tbody> </table>	Enumeration			Binary	Value	Description	1	Read	read	2	Write	write																											
Enumeration																																									
Binary	Value	Description																																							
1	Read	read																																							
2	Write	write																																							
VMIndex	UINT16	<p>VM table index for this FeederNetID</p> <table border="1"> <thead> <tr> <th colspan="2">Numeric Type, Range: 0-65535</th> </tr> <tr> <th>Action</th><th>Value</th></tr> </thead> <tbody> <tr><td>Multiplier</td><td>1</td></tr> <tr><td>Adder</td><td>0</td></tr> </tbody> </table>	Numeric Type, Range: 0-65535		Action	Value	Multiplier	1	Adder	0																															
Numeric Type, Range: 0-65535																																									
Action	Value																																								
Multiplier	1																																								
Adder	0																																								
VoltageChannel	UINT16	<p>Voltage Channel</p> <table border="1"> <thead> <tr> <th colspan="2">Enumeration</th> </tr> </thead> </table>	Enumeration																																						
Enumeration																																									

		<table border="1"> <thead> <tr> <th>Binary</th><th>Value</th><th>Description</th></tr> </thead> <tbody> <tr><td>2</td><td>Sw1VoltA</td><td>Switch 1 Voltage A</td></tr> <tr><td>4</td><td>Sw1VoltB</td><td>Switch 1 Voltage B</td></tr> <tr><td>8</td><td>Sw1VoltC</td><td>Switch 1 Voltage C</td></tr> <tr><td>32</td><td>Sw2VoltA</td><td>Switch 2 Voltage A</td></tr> <tr><td>64</td><td>Sw2VoltB</td><td>Switch 2 Voltage B</td></tr> <tr><td>128</td><td>Sw2VoltC</td><td>Switch 2 Voltage C</td></tr> </tbody> </table>	Binary	Value	Description	2	Sw1VoltA	Switch 1 Voltage A	4	Sw1VoltB	Switch 1 Voltage B	8	Sw1VoltC	Switch 1 Voltage C	32	Sw2VoltA	Switch 2 Voltage A	64	Sw2VoltB	Switch 2 Voltage B	128	Sw2VoltC	Switch 2 Voltage C
Binary	Value	Description																					
2	Sw1VoltA	Switch 1 Voltage A																					
4	Sw1VoltB	Switch 1 Voltage B																					
8	Sw1VoltC	Switch 1 Voltage C																					
32	Sw2VoltA	Switch 2 Voltage A																					
64	Sw2VoltB	Switch 2 Voltage B																					
128	Sw2VoltC	Switch 2 Voltage C																					
XferInactiveReason	UINT16	<table border="1"> <thead> <tr> <th colspan="3">Enumeration</th> </tr> <tr> <th>Binary</th><th>Value</th><th>Description</th></tr> </thead> <tbody> <tr><td>1</td><td>XferDecline</td><td>Xfer Decline</td></tr> <tr><td>2</td><td>XferSuccess</td><td>Xfer Success</td></tr> <tr><td>3</td><td>XferStopped</td><td>Xfer Stopped</td></tr> <tr><td>4</td><td>TimerExpired</td><td>Timer Expired</td></tr> </tbody> </table>	Enumeration			Binary	Value	Description	1	XferDecline	Xfer Decline	2	XferSuccess	Xfer Success	3	XferStopped	Xfer Stopped	4	TimerExpired	Timer Expired			
Enumeration																							
Binary	Value	Description																					
1	XferDecline	Xfer Decline																					
2	XferSuccess	Xfer Success																					
3	XferStopped	Xfer Stopped																					
4	TimerExpired	Timer Expired																					
xmtresultcode	UINT16	<table border="1"> <thead> <tr> <th colspan="3">Enumeration</th> </tr> <tr> <th>Binary</th><th>Value</th><th>Description</th></tr> </thead> <tbody> <tr><td>0</td><td>NETRETURNSUCCESS</td><td>NET return is successful</td></tr> <tr><td>1</td><td>NETRETURNERROR</td><td>NET return has an error</td></tr> </tbody> </table>	Enumeration			Binary	Value	Description	0	NETRETURNSUCCESS	NET return is successful	1	NETRETURNERROR	NET return has an error									
Enumeration																							
Binary	Value	Description																					
0	NETRETURNSUCCESS	NET return is successful																					
1	NETRETURNERROR	NET return has an error																					

Table 3. Historic Events (1142 items)

Event Code (hex)	Event Code (dec)	Description	Category	Logging Level	Definition
0201	513	Event Register OK	DAT[MCU]	Normal	<p>The task indicated has enabled event registering for the specified team. The registering of an event is the process of making all team members aware that an event has occurred.</p> <p>Data 1: Team Data1 Type: Team Data 2: Task Data2 Type: Task Data 3:Debug Data Data3 Type: ushort Data 4:Debug Data Data4 Type: ushort</p>
0202	514	Error Getting Internal 6800 Data	DAT[MCU]	Normal	<p>An error was detected when the IntelliTEAM II software collected data related to the internal switch function.</p> <p>Data 1:Debug Data Data1 Type: ushort Data 2:Debug Data Data2 Type: ushort Data 3:Debug Data Data3 Type: ushort Data 4:Debug Data Data4 Type: ushort</p>
0203	515	Error Getting Local 6800 Data	DAT[MCU]	Normal	<p>An error was detected when the IntelliTEAM II software retrieved data for the local switch in the specified team. This may occur if the switch/position number configured on the SETUP: Team screen is incorrect.</p> <p>Data 1: Team Data1 Type: Team Data 2:Debug Data Data2 Type: ushort Data 3:Debug Data Data3 Type: ushort Data 4:Debug Data Data4 Type: ushort</p>
0204	516	Error Writing Coach Task-List Full	DAT[MCU]	Normal	<p>The list of pending tasks that the coach carries between team members is full in the specified team. No more tasks can be put on this list until one or more of the existing tasks have been completed.</p> <p>Data 1: Team Data1 Type: Team Data 2:Debug Data Data2 Type: ushort Data 3:Debug Data Data3 Type: ushort Data 4:Debug Data Data4 Type: ushort</p>
0205	517	Error Writing Event Task-List Full	DAT[MCU]	Normal	<p>The list of pending team-related tasks is full in the specified team. No more tasks can be put on this list until one or more of the existing tasks have been completed.</p> <p>Data 1: Team Data1 Type: Team</p>

Definitions of Historic Events

					Data 2:Debug Data Data2 Type: ushort Data 3:Debug Data Data3 Type: ushort Data 4:Debug Data Data4 Type: ushort
0206	518	Error Writing Member Task-List Full	DAT[MCU]	Normal	The list of pending member-process tasks is full in the specified team. No more tasks can be put on this list until one or more of the existing tasks have been completed. Data 1: Team Data1 Type: Team Data 2:Debug Data Data2 Type: ushort Data 3:Debug Data Data3 Type: ushort Data 4:Debug Data Data4 Type: ushort
0207	519	Error Writing Comm Task-List Full	DAT[MCU]	Normal	The coach or the team member needs to send a new message to another team member and the DNP communications buffer is full. Existing transactions must be completed before more are put on the communications list. Data 1:Debug Data Data1 Type: ushort Data 2:Debug Data Data2 Type: ushort Data 3:Debug Data Data3 Type: ushort Data 4:Debug Data Data4 Type: ushort
0208	520	Error Getting Comm Task From List	DAT[MCU]	Normal	An error was detected when removing a message from the DNP communications buffer. Data 1:Debug Data Data1 Type: ushort Data 2:Debug Data Data2 Type: ushort Data 3:Debug Data Data3 Type: ushort Data 4:Debug Data Data4 Type: ushort
0209	521	New Coach Generated	DAT[MCU]	Normal	A new coach has been generated at the local team member for the specified team. This could be caused by a power up state, by the existing coach being lost due to communications failure, or by the existing coach data being inconsistent. Data 1: Team Data1 Type: Team Data 2:Debug Data Data2 Type: ushort Data 3:Debug Data Data3 Type: ushort Data 4:Debug Data Data4 Type: ushort
020A	522	Coach Old - Duplicate or CRC Bad	DAT[MCU]	Extended	The coach received by the specified team is not the current coach - it is a duplicate of the current coach or it contains data inconsistent with the presently expected data. The coach is rejected. Data 1: Team Data1 Type: Team Data 2: Coach Rejection Code Data2 Type: CoachRejectionCode Data 3:Debug Data Data3 Type: ushort Data 4:Debug Data Data4 Type: ushort
020B	523	Old or Duplicate Task Discarded	DAT[MCU]	All	The task taken from the event list on the specified team is either old or is a duplicate of an existing task. This occurs normally in the operation of the team as events are distributed throughout the team. Data 1: Team Data1 Type: Team Data 2:Debug Data Data2 Type: ushort Data 3:Debug Data Data3 Type: ushort Data 4:Debug Data Data4 Type: ushort
020C	524	Switch Not Ready for Transfer	DAT[MCU]	Normal	The local 6800 on the specified team is not ready for transfer operations. This may be caused by an internal switch error (for example, a bad battery). Data 1:Debug Data Data1 Type: ushort Data 2:Debug Data Data2 Type: ushort Data 3:Debug Data Data3 Type: ushort Data 4:Debug Data Data4 Type: ushort
020D	525	Unknown Event/Task Request	DAT[MCU]	Normal	An event or task for which the local team member is not programmed was requested within the specified team. Data 1: Team Data1 Type: Team Data 2:Debug Data Data2 Type: ushort Data 3:Debug Data Data3 Type: ushort Data 4:Debug Data Data4 Type: ushort

Definitions of Historic Events

020E	526	Find Alternate Source Result	DAT[MCU]	Normal	<p>During a transfer event, the team must find an alternate source, based on the alternate source sequence and the normal function of the switches within the team (both entered on the SETUP: Team screen). This message indicates the resulting switch record, to be used for the team indicated.</p> <p>Data 1: Team Data1 Type: Team Data 2: Rec Data2 Type: MemberWithDoneAndEOL Data 3:Debug Data Data3 Type: ushort Data 4:Debug Data Data4 Type: ushort</p>
020F	527	Register Event Disabled	DAT[MCU]	Normal	<p>The registering of events for distribution within the specified team has been disabled at the local team member. This was probably caused by a change in the team's configuration on the SETUP: Team screen.</p> <p>Data 1: Team Data1 Type: Team Data 2:Debug Data Data2 Type: ushort Data 3:Debug Data Data3 Type: ushort Data 4:Debug Data Data4 Type: ushort</p>
0210	528	Member Requested	DAT[MCU]	All	<p>The specified team has requested that the local team member execute the task indicated.</p> <p>Data 1: Team Data1 Type: Team Data 2: Task Data2 Type: Task Data 3:Debug Data Data3 Type: ushort Data 4:Debug Data Data4 Type: ushort</p>
0211	529	Close Switch OK	DAT[MCU]	Normal	<p>The switch/position indicated was successfully closed by the specified team.</p> <p>Data 1: Team Data1 Type: Team Data 2: Switch Position Data2 Type: SwitchPosition Data 3:Debug Data Data3 Type: ushort Data 4:Debug Data Data4 Type: ushort</p>
0212	530	Switch Closing Issue	DAT[MCU]	Extended	<p>The switch/position indicated failed to close or remain closed after a request by the specified team. Automatic operation may have been disabled at this team member, or the switch may have reopened during the shots-to-lockout time period.</p> <p>Data 1: Team Data1 Type: Team Data 2: Switch position Data2 Type: SwitchPosition Data 3:Debug Data Data3 Type: ushort Data 4:Debug Data Data4 Type: ushort</p>
0213	531	Transfer Approved	DAT[MCU]	Normal	<p>The transfer operation requested by the specified team, using the alternate source switch previously determined, was approved by the adjacent teams. The approval code is also shown. For details on the code, contact S&C.</p> <p>Data 1: Team Data1 Type: Team Data 2: Restore Condition Test Result Data2 Type: RestoreConditionTestResult Data 3:Debug Data Data3 Type: ushort Data 4:Debug Data Data4 Type: ushort</p>
0214	532	Transfer Declined	DAT[MCU]	Normal	<p>The transfer operation requested by the specified team has been declined by the adjacent teams. The requesting team must look for another alternate source, or retry the operation on this alternate source if no other exists. Possible codes are: (code- definition) 2- Fault isolated, 3- Excessive load, 4- Open team not prepared for the transfer, 5- Closed team not prepared for the transfer, 6- Line segment limit exceeded, 7- Issue detected on one of the teams, 8- Phase loss isolated, 9- Source breaker isolated.</p> <p>Data 1: Team Data1 Type: Team Data 2: Restore Condition Test Result Data2 Type: RestoreConditionTestResult Data 3:Debug Data Data3 Type: ushort Data 4:Debug Data Data4 Type: ushort</p>
0215	533	Switch Open OK	DAT[MCU]	Normal	<p>The specified team successfully opened the switch/position indicated.</p>

Definitions of Historic Events

					Data 1: Team Data1 Type: Team Data 2: Switch Position Data2 Type: SwitchPosition Data 3:Debug Data Data3 Type: ushort Data 4:Debug Data Data4 Type: ushort
0216	534	Switch Opening Unsuccessful	DAT[MCU]	Normal	The specified team was unable to open the switch/position indicated. Data 1: Team Data1 Type: Team Data 2: Switch Position Data2 Type: SwitchPosition Data 3:Debug Data Data3 Type: ushort Data 4:Debug Data Data4 Type: ushort
0217	535	Operation Switch Function Return	DAT[MCU]	Extended	This message displays the internal code returned during the operation of the local switch in the specified team. Contact S&C for code details, this code is application specific. Data 1: Team Data1 Type: Team Data 2: Switch Operation Result Code Data2 Type: SwitchOperationResult Data 3:Debug Data Data3 Type: ushort Data 4:Debug Data Data4 Type: ushort
0218	536	Coach Arrived	DAT[MCU]	All	This message logs the arrival of the coach, along with all the updated data, at the local team member for the specified team. Data 1: Team Data1 Type: Team Data 2:Debug Data Data2 Type: ushort Data 3:Debug Data Data3 Type: ushort Data 4:Debug Data Data4 Type: ushort
0219	537	Coach Has Departed	DAT[MCU]	All	This message logs the departure of the coach from the local team member for the specified team, and indicates where the coach is going next. Data 1: Team Data1 Type: Team Data 2: Goto Rec Data2 Type: TeamRecord Data 3:Debug Data Data3 Type: ushort Data 4:Debug Data Data4 Type: ushort
021A	538	Sequence Numbers Resynchronization	DAT[MCU]	Normal	The sequence numbers of events for the specified team have fallen out of synchronization. The last sequence number received is shown. The local team member will now resynchronize the number. Data 1: Team Data1 Type: Team Data 2:Debug Data Data2 Type: ushort Data 3:Debug Data Data3 Type: ushort Data 4:Debug Data Data4 Type: ushort
021B	539	Coach Arrived on Request	DAT[MCU]	All	This message logs the arrival of the coach at the local team member of the specified team after the local team member requested the coach. Data 1: Team Data1 Type: Team Data 2:Debug Data Data2 Type: ushort Data 3:Debug Data Data3 Type: ushort Data 4:Debug Data Data4 Type: ushort
021C	540	Volt/Fault Reset Occurred	DAT[MCU]	Extended	The voltage loss and overcurrent indications maintained by the IntelliTEAM II software have been reset after either the Sectionalizer Reset Time or, if a transfer event has occurred, after team reconfiguration is complete. Data 1: Switch Position Data1 Type: SwitchPosition Data 2:Debug Data Data2 Type: ushort Data 3:Debug Data Data3 Type: ushort Data 4:Debug Data Data4 Type: ushort
021D	541	Coach is Held by Team Member	DAT[MCU]	All	The coach for the specified team is being held by the local team member. This occurs when a process is taking place at the local team member that requires the presence of coaches from both adjacent teams. Data 1: Team Data1 Type: Team

Definitions of Historic Events

					Data 2:Debug Data Data2 Type: ushort Data 3:Debug Data Data3 Type: ushort Data 4:Debug Data Data4 Type: ushort
021E	542	Line Segment Faulted	DAT[MCU]	Normal	The line segment protected by the specified team is the location of the overcurrent fault on the circuit. The team will not attempt to restore service to this line segment. Data 1: Team Data1 Type: Team Data 2:Debug Data Data2 Type: ushort Data 3:Debug Data Data3 Type: ushort Data 4:Debug Data Data4 Type: ushort
021F	543	Device Opened for Transfer	DAT[MCU]	Normal	During a transfer event, the coach of the specified team opened the switch indicated to allow the transfer operation to continue. This may occur when one or more switches within the team are not coordinated to open at the same time as the other switches. Data 1: Team Data1 Type: Team Data 2: Rec Data2 Type: SwitchRecord Data 3:Debug Data Data3 Type: ushort Data 4:Debug Data Data4 Type: ushort
0220	544	Return to Normal Start Event Request	DAT[MCU]	Normal	The Return to Normal timer has expired, allowing the Return to Normal process to start on the specified team. This message indicates that the specified team generated the event. Data 1: Team Data1 Type: Team Data 2:Debug Data Data2 Type: ushort Data 3:Debug Data Data3 Type: ushort Data 4:Debug Data Data4 Type: ushort
0221	545	Return To Normal Disabled at Switch	DAT[MCU]	Normal	The Return to Normal process will not be carried out on the specified team because Return to Normal is disabled on the SETUP: Team screen. Data 1: Team Data1 Type: Team Data 2:Debug Data Data2 Type: ushort Data 3:Debug Data Data3 Type: ushort Data 4:Debug Data Data4 Type: ushort
0222	546	Return to Normal Timer Started	DAT[MCU]	Normal	The Return to Normal timer was started by the local team member of the specified team. Data 1: Team Data1 Type: Team Data 2:Debug Data Data2 Type: ushort Data 3:Debug Data Data3 Type: ushort Data 4:Debug Data Data4 Type: ushort
0223	547	Return to Normal Start Event Received	DAT[MCU]	Normal	The local team member of the specified team received a request to start the Return to Normal process. This follows the end of the Return to Normal timer and the subsequent event request. Data 1: Team Data1 Type: Team Data 2:Debug Data Data2 Type: ushort Data 3:Debug Data Data3 Type: ushort Data 4:Debug Data Data4 Type: ushort
0224	548	Return to Normal Process Stopped	DAT[MCU]	Extended	The Return to Normal process completed at the local team member with the indicated completion code. For details on the code, contact S&C. Data 1: Team Data1 Type: Team Data 2: Code Data2 Type: InternalCode Data 3:Debug Data Data3 Type: ushort Data 4:Debug Data Data4 Type: ushort
0225	549	Return to Normal Continue OK	DAT[MCU]	Normal	The internal Return to Normal process for the specified team indicated that Return to Normal may continue to the next step. The process result code is also shown. Data 1: Team Data1 Type: Team Data 2: Code Data2 Type: InternalCode Data 3:Debug Data Data3 Type: ushort Data 4:Debug Data Data4 Type: ushort

Definitions of Historic Events

0226	550	Task Travel	DAT[MCU]	All	<p>During a Return to Normal process, tasks associated with the process travel among multiple teams between the normal source and the normal tie point of the circuit. This message traces the path of the tasks.</p> <p>Data 1: from Team Data1 Type: Team Data 2: Team Data2 Type: Team Data 3:Debug Data Data3 Type: ushort Data 4:Debug Data Data4 Type: ushort</p>
0227	551	Return to Normal Process Unsuccessful	DAT[MCU]	Normal	<p>The internal Return to Normal process for the specified team indicated that Return to Normal cannot continue. This may be caused by a team member that has Return to Normal disabled (Code 7), or by the adjacent source team not yet being in its normal state (Code 6).</p> <p>Data 1: Team Data1 Type: Team Data 2: Code Data2 Type: InternalCode Data 3:Debug Data Data3 Type: ushort Data 4:Debug Data Data4 Type: ushort</p>
0228	552	Config Update - Operation Suspended	DAT[MCU]	Normal	<p>The team configuration of any of the active local teams is being changed on the SETUP: Team screen. While this change is in progress, team operation is suspended.</p> <p>Data 1:Debug Data Data1 Type: ushort Data 2:Debug Data Data2 Type: ushort Data 3:Debug Data Data3 Type: ushort Data 4:Debug Data Data4 Type: ushort</p>
022A	554	Internal Test Point	DAT[MCU]	Normal	<p>A general internal message to display data that may be helpful during diagnostics. Please contact S&C if you see this message.</p> <p>Data 1:Debug Data Data1 Type: ushort Data 2:Debug Data Data2 Type: ushort Data 3:Debug Data Data3 Type: ushort Data 4:Debug Data Data4 Type: ushort</p>
022B	555	Coach Collect Data	DAT[MCU]	Extended	<p>This message logs the collection of new data by the coach in the specified team. This data collection process occurs during the start of a transfer event. The team record where the coach is going is also shown.</p> <p>Data 1: Team Data1 Type: Team Data 2: Goto Rec Data2 Type: MemberWithDoneAndEOL Data 3:Debug Data Data3 Type: ushort Data 4:Debug Data Data4 Type: ushort</p>
022C	556	Coach Hold Override	DAT[MCU]	All	<p>When the team member of the specified team holds the coach for an extended period of time, an override occurs that allows the coach to briefly visit other team members. This prevents the coach from becoming old and regenerated by an adjacent team member. The team record where the coach is going is also shown.</p> <p>Data 1: Team Data1 Type: Team Data 2: Goto Rec Data2 Type: TeamRecord Data 3:Debug Data Data3 Type: ushort Data 4:Debug Data Data4 Type: ushort</p>
022D	557	Rebuilding Coach	DAT[MCU]	Normal	<p>The coach for the specified team is being regenerated. This may be caused by a power up event, a configuration change in the team, or a lost coach due to communications failure. A diagnostic code is also shown, contact S&C for code details.</p> <p>Data 1: Team Data1 Type: Team Data 2:Task identifier Data2 Type: ushort Data 3:Debug Data Data3 Type: ushort Data 4:Debug Data Data4 Type: ushort</p>
0230	560	Team Not Ready - Discard Task	DAT[MCU]	All	<p>The indicated task has been discarded because the specified team was not ready to transfer. This is typically the result of a local or team error condition.</p> <p>Data 1: Team Data1 Type: Team Data 2: Task Data2 Type: Task</p>

Definitions of Historic Events

					Data 3:Debug Data Data3 Type: ushort Data 4:Debug Data Data4 Type: ushort
0231	561	SCADA Prohibit Restoration Active	DAT[MCU]	Normal	A SCADA command was received to prevent the restoration of any load by this team member (the switch may not close automatically), however protection is not affected. If applicable, this message will also be displayed on power up. Data 1:Debug Data Data1 Type: PRReason Data 2:Debug Data Data2 Type: ushort Data 3:Debug Data Data3 Type: ushort Data 4:Debug Data Data4 Type: ushort
0232	562	Timer Prohibit Restoration Active	DAT[MCU]	Normal	The Prohibit Restoration Timer expired, preventing the restoration of load by the team for which the timer expired, however automatic sectionalizing is not affected. If applicable, this message will also be displayed on power-up. Data 1:Debug Data Data1 Type: ushort Data 2:Debug Data Data2 Type: ushort Data 3:Debug Data Data3 Type: ushort Data 4:Debug Data Data4 Type: ushort
0233	563	Closed Loop RSD Center Recalc Event	DAT[MCU]	Normal	Closed Loop RSD Center Recalculation Event. Data 1:Debug Data Data1 Type: ushort Data 2:Debug Data Data2 Type: ushort Data 3:Debug Data Data3 Type: ushort Data 4:Debug Data Data4 Type: ushort
0234	564	Extended STL Requested	DAT[MCU]	Normal	Extended STL Requested. Data 1:Debug Data Data1 Type: SW1Or2 Data 2:Debug Data Data2 Type: EnabDisab Data 3:Debug Data Data3 Type: ushort Data 4:Debug Data Data4 Type: ushort
0235	565	Team Communication Error	DAT[MCU]	Normal	A team-related message could not be delivered. Data 1: Team Data1 Type: Team Data 2: RTU Data2 Type: RTUAddress Data 3:Debug Data Data3 Type: ushort Data 4:Debug Data Data4 Type: ushort
0236	566	Monitor Line Segment	DAT[MCU]	All	The specified team has an indication to start a transfer event, but the line segment is still energized. The team monitors the segment until it is deenergized. Data 1: Team Data1 Type: Team Data 2:Debug Data Data2 Type: ushort Data 3:Debug Data Data3 Type: ushort Data 4:Debug Data Data4 Type: ushort
0237	567	Closed Loop Member Center Change	DAT[MCU]	Normal	Closed Loop Member Center Change. Data 1:Debug Data Data1 Type: ushort Data 2:Debug Data Data2 Type: ushort Data 3:Debug Data Data3 Type: ushort Data 4:Debug Data Data4 Type: ushort
0238	568	Not All Configured Teams Xfer Ready	DAT[MCU]	Normal	At least one of the active teams where the local control is a member is not fully operational. Data 1:Debug Data Data1 Type: ushort Data 2:Debug Data Data2 Type: ushort Data 3:Debug Data Data3 Type: ushort Data 4:Debug Data Data4 Type: ushort
0239	569	Transfer in Progress on Any Team	DAT[MCU]	Normal	A team is in the process of reconfiguring the circuit and transferring load to an alternate source. Data 1:Debug Data Data1 Type: ushort Data 2:Debug Data Data2 Type: ushort Data 3:Debug Data Data3 Type: ushort Data 4:Debug Data Data4 Type: ushort

Definitions of Historic Events

023A	570	RTN in Progress on Any Team	DAT[MCU]	Normal	<p>A team is presently returning the circuit to its normal configuration.</p> <p>Data 1:Debug Data Data1 Type: ushort Data 2:Debug Data Data2 Type: ushort Data 3:Debug Data Data3 Type: ushort Data 4:Debug Data Data4 Type: ushort</p>
023B	571	Adjust Line Segment Count	DAT[MCU]	Extended	<p>Specified team has increased or decreased the line segment count associated with the Line Segment Limit set point, following a transfer event.</p> <p>Data 1: Team Data1 Type: Team Data 2:Debug Data Data2 Type: ushort Data 3:Debug Data Data3 Type: ushort Data 4:Debug Data Data4 Type: ushort</p>
023C	572	Software Mismatch on Arriving Coach	DAT[MCU]	Normal	<p>There is a software revision incompatibility within the team. The data fields show revision and version information for the team member from which the coach just arrived.</p> <p>Data 1:Debug Data Data1 Type: ushort Data 2:Debug Data Data2 Type: ushort Data 3:Debug Data Data3 Type: ushort Data 4:Debug Data Data4 Type: ushort</p>
023D	573	Switch Open - Extended Parallel	DAT[MCU]	Normal	<p>During a closed transition Return to Normal, the team member at a tie switch automatically opened the switch after a prescribed timeout. This insured that a circuit parallel was not left in place indefinitely. This condition is not normal, and may have resulted in load being dropped.</p> <p>Data 1:Debug Data Data1 Type: ushort Data 2:Debug Data Data2 Type: ushort Data 3:Debug Data Data3 Type: ushort Data 4:Debug Data Data4 Type: ushort</p>
023E	574	Unexpected State Change	DAT[MCU]	Extended	<p>The transfer state went through an unexpected transition at the specified team. This error might stop an ongoing transfer process.</p> <p>Data 1: Team Data1 Type: Team Data 2:Debug Data Data2 Type: ushort Data 3:Debug Data Data3 Type: ushort Data 4:Debug Data Data4 Type: ushort</p>
023F	575	Loading Data Reset	DAT[MCU]	Extended	<p>When a transfer with a known load value occurs, the IntelliTEAM II software resets the loading data to reflect the new value. This updates the information more quickly than the 2-minute load averaging. The code relates to the state of the reset process.</p> <p>Data 1: Team Data1 Type: Team Data 2:Task identifier Data2 Type: ushort Data 3:Debug Data Data3 Type: ushort Data 4:Debug Data Data4 Type: ushort</p>
0240	576	Contract Receiver Busy	DAT[MCU]	Extended	<p>A contract agent's receiver buffer was full, so a contract message was dropped. The numbers for the specified agent are associated with the RTU address at the originating team member.</p> <p>Data 1: Agent Data1 Type: Agent Data 2: SwitchPosition Data2 Type: SwitchPosition Data 3: Agent Data3 Type: Agent Data 4:Debug Data Data4 Type: ushort</p>
0241	577	Contract Added to List	DAT[MCU]	All	<p>A new contract was added to the list of contracts being maintained. This message shows both the requesting and granting teams associated with the transfer process. The requesting team (Team 1) identifies the origin of the contract.</p> <p>Data 1: Agent Data1 Type: Agent Data 2: SwitchPosition Data2 Type: SwitchPosition Data 3:Team Data3 Type: Team Data 4:Team Data4 Type: Team</p>
0242	578	New Contract Addition Issue	DAT[MCU]	Extended	<p>A contract agent tried to add a new contract to its list but could not, so the contract was declined. The number for the specified agent is associated with the RTU address at the originating team member.</p>

Definitions of Historic Events

					Data 1: Agent Data1 Type: Agent Data 2: SwitchPosition Data2 Type: SwitchPosition Data 3:Debug Data Data3 Type: ushort Data 4:Debug Data Data4 Type: ushort
0243	579	Contract Pending Issue	DAT[MCU]	Extended	The requesting contract agent was waiting for a response when the timer ran out, so if the contract was unsuccessful. The coach may restart the contract request if it cannot find another alternate source. This message shows the two teams involved with the transfer process at this team member location, where (Team 1) is the requesting team. Data 1: Agent Data1 Type: Agent Data 2: SwitchPosition Data2 Type: SwitchPosition Data 3:Debug Data Data3 Type: ushort Data 4:Debug Data Data4 Type: ushort
0244	580	Contract Request Was Declined	DAT[MCU]	Normal	The granting agent declined the contract request. The number for the specified agent is associated with the RTU address at the originating team member. Note that this message can appear at any agent with the contract on its list. Data 1: Agent Data1 Type: Agent Data 2:SwitchPosition Data2 Type: SwitchPosition Data 3:Debug Data Data3 Type: ushort Data 4:Debug Data Data4 Type: ushort
0245	581	Contract General Error	DAT[MCU]	Extended	The specified contract agent detected a contract error. The number for the agent is associated with the RTU address at the team member. Data 1: Agent Data1 Type: Agent Data 2:Debug Data Data2 Type: ushort Data 3:Debug Data Data3 Type: ushort Data 4:Debug Data Data4 Type: ushort
0246	582	Contract Request Travel	DAT[MCU]	All	A contract request is traveling between teams. (Team 1) is the segment through which the request just came, and (Rec 2) is the team member in the direction where the request is headed. Data 1: Agent Data1 Type: Agent Data 2: Team Data2 Type: Team Data 3: TeamRecord Data3 Type: TeamRecord Data 4:Debug Data Data4 Type: ushort
0247	583	Contract Request Was Accepted	DAT[MCU]	Normal	The granting agent accepted the contract. The number for the specified agent is associated with the RTU address at the originating team member. Data 1: Agent Data1 Type: Agent Data 2:Debug Data Data2 Type: ushort Data 3:Debug Data Data3 Type: ushort Data 4:Debug Data Data4 Type: ushort
0248	584	Contract is Being Dissolved	DAT[MCU]	Extended	An active contract is no longer needed and is in the process of being dissolved. The number for the specified agent is associated with the RTU address at the originating team member. Data 1: Agent Data1 Type: Agent Data 2: SwitchPosition Data2 Type: SwitchPosition Data 3:Debug Data Data3 Type: ushort Data 4:Debug Data Data4 Type: ushort
0249	585	Contract Started by Member	DAT[MCU]	All	A member of the specified team has determined that it can close based on information from the coach, but it must first request a contract. Data 1: Agent Data1 Type: Agent Data 2: SwitchPosition Data2 Type: SwitchPosition Data 3: Team Data3 Type: Team Data 4: TeamRecord Data4 Type: TeamRecord
024A	586	Contract Approved Switch Close	DAT[MCU]	Normal	The specified team requested a contract, which then traveled to the granting agent, was approved, and came back. The switch has closed to energize the line segment.

Definitions of Historic Events

					Data 1: Agent Data1 Type: Agent Data 2: SwitchPosition Data2 Type: SwitchPosition Data 3: Team Data3 Type: Team Data 4:Debug Data Data4 Type: ushort
024B	587	Contract Declined	DAT[MCU]	Normal	The contract request made by the specified team was declined. Data 1: Agent Data1 Type: Agent Data 2: SwitchPosition Data2 Type: SwitchPosition Data 3: Team Data3 Type: Team Data 4:Debug Data Data4 Type: ushort
024C	588	Contract Requested by Member	DAT[MCU]	Normal	The local team member has requested that the contract agent negotiate a contract on behalf of the specified team. Data 1: Agent Data1 Type: Agent Data 2: SwitchPosition Data2 Type: SwitchPosition Data 3:Debug Data Data3 Type: ushort Data 4:Debug Data Data4 Type: ushort
024D	589	Contract Requires Member Wait	DAT[MCU]	All	The specified team is waiting for a contract to be requested, granted, or declined. Data 1: Agent Data1 Type: Agent Data 2: SwitchPosition Data2 Type: SwitchPosition Data 3: Team Data3 Type: Team Data 4:Debug Data Data4 Type: ushort
024E	590	Contract Communication Received	DAT[MCU]	All	The contract agent has received a message. (Team 1) refers to the contract's originating segment, and (Team 2) refers to the temporary segment, usually the segment through which the message just passed. Data 1: Agent Data1 Type: Agent Data 2: SwitchPosition Data2 Type: SwitchPosition Data 3:Debug Data Data3 Type: ushort Data 4: ContractState Data4 Type: ContractState
024F	591	Contract Maintained	DAT[MCU]	All	Scheduled maintenance of a contract was performed by the specified requesting agent to confirm the continued need for the contract. The number for the agent is associated with the RTU address at the team member. Data 1: Agent Data1 Type: Agent Data 2: SwitchPosition Data2 Type: SwitchPosition Data 3:Debug Data Data3 Type: ushort Data 4:Debug Data Data4 Type: ushort
0250	592	Duplicate Contract Received	DAT[MCU]	All	The specified requesting agent received an old or duplicate contract message, which refers to the indicated contract state. The number for the agent is associated with the RTU address at the team member. Data 1: Agent Data1 Type: Agent Data 2: SwitchPosition Data2 Type: SwitchPosition Data 3: ContractState Data3 Type: ContractState Data 4:Debug Data Data4 Type: ushort
0251	593	Contract Transmit Busy	DAT[MCU]	All	A contract agent's transmit buffer was full. The message is held until the transmit buffer has space, and is then sent. The number for the specified agent is associated with the RTU address at the originating team member. Data 1: Agent Data1 Type: Agent Data 2: SwitchPosition Data2 Type: SwitchPosition Data 3:Debug Data Data3 Type: ushort Data 4:Debug Data Data4 Type: ushort
0252	594	Contract Dissolved by Member	DAT[MCU]	Extended	The local team member has started the process to dissolve an active contract on behalf of the specified team. Data 1: Agent Data1 Type: Agent Data 2: SwitchPosition Data2 Type: SwitchPosition Data 3: Team Data3 Type: Team Data 4:Debug Data Data4 Type: ushort

Definitions of Historic Events

0253	595	Contract Resource Limitation	DAT[MCU]	Normal	<p>A contract agent found that resources were not available for load transfer, because of either segment limitations (Code 2) or capacity limitations (Code 3). The contract agent did not forward the contract any further.</p> <p>Data 1: Agent Data1 Type: Agent Data 2: ushort Data2 Type: ushort Data 3: ushort Data3 Type: ushort Data 4: ushort Data4 Type: ushort</p>
0254	596	Contract Cannot Travel	DAT[MCU]	All	<p>The requesting contract agent does not know where the present source is, so it could not forward the contract request. The contract failed. The number for the specified agent is associated with the RTU address at the team member.</p> <p>Data 1: Agent Data1 Type: Agent Data 2: SwitchPosition Data2 Type: SwitchPosition Data 3:Debug Data Data3 Type: ushort Data 4:Debug Data Data4 Type: ushort</p>
0255	597	Contract Not Found	DAT[MCU]	All	<p>A contract agent received a message about a contract that is not in its list. This may result in the contract being dissolved and, if necessary, reactivated. The number for the specified agent is associated with the RTU address at the originating team member.</p> <p>Data 1: Agent Data1 Type: Agent Data 2: SwitchPosition Data2 Type: SwitchPosition Data 3:Debug Data Data3 Type: ushort Data 4:Debug Data Data4 Type: ushort</p>
0256	598	Contract Reactivated	DAT[MCU]	Extended	<p>The contract is missing somewhere along its routing path, so the requesting agent reactivated the contract. The number for the specified agent is associated with the RTU address at the originating team member.</p> <p>Data 1: Agent Data1 Type: Agent Data 2: SwitchPosition Data2 Type: SwitchPosition Data 3:Debug Data Data3 Type: ushort Data 4:Debug Data Data4 Type: ushort</p>
0257	599	Alternate Source Flag Cleared	DAT[MCU]	Extended	<p>The line segment associated with the specified team is no longer being fed from an alternate source. This message usually follows a Return to Normal operation.</p> <p>Data 1: Team Data1 Type: Team Data 2:Debug Data Data2 Type: ushort Data 3:Debug Data Data3 Type: ushort Data 4:Debug Data Data4 Type: ushort</p>
0258	600	Member Cleared Task Lock Attributes	DAT[MCU]	All	<p>The team member logic cleared the execution lock on tasks present on the task list. These tasks may now be executed by the team member.</p> <p>Data 1:Debug Data Data1 Type: ushort Data 2:Debug Data Data2 Type: ushort Data 3:Debug Data Data3 Type: ushort Data 4:Debug Data Data4 Type: ushort</p>
0259	601	Pending Comm Message Cleared	DAT[MCU]	All	<p>The coach has determined that a pending message is no longer valid, and should be removed from the communications transmit list.</p> <p>Data 1: Team Data1 Type: Team Data 2:Debug Data Data2 Type: ushort Data 3:Debug Data Data3 Type: ushort Data 4:Debug Data Data4 Type: ushort</p>
025A	602	Prohibit Restoration Timer Expired	DAT[MCU]	Normal	<p>The timer for the Prohibit Restoration feature has expired and will cause Prohibit Restoration to become active. (Team 1) indicates the team number to which this event applies.</p> <p>Data 1:Debug Data Data1 Type: ushort Data 2:Debug Data Data2 Type: ushort Data 3:Debug Data Data3 Type: ushort Data 4:Debug Data Data4 Type: ushort</p>

Definitions of Historic Events

025B	603	Action Path Complete	DAT[MCU]	All	<p>This message is displayed when the action path for operating the switch gear has completed all possible steps in either the forward or reverse direction.</p> <p>Data 1: Team Data1 Type: Team Data 2:Debug Data Data2 Type: ushort Data 3:Debug Data Data3 Type: ushort Data 4:Debug Data Data4 Type: ushort</p>
025C	604	Next Action	DAT[MCU]	All	<p>The operation of the switch gear is progressing to the next action within the action path. (Action 1) indicates the action to be taken and can be one of the following codes: 3 Close for xfer, 20 Contract request, 21 Contract Terminate, 30 Block recloser, 31 Unblock recloser, 33 Block ground trip, 34 Unblock ground trip, 36 Alternate settings, 37 Normal, 253 Action path done. (Direction 2) is the direction the action path is going, either Forward (1) or Reverse (2).</p> <p>Data 1: Action Data1 Type: Action Data 2: Direction Data2 Type: Direction Data 3:Debug Data Data3 Type: ushort Data 4:Debug Data Data4 Type: ushort</p>
025D	605	Control Feature OK	DAT[MCU]	Extended	<p>Indicates the requested control feature executed normally. Possible point values are: 1 Point to operate switch, 2 Point to block reclosing, 3 Point to block ground trip, 4 Point to change profile.</p> <p>Data 1: Team Data1 Type: Team Data 2: Point Data2 Type: Point Data 3:Debug Data Data3 Type: ushort Data 4:Debug Data Data4 Type: ushort</p>
025E	606	Control Feature Unsuccessful	DAT[MCU]	Normal	<p>Indicates the requested control feature did not execute normally. Data2 Points: 1= Operate 6800, 2= Block reclosing, 3= Block ground trip, 4= Change profile.</p> <p>Data 1: Team Data1 Type: Team Data 2: Point Data2 Type: Point Data 3:Debug Data Data3 Type: ushort Data 4:Debug Data Data4 Type: ushort</p>
025F	607	Alternate Source Flag Set	DAT[MCU]	Normal	<p>Alternate Source Flag Set.</p> <p>Data 1: Data1 Type: ushort Data 2: Data2 Type: ushort Data 3:Debug Data Data3 Type: ushort Data 4:Debug Data Data4 Type: ushort</p>
0260	608	Closed Loop RSD Recalc Timer Expiration	DAT[MCU]	Normal	<p>Closed Loop RSD Recalculation Timer Expiration.</p> <p>Data 1:Debug Data Data1 Type: ushort Data 2:Debug Data Data2 Type: ushort Data 3:Debug Data Data3 Type: ushort Data 4:Debug Data Data4 Type: ushort</p>
0261	609	Closed Loop Member Revert Center	DAT[MCU]	Normal	<p>Closed Loop Member Revert Center.</p> <p>Data 1:Debug Data Data1 Type: ushort Data 2:Debug Data Data2 Type: ushort Data 3:Debug Data Data3 Type: ushort Data 4:Debug Data Data4 Type: ushort</p>
0263	611	Closed Loop Incorrect Circuit Topology	DAT[MCU]	Normal	<p>Closed Loop Incorrect Circuit Topology.</p> <p>Data 1:Debug Data Data1 Type: ushort Data 2:Debug Data Data2 Type: ushort Data 3:Debug Data Data3 Type: ushort Data 4:Debug Data Data4 Type: ushort</p>
0264	612	Volt/Fault Idle Transfer State	DAT[MCU]	All	<p>This message is output when all teams that the 6800 is a member of have their transfer stated back to idle, signaling a reset of the total 3 phase average load.</p> <p>Data 1: Switch Position Data1 Type: SwitchPosition Data 2:Debug Data Data2 Type: ushort</p>

Definitions of Historic Events

					Data 3:Debug Data Data3 Type: ushort Data 4:Debug Data Data4 Type: ushort
0265	613	Closed Loop Incorrect RT Load	DAT[MCU]	Normal	Closed Loop Incorrect RT Load. Data 1:Debug Data Data1 Type: ushort Data 2:Debug Data Data2 Type: ushort Data 3:Debug Data Data3 Type: ushort Data 4:Debug Data Data4 Type: ushort
0266	614	Volt/Fault Overcurrent Cleared	DAT[MCU]	All	This message is output when an overcurrent fault was previously detected, the field now is not faulted and 3 phase voltage has returned, causing the coach to clear the latched overcurrent condition. For details on (Rec 2) contact S&C. Data 1: Team Data1 Type: TeamRecord Data 2: Rec Data2 Type: SwitchRecord Data 3:Debug Data Data3 Type: ushort Data 4:Debug Data Data4 Type: ushort
0267	615	Volt/Fault Voltage Loss Cleared	DAT[MCU]	All	The coach clears a 3 phase voltage loss when: 3 phase voltage loss was previously detected and real time 3 phase voltage is now present and either the external device is in its normal state or the external device's normal job is a source sub. For details on Rec 2, contact S&C. Data 1: Team Data1 Type: TeamRecord Data 2: Rec Data2 Type: SwitchRecord Data 3:Debug Data Data3 Type: ushort Data 4:Debug Data Data4 Type: ushort
0268	616	Volt/Fault Phase Loss Cleared	DAT[MCU]	All	This message is output when a phase loss was previously detected, the external device is now in its normal open or close state, real time 3 phase voltage is present, causing the coach to clear the latched phase loss condition. For details on (Rec 2) contact S&C. Data 1: Team Data1 Type: TeamRecord Data 2: Rec Data2 Type: SwitchRecord Data 3:Debug Data Data3 Type: ushort Data 4:Debug Data Data4 Type: ushort
0269	617	DNP Feeder Loading Data Received	DAT[MCU]	All	Feeder loading data has been received from the source substation or breaker, and may be used in determining the capacity of the circuit during transfer operations. Data 1 indicates the circuit loading received in increments of 10 amps per count. Data 1: Data Data1 Type: LoadingCurrent Data 2:Debug Data Data2 Type: ushort Data 3:Debug Data Data3 Type: ushort Data 4:Debug Data Data4 Type: ushort
026A	618	Error Cleared - Gathering Data	DAT[MCU]	Normal	The error collecting data related to the internal switch function was cleared. Data 1:Debug Data Data1 Type: ushort Data 2:Debug Data Data2 Type: ushort Data 3:Debug Data Data3 Type: ushort Data 4:Debug Data Data4 Type: ushort
026B	619	Device is Ready for Transfer	DAT[MCU]	Normal	The local switch on the specified team is ready for transfer operations. Data 1:Debug Data Data1 Type: ushort Data 2:Debug Data Data2 Type: ushort Data 3:Debug Data Data3 Type: ushort Data 4:Debug Data Data4 Type: ushort
026C	620	Config Update Operation Resumed	DAT[MCU]	Normal	The team configuration of any of the active local teams has been re-enabled on the SETUP: Team screen. Team operation is resumed. Data 1:Debug Data Data1 Type: ushort Data 2:Debug Data Data2 Type: ushort Data 3:Debug Data Data3 Type: ushort Data 4:Debug Data Data4 Type: ushort

Definitions of Historic Events

026D	621	SCADA Prohibit Restoration Cleared	DAT[MCU]	Normal	<p>A SCADA command was received to reenable the restoration of load by this team member, and the switch may be closed automatically. If applicable, this message will also be displayed on power up.</p> <p>Data 1:Debug Data Data1 Type: ushort Data 2:Debug Data Data2 Type: ushort Data 3:Debug Data Data3 Type: ushort Data 4:Debug Data Data4 Type: ushort</p>
026E	622	Timer Prohibit Restoration Cleared	DAT[MCU]	Normal	<p>A SCADA command was received to reenable the restoration of load by this team member, and the switch may be closed automatically. If applicable, this message will also be displayed on power up.</p> <p>Data 1:Debug Data Data1 Type: ushort Data 2:Debug Data Data2 Type: ushort Data 3:Debug Data Data3 Type: ushort Data 4:Debug Data Data4 Type: ushort</p>
026F	623	All Teams Are Transfer Ready	EVT[MCU]	Normal	<p>All teams are fully operational, and may close switches as necessary to transfer load and reconfigure the circuit.</p> <p>Data 1:Debug Data Data1 Type: ushort Data 2:Debug Data Data2 Type: ushort Data 3:Debug Data Data3 Type: ushort Data 4:Debug Data Data4 Type: ushort</p>
0270	624	Transfer Not Active on Any Team	DAT[MCU]	Normal	<p>No teams are presently reconfiguring the circuit or transferring load.</p> <p>Data 1:Debug Data Data1 Type: ushort Data 2:Debug Data Data2 Type: ushort Data 3:Debug Data Data3 Type: ushort Data 4:Debug Data Data4 Type: ushort</p>
0271	625	RTN Not Active on Any Team	DAT[MCU]	Normal	<p>No teams are presently returning the circuit to its normal configuration.</p> <p>Data 1:Debug Data Data1 Type: ushort Data 2:Debug Data Data2 Type: ushort Data 3:Debug Data Data3 Type: ushort Data 4:Debug Data Data4 Type: ushort</p>
0272	626	Unknown Message Type Received	DAT[MCU]	Normal	<p>An IntelliTEAM message was received over communications but contains a message type that is not recognized. The team the message was intended for, and the message type received, are included in the data.</p> <p>Data 1: Team Data1 Type: Team Data 2: Message Type Received Data2 Type: ushort Data 3:Debug Data Data3 Type: ushort Data 4:Debug Data Data4 Type: ushort</p>
0273	627	Request Xfer Trip Prohibit Restoration	DAT[MCU]	Normal	<p>Data 1:Debug Data Data1 Type: ushort Data 2:Debug Data Data2 Type: ushort Data 3:Debug Data Data3 Type: ushort Data 4:Debug Data Data4 Type: ushort</p>
0274	628	Req Xfer Trip Prohibit Rest on DG Team	DAT[MCU]	Normal	<p>Data 1:Debug Data Data1 Type: ushort Data 2:Debug Data Data2 Type: ushort Data 3:Debug Data Data3 Type: ushort Data 4:Debug Data Data4 Type: ushort</p>
0275	629	Xfer Trip Prohibit Restoration Active	DAT[MCU]	Normal	<p>Data 1:Debug Data Data1 Type: ushort Data 2:Debug Data Data2 Type: ushort Data 3:Debug Data Data3 Type: ushort Data 4:Debug Data Data4 Type: ushort</p>

0276	630	Xfer Trip Prohibit Restoration Cleared	DAT[MCU]	Normal	Data 1:Debug Data Data1 Type: ushort Data 2:Debug Data Data2 Type: ushort Data 3:Debug Data Data3 Type: ushort Data 4:Debug Data Data4 Type: ushort
0277	631	DG Reconnect Delay Started	DAT[MCU]	Normal	Data 1:Debug Data Data1 Type: ushort Data 2:Debug Data Data2 Type: ushort Data 3:Debug Data Data3 Type: ushort Data 4:Debug Data Data4 Type: ushort
0278	632	DG Reconnect Delay Expired	DAT[MCU]	Normal	Data 1:Debug Data Data1 Type: ushort Data 2:Debug Data Data2 Type: ushort Data 3:Debug Data Data3 Type: ushort Data 4:Debug Data Data4 Type: ushort
0279	633	Not All Prohibit Rest Flags Cleared	DAT[MCU]	Normal	Data 1:Debug Data Data1 Type: ushort Data 2:Debug Data Data2 Type: ushort Data 3:Debug Data Data3 Type: ushort Data 4:Debug Data Data4 Type: ushort
027A	634	Request Switch Close For DG Reconnect	DAT[MCU]	Normal	Data 1:Debug Data Data1 Type: ushort Data 2:Debug Data Data2 Type: ushort Data 3:Debug Data Data3 Type: ushort Data 4:Debug Data Data4 Type: ushort
027B	635	Switch Closed For DG Reconnection	DAT[MCU]	Normal	Data 1:Debug Data Data1 Type: ushort Data 2:Debug Data Data2 Type: ushort Data 3:Debug Data Data3 Type: ushort Data 4:Debug Data Data4 Type: ushort
027C	636	DG Reconnect Delay Terminated	DAT[MCU]	Normal	Data 1:Debug Data Data1 Type: ushort Data 2:Debug Data Data2 Type: ushort Data 3:Debug Data Data3 Type: ushort Data 4:Debug Data Data4 Type: ushort
027D	637	DG Reconnect Delay Disabled	DAT[MCU]	Normal	Data 1:Debug Data Data1 Type: ushort Data 2:Debug Data Data2 Type: ushort Data 3:Debug Data Data3 Type: ushort Data 4:Debug Data Data4 Type: ushort
027E	638	DG Reconnect Delay Counting Down	DAT[MCU]	Normal	Data 1:Debug Data Data1 Type: ushort Data 2:Debug Data Data2 Type: ushort Data 3:Debug Data Data3 Type: ushort Data 4:Debug Data Data4 Type: ushort
027F	639	Start Monitoring TTPR	DAT[MCU]	Normal	Data 1:Debug Data Data1 Type: ushort Data 2:Debug Data Data2 Type: ushort Data 3:Debug Data Data3 Type: ushort Data 4:Debug Data Data4 Type: ushort
0280	640	Continue Monitoring TTPR	DAT[MCU]	Normal	Data 1:Debug Data Data1 Type: ushort Data 2:Debug Data Data2 Type: ushort Data 3:Debug Data Data3 Type: ushort Data 4:Debug Data Data4 Type: ushort

Definitions of Historic Events

0281	641	Could Not Find DG	DAT[MCU]	Normal	Data 1:Debug Data Data1 Type: ushort Data 2:Debug Data Data2 Type: ushort Data 3:Debug Data Data3 Type: ushort Data 4:Debug Data Data4 Type: ushort
0282	642	Could Not Find Normal Source	DAT[MCU]	Normal	Data 1:Debug Data Data1 Type: ushort Data 2:Debug Data Data2 Type: ushort Data 3:Debug Data Data3 Type: ushort Data 4:Debug Data Data4 Type: ushort
0283	643	Stop Monitoring TTPR	DAT[MCU]	Normal	Data 1:Debug Data Data1 Type: ushort Data 2:Debug Data Data2 Type: ushort Data 3:Debug Data Data3 Type: ushort Data 4:Debug Data Data4 Type: ushort
0284	644	Source Side Team Not Defined	DAT[MCU]	Normal	Data 1:Debug Data Data1 Type: ushort Data 2:Debug Data Data2 Type: ushort Data 3:Debug Data Data3 Type: ushort Data 4:Debug Data Data4 Type: ushort
0285	645	Could Not Start Monitoring TTPR	DAT[MCU]	Normal	Data 1:Debug Data Data1 Type: ushort Data 2:Debug Data Data2 Type: ushort Data 3:Debug Data Data3 Type: ushort Data 4:Debug Data Data4 Type: ushort
0286	646	Closed Loop Center Determination Problem	DAT[MCU]	Normal	Closed Loop Center Determination Problem. Data 1:Debug Data Data1 Type: ushort Data 2:Debug Data Data2 Type: ushort Data 3:Debug Data Data3 Type: ushort Data 4:Debug Data Data4 Type: ushort
0287	647	Transfer Declined	DAT[MCU]	Normal	Data 1: Team Data1 Type: Team Data 2: ExcessLoad Data2 Type: ExcessLoad Data 3: Unused Data3 Type: ushort Data 4: Debug Data Data4 Type: HealingType
0288	648	Transfer Declined Excess Load Inactive	DAT[MCU]	Normal	Data 1: Team Data1 Type: Team Data 2: Debug Data Data2 Type: XferInactiveReason Data 3: Unused Data3 Type: ushort Data 4: Unused Data4 Type: ushort
0289	649	Transfer Declined	DAT[MCU]	Normal	Data 1: Team Data1 Type: Team Data 2: LineSegLimit Data2 Type: LineSegLimit Data 3: Unused Data3 Type: ushort Data 4: Debug Data Data4 Type: HealingType
028A	650	Transfer Declined Line Seg Limit Off	DAT[MCU]	Normal	Data 1: Team Data1 Type: Team Data 2: Debug Data Data2 Type: XferInactiveReason Data 3: Unused Data3 Type: ushort Data 4: Unused Data4 Type: ushort
028D	653	DG Reconnect Delay Terminated Cleared	DAT[MCU]	Normal	Data 1:Debug Data Data1 Type: ushort Data 2:Debug Data Data2 Type: ushort Data 3:Debug Data Data3 Type: ushort Data 4:Debug Data Data4 Type: ushort

Definitions of Historic Events

0290	656	Normally Open Switch Automatic Open	DAT[MCU]	Normal	<p>A normally open team member has opened for an automatic (IntelliTEAM-initiated) reason. This may happen during Return To Normal process. The team and the member record number are provided.</p> <p>Data 1: Team Data1 Type: Team Data 2: Rec Data2 Type: SwitchRecord Data 3:Debug Data Data3 Type: ushort Data 4:Debug Data Data4 Type: ushort</p>
0291	657	DNP Message Rejected	DAT[MCU]	Normal	<p>An IntelliTEAM communication message to the provided RTU was rejected by communications. The rejection code is provided.</p> <p>Data 1: Rtu Data1 Type: RTUAddress Data 2: Code Data2 Type: CommErrorCode Data 3:Debug Data Data3 Type: ushort Data 4:Debug Data Data4 Type: ushort</p>
0292	658	Transfer State Change	DAT[MCU]	All	<p>The transfer state changed for the specified team.</p> <p>Data 1: Team Data1 Type: Team Data 2:Debug Data Data2 Type: ushort Data 3:Debug Data Data3 Type: ushort Data 4:Debug Data Data4 Type: ushort</p>
0293	659	Manual Operation Team Condition On Sw1	DAT[MCU]	Normal	<p>A team entered a non-operational state because an unexpected manual switch operation occurred. Typically the only expected manual switch operation is closing a source switch on a previously faulted team which proves that the fault is gone, and allows RTN process to take place (if RTN is enabled).</p> <p>Data 1: Team Data1 Type: Team Data 2:Debug Data Data2 Type: ushort Data 3:Debug Data Data3 Type: ushort Data 4:Debug Data Data4 Type: ushort</p>
0294	660	Manual Operation Team Condition OFF Sw1	DAT[MCU]	Normal	<p>The unexpected manual switch operation team condition was cleared. This can only occur as a result of a user request.</p> <p>Data 1: Team Data1 Type: Team Data 2:Debug Data Data2 Type: ushort Data 3:Debug Data Data3 Type: ushort Data 4:Debug Data Data4 Type: ushort</p>
0295	661	Manual Operation Not Cleared	DAT[MCU]	Normal	<p>Manual Operation condition could not be cleared on a user request because the local team member is not in its normal state.</p> <p>Data 1: Team Data1 Type: Team Data 2:Debug Data Data2 Type: ushort Data 3:Debug Data Data3 Type: ushort Data 4:Debug Data Data4 Type: ushort</p>
0296	662	Wait For Team to Open	DAT[MCU]	Normal	<p>IntelliTEAM is waiting for all switches in the team to open so that it can attempt to restore service to the team. This is likely to occur only during a 2nd contingency event.</p> <p>Data 1: team Data1 Type: Team Data 2:Debug Data Data2 Type: ushort Data 3:Debug Data Data3 Type: ushort Data 4:Debug Data Data4 Type: ushort</p>
0297	663	Bad Voltage Reopen Flag	DAT[MCU]	Normal	<p>Associated with the Team Member Requalify Time feature. Value of 1 means that the team member is disqualified on an unsuccessful attempt to close and a timer is started. Value of 0 means that the timer has cleared, and the team member can be considered as an alternate source again.</p> <p>Data 1: Team Data1 Type: Team Data 2: Flag value Data2 Type: ushort Data 3:Debug Data Data3 Type: ushort Data 4:Debug Data Data4 Type: ushort</p>
0298	664	ITII Source Loading Data Active	DAT[MCU]	Normal	
0299	665	ITII Source Loading Data Not Active	DAT[MCU]	Normal	
029A	666	ITII RT-Load Data Problem	DAT[MCU]	Normal	

Definitions of Historic Events

029B	667	ITII RT-Load Data Problem Cleared	DAT[MCU]	Normal	
029C	668	ITII Cycling Status Cleared(team rec)	DAT[MCU]	Normal	Data 1: Team Data1 Type: TeamRecord Data 2: Rec Data2 Type: SwitchRecord
029D	669	Team 1 is Ready to Transfer	EVT[MCU]	Extended	
029E	670	Team 1 is in Not Ready state	EVT[MCU]	Extended	
029F	671	Team 2 is Ready to Transfer	EVT[MCU]	Extended	
02A0	672	Team 2 is in Not Ready state	EVT[MCU]	Extended	
02A1	673	Team 3 is Ready to Transfer	EVT[MCU]	Extended	
02A2	674	Team 3 is in Not Ready state	EVT[MCU]	Extended	
02A3	675	Team 4 is Ready to Transfer	EVT[MCU]	Extended	
02A4	676	Team 4 is in Not Ready state	EVT[MCU]	Extended	
02A5	677	Team 5 is Ready to Transfer	EVT[MCU]	Extended	
02A6	678	Team 5 is in Not Ready state	EVT[MCU]	Extended	
02A7	679	Team 6 is Ready to Transfer	EVT[MCU]	Extended	
02A8	680	Team 6 is in Not Ready state	EVT[MCU]	Extended	
02A9	681	Team 7 is Ready to Transfer	EVT[MCU]	Extended	
02AA	682	Team 7 is in Not Ready state	EVT[MCU]	Extended	
02AB	683	Team 8 is Ready to Transfer	EVT[MCU]	Extended	
02AC	684	Team 8 is in Not Ready state	EVT[MCU]	Extended	
02AD	685	RSH start after switch open	DAT[MCU]	All	Rapid Self Healing is being started after a switch has opened to isolate trouble. Data 1: Team Data1 Type: ushort
02AE	686	RSH failed - downstream team	DAT[MCU]	All	Rapid Self Healing was unable to restore load based on information from a team on the load side of the fault. Data 1: Team Data1 Type: ushort
02AF	687	RSH failed - faulted team	DAT[MCU]	All	Rapid Self Healing was unable to restore load based on the information from the faulted team. Data 1: Team Data1 Type: ushort
02B0	688	RSH monitoring in process	DAT[MCU]	All	Indicates that a coach monitoring task was started to watch the progress of the Rapid Self Healing process. This task will be used to revert back to a standard restoration process if Rapid Self Healing is unable to restore the load. Data 1: Team Data1 Type: ushort
02B1	689	RSH has become active	DAT[MCU]	All	Logged when the coach is requested to make Rapid Self Healing active in that team. Data 1: Team Data1 Type: ushort
02B2	690	RSH has become inactive	DAT[MCU]	All	Logged when the coach is requested to make Rapid Self Healing inactive in that team. Data 1: Team Data1 Type: ushort
02B3	691	RSH is being started by player	DAT[MCU]	All	Logged when the coach has requested the team member to initiate the Rapid Self Healing process. Data1= Team Number, Data2= RSH Team. Data 1:Debug Data Data1 Type: ushort Data 2:Debug Data Data2 Type: ushort Data 3:Debug Data Data3 Type: ushort Data 4:Debug Data Data4 Type: ushort
02B4	692	RSH failed - reported by player	DAT[MCU]	All	If the team member finds that Rapid Self Healing is unable to complete it will log this message. If there are other tie points that may be used for RSH it will try those, indicated by the Try Number. The result code may be one of: (if code location 0 or 2) 1= No Alternate Source, 2= Not Enough Capacity, 3= Switch Trouble, 4= Timer Unavailable, 5= Unable to Register Peer, 6= Comm List Full, 7= Bad Try Number, 8= Bad Netlist, 9= Not RSH Enabled. (if code location 1) 3=Problem while waiting for RSH, 4= Timeout

Definitions of Historic Events

					while waiting for RSH. Data1= Team Number, Data2= Result Code, Data3= Try Number, Data4= Code Location.
					Data 1:Debug Data Data1 Type: ushort Data 2:Debug Data Data2 Type: ushort Data 3:Debug Data Data3 Type: ushort Data 4:Debug Data Data4 Type: ushort
02B5	693	RSH action requested by player	DAT[MCU]	All	The member's initial request to start Rapid Self Healing was successful. Data1= Team Number. Data 1:Debug Data Data1 Type: ushort Data 2:Debug Data Data2 Type: ushort Data 3:Debug Data Data3 Type: ushort Data 4:Debug Data Data4 Type: ushort
02B6	694	RSH action successful	DAT[MCU]	All	The team member has received an indication that Rapid Self Healing has been successful. Success code will be 2. Data1= Team Number, Data2= Success Code. Data 1:Debug Data Data1 Type: ushort Data 2:Debug Data Data2 Type: ushort Data 3:Debug Data Data3 Type: ushort Data 4:Debug Data Data4 Type: ushort
02B7	695	RSH action taking place	DAT[MCU]	All	The team member has initiated a Rapid Self Healing operation and is waiting for a result. Data1= Team Number. Data 1:Debug Data Data1 Type: ushort Data 2:Debug Data Data2 Type: ushort Data 3:Debug Data Data3 Type: ushort Data 4:Debug Data Data4 Type: ushort
02B8	696	RSH init at startup	DAT[MCU]	All	A peer device was unable to be registered with the DNP communication system. The return code can be: 1= Error, 2= Already On List, 3= List Full, 4= Not On List, 5= Not Peer-To-Peer Compatible, 6= Delay Before Retrying. Data1= Return Code, Data2= Peer Address, Data3= Code Location. Data 1:Debug Data Data1 Type: ushort Data 2:Debug Data Data2 Type: ushort Data 3:Debug Data Data3 Type: ushort Data 4:Debug Data Data4 Type: ushort
02B9	697	RSH timer was not available	DAT[MCU]	Normal	Logged during startup if no timer is available for the Rapid Self Healing process. Data 1:Debug Data Data1 Type: ushort Data 2:Debug Data Data2 Type: ushort Data 3:Debug Data Data3 Type: ushort Data 4:Debug Data Data4 Type: ushort
02BA	698	RSH disabled or switch trouble	DAT[MCU]	All	If the switch is in manual mode, or IntelliTEAM event processing has not yet been in the associated teams, this message will be logged and Rapid Self Healing will not be allowed. Data 1:Debug Data Data1 Type: ushort Data 2:Debug Data Data2 Type: ushort Data 3:Debug Data Data3 Type: ushort Data 4:Debug Data Data4 Type: ushort
02BB	699	RSH trouble registering DNP peer	DAT[MCU]	All	A peer device was unable to be registered with the DNP communication system. The return code can be: 1= Error, 2= Already On List, 3= List Full, 4= Not On List, 5= Not Peer-to-Peer Compatible, 6= Delay Before Retrying. Data1= Return Code, Data2= Peer Address, Data3= Code Location. Data 1:Debug Data Data1 Type: ushort Data 2:Debug Data Data2 Type: ushort Data 3:Debug Data Data3 Type: ushort Data 4:Debug Data Data4 Type: ushort
02BC	700	RSH throw back operation	DAT[MCU]	All	This indicates that the tie switch has completed its Rapid Self Healing operation and sending a response message back to the originating switch. The status can be: 6= Success, 7= Unable to Close Switch. Data1= Tie Switch Address, Data2= Originating Switch Address, Data3= RSH Status.

Definitions of Historic Events

					Data 1:Debug Data Data1 Type: ushort Data 2:Debug Data Data2 Type: ushort Data 3:Debug Data Data3 Type: ushort Data 4:Debug Data Data4 Type: ushort
02BD	701	RSH peer removed after complete	DAT[MCU]	All	The reported switch address has been removed from the DNP peer communications peer association list. Data1= Switch address. Data 1:Debug Data Data1 Type: ushort Data 2:Debug Data Data2 Type: ushort Data 3:Debug Data Data3 Type: ushort Data 4:Debug Data Data4 Type: ushort
02BE	702	RSH trouble starting operation	DAT[MCU]	All	Rapid Self Healing was unable to begin due to one of the following reasons: 1= No Alternate Source, 2= Not Enough Capacity, 3= Switch Trouble, 4= Timer Unavailable, 5= Unable to Register Peer, 6= Comm List Full, 7= Bad Try Number, 8= Bad Netlist, 9= Not RSH Enabled. Data1= Trouble Code. Data 1:Debug Data Data1 Type: ushort Data 2:Debug Data Data2 Type: ushort Data 3:Debug Data Data3 Type: ushort Data 4:Debug Data Data4 Type: ushort
02BF	703	RSH initiated	DAT[MCU]	All	Logged at the originating team member when Rapid Self Healing has been initiated successfully. The message sent to the tie point includes the number of teams that will be restored, and the amount of load that will be restored, if the RSH action is executed at the tie switch. A response is then expected to find out whether the tie switch was able to close. Data1= Tie Switch Address, Data2= Tie Switch Position, Data3= Number of Teams, Data4= Load to Restore. Data 1:Debug Data Data1 Type: ushort Data 2:Debug Data Data2 Type: ushort Data 3:Debug Data Data3 Type: ushort Data 4:Debug Data Data4 Type: ushort
02C0	704	RSH switch operation trouble	DAT[MCU]	All	Logged if the tie switch location is unable to close the switch. The specific reason for this trouble is related to the code location: 1= Rapid Self Healing Inactive, 2= Request Team Invalid, 3+4= RSH Disabled on Team, 5+6= Team Errors Present, 7= Switch Is Not Open, 8= Voltage State Issue, 9= Team Is Faulted, 10= Too Many Teams to Restore, 11+12= Not Enough Capacity, 13= Coach Task List Full, 14= Grant Team Invalid. Contact S&C for further definitions of Data1, Data2, and Data3. Data4= Code Location. Data 1:Debug Data Data1 Type: ushort Data 2:Debug Data Data2 Type: ushort Data 3:Debug Data Data3 Type: ushort Data 4:Debug Data Data4 Type: ushort
02C1	705	RSH switch op final status	DAT[MCU]	Normal	Indicates the status of operating a switch based on Rapid Self Healing. Switch operation status includes: 1= Good Operation, 2= Bad Operation, 3= Operation Timed Out. The RSH process status can be: 4= Timeout, 6= Good Status, 7= Bad Status. Data1= Switch Operation Status, Data2= RSH Process Status, Data4= Code Location. Data 1:Debug Data Data1 Type: ushort Data 2:Debug Data Data2 Type: ushort Data 3:Debug Data Data3 Type: ushort Data 4:Debug Data Data4 Type: ushort
02C2	706	RSH rcvd unexpected state change	DAT[MCU]	All	Logged if a Rapid Self Healing message is received that contains a state that conflicts with the present local RSH state. In general, if RSH is idle then a request to close may be accepted, and if a request to close has been transmitted then only a result response message can be accepted. RSH states include: 1= Idce, 2= Waiting, 3= Error, 4= Timeout, 5= Close Switch, 6= Result Response, 7= Remove Peer, 8= Waiting, 9= Responding. Data1= Present RSH State, Data2= Received RSH State, Data3= Present RSH Status.

Definitions of Historic Events

					Data 1:Debug Data Data1 Type: ushort Data 2:Debug Data Data2 Type: ushort Data 3:Debug Data Data3 Type: ushort Data 4:Debug Data Data4 Type: ushort
02C3	707	Netlist initialization trouble	DAT[MCU]	Normal	If a Netlist is unable to be imported into the Team database this message is logged to indicate the reason. Data1= Trouble Code (1= Present states of local switches do not match normal states, 2= IntelliTEAM may be in the process of reconfiguration, 3= Netlist data is invalid, such as no local teams, 4= Presently processing a new netlist, 5= Device is not configured with an RTU address). Data 1:Debug Data Data1 Type: ushort Data 2:Debug Data Data2 Type: ushort Data 3:Debug Data Data3 Type: ushort Data 4:Debug Data Data4 Type: ushort
02C4	708	Netlist accepted by IntelliTEAM	DAT[MCU]	Normal	Indicates that a Netlist was successfully imported into the Team Database. The count of the number of teams included is also reported. Data1= Team Count. Data 1:Debug Data Data1 Type: ushort Data 2:Debug Data Data2 Type: ushort Data 3:Debug Data Data3 Type: ushort Data 4:Debug Data Data4 Type: ushort
02C5	709	Netlist rejected by IntelliTEAM	DAT[MCU]	Normal	During import into the team database the Netlist was rejected either due to this device not being included in the Netlist, or trouble with the data while unpacking the Netlist. Data 1:Debug Data Data1 Type: ushort Data 2:Debug Data Data2 Type: ushort Data 3:Debug Data Data3 Type: ushort Data 4:Debug Data Data4 Type: ushort
02C6	710	RSH alt source search result	DAT[MCU]	Extended	Logged when the Rapid Self Healing process searches for alternate sources during a reconfiguration process. The number of possible alternate sources Found is reported, along with the number Available for restoration after checking each alternate source for available capacity. Data1= Found, Data2= Available. Data 1:Debug Data Data1 Type: ushort Data 2:Debug Data Data2 Type: ushort Data 3:Debug Data Data3 Type: ushort Data 4:Debug Data Data4 Type: ushort
02C7	711	Loading Agent Timer Unavailable	DAT[MCU]	Normal	Data 1:Debug Data Data1 Type: ushort Data 2:Debug Data Data2 Type: ushort Data 3:Debug Data Data3 Type: ushort Data 4:Debug Data Data4 Type: ushort
02C8	712	Load Shedding Initiated	DAT[MCU]	Normal	Data 1:Debug Data Data1 Type: ushort Data 2:Debug Data Data2 Type: ushort Data 3:Debug Data Data3 Type: ushort Data 4:Debug Data Data4 Type: ushort
02C9	713	Trouble Starting Load Shedding Operation	DAT[MCU]	Normal	A new coach has been generated at a team member of the specified team. This can occur during power-up, if existing coach is lost due to communication failure, or existing coach data is inconsistent. Data1= Team. Data 1:Debug Data Data1 Type: ushort Data 2:Debug Data Data2 Type: ushort Data 3:Debug Data Data3 Type: ushort Data 4:Debug Data Data4 Type: ushort
02CA	714	Recv Shd Rqst While in Process	DAT[MCU]	Extended	Indicates that a request to shed load was received while a previous request is in process. Data1= State (1= Start, 2= Return Response, 3= Cleanup, 4= Remove Peer, 5= Back to Normal, 65535= Idle), Data2= Target. Data 1:Debug Data Data1 Type: ushort

Definitions of Historic Events

					Data 2:Debug Data Data2 Type: ushort Data 3:Debug Data Data3 Type: ushort Data 4:Debug Data Data4 Type: ushort
02CB	715	Trouble During Shed Operation	DAT[MCU]	Extended	<p>Indication of trouble during shed operations is dependent on the Code Location. Code Location 1 indicates the target switch is not presently closed (Data1 indicates switch state). Code Location 2 indicates associated team numbers are inconsistent (Data1 and Data2 are actual team numbers, Data3 is the requested team number). Code Location 3 indicates that team errors may be present (Data1 and Data2 are associated team numbers). Code Location 6 indicates that the priority of the load to be shed is too high to shed (Data1 shows the configured load priority). Code Location 7 indicates that there was trouble returning a load shed response message (Data1 is the destination address). Data1, Data2, and Data3 see above. Data4= Code Location.</p> <p>Data 1:Debug Data Data1 Type: ushort Data 2:Debug Data Data2 Type: ushort Data 3:Debug Data Data3 Type: ushort Data 4:Debug Data Data4 Type: ushort</p>
02CC	716	Load Agent Throwback Operation	DAT[MCU]	All	<p>A load shed response message was sent back to the requesting device. The destination address is included. Data1= Destination.</p> <p>Data 1:Debug Data Data1 Type: ushort Data 2:Debug Data Data2 Type: ushort Data 3:Debug Data Data3 Type: ushort Data 4:Debug Data Data4 Type: ushort</p>
02CD	717	Load Agent Trouble Adding DNP Peer	DAT[MCU]	Extended	<p>This is logged when a destination device for a load shed message is unable to be added (code location 2) or removed (code location 1) from the DNP peer list Data1= Return Code (1= Error, 2= Already on list, 3= list full, 4= not on list) Data2= Destination, Data4= Code Location.</p> <p>Data 1:Debug Data Data1 Type: ushort Data 2:Debug Data Data2 Type: ushort Data 3:Debug Data Data3 Type: ushort Data 4:Debug Data Data4 Type: ushort</p>
02CE	718	Load agent removed DNP peer	DAT[MCU]	All	<p>A destination peer device was successfully removed from the DNP peer list after a load shed operation was completed. This prevents the peer list from filling up over time. Data1= Destination.</p> <p>Data 1:Debug Data Data1 Type: ushort Data 2:Debug Data Data2 Type: ushort Data 3:Debug Data Data3 Type: ushort Data 4:Debug Data Data4 Type: ushort</p>
02CF	719	Load agent remove restrictions	DAT[MCU]	Extended	<p>Indicates that a switch that was used to shed load can again be used as a source for that load. The restriction from closing has been removed.</p> <p>Data 1:Debug Data Data1 Type: ushort Data 2:Debug Data Data2 Type: ushort Data 3:Debug Data Data3 Type: ushort Data 4:Debug Data Data4 Type: ushort</p>
02D0	720	Load Shedding Switch Mode Status	DAT[MCU]	All	<p>This is logged to show whether the Switch Mode status indicates that the team member is being blocked from operations due to a load shed operation. Data1= Team Number, Data2= Member Number, Data3= State (1= Transition to On, 2= Transition to Off).</p> <p>Data 1:Debug Data Data1 Type: ushort Data 2:Debug Data Data2 Type: ushort Data 3:Debug Data Data3 Type: ushort Data 4:Debug Data Data4 Type: ushort</p>
02D1	721	Overload monitoring started	DAT[MCU]	Normal	<p>Indicates beginning of load monitoring for the substation associated with this control since it is supplying sections that it normally does not supply. Data1= Source List Index in Net View.</p> <p>Data 1:Debug Data Data1 Type: ushort Data 2:Debug Data Data2 Type: ushort</p>

Definitions of Historic Events

					Data 3:Debug Data Data3 Type: ushort Data 4:Debug Data Data4 Type: ushort
02D2	722	Overload monitoring stopped	DAT[MCU]	Normal	Indicates that load monitoring is no longer required for this source, since it is no longer carrying non-normal sections. Data1= Source List Index in Net View, Data2= Source Capacity, Data3= Present Load. Data 1:Debug Data Data1 Type: ushort Data 2:Debug Data Data2 Type: ushort Data 3:Debug Data Data3 Type: ushort Data 4:Debug Data Data4 Type: ushort
02D3	723	Qualified Overload is present	DAT[MCU]	All	Indicates that an overload condition has been present for the specified length of time - this is the declaration we are not seeing a momentary transient. Data1= Source List Index in Netview, Data2= Source Capacity, Data3= Present Load. Data 1:Debug Data Data1 Type: ushort Data 2:Debug Data Data2 Type: ushort Data 3:Debug Data Data3 Type: ushort Data 4:Debug Data Data4 Type: ushort
02D4	724	Overload Alarm Active	DAT[MCU]	Normal	Alarm is active once an overload has been declared. Data 1:Debug Data Data1 Type: ushort Data 2:Debug Data Data2 Type: ushort Data 3:Debug Data Data3 Type: ushort Data 4:Debug Data Data4 Type: ushort
02D5	725	Overload Alarm Removed	DAT[MCU]	Normal	Overload condition has cleared and/or the source is no longer carrying extra sections. Data 1:Debug Data Data1 Type: ushort Data 2:Debug Data Data2 Type: ushort Data 3:Debug Data Data3 Type: ushort Data 4:Debug Data Data4 Type: ushort
02D6	726	Load shed sequence started	DAT[MCU]	Extended	Indicates that the time on alarm state limit has passed, and an attempt will be made for a section to be transferred or shed to attempt to alleviate the condition. Data1= Source List Index in Net View, Data2= Source Capacity, Data3= Present Load. Data 1:Debug Data Data1 Type: ushort Data 2:Debug Data Data2 Type: ushort Data 3:Debug Data Data3 Type: ushort Data 4:Debug Data Data4 Type: ushort
02D7	727	Load shed request sent	DAT[MCU]	All	Shed request was sent to the specified RTU address. Data1= Destination Switch RTU, Data2= Destination Switch Team Number, Data3= Load Request. Data 1:Debug Data Data1 Type: ushort Data 2:Debug Data Data2 Type: ushort Data 3:Debug Data Data3 Type: ushort Data 4:Debug Data Data4 Type: ushort
02D8	728	Load shed request not sent	DAT[MCU]	All	Problem with communications prevented sending a shed request to the specified RTU address. Data1= Destination Switch RTU, Data2= Destination Switch Team Number, Data3= Load Request. Data 1:Debug Data Data1 Type: ushort Data 2:Debug Data Data2 Type: ushort Data 3:Debug Data Data3 Type: ushort Data 4:Debug Data Data4 Type: ushort
02D9	729	Load shed request accepted	DAT[MCU]	All	Target RTU address device accepted the request and will act on it. Data 1:Debug Data Data1 Type: ushort Data 2:Debug Data Data2 Type: ushort Data 3:Debug Data Data3 Type: ushort Data 4:Debug Data Data4 Type: ushort
02DA	730	Load shed request rejected	DAT[MCU]	All	Target RTU address device rejected the request and will not act on it. Data 1:Debug Data Data1 Type: ushort

Definitions of Historic Events

					Data 2:Debug Data Data2 Type: ushort Data 3:Debug Data Data3 Type: ushort Data 4:Debug Data Data4 Type: ushort
02DB	731	Add to shed reject list	DAT[MCU]	All	<p>Target RTU address will not be asked again during this overload occurrence. Data1= Destination RTU address Data2= Quantity in list.</p> <p>Data 1:Debug Data Data1 Type: ushort Data 2:Debug Data Data2 Type: ushort Data 3:Debug Data Data3 Type: ushort Data 4:Debug Data Data4 Type: ushort</p>
02DC	732	Calculated alt source capacity	DAT[MCU]	All	<p>This message indicates the resources that are available on an alternate feeder as calculated during the RSH process. Data1= Return Code (0= Nodata, 1= Netlist update occurring, 2= Netlist good), Data2= Capacity, Data3= Segment Count, Data4= Netlist Team ID.</p> <p>Data 1:Debug Data Data1 Type: ushort Data 2:Debug Data Data2 Type: ushort Data 3:Debug Data Data3 Type: ushort Data 4:Debug Data Data4 Type: ushort</p>
02DD	733	Close Fail - Pulsing In-Op	DAT[MCU]	All	<p>Data 1:Debug Data Data1 Type: ushort Data 2:Debug Data Data2 Type: ushort Data 3:Debug Data Data3 Type: ushort Data 4:Debug Data Data4 Type: ushort</p>
02DE	734	Switch Open Request	DAT[MCU]	Normal	<p>Target RTU address will not be asked again during this overload occurrence.</p> <p>Data 1: Team Number Data1 Type: Team Data 2:Player Task ID Data2 Type: ushort Data 3: Switch Position Number Data3 Type: SwitchPosition Data 4:Debug Data Data4 Type: ushort</p>
02E0	736	Team Dropped for Load Shed	DAT[MCU]	Normal	<p>The team has been deenergized to reduce substation loading and will not be restored until the circuit is back to normal.</p> <p>Data 1:Debug Data Data1 Type: Team Data 2:Debug Data Data2 Type: ushort Data 3:Debug Data Data3 Type: ushort Data 4:Debug Data Data4 Type: ushort</p>
02E1	737	PR due to Load Shed Active	DAT[MCU]	Normal	<p>Prohibit Restoration is active to prevent shed load from being restored from an alternate source.</p> <p>Data 1:Debug Data Data1 Type: Team Data 2:Debug Data Data2 Type: ushort Data 3:Debug Data Data3 Type: ushort Data 4:Debug Data Data4 Type: ushort</p>
02E2	738	PR due to Load Shed InActive	DAT[MCU]	Normal	<p>Prohibit Restoration is inactive to prevent shed load from being restored from an alternate source.</p> <p>Data 1:Debug Data Data1 Type: Team Data 2:Debug Data Data2 Type: ushort Data 3:Debug Data Data3 Type: ushort Data 4:Debug Data Data4 Type: ushort</p>
02E3	739	Switch 1 Open For Phase Isolation ON	DAT[MCU]	Normal	<p>Switch 1 Opened For Phase Isolation Active</p> <p>Data 1: Data1 Type: ushort Data 2: Data2 Type: ushort Data 3: Data3 Type: ushort Data 4: Data4 Type: ushort</p>
02E4	740	Switch 1 Open For Phase Isolation OFF	DAT[MCU]	Normal	<p>Switch 1 Opened For Phase Isolation NOT Active</p> <p>Data 1: Data1 Type: ushort Data 2: Data2 Type: ushort Data 3: Data3 Type: ushort Data 4: Data4 Type: ushort</p>

Definitions of Historic Events

					Switch 2 Opened For Phase Isolation Active
02E5	741	Switch 2 Open For Phase Isolation ON	DAT[MCU]	Normal	Data 1: Data1 Type: ushort Data 2: Data2 Type: ushort Data 3: Data3 Type: ushort Data 4: Data4 Type: ushort
02E6	742	Switch 2 Open For Phase Isolation OFF	DAT[MCU]	Normal	Switch 2 Opened For Phase Isolation NOT Active Data 1: Data1 Type: ushort Data 2: Data2 Type: ushort Data 3: Data3 Type: ushort Data 4: Data4 Type: ushort
02E7	743	Phase Loss Timing Complete	DAT[MCU]	Normal	Phase Loss Timing Complete Data 1: Data1 Type: ushort Data 2: Data2 Type: ushort Data 3: Data3 Type: ushort Data 4: Data4 Type: ushort
02E8	744	Phase Loss Isolation Event Continue	DAT[MCU]	Normal	Phase Loss Isolation Event Continue Data 1: Data1 Type: ushort Data 2: Data2 Type: ushort Data 3: Data3 Type: ushort Data 4: Data4 Type: ushort
02E9	745	Sw1 Auto Manl Op. Clear Timer Started	DAT[MCU]	Normal	Sw1 Auto Manual Operation Clearing Timer Started Data 1: Data1 Type: ushort Data 2: Data2 Type: ushort Data 3: Data3 Type: ushort Data 4: Data4 Type: ushort
02EA	746	Xfer Declined Load Data	DAT[MCU]	Normal	Xfer Declined Load Data Data 1: Data1 Type: ushort Data 2: Data2 Type: ushort Data 3: Data3 Type: ushort Data 4: Data4 Type: ushort
02EB	747	Manual Operation Team Condition On Sw2	DAT[MCU]	Normal	A team entered a non-operational state because an unexpected manual switch operation occurred. Typically the only expected manual switch operation is closing a source switch on a previously faulted team which proves that the fault is gone, and allows RTN process to take place (if RTN is enabled). Data 1: Team Data1 Type: Team Data 2:Debug Data Data2 Type: ushort Data 3:Debug Data Data3 Type: ushort Data 4:Debug Data Data4 Type: ushort
02EC	748	Manual Operation Team Condition OFF Sw2	DAT[MCU]	Normal	The unexpected manual switch operation team condition was cleared. This can only occur as a result of a user request. Data 1: Team Data1 Type: Team Data 2:Debug Data Data2 Type: ushort Data 3:Debug Data Data3 Type: ushort Data 4:Debug Data Data4 Type: ushort
02ED	749	Load Shed Alarm Active	DAT[MCU]	Normal	Alarm is active once a requirement to shed load been declared. Data 1:Debug Data Data1 Type: ushort Data 2:Debug Data Data2 Type: ushort Data 3:Debug Data Data3 Type: ushort Data 4:Debug Data Data4 Type: ushort
02EE	750	Sys Voltage Classification Diff Detected	DAT[MCU]	Normal	Alarm is active once a requirement to shed load been declared. Data 1:Debug Data Data1 Type: SystemVoltage Data 2:Debug Data Data2 Type: SystemVoltage Data 3:Debug Data Data3 Type: MoreThanOneDiffFound Data 4:Debug Data Data4 Type: ushort
02EF	751	Load Shed Alarm Removed	DAT[MCU]	Normal	No longer need to shed load - load is below the limit or back to normal for Feeder Configuration.

Definitions of Historic Events

					Data 1:Debug Data Data1 Type: ushort Data 2:Debug Data Data2 Type: ushort Data 3:Debug Data Data3 Type: ushort Data 4:Debug Data Data4 Type: ushort
02F0	752	Return to Loop Timer Started	DAT[MCU]	Normal	The Return to Loop timer was started by the local team member of the specified team. Data 1: Team Data1 Type: Team Data 2:Debug Data Data2 Type: ushort Data 3:Debug Data Data3 Type: ushort Data 4:Debug Data Data4 Type: ushort
02F1	753	Return to Loop Continue OK	DAT[MCU]	Normal	The internal Return to Loop process for the specified team indicated that Return to Loop may continue to the next step. The process result code is also shown. Data 1: Team Data1 Type: Team Data 2: Code Data2 Type: InternalCode Data 3:Debug Data Data3 Type: ushort Data 4:Debug Data Data4 Type: ushort
02F2	754	Disregard First Overcurrent Enabled	DAT[MCU]	Normal	Disregard First Overcurrent Enabled. Data 1:Debug Data Data1 Type: ushort Data 2:Debug Data Data2 Type: ushort Data 3:Debug Data Data3 Type: ushort Data 4:Debug Data Data4 Type: ushort
02F3	755	Disregard First Overcurrent Disabled	DAT[MCU]	Normal	Disregard First Overcurrent Enabled. Data 1:Debug Data Data1 Type: ushort Data 2:Debug Data Data2 Type: ushort Data 3:Debug Data Data3 Type: ushort Data 4:Debug Data Data4 Type: ushort
02F4	756	OC Indication Requires Clearing	DAT[MCU]	Normal	OC Indication Requires Clearing Data 1:Debug Data Data1 Type: TeamNumber Data 2:Debug Data Data2 Type: SWPos Data 3:Debug Data Data3 Type: TransferState Data 4:Debug Data Data4 Type: ushort
02F5	757	Ignoring First OC is Active	DAT[MCU]	Normal	Ignoring first OC is active Data 1:Debug Data Data1 Type: ushort Data 2:Debug Data Data2 Type: ushort Data 3:Debug Data Data3 Type: ushort Data 4:Debug Data Data4 Type: ushort
02F6	758	Ignoring First OC is Inactive	DAT[MCU]	Normal	Ignoring First OC is Inactive Data 1:Debug Data Data1 Type: ushort Data 2:Debug Data Data2 Type: ushort Data 3:Debug Data Data3 Type: ushort Data 4:Debug Data Data4 Type: ushort
02F7	759	Average Loading Stopped	DAT[MCU]	Normal	Average Loading Stopped Data 1:Debug Data Data1 Type: ushort Data 2:Debug Data Data2 Type: ushort Data 3:Debug Data Data3 Type: ushort Data 4:Debug Data Data4 Type: ushort
02F8	760	Average Loading Restored	DAT[MCU]	Normal	Average Loading Restored Data 1:Debug Data Data1 Type: ushort Data 2:Debug Data Data2 Type: ushort Data 3:Debug Data Data3 Type: ushort Data 4:Debug Data Data4 Type: ushort
02F9	761	Calculated Real Capacity	DAT[MCU]	Normal	Calculated Real Capacity Data 1:Debug Data Data1 Type: ushort Data 2:Debug Data Data2 Type: ushort

Definitions of Historic Events

					Data 3:Debug Data Data3 Type: ushort Data 4:Debug Data Data4 Type: ushort
02FA	762	Not All Teams Xfer Rdy Timer Active	DAT[MCU]	Normal	Not All Teams Xfer Rdy Timer Active Data 1:Debug Data Data1 Type: ushort Data 2:Debug Data Data2 Type: ushort Data 3:Debug Data Data3 Type: ushort Data 4:Debug Data Data4 Type: ushort
02FB	763	Not All Teams Xfer Rdy Timer Cleared	DAT[MCU]	Normal	Not All Teams Xfer Rdy Timer Cleared Data 1:Debug Data Data1 Type: ushort Data 2:Debug Data Data2 Type: ushort Data 3:Debug Data Data3 Type: ushort Data 4:Debug Data Data4 Type: ushort
02FC	764	Start Sending Transfer Trip	DAT[MCU]	Normal	Start Sending Transfer Trip Data 1:Debug Data Data1 Type: ushort Data 2:Debug Data Data2 Type: ushort Data 3:Debug Data Data3 Type: ushort Data 4:Debug Data Data4 Type: ushort
02FD	765	Transfer Trip Sending Rejected by RTL	DAT[MCU]	Normal	Transfer Trip Sending Rejected by RTL Data 1:Debug Data Data1 Type: ushort Data 2:Debug Data Data2 Type: ushort Data 3:Debug Data Data3 Type: ushort Data 4:Debug Data Data4 Type: ushort
02FE	766	Transfer Trip Sent Successfully	DAT[MCU]	Normal	Transfer Trip Sent Successfully Data 1:Debug Data Data1 Type: ushort Data 2:Debug Data Data2 Type: ushort Data 3:Debug Data Data3 Type: ushort Data 4:Debug Data Data4 Type: ushort
02FF	767	Transfer Trip Sent Unsuccessfully	DAT[MCU]	Normal	Transfer Trip Sent Unsuccessfully Data 1:Debug Data Data1 Type: ushort Data 2:Debug Data Data2 Type: ushort Data 3:Debug Data Data3 Type: ushort Data 4:Debug Data Data4 Type: ushort
0300	768	Compact Flash Operational Issue	LOG[MCU]	All	Data 1:Error Code Data1 Type: ushort
0301	769	Logging Overflow (last events)	LOG[MCU]	All	Data 1: Event ID Data1 Type: ushort Data 2: Event ID Data2 Type: ushort Data 3: Event ID Data3 Type: ushort Data 4: Event ID Data4 Type: ushort
0302	770	DNP Irregularity	LOG[MCU]	All	Data 1:Trace Info Data1 Type: ushort Data 2:Error Code Data2 Type: ushort
0305	773	High Volume Event Storage to CF	LOG[MCU]	All	The task that writes the compact flash file has been rescheduled to run immediately because the event log input buffer is full.
0307	775	Invalid Log Request	LOG[MCU]	All	Data 1:Trace Info Data1 Type: ushort
0308	776	Diag. Data Definition Error	LOG[MCU]	Normal	Data 1: Diagnostic Data Type (Alarm or Warning or Error) Data1 Type: LOGDiagType Data 2:On-Event handle Data2 Type: ushort Data 3:Off-Event handle Data3 Type: ushort Data 4:Trace Info Data4 Type: ushort
0309	777	Diag. Data Processing Error	LOG[MCU]	Normal	Data 1: Diagnostic Data Type (Alarm or Warning or Error) Data1 Type: LOGDiagType

Definitions of Historic Events

					Data 2:Debug Data2 Type: ushort Data 3:Debug Data3 Type: ushort Data 4:Trace Info Data4 Type: ushort
030A	778	Alarm Condition is ON	LOG[MCU]	Normal	
030B	779	Alarm Condition is OFF	LOG[MCU]	Normal	
030C	780	Warning Condition is ON	LOG[MCU]	Normal	
030D	781	Warning Condition is OFF	LOG[MCU]	Normal	
030E	782	Error Condition is On	LOG[MCU]	Normal	
030F	783	Error Condition is Off	LOG[MCU]	Normal	
0310	784	Next Averaging Period	LOG[MCU]	All	Data 1:Period Number Data1 Type: ushort
0311	785	Averaging Data CF Write	LOG[MCU]	All	Data 1:File Cycle Number Data1 Type: ushort
0312	786	Next Daily High/Low Period	LOG[MCU]	All	Data 1:Period Number Data1 Type: ushort
0313	787	Daily High/Low CF Write	LOG[MCU]	All	Data 1:File Cycle Number Data1 Type: ushort
0314	788	Shutdown Processing LOG	LOG[MCU]	Normal	Data 1:Trace Info Data1 Type: ushort
0315	789	Communication Processor Startup	EVT[MCU]	Normal	
0316	790	Spec. Evt Counters Cleared	LOG[MCU]	Normal	
0317	791	Status Counters Cleared	LOG[MCU]	Normal	
0318	792	Log Flooding Condition ON	LOG[MCU]	Normal	Data 1:event ID Data1 Type: ushort
0319	793	Log Flooding Condition OFF	LOG[MCU]	Normal	
0320	800	CF Query Action	LOG[MCU]	All	Data 1: Data1 Type: ushort Data 2: Data2 Type: ushort Data 3: Data3 Type: ushort Data 4: Data4 Type: ushort
0321	801	CF Query Received	LOG[MCU]	All	Data 1: Client-generated query code Data1 Type: ushort
0322	802	CF Query Frame Furnished	LOG[MCU]	All	Data 1: Next Frame Sequence Number Data1 Type: ushort Data 2: Position in CF read buffer Data2 Type: ushort Data 3: Number of events in this frame Data3 Type: ushort
0333	819	CF Query New Frame Rqst	LOG[MCU]	All	Data 1: Frame Sequence Number Data1 Type: ushort
0334	820	CF Query: Last Frame Furnished	LOG[MCU]	All	Data 1: Next Frame Sequence Number Data1 Type: ushort Data 2: Position in CF read buffer Data2 Type: ushort Data 3: Number of events in this frame Data3 Type: ushort
0335	821	CF Query Abort Request	LOG[MCU]	All	Data 1: Frame Sequence Number Data1 Type: ushort
0336	822	CF Query Has Timed Out	LOG[MCU]	All	
0337	823	CF Query Disk Issue	LOG[MCU]	All	Data 1: Issue Code Data1 Type: ushort Data 2: Data2 Type: ushort
0338	824	Double Status Counters Cleared	LOG[MCU]	All	

Definitions of Historic Events

0339	825	Double Stat Reg Point Not Found	LOG[MCU]	All	Data 1: Data1 Type: PointType
0340	832	Double Stat Reg Could Not Add Point Rec	LOG[MCU]	All	Data 1: Data1 Type: RegType
0401	1025	AC Power Present - ON	BAT[MCU]	All	Data 1:Temperature Data1 Type: short Data 2:Battery Voltage Data2 Type: ushort Data 3:Impedance Data3 Type: ushort Data 4:Surface Voltage Data4 Type: ushort
0402	1026	AC Power Present - OFF	BAT[MCU]	Normal	Data 1:Temperature Data1 Type: short Data 2:Battery Voltage Data2 Type: ushort Data 3:Impedance Data3 Type: ushort Data 4:Surface Voltage Data4 Type: ushort
0403	1027	Battery Temperature Problem	BAT[MCU]	Normal	Data 1:Temperature Data1 Type: short Data 2:Battery Voltage Data2 Type: ushort Data 3:Impedance Data3 Type: ushort Data 4:Surface Voltage Data4 Type: ushort
0404	1028	Battery Temperature Normal	BAT[MCU]	Normal	Data 1:Temperature Data1 Type: short Data 2:Battery Voltage Data2 Type: ushort Data 3:Impedance Data3 Type: ushort Data 4:Surface Voltage Data4 Type: ushort
0405	1029	Battery Voltage Low	BAT[MCU]	Normal	Data 1:Temperature Data1 Type: short Data 2:Battery Voltage Data2 Type: ushort Data 3:Impedance Data3 Type: ushort Data 4:Surface Voltage Data4 Type: ushort
0406	1030	Battery Voltage Normal	BAT[MCU]	Normal	Data 1:Temperature Data1 Type: short Data 2:Battery Voltage Data2 Type: ushort Data 3:Impedance Data3 Type: ushort Data 4:Surface Voltage Data4 Type: ushort
0407	1031	Battery Needs to Be Replaced	BAT[MCU]	Normal	Data 1:Temperature Data1 Type: short Data 2:Battery Voltage Data2 Type: ushort Data 3:Impedance Data3 Type: ushort Data 4:Surface Voltage Data4 Type: ushort
0408	1032	Battery OK	BAT[MCU]	Normal	Data 1:Temperature Data1 Type: short Data 2:Battery Voltage Data2 Type: ushort Data 3:Impedance Data3 Type: ushort Data 4:Surface Voltage Data4 Type: ushort
0409	1033	Battery Charger Normal	BAT[MCU]	Normal	Data 1:Temperature Data1 Type: short Data 2:Battery Voltage Data2 Type: ushort Data 3:Impedance Data3 Type: ushort Data 4:Surface Voltage Data4 Type: ushort
040A	1034	Battery Charger Overvoltage	BAT[MCU]	Normal	Data 1:Temperature Data1 Type: short Data 2:Battery Voltage Data2 Type: ushort Data 3:Impedance Data3 Type: ushort Data 4:Surface Voltage Data4 Type: ushort

Definitions of Historic Events

040B	1035	Battery Impedance Normal	BAT[MCU]	Normal	Data 1:Temperature Data1 Type: short Data 2:Battery Voltage Data2 Type: ushort Data 3:Impedance Data3 Type: ushort Data 4:Surface Voltage Data4 Type: ushort
040C	1036	Battery Impedance Low	BAT[MCU]	Normal	Data 1:Temperature Data1 Type: short Data 2:Battery Voltage Data2 Type: ushort Data 3:Impedance Data3 Type: ushort Data 4:Surface Voltage Data4 Type: ushort
040D	1037	Start Battery Test	BAT[MCU]	Normal	Data 1:Temperature Data1 Type: short Data 2:Battery Voltage Data2 Type: ushort Data 3:Impedance Data3 Type: ushort Data 4:Surface Voltage Data4 Type: ushort
040E	1038	Battery Test Finished	BAT[MCU]	Normal	Data 1:Temperature Data1 Type: short Data 2:Battery Voltage Data2 Type: ushort Data 3:Impedance Data3 Type: ushort Data 4:Surface Voltage Data4 Type: ushort
040F	1039	Hardware Fault Occured	BAT[MCU]	Normal	Data 1:Temperature Data1 Type: short Data 2:Battery Voltage Data2 Type: ushort Data 3:Impedance Data3 Type: ushort Data 4:Surface Voltage Data4 Type: ushort
0410	1040	Hardware Fault Resolved	BAT[MCU]	Normal	Data 1:Temperature Data1 Type: short Data 2:Battery Voltage Data2 Type: ushort Data 3:Impedance Data3 Type: ushort Data 4:Surface Voltage Data4 Type: ushort
0411	1041	Power Up	BAT[MCU]	Normal	Data 1:Output IO Data1 Type: ushort
0412	1042	Power Up Clear	BAT[MCU]	Normal	Data 1:Output IO Data1 Type: ushort
0413	1043	Battery Disconnected	BAT[MCU]	Normal	
0414	1044	Battery Connected	BAT[MCU]	Normal	
041B	1051	Set Charger On	BAT[MCU]	All	Set Charger On.
041C	1052	Set Charger Off	BAT[MCU]	All	Set Charger Off.
041D	1053	Set Small Load Test On	BAT[MCU]	All	Set Small Load Test On. Data 1:Temperature Data1 Type: short Data 2:Battery Voltage Data2 Type: ushort Data 3:Impedance Data3 Type: ushort Data 4:Surface Voltage Data4 Type: ushort
041E	1054	Set Small Load Test Off	BAT[MCU]	All	Set Small Load Test Off. Data 1:Temperature Data1 Type: short Data 2:Battery Voltage Data2 Type: ushort Data 3:Impedance Data3 Type: ushort Data 4:Surface Voltage Data4 Type: ushort
041F	1055	Set Big Load Test On	BAT[MCU]	All	Set Big Load Test On. Data 1:Temperature Data1 Type: short Data 2:Battery Voltage Data2 Type: ushort Data 3:Impedance Data3 Type: ushort Data 4:Surface Voltage Data4 Type: ushort
0420	1056	Set Big Load Test Off	BAT[MCU]	All	Set Big Load Test Off.

Definitions of Historic Events

					Data 1:Temperature Data1 Type: short Data 2:Battery Voltage Data2 Type: ushort Data 3:Impedance Data3 Type: ushort Data 4:Surface Voltage Data4 Type: ushort
0421	1057	HW Maintenance Required Active	BAT[MCU]	All	HW Maintenance Required Active Data 1:Temperature Data1 Type: short Data 2:Battery Voltage Data2 Type: ushort Data 3:Impedance Data3 Type: ushort Data 4:Surface Voltage Data4 Type: ushort
0422	1058	HW Maintenance Required Cleared	BAT[MCU]	All	HW Maintenance Required Cleared Data 1:Temperature Data1 Type: short Data 2:Battery Voltage Data2 Type: ushort Data 3:Impedance Data3 Type: ushort Data 4:Surface Voltage Data4 Type: ushort
0423	1059	BAT Wrong Voltage Active	BAT[MCU]	All	BAT Wrong Voltage Active Data 1:Wrong Voltage Data1 Type: ushort Data 2:Battery Voltage Data2 Type: ushort
0424	1060	BAT Wrong Voltage Cleared	BAT[MCU]	All	BAT Wrong Voltage Cleared Data 1:Wrong Voltage Data1 Type: ushort Data 2:Battery Voltage Data2 Type: ushort
0425	1061	AC Power Not Present - OFF	BAT[MCU]	All	AC Power Present Data 1:Temperature Data1 Type: short Data 2:Battery Voltage Data2 Type: ushort Data 3:Impedance Data3 Type: ushort Data 4:Surface Voltage Data4 Type: ushort
0426	1062	AC Power Not Present - ON	BAT[MCU]	All	AC Power Not Present Data 1:Temperature Data1 Type: short Data 2:Battery Voltage Data2 Type: ushort Data 3:Impedance Data3 Type: ushort Data 4:Surface Voltage Data4 Type: ushort
0500	1280	User Configuration Backed Up to BMM	SUM[MCU]	Normal	User configurable settings successfully stored to the base memory.
0501	1281	BMM Setting Restoration Unsuccessful	SUM[MCU]	Normal	An issue was encountered restoring user settings from the base memory. The settings were not restored. Data 1:SUM Error Code Data1 Type: ushort Data 2:Called Function Return Data2 Type: ushort Data 3:Step Data3 Type: ushort
0502	1282	User Configuration Restored From BMM	SUM[MCU]	Normal	User configurable settings successfully restored from the base memory.
0503	1283	BMM Backup Configuration Unsuccessful	SUM[MCU]	Normal	An issue was encountered storing user settings to the base memory. The settings were not successfully stored. Data 1:SUM Error Code Data1 Type: ushort Data 2:Called Function Return Data2 Type: ushort Data 3:Step Data3 Type: ushort
0504	1284	User Configuration Backed Up to CF	SUM[MCU]	Normal	User configurable settings successfully stored to a compact flash file.
0505	1285	CF Backup Settings Save Unsuccessful	SUM[MCU]	Normal	An issue was encountered storing user settings to a compact flash file. The settings were not successfully stored. Data 1:SUM Error Code Data1 Type: ushort Data 2:Called Function Return Data2 Type: ushort Data 3:Step Data3 Type: ushort
0506	1286	User Configuration Restored to CF	SUM[MCU]	Normal	User configurable settings successfully restored from the a compact flash file.
0507	1287	CF Restoration Settings Unsuccessful	SUM[MCU]	Normal	An issue was encountered restoring user settings from a compact flash file. The settings were not restored. Data 1:SUM Error Code Data1 Type: ushort

Definitions of Historic Events

					Data 2:Called Function Return Data2 Type: ushort Data 3:Step Data3 Type: ushort
0508	1288	Validate Settings Successful	SUM[MCU]	Normal	The settings are valid.
0509	1289	Settings Validation Unsuccessful	SUM[MCU]	Normal	An issue was encountered during a setting validation attempt. The settings are not valid and cannot be applied. Data 1: Settings Group Data1 Type: ushort Data 2: Instance Data2 Type: ushort Data 3: Error Data3 Type: ushort
050A	1290	Applied Settings Successfully	EVT[MCU]	Normal	The settings were applied and are active in the control.
050B	1291	Settings Application Unsuccessful	EVT[MCU]	Normal	An issue was encountered while trying to apply settings to the control. All settings were not successfully applied. This most commonly occurs when settings are transferred from the MCU to the DSP. Data 1:Error Code Data1 Type: ushort
050C	1292	Refresh Settings Buffer Successfully	SUM[MCU]	Normal	The settings buffer has been refreshed with the active settings.
050D	1293	Refresh Settings Buffer Issue	SUM[MCU]	Normal	An issue was encountered while attempting to refresh the settings buffer. Values on the settings screens may not accurately reflect the active settings in the control. Data 1:Error Code Data1 Type: ushort
050E	1294	Register Settings Block Issue	SUM[MCU]	Normal	An issue was encountered during application initialization that prevented a group of settings from being successfully registered with the setup manager. Data 1:Error Code Data1 Type: ushort
050F	1295	Register Callback Issue	SUM[MCU]	Normal	An issue was encountered during application initialization that prevented settings related functions from a subsystem from being successfully registered with the setup manager. Data 1:Error Code Data1 Type: ushort
0510	1296	Register DNP Special Function Warning	SUM[MCU]	Normal	An issue was encountered during application initialization that will prevent the functionality of one or more DNP commands. Data 1:DNP Error Code Data1 Type: ushort Data 2:Instance Data2 Type: ushort
0511	1297	Register Non-Settings Block Issue	SUM[MCU]	Normal	An issue was encountered during application initialization that prevented a group of non-settings from being successfully registered with the setup manager for access rights checking. Data 1:Error Code Data1 Type: ushort
0512	1298	User Login Access Denied	SUM[MCU]	Normal	Access to Login was denied. Data 1: Access Denied Reason Data1 Type: ushort
0513	1299	User Logout Access Denied	SUM[MCU]	Normal	Access to Logout was denied. Data 1: Access Denied Reason Data1 Type: ushort
0514	1300	BMM Not Ready	SUM[MCU]	Normal	The base memory module cannot be accessed. Data 1:BMM State Data1 Type: ushort
0515	1301	User Session Started	EVT[MCU]	Normal	A user session was started. Data 1: User Id Data1 Type: ushort Data 2: Port Number Data2 Type: PortCode
0516	1302	User Session Ended	EVT[MCU]	Normal	A user session was terminated. Data 1: User Id Data1 Type: ushort Data 2: Session Ended Reason Data2 Type: SUMSessionEndReason Data 3: Port Number Data3 Type: PortCode
0517	1303	User Access Denied	SUM[MCU]	Normal	Access to write a VM location was denied. Data 1: Access Denied Reason Data1 Type: ushort Data 2:Optional Data Depending on Reason Data2 Type: ushort

Definitions of Historic Events

0518	1304	Register Command to Block Issue	SUM[MCU]	Normal	An issue was encountered during application initialization that prevented a command from being successfully registered with the setup manager to block based on source (IntelliLink WiFi or IntelliLink Remote). Data 1:Error Code Data1 Type: ushort
0519	1305	Request BMM Backup Received	SUM[MCU]	Normal	The Setup Manager received a request from another subsystem to do a backup to base memory.
0520	1312	Apply Settings Started	SUM[MCU]	Normal	Apply of user configurable settings has started.
0521	1313	Password Setting Changed	SUM[MCU]	Normal	A user group password settings change was applied. Data 1: GroupId Data1 Type: ushort
0522	1314	IntelliLink Intrusion On	SUM[MCU]	Normal	User attempted three unsuccessful logons.
0523	1315	IntelliLink Intrusion Off	SUM[MCU]	Normal	Alarm re user attempting three unsuccessful logons was cleared
0524	1316	IntelliLink Intrusion Attempt	SUM[MCU]	Normal	User attempted unsuccessful logon
0708	1800	WFC Transfer to CF Successful	EVT[MCU]	Normal	Data 1: Data1 Type: CycleNumber Data 2: Data2 Type: SecondaryEvent Data 3: Data3 Type: NumberFrames
0800	2048	DNP Initialization Complete	DNP[MCU]	Normal	Displayed when initialization of DNP processes has completed without error. Data 1:Debug Data Data1 Type: ushort Data 2:Debug Data Data2 Type: ushort Data 3:Debug Data Data3 Type: ushort Data 4:Debug Data Data4 Type: ushort
0801	2049	Route Table Initialization Error	DNP[MCU]	Normal	The routing table was unable to be initialized, preventing initialization of DNP processes from being completed. Data 1:Debug Data Data1 Type: ushort Data 2:Debug Data Data2 Type: ushort Data 3:Debug Data Data3 Type: ushort Data 4:Debug Data Data4 Type: ushort
0802	2050	Point Map Initialization Error	DNP[MCU]	Normal	The point mapping table was unable to be initialized, preventing initialization of DNP processes from being completed. Data 1:Debug Data Data1 Type: ushort Data 2:Debug Data Data2 Type: ushort Data 3:Debug Data Data3 Type: ushort Data 4:Debug Data Data4 Type: ushort
0803	2051	Error in Configuration Data	DNP[MCU]	Normal	A configuration setup parameter was found to be set incorrectly or out of range. Data 1: Setup Value Data1 Type: ushort Data 2: Min Value Data2 Type: ushort Data 3: Max Value Data3 Type: ushort Data 4:Debug Data Data4 Type: ushort
0804	2052	Old Configuration Remains in Effect	DNP[MCU]	Normal	Indicates that due to an error in configuration data the existing setup will continue to be used by the application. Data 1:Debug Data Data1 Type: ushort Data 2:Debug Data Data2 Type: ushort Data 3:Debug Data Data3 Type: ushort Data 4:Debug Data Data4 Type: ushort
0805	2053	Configuration Change Accepted	DNP[MCU]	Normal	Changes to the communications setup parameters were validated and have been made active within the application. Data 1:Debug Data Data1 Type: ushort Data 2:Debug Data Data2 Type: ushort Data 3:Debug Data Data3 Type: ushort Data 4:Debug Data Data4 Type: ushort
0806	2054	Master Record Not Added	DNP[MCU]	Normal	The master record was unable to be added to the peer device list due to either an incorrect parameter or the peer device list is full. Data 1: Master Record Add Error Data1 Type:

Definitions of Historic Events

					MasterRecAddError Data 2: Code Location Data2 Type: ushort Data 3:Master Number Data3 Type: ushort Data 4:Debug Data Data4 Type: ushort
0807	2055	Map Change Callback Init Error	DNP[MCU]	Normal	A DNP point map change callback function was unable to be registered due to a full callback list. This prevented initialization of DNP processes from being completed. Data 1:Debug Data Data1 Type: ushort Data 2:Debug Data Data2 Type: ushort Data 3:Debug Data Data3 Type: ushort Data 4:Debug Data Data4 Type: ushort
0808	2056	Incorrect Frame Length	DNP[MCU]	Extended	The actual length of the received DNP frame does not match the length indicated in the DNP data link header. The frame is discarded. Data 1: Actual Length Data1 Type: ushort Data 2: Indicated Length Data2 Type: ushort Data 3:Debug Data Data3 Type: ushort Data 4: Code Location Data4 Type: ushort
0809	2057	Serial Port Reset Error	DNP[MCU]	Normal	An error occurred in reset of a serial port during a communications setpoint configuration change. Changes to serial port configuration may not have taken affect. Data 1: Port Number Data1 Type: PortCode Data 2:Debug Data Data2 Type: ushort Data 3:Debug Data Data3 Type: ushort Data 4:Debug Data Data4 Type: ushort
080A	2058	P2P Receive buffer full	DNP[MCU]	Normal	
080B	2059	P2P Fragment received from transport	DNP[MCU]	All	Data 1: Peer Address Data1 Type: ushort Data 2: Fragment Length Data2 Type: ushort Data 3: Port ID Data3 Type: ushort Data 4: Fragment ID Data4 Type: ushort
080C	2060	Error Registering Special Function	DNP[MCU]	Normal	
080D	2061	P2P Notification received	DNP[MCU]	All	Data 1: Source Address / ID Data1 Type: ushort Data 2: Destination Address /Code Data2 Type: ushort Data 3: Sequence Number / Layer Data3 Type: ushort Data 4: Connection ID/0 Data4 Type: ushort
080E	2062	TCP Port Maintenance	DNP[MCU]	Extended	The actual length of the received DNP frame does not match the length indicated in the DNP data link header. The frame is discarded. Data 1: TCP Port Connect State Data1 Type: TCPPortConnectState Data 2: TCP Port Active State Data2 Type: TCPPortActiveState Data 3: Destination RTU Address Data3 Type: RTUAddress Data 4: Diagnostic Value Data4 Type: ushort
0820	2080	Invalid Transport Segment Length	DNP[MCU]	Extended	The transport segment length of the DNP frame is invalid. The frame was discarded. The valid range is from 3 to 250. Data 1: Segment Length Data1 Type: ushort Data 2:Debug Data Data2 Type: ushort Data 3:Debug Data Data3 Type: ushort Data 4:Debug Data Data4 Type: ushort
0821	2081	Receive Message Buffer Full	DNP[MCU]	Extended	The transport function receive message buffers are full. These buffers hold the frame header information and other message details. The new frame is discarded. Data 1:Debug Data Data1 Type: ushort Data 2:Debug Data Data2 Type: ushort Data 3:Debug Data Data3 Type: ushort Data 4:Debug Data Data4 Type: ushort

0822	2082	Receive Data Buffer Full	DNP[MCU]	Extended	<p>The transport function receive data buffers are full. These buffers hold the data portion of the received DNP frames. The new frame is discarded.</p> <p>Data 1:Debug Data Data1 Type: ushort Data 2:Debug Data Data2 Type: ushort Data 3:Debug Data Data3 Type: ushort Data 4:Debug Data Data4 Type: ushort</p>
0823	2083	Removed Old FIR-Only Message	DNP[MCU]	All	<p>An incomplete fragment was discarded due to a newer message being received from the same source device.</p> <p>Data 1: Transport Header Data1 Type: DNPTTransportHeader Data 2:Debug Data Data2 Type: ushort Data 3: Source Address Data3 Type: RTUAddress Data 4:Debug Data Data4 Type: ushort</p>
0824	2084	App Layer Accepted FIR/FIN Message	DNP[MCU]	All	<p>A single-frame fragment was successfully processed by the application layer and is being removed from the transport function buffers.</p> <p>Data 1: Transport Header Data1 Type: DNPTTransportHeader Data 2: Fragment Length Data2 Type: ushort Data 3: Source Address Data3 Type: RTUAddress Data 4:Debug Data Data4 Type: ushort</p>
0825	2085	App Layer Accepted FIN Only Message	DNP[MCU]	All	<p>A multi-frame fragment was successfully processed by the application layer and is being removed from the transport function buffers.</p> <p>Data 1: Transport Header Data1 Type: DNPTTransportHeader Data 2: Fragment Length Data2 Type: ushort Data 3: Source Address Data3 Type: RTUAddress Data 4:Debug Data Data4 Type: ushort</p>
0826	2086	Frame Addition Unsuccessful	DNP[MCU]	Extended	<p>A newly received frame of a multi-frame fragment was unable to be added to the fragment due to the 2k fragment size restriction. The fragment was discarded.</p> <p>Data 1: Transport Header of Fragment Data1 Type: DNPTTransportHeader Data 2: Transport Header of Frame Data2 Type: DNPTTransportHeader Data 3: Source Address Data3 Type: RTUAddress Data 4:Debug Data Data4 Type: ushort</p>
0827	2087	Fragment Not Found	DNP[MCU]	Extended	<p>A matching fragment was not found in the buffers for a newly received frame of a multi-frame fragment. The frame was discarded.</p> <p>Data 1: Transport Header Data1 Type: DNPTTransportHeader Data 2:Debug Data Data2 Type: ushort Data 3: Source Address Data3 Type: RTUAddress Data 4:Debug Data Data4 Type: ushort</p>
0828	2088	Transp. Layer Transmit Fragment Too Long	DNP[MCU]	Extended	<p>The application layer was requested to send a fragment larger than the 2k size limitation.</p> <p>Data 1: Fragment Length Data1 Type: ushort Data 2:Debug Data Data2 Type: ushort Data 3:Debug Data Data3 Type: ushort Data 4:Debug Data Data4 Type: ushort</p>
0829	2089	Transp. Layer TX Fragment Buffer Full	DNP[MCU]	Extended	<p>No free buffer was found in the transport function transmit buffers. The application layer may save this message and reattempt to transmit.</p> <p>Data 1:Debug Data Data1 Type: ushort Data 2:Debug Data Data2 Type: ushort Data 3:Debug Data Data3 Type: ushort Data 4:Debug Data Data4 Type: ushort</p>
082A	2090	Frame Accepted by Data Link Layer	DNP[MCU]	All	<p>A single frame was successfully handed off to the data link layer for transmit. Note that this may be a single frame of a multi-frame fragment.</p>

Definitions of Historic Events

					Data 1: Source Address Data1 Type: RTUAddress Data 2: Destination Address Data2 Type: RTUAddress Data 3: Transport Header Data3 Type: DNPTTransportHeader Data 4: Frame Length Data4 Type: ushort
082B	2091	Message Timed Out on Receive List	DNP[MCU]	Extended	A fragment was removed from the transport function receive buffer after an extended period of inactivity. Data 1: Transport Header Data1 Type: DNPTTransportHeader Data 2:Debug Data Data2 Type: ushort Data 3: Source Address Data3 Type: RTUAddress Data 4:Debug Data Data4 Type: ushort
082C	2092	Message Timed Out on Transmit List	DNP[MCU]	Extended	A fragment was removed from the transport function transmit buffer after an extended period of inactivity. Data 1: Transport Header Data1 Type: DNPTTransportHeader Data 2:Debug Data Data2 Type: ushort Data 3: Source Address Data3 Type: RTUAddress Data 4:Debug Data Data4 Type: ushort
082D	2093	Removed Deferred Read Request	DNP[MCU]	Extended	A DNP read request that was deferred due to an outstanding unsolicited message was removed due to reception of a newer request. Data 1:Debug Data Data1 Type: ushort Data 2:Debug Data Data2 Type: ushort Data 3:Debug Data Data3 Type: ushort Data 4:Debug Data Data4 Type: ushort
082E	2094	Frame Declined by Datalink	DNP[MCU]	Extended	The datalink layer was unable to accept the request to transmit this frame. The frame transmit will be retried until it is accepted or the message times out on the transmit list. Data 1: Error code returned by OS Data1 Type: ushort Data 2: Destination Address Data2 Type: RTUAddress Data 3: Transport Header Data3 Type: DNPTTransportHeader Data 4: Frame Length Data4 Type: ushort
082F	2095	Port Undefined in Transport	DNP[MCU]	All	Data 1: Destination Address Data1 Type: ushort
0840	2112	Reset Peer Link Sent	DNP[MCU]	Extended	A Reset data link frame was sent to a peer device in an attempt to reinitialize peer-to-peer communications. Data 1: Source Address Data1 Type: RTUAddress Data 2: Destination Address Data2 Type: RTUAddress Data 3:Debug Data Data3 Type: ushort Data 4:Debug Data Data4 Type: ushort
0841	2113	Reset Peer Link Received	DNP[MCU]	Extended	A Reset data link frame was received from the reported peer device. Data 1: Source Address Data1 Type: RTUAddress Data 2: Action Taken 1=record reinit 2=reset seq num only 3=new peer added Data2 Type: DNPDLAction Data 3:Debug Data Data3 Type: ushort Data 4:Debug Data Data4 Type: ushort
0842	2114	Message Taken Off Xmit List - No Peer	DNP[MCU]	Extended	The destination peer device was not found in the peer list, possibly due to a change in configuration. The message was discarded. Data 1: Source Address Data1 Type: RTUAddress Data 2: Destination Address Data2 Type: RTUAddress Data 3: Application Control Data3 Type: DNPApControl Data 4: Function Code Data4 Type: DNPApFunctionCode
0843	2115	Set URBE Timer Error	DNP[MCU]	Extended	An error was detected when attempting to start an internal timer. Data 1:Debug Data Data1 Type: ushort Data 2:Debug Data Data2 Type: ushort Data 3:Debug Data Data3 Type: ushort Data 4:Debug Data Data4 Type: ushort
0844	2116	No URBE Delay Timer	DNP[MCU]	Extended	No free timer was found when attempting to start an internal timer.

					Data 1:Debug Data Data1 Type: ushort Data 2:Debug Data Data2 Type: ushort Data 3:Debug Data Data3 Type: ushort Data 4:Debug Data Data4 Type: ushort
0845	2117	Duplicate Fragment Received	DNP[MCU]	Extended	The application layer detected reception of a duplicate fragment. The previous response will be resent.
0846	2118	App.Layer.Transmi.tFragment.Too.Long	DNP[MCU]	Extended	Data 1: Source Address Data1 Type: RTUAddress Data 2: Destination Address Data2 Type: RTUAddress Data 3: Application Control Data3 Type: DNPAppControl Data 4:Debug Data Data4 Type: ushort
0847	2119	App. Layer TX Fragment Buffer Full	DNP[MCU]	Extended	The application layer was requested to send a fragment larger than the 2k size limitation.
0848	2120	Invalid Fragment Length Received	DNP[MCU]	Extended	No free buffer was found in the application layer transmit list. The fragment may be retried or discarded.
0849	2121	Incorrect Amount of Data Received	DNP[MCU]	Extended	Data 1: Fragment Length Data1 Type: ushort Data 2:Debug Data Data2 Type: ushort Data 3:Debug Data Data3 Type: ushort Data 4:Debug Data Data4 Type: ushort
084A	2122	Fragment Timed Out on Transmit List	DNP[MCU]	Extended	The application layer detected a fragment with an invalid length. The valid range is from 2 to 2048 bytes. The fragment was discarded.
084B	2123	App Layer Accepted Good Fragment	DNP[MCU]	All	Data 1: Source Address Data1 Type: RTUAddress Data 2: Destination Address Data2 Type: RTUAddress Data 3: Application Control Data3 Type: DNPAppControl Data 4: Function Code Data4 Type: DNPAFunctionCode
084C	2124	Peer Device Buffer Full	DNP[MCU]	Extended	The fragment was removed from the application layer transmit list after an extended period of inactivity. This will normally only occur if the transport function and data link layer are unable to service transmit requests.
084D	2125	Peer Device Already on List	DNP[MCU]	Extended	Data 1: Peer RTU Address Data1 Type: RTUAddress Data 2:Debug Data Data2 Type: ushort

Definitions of Historic Events

					Data 3:Debug Data Data3 Type: ushort Data 4:Debug Data Data4 Type: ushort
084E	2126	Peer Device Removed From List	DNP[MCU]	Extended	The peer device was successfully removed from the peer device list. Data 1: Peer RTU Address Data1 Type: RTUAddress Data 2: Code Location Data2 Type: ushort Data 3:Debug Data Data3 Type: ushort Data 4:Debug Data Data4 Type: ushort
084F	2127	Peer Device Added to List	DNP[MCU]	Extended	The peer device was successfully added to the peer device list. Data 1: Peer RTU Address Data1 Type: RTUAddress Data 2: Connection ID Data2 Type: ConnectionID Data 3: Port Code Data3 Type: PortCode Data 4:Master Number Data4 Type: Master
0850	2128	FIR/FIN Not Set	DNP[MCU]	Extended	The application layer found that the FIR and FIN bits of the Application Control byte were not set. The fragment was discarded. Data 1: Source Address Data1 Type: RTUAddress Data 2: Destination Address Data2 Type: RTUAddress Data 3: Application Control Data3 Type: DNPApControl Data 4:Debug Data Data4 Type: ushort
0851	2129	Sequence Number Mismatch	DNP[MCU]	Extended	The application layer found that the sequence number in the Application Control byte was inconsistent with what was expected. The fragment was discarded. Data 1: Source Address Data1 Type: RTUAddress Data 2: Destination Address Data2 Type: RTUAddress Data 3: Application Control Data3 Type: DNPApControl Data 4:Debug Data Data4 Type: ushort
0852	2130	Transient Peer Device Addition Issue	DNP[MCU]	Extended	The source of this fragment was unknown so an attempt was made to add it to the peer device list. The attempt was unsuccessful so the fragment was discarded. Data 1: Source Address Data1 Type: RTUAddress Data 2: Application Control Data2 Type: DNPApControl Data 3:Debug Data Data3 Type: ushort Data 4:Debug Data Data4 Type: ushort
0853	2131	No Peer Record Found During Xmit	DNP[MCU]	Extended	A transmit was attempted to a device that was not found on the peer device list. The transmit was aborted. Data 1: Code Location Data1 Type: ushort Data 2:Debug Data Data2 Type: ushort Data 3:Debug Data Data3 Type: ushort Data 4:Debug Data Data4 Type: ushort
0854	2132	URBE Registration Buffer Full	DNP[MCU]	Extended	The buffer containing callback functions for unsolicited messages was full when attempting to add another function. Data 1:Debug Data Data1 Type: ushort Data 2:Debug Data Data2 Type: ushort Data 3:Debug Data Data3 Type: ushort Data 4:Debug Data Data4 Type: ushort
0855	2133	Peer Device Not on List	DNP[MCU]	Extended	The requested peer device was not found on the peer device list when attempting to remove the device from the list. Data 1: Peer RTU Address Data1 Type: RTUAddress Data 2:Debug Data Data2 Type: ushort Data 3:Debug Data Data3 Type: ushort Data 4:Debug Data Data4 Type: ushort
0856	2134	Initial Unsolicited Message Confirmed	DNP[MCU]	Extended	Indicates that a confirmation message was received for the unsolicited null messages that must be sent on power up. Data 1: Callback Status Data1 Type: CallbackStatus Data 2:RTU Address Data2 Type: RTUAddress Data 3:Debug Data Data3 Type: ushort Data 4:Debug Data Data4 Type: ushort

Definitions of Historic Events

0857	2135	URBE Enabled Via SCADA	DNP[MCU]	Extended	<p>Unsolicited Report by Exception processing was enabled over SCADA.</p> <p>Data 1: Source Address Data1 Type: RTUAddress Data 2: URBE Status Data2 Type: URBEStatus Data 3:Active URBE Class Mask Data3 Type: ActiveURBEClassMask Data 4:Debug Data Data4 Type: ushort</p>	
0858	2136	URBE Disabled Via SCADA	DNP[MCU]	Extended	<p>Unsolicited Report by Exception processing was disabled over SCADA.</p> <p>Data 1: Source Address Data1 Type: RTUAddress Data 2: URBE Status Data2 Type: URBEStatus Data 3:Active URBE Class Mask Data3 Type: ActiveURBEClassMask Data 4:Debug Data Data4 Type: ushort</p>	
0859	2137	Port Code Invalid	DNP[MCU]	Extended	<p>An invalid port code was detected when attempting to add a peer device to the peer device list.</p> <p>Data 1: Peer RTU Address Data1 Type: RTUAddress Data 2: Invalid Port Code value Data2 Type: ushort Data 3:Debug Data Data3 Type: ushort Data 4:Debug Data Data4 Type: ushort</p>	
085A	2138	Cold Restart Requested	EVT[MCU]	Normal	<p>A cold restart of the control has been requested over SCADA, and will be performed in two seconds.</p> <p>Data 1: Source Address Data1 Type: RTUAddress Data 2: Destination Address Data2 Type: RTUAddress Data 3:Debug Data Data3 Type: ushort Data 4:Debug Data Data4 Type: ushort</p>	
085B	2139	Function Code Not Implemented	DNP[MCU]	Extended	<p>The application layer received a message containing a DNP function code that is invalid or is not implemented.</p> <p>Data 1: Source Address Data1 Type: RTUAddress Data 2: Destination Address Data2 Type: RTUAddress Data 3: Function Code Data3 Type: DNPApFunctionCode Data 4:Debug Data Data4 Type: ushort</p>	
085C	2140	Unknown Master Access Restricted	DNP[MCU]	Extended	<p>A device that was previously unknown has requested an action that is restricted to configured master stations. The restricted actions are writes, select/operate and cold restart.</p> <p>Data 1: Source Address Data1 Type: RTUAddress Data 2: Destination Address Data2 Type: RTUAddress Data 3: Function Code Data3 Type: DNPApFunctionCode Data 4:Debug Data Data4 Type: ushort</p>	
085D	2141	Peer Device Modified on List	DNP[MCU]	Extended	<p>The peer device was successfully modified on the peer device list.</p> <p>Data 1: Peer RTU Address Data1 Type: RTUAddress Data 2: Code Location Data2 Type: ushort Data 3:Debug Data Data3 Type: ushort Data 4:Master Number Data4 Type: ushort</p>	
085E	2142	Request time synchronization received	DNP[MCU]	All	<p>A response was received with the need-time IIN set and a time sync is being attempted.</p> <p>Data 1: Status Data1 Type: ushort Data 2: Source Address Data2 Type: RTUAddress Data 3: Destination Address Data3 Type: RTUAddress Data 4:Debug Data Data4 Type: ushort</p>	
085F	2143	P2P Bad transmit fragment length	DNP[MCU]	All	<p>Data 1: Length of Fragment Data1 Type: ushort Data 2:Debug text Data2 Type: ushort Data 3:Debug text Data3 Type: ushort Data 4:Debug text Data4 Type: ushort</p>	
0860	2144	P2P Transmit fragment buffer full	DNP[MCU]	Normal		
0861	2145	P2P No peer device record	DNP[MCU]	All		

Definitions of Historic Events

					Data 1: Destination Address Data1 Type: ushort
0862	2146	P2P Fragment declined by transport	DNP[MCU]	Extended	Data 1: Result Code Data1 Type: ushort Data 2: Destination Address/Code Data2 Type: ushort Data 3: Fragment Length Data3 Type: ushort Data 4: Code Location Data4 Type: ushort
0863	2147	P2P No peer for received fragment	DNP[MCU]	All	Data 1: Peer Address Data1 Type: ushort
0864	2148	P2P Application layer CRC error	DNP[MCU]	All	Data 1: Source Address Data1 Type: ushort Data 2: Local Address Data2 Type: ushort Data 3: Expected Sequence Number Data3 Type: ushort
0865	2149	P2P App layer sequence error	DNP[MCU]	Extended	Data 1: Source Address Data1 Type: ushort Data 2: Connection ID Data2 Type: ushort Data 3: Expected sequence number Data3 Type: ushort Data 4: Received sequence number Data4 Type: ushort
0866	2150	P2P Unknown peer access restricted	DNP[MCU]	Extended	Data 1: Local Peer Addr Data1 Type: ushort Data 2: Source Peer Addr Data2 Type: ushort Data 3: Requested Function Data3 Type: ushort Data 4: Connection ID Data4 Type: ushort
0867	2151	P2P Error block received from peer	DNP[MCU]	Normal	Data 1: Source Addr Data1 Type: ushort Data 2: Connection ID Data2 Type: ushort Data 3: Errant Object Data3 Type: ushort Data 4: Errant Code Data4 Type: ushort
0868	2152	P2P Function code not implemented	DNP[MCU]	All	Data 1: Local Peer Addr Data1 Type: ushort Data 2: Source Peer Addr Data2 Type: ushort Data 3: Requested Function Data3 Type: ushort Data 4: Connection ID Data4 Type: ushort
0869	2153	P2P Peer not P2P compatible	DNP[MCU]	All	Data 1: Destination Address Data1 Type: ushort Data 2: Connection ID Data2 Type: ushort
086A	2154	P2P Protocol not recognized	DNP[MCU]	All	Data 1: Protocol Type Data1 Type: ushort
086B	2155	P2P Error found in response data	DNP[MCU]	Extended	Data 1: Source Address Data1 Type: ushort Data 2: Connection ID Data2 Type: ushort Data 3: Errant Object Data3 Type: ushort Data 4: Errant Code Data4 Type: ushort
086C	2156	Association reset link sent	DNP[MCU]	All	Data 1: Source Addr Data1 Type: ushort Data 2: Destination Addr Data2 Type: ushort Data 3: Port ID Data3 Type: ushort
086D	2157	Association reset link send failed	DNP[MCU]	Extended	Data 1: Source Addr Data1 Type: ushort Data 2: Destination Addr Data2 Type: ushort Data 3: Port ID Data3 Type: ushort
086E	2158	Association reset link ack rcvd	DNP[MCU]	All	Data 1: Peer Addr Data1 Type: ushort Data 2: Connection ID Data2 Type: ushort

086	2159	P2P Association test sent	DNP[MCU]	All	Data 1: Destination Addr Data1 Type: ushort
0870	2160	P2P Association test unsuccessful	DNP[MCU]	Extended	Data 1: Destination Addr Data1 Type: ushort
0871	2161	P2P Association test response rcvd	DNP[MCU]	All	Data 1: Peer Device Address Data1 Type: ushort Data 2: P2P Support Flag Data2 Type: ushort Data 3: MTU Size Data3 Type: ushort
0872	2162	P2P Support query received	DNP[MCU]	All	Data 1: Source Address Data1 Type: ushort
0873	2163	P2P Reset Association frame sent	DNP[MCU]	All	Data 1: Peer Device Address Data1 Type: ushort
0874	2164	Association negotiation incomplete	DNP[MCU]	Extended	Data 1: Destination Address Data1 Type: ushort Data 2: Association State Data2 Type: ushort
0875	2165	P2P Xmt temporarily suspended	DNP[MCU]	All	Data 1: Destination Addr Data1 Type: ushort Data 2: Connection ID Data2 Type: ushort Data 3: Suspend Countdown Timer Value Data3 Type: ushort
0876	2166	P2P App layer fragment xmit	DNP[MCU]	All	Data 1: Transmit Result Code Data1 Type: ushort Data 2: Destination Addr Data2 Type: ushort Data 3: Port ID Data3 Type: ushort Data 4: Fragment Length Data4 Type: ushort
0877	2167	Local/Remote Callback Func. Registered	DNP[MCU]	Normal	
					An attempt by the application to register a special memory read/write function was rejected because the buffer was full.
0880	2176	Special Function Buffer Full	DNP[MCU]	Extended	Data 1:Debug Data Data1 Type: ushort Data 2:Debug Data Data2 Type: ushort Data 3:Debug Data Data3 Type: ushort Data 4:Debug Data Data4 Type: ushort
0881	2177	Special Function Already on List	DNP[MCU]	Extended	An attempt by the application to register a special memory read/write function was rejected because a special function for that memory location already exists in the buffer. Data 1:Debug Data Data1 Type: ushort Data 2:Debug Data Data2 Type: ushort Data 3:Debug Data Data3 Type: ushort Data 4:Debug Data Data4 Type: ushort
0882	2178	Error in Object Parse	DNP[MCU]	Extended	The header or data portion of an object that was returned in a response message was invalid or otherwise unexpected. If possible other objects within the response will still be processed. Data 1: Object Type Data1 Type: DNPObjectType Data 2: Source Address Data2 Type: RTUAddress Data 3: Destination Address Data3 Type: RTUAddress Data 4: Data4 Type: ushort
0883	2179	Object Variation Error	DNP[MCU]	Extended	The variation of the object that was returned in the response message is invalid or unsupported. Data 1: Object Type Data1 Type: DNPObjectType Data 2: Source Address Data2 Type: RTUAddress Data 3: Destination Address Data3 Type: RTUAddress Data 4: Variation Data4 Type: DNPObjectVariation
0884	2180	Object Qualifier Error	DNP[MCU]	Extended	The qualifier code of the object that was returned in the response message is invalid or unsupported.

Definitions of Historic Events

					Data 1: Object Type Data1 Type: DNPObjectType Data 2: Source Address Data2 Type: RTUAddress Data 3: Destination Address Data3 Type: RTUAddress Data 4: Invalid Qualifier/ Index code Data4 Type: ushort
0885	2181	Parsed Data Buffer Full	DNP[MCU]	Extended	The data buffer containing the parsed object data is full. No further parsing of this response message will take place.
0886	2182	Object Header Error	DNP[MCU]	Extended	An error was detected in the object header of the DNP message. Data 1: Source Address Data1 Type: RTUAddress Data 2: Destination Address Data2 Type: RTUAddress Data 3: Object Type Data3 Type: DNPObjectType Data 4: Variation Data4 Type: DNPObjectVariation
0887	2183	Error Assembling Object Header	DNP[MCU]	Extended	An error was detected in the object header during assembly of a response message. The response process was aborted. Data 1: Source Address Data1 Type: RTUAddress Data 2: Destination Address Data2 Type: RTUAddress Data 3: Object Type Data3 Type: DNPObjectType Data 4: Variation Data4 Type: DNPObjectVariation
0888	2184	Invalid Object Range Index	DNP[MCU]	Extended	An error was detected in an object header of the current request message related to the data index values. An attempt will be made to process other objects within the message. Data 1: Source Address Data1 Type: RTUAddress Data 2: First Index or Index Size Data2 Type: ushort Data 3: Last Index or Qualifier Data3 Type: ushort Data 4: Code Location Data4 Type: ushort
0889	2185	Fragment Data Size Error	DNP[MCU]	Extended	The amount of data available in the fragment was not consistent with the expected amount of data. The fragment was discarded. Data 1: Source Address Data1 Type: RTUAddress Data 2: Data Length Data2 Type: ushort Data 3: Data Index Data3 Type: ushort Data 4: Code Location Data4 Type: ushort
088A	2186	Object/Variation Not Supported	DNP[MCU]	Extended	The object being processed does not include a support object and variation combination. An attempt will be made to continue parsing other objects within the message. Data 1: Source Address Data1 Type: RTUAddress Data 2: Object Type Data2 Type: DNPObjectType Data 3: Variation Data3 Type: DNPObjectVariation Data 4: Code Location Data4 Type: ushort
088B	2187	Special Function Registered	DNP[MCU]	Extended	A special function related to a specific memory action and virtual memory address was successfully added to the list. Data 1: Action Data1 Type: VMFunctionCode Data 2: Memory Address Data2 Type: VAddr16 Data 3: Debug Data Data3 Type: VAddr16 Data 4: Debug Data Data4 Type: ushort
088C	2188	Virtual Memory Read or Write Error	DNP[MCU]	Extended	A request to read or write virtual memory addresses was unsuccessful. Data 1: Source Address Data1 Type: RTUAddress Data 2: Memory Address Data2 Type: VAddr16 Data 3: Result Code returned by OS Data3 Type: ushort Data 4: Action Data4 Type: VMAccessAction
088D	2189	SBO Select Timer Unavailable	DNP[MCU]	Extended	An internal timer was not available to perform the select-before-operate timing function. The operation request was aborted. Data 1: Object Type Data1 Type: DNPObjectType Data 2: Debug Data Data2 Type: ushort

Definitions of Historic Events

					Data 3:Debug Data Data3 Type: ushort Data 4:Debug Data Data4 Type: ushort
088E	2190	SBO Select Timer Error	DNP[MCU]	Extended	An error was detected when attempting to initialize a select-before-operate timer. The operation request was aborted. Data 1: Object Type Data1 Type: DNPObjectType Data 2: SBO Timer Value Data2 Type: SBOTimerValue Data 3:Debug Data Data3 Type: ushort Data 4:Debug Data Data4 Type: ushort
088F	2191	Issue With Output Block	DNP[MCU]	All	An operation request was unsuccessful due to an issue in the Control Relay Output Block of the message. See DNP documentation for a complete list of DNP Output Block status codes. Data 1: Object Type Data1 Type: DNPObjectType Data 2: DNP Output Block Status Code Data2 Type: DNPOutputBlockStatusCode Data 3: Point Number Data3 Type: ushort Data 4: Function Code Data4 Type: DNPApFunctionCode
08A0	2208	Control Point Function Registered	DNP[MCU]	Extended	A control point special function was successfully added to the list. This function connects a control operation with functionality elsewhere in the application. Data 1: Point Code Data1 Type: DNPPointCode Data 2: Associated RTU Address Data2 Type: RTUAddress Data 3:Debug Data Data3 Type: ushort Data 4:Debug Data Data4 Type: ushort
08A1	2209	Control Point Code Not Mapped	DNP[MCU]	Extended	A control point special function was not added to the list because the control point is not yet included in the point mapping configuration. Data 1: Point Code Data1 Type: DNPPointCode Data 2: Associated RTU Address Data2 Type: RTUAddress Data 3:Debug Data Data3 Type: ushort Data 4:Debug Data Data4 Type: ushort
08A2	2210	Change to Point Map Detected	DNP[MCU]	All	A configuration change to a point map was detected. This change will be processed 30 seconds after the last change is detected. Data 1: Map Number Data1 Type: MapNumber Data 2:Debug Data Data2 Type: ushort Data 3:Debug Data Data3 Type: ushort Data 4:Debug Data Data4 Type: ushort
08A3	2211	Error in Getting Map Timer	DNP[MCU]	Extended	An error was detected when attempting to initialize a map-change timer. The operation will be retried. Data 1: Map Number Data1 Type: MapNumber Data 2:Debug Data Data2 Type: ushort Data 3:Debug Data Data3 Type: ushort Data 4:Debug Data Data4 Type: ushort
08A4	2212	Point Processing Timer Unavailable	DNP[MCU]	Extended	An internal timer was not available to perform the routing table configuration change timing function. DNP initialization will be aborted. Data 1:Debug Data Data1 Type: ushort Data 2:Debug Data Data2 Type: ushort Data 3:Debug Data Data3 Type: ushort Data 4:Debug Data Data4 Type: ushort
08A5	2213	Point Map Reinitialized	DNP[MCU]	Normal	The point map was successfully reinitialized following completion of changes to the point map configuration. Data 1: Map Number Data1 Type: MapNumber Data 2:Debug Data Data2 Type: ushort Data 3:Debug Data Data3 Type: ushort Data 4:Debug Data Data4 Type: ushort
08A6	2214	Point Definition Invalid	DNP[MCU]	Extended	An issue was found in the configuration data of a mapped point. The map will not be initialized until the error is corrected. Data 1: Map Number Data1 Type: MapNumber

Definitions of Historic Events

					Data 2: Point Index Data2 Type: ushort Data 3: Error Data Data3 Type: ushort Data 4: Code Location Data4 Type: ushort
08A7	2215	Input Point Code Not Mapped	DNP[MCU]	Extended	The application attempted to supply input data for a point that was not included in the configured point mapping. Data 1: Point Type Data1 Type: DNPPointType Data 2: Point Code Data2 Type: DNPPointCode Data 3:Debug Data Data3 Type: ushort Data 4:Debug Data Data4 Type: ushort
08A9	2217	Event Buffer Overflow	DNP[MCU]	Extended	An overflow condition has been reached for the event buffer of the reported point type. The oldest event will be removed to make room for this new event, and the overflow IIN bit will be set. Data 1: DNP Point Type Data1 Type: DNPPointType Data 2:Master Number Data2 Type: ushort Data 3:Debug Data Data3 Type: ushort Data 4:Debug Data Data4 Type: ushort
08AA	2218	Analog Output Function Registered	DNP[MCU]	Extended	An analog output point special function was successfully added to the list. This function connects an Analog output operation with functionality elsewhere in the application. Data 1: Point Code Data1 Type: DNPPointCode Data 2: Associated RTU Address Data2 Type: RTUAddress Data 3:Debug Data Data3 Type: ushort Data 4:Debug Data Data4 Type: ushort
08AB	2219	Analog Output Code Not Mapped	DNP[MCU]	Extended	An analog output point special function was not added to the list because the analog output point is not yet included in the point mapping configuration. Data 1: Point Code Data1 Type: DNPPointCode Data 2: Associated RTU Address Data2 Type: RTUAddress Data 3:Debug Data Data3 Type: ushort Data 4:Debug Data Data4 Type: ushort
08AC	2220	Map Change Callback Buffer Full	DNP[MCU]	Extended	A special function to be used to inform the application about map changes was unable to be added to the list. The list was full. Data 1:Debug Data Data1 Type: ushort Data 2:Debug Data Data2 Type: ushort Data 3:Debug Data Data3 Type: ushort Data 4:Debug Data Data4 Type: ushort
08AD	2221	Map Change Callback Registered	DNP[MCU]	Extended	A special function to be used to inform the application about map changes was successfully added to the list. Data 1:Debug Data Data1 Type: ushort Data 2:Debug Data Data2 Type: ushort Data 3:Debug Data Data3 Type: ushort Data 4:Debug Data Data4 Type: ushort
08C0	2240	Route Processing Timer Unavailable	DNP[MCU]	Extended	An internal timer was not available to perform the map-change timing function. DNP initialization will be aborted. Data 1: Map Number Data1 Type: MapNumber Data 2:Debug Data Data2 Type: ushort Data 3:Debug Data Data3 Type: ushort Data 4:Debug Data Data4 Type: ushort
08C1	2241	Route Entry Invalid	DNP[MCU]	Extended	An issue was found with one of the configured route entries. The route table will not be initialized until the issue is corrected. Data 1: Route RTU Address Data1 Type: RTUAddress Data 2: Route Table Index Data2 Type: ushort Data 3: Route Entry Error Data3 Type: RouteEntryError Data 4:Debug Data Data4 Type: ushort
08C2	2242	Route Could Not be Added	DNP[MCU]	Extended	The routing table did not have room for the new route. The route table will not be initialized. Data 1: Route RTU Address Data1 Type: RTUAddress Data 2: Route Table Index Data2 Type: ushort

Definitions of Historic Events

					Data 3:Debug Data Data3 Type: ushort Data 4:Debug Data Data4 Type: ushort
08C3	2243	Route Table Initialized	DNP[MCU]	Normal	The route table was successfully initialized with configured routes and routing was enabled. Data 1: Count of Routes Data1 Type: ushort Data 2:Debug Data Data2 Type: ushort Data 3:Debug Data Data3 Type: ushort Data 4:Debug Data Data4 Type: ushort
08C4	2244	Route Configuration Change Detected	DNP[MCU]	All	A configuration change to the routing table was detected. This change will be processed 30 seconds after the last change is detected. Data 1:Debug Data Data1 Type: ushort Data 2:Debug Data Data2 Type: ushort Data 3:Debug Data Data3 Type: ushort Data 4:Debug Data Data4 Type: ushort
08C5	2245	Error in Route Change Timer	DNP[MCU]	Extended	An error was detected when attempting to initialize a route table-change timer. The operation will be retried. Data 1:Debug Data Data1 Type: ushort Data 2:Debug Data Data2 Type: ushort Data 3:Debug Data Data3 Type: ushort Data 4:Debug Data Data4 Type: ushort
08C6	2246	Pass-Through Routing Enabled	DNP[MCU]	Normal	A valid pass-through route configuration was found and pass-through routing was enabled. Data 1:Debug Data Data1 Type: ushort Data 2:Debug Data Data2 Type: ushort Data 3:Debug Data Data3 Type: ushort Data 4:Debug Data Data4 Type: ushort
08C7	2247	Pass-Through Routing Disabled	DNP[MCU]	Normal	A valid pass-through route configuration was not found and pass-through routing was disabled. Data 1:Debug Data Data1 Type: ushort Data 2:Debug Data Data2 Type: ushort Data 3:Debug Data Data3 Type: ushort Data 4:Debug Data Data4 Type: ushort
08C8	2248	DNP Diag Test Start	DNP[MCU]	Normal	Data 1: Test Type Data1 Type: DiagTestType Data 2:Debug Data Data2 Type: ushort Data 3:Debug Data Data3 Type: ushort Data 4:Debug Data Data4 Type: ushort
08C9	2249	DNP Diag KeepAlive Start	DNP[MCU]	Normal	Data 1: Test Type Data1 Type: DiagTestType Data 2:Debug Data Data2 Type: ushort Data 3:Debug Data Data3 Type: ushort Data 4:Debug Data Data4 Type: ushort
08CA	2250	DNP Diag Test Ending	DNP[MCU]	Normal	Data 1: Test Type Data1 Type: DiagTestType Data 2:Debug Data Data2 Type: ushort Data 3:Debug Data Data3 Type: ushort Data 4:Debug Data Data4 Type: ushort
08CB	2251	DNP Diag KeepAlive End	DNP[MCU]	Normal	Data 1: Test Type Data1 Type: DiagTestType Data 2:Debug Data Data2 Type: ushort Data 3:Debug Data Data3 Type: ushort Data 4:Debug Data Data4 Type: ushort
08CC	2252	DNP Diag Ping Timeout	DNP[MCU]	Normal	Data 1:Debug Data Data1 Type: ushort Data 2:Debug Data Data2 Type: ushort

Definitions of Historic Events

					Data 3:Debug Data Data3 Type: ushort Data 4:Debug Data Data4 Type: ushort
08CD	2253	DNPDiag Send Error	DNP[MCU]	Normal	Data 1: DNP Address Data1 Type: DNPAddress Data 2:Debug Data Data2 Type: ushort Data 3:Debug Data Data3 Type: ushort Data 4:Debug Data Data4 Type: ushort
08CE	2254	DNP Diag Max Peers	DNP[MCU]	Normal	Data 1: Max Peers When This Occurs Data1 Type: MaxPeersWhen Data 2:Debug Data Data2 Type: ushort Data 3:Debug Data Data3 Type: ushort Data 4:Debug Data Data4 Type: ushort
08CF	2255	DNP Diag No Peers	DNP[MCU]	Normal	Data 1: No Peers When This Occurs Data1 Type: NoPeersWhen Data 2:Debug Data Data2 Type: ushort Data 3:Debug Data Data3 Type: ushort Data 4:Debug Data Data4 Type: ushort
08D0	2256	DNPDiag Test Suspended	DNP[MCU]	Normal	Data 1:Debug Data Data1 Type: ushort Data 2:Debug Data Data2 Type: ushort Data 3:Debug Data Data3 Type: ushort Data 4:Debug Data Data4 Type: ushort
08D1	2257	DNPDiag Test Resumed	DNP[MCU]	Normal	Data 1:Debug Data Data1 Type: ushort Data 2:Debug Data Data2 Type: ushort Data 3:Debug Data Data3 Type: ushort Data 4:Debug Data Data4 Type: ushort
08D2	2258	DNPDiag WatchDog Triggered	DNP[MCU]	Normal	Data 1:Debug Data Data1 Type: ushort Data 2:Debug Data Data2 Type: ushort Data 3:Debug Data Data3 Type: ushort Data 4:Debug Data Data4 Type: ushort
08D3	2259	DNP Comm Sys Alarm On	DNP[MCU]	Normal	Data 1:Debug Data Data1 Type: ushort Data 2:Debug Data Data2 Type: ushort Data 3:Debug Data Data3 Type: ushort Data 4:Debug Data Data4 Type: ushort
08D4	2260	DNP Comm Sys Alarm Off	DNP[MCU]	Normal	Data 1:Debug Data Data1 Type: ushort Data 2:Debug Data Data2 Type: ushort Data 3:Debug Data Data3 Type: ushort Data 4:Debug Data Data4 Type: ushort
08D5	2261	No Diagnostics On Peer. Cannot Test.	DNP[MCU]	All	Remote Peer does not have diagnostics installed, so tests cannot be performed with it. Data 1: DNP Address Data1 Type: DNPAddress Data 2:Debug Data Data2 Type: ushort Data 3:Debug Data Data3 Type: ushort Data 4:Debug Data Data4 Type: ushort
08D6	2262	Switching to Failover Master	DNP[MCU]	Extended	Switching to Failover Master Data 1: Master RTU Address Data1 Type: RTUAddress Data 2: IP addr first half Data2 Type: Hexushort Data 3:IP addr second half Data3 Type: Hexushort Data 4:Master Number Data4 Type: ushort
08D7	2263	Switching to Master Primary	DNP[MCU]	Extended	Switching to Master Primary Data 1: Master RTU Address Data1 Type: RTUAddress

Definitions of Historic Events

					Data 2: IP addr first half Data2 Type: Hexushort Data 3:IP addr second half Data3 Type: Hexushort Data 4:Master Number Data4 Type: ushort
08D8	2264	Master Wrong IP Addr Cmd Rejected	DNP[MCU]	Extended	Switching to Master Primary Data 1: Master RTU Address Data1 Type: RTUAddress Data 2: IP addr first half Data2 Type: Hexushort Data 3:IP addr second half Data3 Type: Hexushort Data 4:Port Code Data4 Type: ushort
08D9	2265	Invalid Master Cmd Rejected	DNP[MCU]	Extended	Switching to Master Primary Data 1: Master RTU Address Data1 Type: RTUAddress Data 2: IP addr first half Data2 Type: Hexushort Data 3:IP addr second half Data3 Type: Hexushort Data 4:Function Code Data4 Type: Hexushort
08DA	2266	Master has wrong port type Cmd Rejected	DNP[MCU]	Extended	Switching to Master Primary Data 1: Master RTU Address Data1 Type: RTUAddress Data 2: IP addr first half Data2 Type: Hexushort Data 3:IP addr second half Data3 Type: Hexushort Data 4:Port Code Data4 Type: ushort
08DB	2267	Master used reserved addr. Cmd Rejected	DNP[MCU]	Extended	Switching to Master Primary Data 1: Master RTU Address Data1 Type: RTUAddress Data 2: IP addr first half Data2 Type: Hexushort Data 3:IP addr second half Data3 Type: Hexushort Data 4:Port Code Data4 Type: ushort
08DC	2268	SCADA Set Date/Time	DNP[MCU]	All	SCADA Set Date/Time Data 1:Debug Data Data1 Type: ushort Data 2:Debug Data Data2 Type: ushort Data 3:Debug Data Data3 Type: ushort Data 4:Debug Data Data4 Type: ushort
08DD	2269	Recorded Time is 0	DNP[MCU]	All	Recorded Time is 0 Data 1:Debug Data Data1 Type: ushort Data 2:Debug Data Data2 Type: ushort Data 3:Debug Data Data3 Type: ushort Data 4:Debug Data Data4 Type: ushort
08DE	2270	Cold Restart Command Disabled	DNP[MCU]	All	Cold Restart Command Disabled Data 1:Debug Data Data1 Type: RTUAddress Data 2:Debug Data Data2 Type: RTUAddress Data 3:Debug Data Data3 Type: ushort Data 4:Debug Data Data4 Type: ushort
0B00	2816	Disk Error	CFM[MCU]	All	 Data 1:Trace Info Data1 Type: ushort Data 2:Error Code Data2 Type: ushort
0B01	2817	File Allocation In Progress	CFM[MCU]	Normal	
0B02	2818	File Allocation Not In Progress	CFM[MCU]	Normal	
0B03	2819	File Allocation Issue	CFM[MCU]	All	 Data 1:Trace Info Data1 Type: ushort Data 2:Error Code Data2 Type: ushort
0B04	2820	Compact Flash Card Not Found	CFM[MCU]	Extended	 Data 1:Debug Info (Card State) Data1 Type: ushort
0B05	2821	Disk Check Issue	CFM[MCU]	All	 Data 1:Error Code Data1 Type: ushort
0B06	2822	Set Bad Disk Condition to On	CFM[MCU]	Normal	
0B07	2823	Set Bad Disk Condition to Off	CFM[MCU]	Normal	
0B08	2824	Allocated File Size Exceeded	CFM[MCU]	All	 Data 1:File Class Data1 Type: ushort

Definitions of Historic Events

					Data 2: Allocated Size (kB) Data2 Type: ushort Data 3: Written Size (kB) Data3 Type: ushort
0B09	2825	Shutdown Processing CFM	CFM[MCU]	Normal	Data 1:Trace Info Data1 Type: ushort
0B0A	2826	CFM:Disk Tampered Indication	CFM[MCU]	Normal	Directory Contents Corruption Was Detected on Startup.
0B0B	2827	CFM:Disk Tampered Indication Cleared	CFM[MCU]	Normal	Directory Contents Corruption Was Detected on Startup.
0C00	3072	SW1: Control Open Request	IIM[MCU]	Normal	
0C01	3073	SW1: Control Open OK	IIM[MCU]	Normal	
0C02	3074	SW1: Control Close Request	IIM[MCU]	Normal	
0C03	3075	SW1: Control Close OK	IIM[MCU]	Normal	
0C04	3076	SW2: Control Open Request	IIM[MCU]	Normal	
0C05	3077	SW2: Control Open OK	IIM[MCU]	Normal	
0C06	3078	SW2: Control Close Request	IIM[MCU]	Normal	
0C07	3079	SW2: Control Close OK	IIM[MCU]	Normal	
0C08	3080	Control Operation Request Problem	IIM[MCU]	Normal	Data 1: Data1 Type: ControlCode
0C09	3081	Control Operation Problem	IIM[MCU]	Normal	Data 1: Data1 Type: ControlCode
0C0A	3082	Average Load Reset	IIM[MCU]	Normal	Data 1: Data1 Type: AverageLoad Data 4: Data4 Type: ushort
0C0B	3083	SCADA Cleared Manual Operation	IIM[MCU]	Normal	
0C0C	3084	SW1: Any Phase Overcurrent	IIM[MCU]	Normal	Data 1: Data1 Type: FaultBits
0C0D	3085	SW1: Overcurrents Cleared	IIM[MCU]	Normal	
0C0E	3086	SW1: Any Phase Loss Active	IIM[MCU]	Normal	Data 1: Data1 Type: AnyPhaseLoss
0C0F	3087	SW1: Any Phase Loss Cleared	IIM[MCU]	Normal	
0C10	3088	SW1: Manual Operation Detected	IIM[MCU]	Normal	
0C11	3089	SW1: Manual Operation Cleared	IIM[MCU]	Normal	
0C12	3090	SW1: Hot-Line Tag Active	IIM[MCU]	Normal	
0C13	3091	SW1: Hot-Line Tag Cleared	IIM[MCU]	Normal	
0C14	3092	Frequency Trip Active	IIM[MCU]	Normal	Data 1: Data1 Type: FreqTripType
0C15	3093	Frequency Trip Cleared	IIM[MCU]	Normal	
0C16	3094	SW1: Trip to Lockout Active	IIM[MCU]	Normal	
0C17	3095	SW1: Trip to Lockout Cleared	IIM[MCU]	Normal	
0C18	3096	SW1 Opened	IIM[MCU]	Normal	
0C19	3097	SW1 Closed IIM	IIM[MCU]	Normal	
0C1A	3098	SW2 Open IIM	IIM[MCU]	Normal	
0C1B	3099	SW2 Closed IIM	IIM[MCU]	Normal	
0C1C	3100	Device In Reset State	IIM[MCU]	Normal	
0C1D	3101	Device Not In Reset State	IIM[MCU]	Normal	
0C1E	3102	Inst. Replay Status Update	IIM[MCU]	All	Data 1:Sw. Status Data1 Type: ushort Data 2:OC Status Data2 Type: ushort Data 3:VL Status Data3 Type: ushort
0C1F	3103	Manual Operation Report	IIM[MCU]	Normal	
0C20	3104	SW2: Any Phase Overcurrent	IIM[MCU]	Normal	Data 1: Data1 Type: FaultBits
0C21	3105	SW2: Overcurrents Cleared	IIM[MCU]	Normal	

0C22	3106	SW2: Any Phase Loss Active	IIM[MCU]	Normal	
0C23	3107	SW2: Any Phase Loss Cleared	IIM[MCU]	Normal	
0C24	3108	SW2: Manual Operation Detected	IIM[MCU]	Normal	
0C25	3109	SW2: Manual Operation Cleared	IIM[MCU]	Normal	
0C26	3110	SW2: Hot Line Tag Activated	IIM[MCU]	Normal	
0C27	3111	SW2: Hot Line Tag Cleared	IIM[MCU]	Normal	
0C28	3112	SW2: Trip to Lockout Active	IIM[MCU]	Normal	
0C29	3113	SW2: Trip to Lockout Cleared	IIM[MCU]	Normal	
0C2A	3114	System Voltage Unrecognized Active	IIM[MCU]	All	System Voltage Unrecognized Active Data 1:Debug Data Data1 Type: ushort Data 2:Debug Data Data2 Type: ushort Data 3:Debug Data Data3 Type: ushort Data 4:Debug Data Data4 Type: ushort
0C2B	3115	System Voltage Unrecognized Inactive	IIM[MCU]	All	System Voltage Unrecognized Inactive Data 1:Debug Data Data1 Type: ushort Data 2:Debug Data Data2 Type: ushort Data 3:Debug Data Data3 Type: ushort Data 4:Debug Data Data4 Type: ushort
0C30	3120	Switch 1 not in normal state inactive	DAT[MCU]	All	Switch 1 not in normal state inactive Data 1:Debug Data Data1 Type: ushort Data 2:Debug Data Data2 Type: ushort Data 3:Debug Data Data3 Type: ushort Data 4:Debug Data Data4 Type: ushort
0C31	3121	Switch 1 not in normal state active	DAT[MCU]	All	Switch 1 not in normal state active Data 1:Debug Data Data1 Type: ushort Data 2:Debug Data Data2 Type: ushort Data 3:Debug Data Data3 Type: ushort Data 4:Debug Data Data4 Type: ushort
0C32	3122	Switch 2 not in normal state inactive	DAT[MCU]	All	Switch 2 not in normal state inactive Data 1:Debug Data Data1 Type: ushort Data 2:Debug Data Data2 Type: ushort Data 3:Debug Data Data3 Type: ushort Data 4:Debug Data Data4 Type: ushort
0C33	3123	Switch 2 not in normal state active	DAT[MCU]	All	Switch 2 not in normal state active Data 1:Debug Data Data1 Type: ushort Data 2:Debug Data Data2 Type: ushort Data 3:Debug Data Data3 Type: ushort Data 4:Debug Data Data4 Type: ushort
0C34	3124	Local Switch 1 is the Closed Loop Center	DAT[MCU]	All	Local Switch 1 is the Closed Loop Center Data 1:Debug Data Data1 Type: ushort Data 2:Debug Data Data2 Type: ushort Data 3:Debug Data Data3 Type: ushort Data 4:Debug Data Data4 Type: ushort
0C35	3125	Local Switch 1 no longer Closed Loop Ctr	DAT[MCU]	All	Local Switch 1 no longer Closed Loop Ctr Data 1:Debug Data Data1 Type: ushort Data 2:Debug Data Data2 Type: ushort Data 3:Debug Data Data3 Type: ushort Data 4:Debug Data Data4 Type: ushort
0C36	3126	RTL Xmit Blocked	IIM[MCU]	All	Data 1:Debug Data Data1 Type: ManualOp Data 2:Debug Data Data2 Type: HLT1 Data 3:Debug Data Data3 Type: HLT2 Data 4:Debug Data Data4 Type: NoMaster
0C37	3127	Local Switch 2 is the Closed Loop Center	DAT[MCU]	All	Local Switch 2 is the Closed Loop Center Data 1:Debug Data Data1 Type: ushort

Definitions of Historic Events

					Data 2:Debug Data Data2 Type: ushort Data 3:Debug Data Data3 Type: ushort Data 4:Debug Data Data4 Type: ushort
0C38	3128	Local Switch 2 no longer Closed Loop Ctr	DAT[MCU]	All	Local Switch 2 no longer Closed Loop Ct Data 1:Debug Data Data1 Type: ushort Data 2:Debug Data Data2 Type: ushort Data 3:Debug Data Data3 Type: ushort Data 4:Debug Data Data4 Type: ushort
0E01	3585	Xfer Trip PR Initiated (DG POI) Active	DAT[MCU]	Normal	Xfer Trip PR Initiated (DG POI) Active Data 1: Data1 Type: ushort Data 2: Data2 Type: ushort Data 3: Data3 Type: ushort Data 4: Data4 Type: ushort
0E02	3586	Xfer Trip PR Initiated (DG POI) Inactive	DAT[MCU]	Normal	Xfer Trip PR Initiated (DG POI) Inactive Data 1: Data1 Type: ushort Data 2: Data2 Type: ushort Data 3: Data3 Type: ushort Data 4: Data4 Type: ushort
0E03	3587	Transfer Trip Sent Active	DAT[MCU]	Normal	Transfer Trip Sent Active Data 1: Data1 Type: RTUAddress Data 2: Data2 Type: SWPos Data 3: Data3 Type: RTUAddress Data 4: Data4 Type: ushort
0E04	3588	Transfer Trip Sent Inactive	DAT[MCU]	Normal	Transfer Trip Sent Inactive Data 1: Data1 Type: RTUAddress Data 2: Data2 Type: SWPos Data 3: Data3 Type: ushort Data 4: Data4 Type: ushort
0E05	3589	DG Reconnect Disqualified On Fault	DAT[MCU]	Normal	DG Reconnect Disqualified On Fault Data 1: Data1 Type: TeamNumberWithUnknown Data 2: Data2 Type: BooleanTrueFalse Data 3: Data3 Type: ushort Data 4: Data4 Type: ushort
0E06	3590	Sw1 Auto Manl Op. Clear Timer Stopped	DAT[MCU]	Normal	Sw1 Auto Manual Operation Clearing Timer Stopped Data 1: Data1 Type: ushort Data 2: Data2 Type: ushort Data 3: Data3 Type: ushort Data 4: Data4 Type: ushort
0E07	3591	Sw2 Auto Manl Op. Clear Timer Stopped	DAT[MCU]	Normal	Sw2 Auto Manual Operation Clearing Timer Stopped Data 1: Data1 Type: ushort Data 2: Data2 Type: ushort Data 3: Data3 Type: ushort Data 4: Data4 Type: ushort
0E08	3592	Sw2 Auto Manl Op. Clear Timer Started	DAT[MCU]	Normal	Sw2 Auto Manual Operation Clearing Timer Started Data 1: Data1 Type: ushort Data 2: Data2 Type: ushort Data 3: Data3 Type: ushort Data 4: Data4 Type: ushort
1000	4096	Auto Operation Enabled	FPX[MCU]	Normal	Auto Operation Enabled
1001	4097	Auto Operation Disabled	SWX[MCU]	Normal	Auto Operation Disabled
1002	4098	Cabinet Door Closed	FPX[MCU]	Normal	Cabinet Door Closed
1003	4099	Cabinet Door Open	SWX[MCU]	Normal	Cabinet Door Open
1004	4100	SCADA Mode - Remote	FPX[MCU]	Normal	SCADA Mode - Remote
1005	4101	SCADA Mode - Local	SWX[MCU]	Normal	SCADA Mode - Local
1006	4102	Auto Restoration Enabled	FPX[MCU]	Normal	Auto Restoration ON
1007	4103	Auto Restoration Disabled	SWX[MCU]	Normal	Auto Restoration OFF

Definitions of Historic Events

1008	4104	USER1 Mode Enabled	FPX[MCU]	Normal	USER1 Mode ON
1009	4105	USER1 Mode Blocked	SWX[MCU]	Normal	USER1 Mode OFF
100A	4106	USER2 Mode Enabled	FPX[MCU]	Normal	USER2 Mode ON
100B	4107	USER2 Mode Blocked	SWX[MCU]	Normal	USER2 Mode OFF
100C	4108	SW1 Auto Operation Enabled	FPX[MCU]	Normal	SW1 Auto Operation Enabled
100D	4109	SW1 Auto Operation Disabled	SWX[MCU]	Normal	SW1 Auto Operation Disabled
100E	4110	SW2 Auto Operation Enabled	FPX[MCU]	Normal	SW2 Auto Operation Enabled
100F	4111	SW2 Auto Operation Disabled	SWX[MCU]	Normal	SW2 Auto Operation Disabled
1010	4112	Switch Trouble	FPX[MCU]	Normal	Switch Trouble
1011	4113	Switch OK	SWX[MCU]	Normal	Switch Trouble Vanishes
1012	4114	Use Alternate Reclose Count	FPX[MCU]	Normal	Use Alternate Reclose Count
1013	4115	Use Regular Reclose Count	SWX[MCU]	Normal	Use Regular Reclose Count
1014	4116	Issued Clr Electronics Bad Cmd	FPX[MCU]	Normal	Issued Clr Electronics Bad Cmd
1015	4117	User-Defined Input 1 On	FPX[MCU]	Normal	User-Defined Input1 On
1016	4118	User-Defined Input 1 Off	FPX[MCU]	Normal	User-Defined Input1 Off
1017	4119	User-Defined Input 2 On	FPX[MCU]	Normal	User-Defined Input 2 On
1018	4120	User-Defined Input 2 Off	FPX[MCU]	Normal	User-Defined Input 2 Off
1019	4121	Aux Digital Input 3 On	FPX[MCU]	Normal	Aux Digital Input 3 On
101A	4122	User-Defined Input 3 Off	FPX[MCU]	Normal	User-Defined Input 3 Off
101B	4123	Switch Operation Blocked	FPX[MCU]	Normal	Switch Operation Blocked Data 1: Data1 Type: SwitchBlockedInput Data 2: Data2 Type: SwitchBlockedType Data 3: Data3 Type: SWXnum Data 4: Command Source Data4 Type: CommandSource
101C	4124	Input J20 Pin 1 On	FPX[MCU]	Normal	
101D	4125	Input J20 Pin 1 Off	FPX[MCU]	Normal	
101E	4126	Input J20 Pin 2 On	FPX[MCU]	Normal	
101F	4127	Input J20 Pin 2 Off	FPX[MCU]	Normal	
1020	4128	Input J20 Pin 3 On	FPX[MCU]	Normal	
1021	4129	Input J20 Pin 3 Off	FPX[MCU]	Normal	
1022	4130	Sw1 Close Op Blocked ON	FPX[MCU]	Normal	
1023	4131	Sw1 Close Op Blocked OFF	FPX[MCU]	Normal	
1024	4132	Sw1 Open Op Blocked ON	FPX[MCU]	Normal	
1025	4133	Sw1 Open Op Blocked OFF	FPX[MCU]	Normal	
1026	4134	Sw2 Close Op Blocked ON	FPX[MCU]	Normal	
1027	4135	Sw2 Close Op Blocked OFF	FPX[MCU]	Normal	
1028	4136	Sw2 Open Op Blocked ON	FPX[MCU]	Normal	
1029	4137	Sw2 Open Op Blocked OFF	FPX[MCU]	Normal	
1100	4352	SW1 Phase A Overcurrent ON	FLT[MCU]	Normal	SW1 Phase A Overcurrent Detected
1101	4353	SW1 Phase A Overcurrent OFF	FLT[MCU]	Normal	SW1 Phase A Overcurrent Cleared
1102	4354	SW1 Phase B Overcurrent ON	FLT[MCU]	Normal	SW1 Phase B Overcurrent Detected
1103	4355	SW1 Phase B Overcurrent OFF	FLT[MCU]	Normal	SW1 Phase B Overcurrent Cleared
1104	4356	SW1 Phase C Overcurrent ON	FLT[MCU]	Normal	SW1 Phase C Overcurrent Detected
1105	4357	SW1 Phase C Overcurrent OFF	FLT[MCU]	Normal	SW1 Phase C Overcurrent Cleared
1106	4358	SW1 Neutral Overcurrent ON	FLT[MCU]	Normal	SW1 Neutral Overcurrent Detected
1107	4359	SW1 Neutral Overcurrent OFF	FLT[MCU]	Normal	SW1 Phase A Overcurrent Cleared
1108	4360	SW2 Phase A Overcurrent ON	FLT[MCU]	Normal	SW2 Phase A Overcurrent Detected
1109	4361	SW2 Phase A Overcurrent OFF	FLT[MCU]	Normal	SW2 Phase A Overcurrent Cleared
110A	4362	SW2 Phase B Overcurrent ON	FLT[MCU]	Normal	SW2 Phase B Overcurrent Detected
110B	4363	SW2 Phase B Overcurrent OFF	FLT[MCU]	Normal	SW2 Phase B Overcurrent Cleared
110C	4364	SW2 Phase C Overcurrent ON	FLT[MCU]	Normal	SW2 Phase C Overcurrent Detected
110D	4365	SW2 Phase C Overcurrent OFF	FLT[MCU]	Normal	SW2 Phase C Overcurrent Cleared
110E	4366	SW2 Neutral Overcurrent ON	FLT[MCU]	Normal	SW2 Neutral Overcurrent Detected
110F	4367	SW2 Neutral Overcurrent OFF	FLT[MCU]	Normal	SW2 Neutral Overcurrent Cleared
1110	4368	SW1 Overcurrent ON	FLT[MCU]	Normal	SW1 Overcurrent Detected

Definitions of Historic Events

1111	4369	SW1 Overcurrent OFF	FLT[MCU]	Normal	SW1 Overcurrent Cleared
1112	4370	SW2 Overcurrent ON	FLT[MCU]	Normal	SW2 Overcurrent Detected
1113	4371	SW2 Overcurrent OFF	FLT[MCU]	Normal	SW2 Overcurrent Cleared
1114	4372	SW1 Loss of Voltage ON	FLT[MCU]	Normal	SW1 Loss of Voltage Detected
1115	4373	SW1 Loss of Voltage OFF	FLT[MCU]	Normal	SW1 Voltage Restored
1116	4374	SW2 Loss of Voltage ON	FLT[MCU]	Normal	SW2 Loss of Voltage Detected
1117	4375	SW2 Loss of Voltage OFF	FLT[MCU]	Normal	SW2 Voltage Restored
1118	4376	SW1 Sectionalizer Trip ON	FLT[MCU]	Normal	SW1 Sectionalizer Tripped
1119	4377	SW1 Sectionalizer Trip OFF	FLT[MCU]	Normal	SW1 Sectionalizer Trip Cleared
111A	4378	SW2 Sectionalizer Trip ON	FLT[MCU]	Normal	SW2 Sectionalizer Tripped
111B	4379	SW2 Sectionalizer Trip OFF	FLT[MCU]	Normal	SW2 Sectionalizer Trip Cleared
111C	4380	SW1 Reverse Current A ON	FLT[MCU]	Normal	SW1 Reverse Current Phase A Detected
111D	4381	SW1 Reverse Current A OFF	FLT[MCU]	Normal	SW1 Phase A Normal Current Direction
111E	4382	SW1 Reverse Current B ON	FLT[MCU]	Normal	SW1 Reverse Current Phase B Detected
111F	4383	SW1 Reverse Current B OFF	FLT[MCU]	Normal	SW1 Phase B Normal Current Direction
1120	4384	SW1 Reverse Current C ON	FLT[MCU]	Normal	SW1 Reverse Current Phase C Detected
1121	4385	SW1 Reverse Current C OFF	FLT[MCU]	Normal	SW1 Phase C Normal Current Direction
1122	4386	SW2 Reverse Current A ON	FLT[MCU]	Normal	SW1 Reverse Current Phase A Detected
1123	4387	SW2 Reverse Current A OFF	FLT[MCU]	Normal	SW2 Phase A Normal Current Direction
1124	4388	SW2 Reverse Current B ON	FLT[MCU]	Normal	SW1 Reverse Current Phase B Detected
1125	4389	SW2 Reverse Current B OFF	FLT[MCU]	Normal	SW1 Phase B Normal Current Direction
1126	4390	SW2 Reverse Current C ON	FLT[MCU]	Normal	SW2 Reverse Current Phase C Detected
1127	4391	SW2 Reverse Current C OFF	FLT[MCU]	Normal	SW2 Phase C Normal Current Direction
1128	4392	Volt Imbal Det On	FLT[MCU]	Normal	Voltage Imbalance Detect On
1129	4393	Volt Imbal Det Off	FLT[MCU]	Normal	Voltage Imbalance Detect Off
					One or More Phases Voltage Lost
112A	4394	Voltage Lost on Phases	FLT[MCU]	Normal	Data 1: SW1 Voltage Lost on Data1 Type: SW1LostPhases Data 2: SW2 Voltage Lost on Data2 Type: SW2LostPhases
112B	4395	Voltage OK on All Phases	FLT[MCU]	Normal	Voltage Returned on All Phases
1132	4402	OC then Volt OK: Load-side Protect Open	FLT[MCU]	Normal	OC then voltage o.k.; Load-side protective open;Noted
1133	4403	OC then VL; Source Side Open; Counting	FLT[MCU]	Normal	OC then VL; Source-side protective open;Counting
1134	4404	Reclose Sequence Ended (time limit)	FLT[MCU]	Normal	Reclose memory time limit; Sequence ended; Count reset
1135	4405	Volt Loss; Source Side Fault; Sect OFF	FLT[MCU]	Normal	VL; Source-side fault; Sectionalizing disarmed
1136	4406	Volt Loss; Load-side fault; Sect ON	FLT[MCU]	Normal	VL; Load-side fault; Sectionalizing armed
1137	4407	Full Count Reached; Source Side Fault	FLT[MCU]	Normal	Full count reached; Source-side fault; Noted
1138	4408	Full Count Reached; Load Side Fault	FLT[MCU]	Normal	Full count reached; Load-side fault; Noted
1139	4409	Full Count Reached w/ Sect. OFF	FLT[MCU]	Normal	Full count reached w/ sectional. disabled; Noted
113A	4410	Full count reached; Open executed	FLT[MCU]	Normal	Full count reached; Open operation executed
113B	4411	No OC before VL; S-Side Open; Counting	FLT[MCU]	Normal	No OC before VL; Source Side open; Counting
113C	4412	Source-side Fuse Blown Load-side Fault	FLT[MCU]	Normal	OC then VL; Source-side fuse blown for load-side fault
113D	4413	Source-side Fuse Blown Source-side Fault	FLT[MCU]	Normal	No OC then VL; Source-side (SS) fuse blown - SS fault
113E	4414	CLOSE Exec Shots-to-Lockout Requested	FLT[MCU]	Normal	CLOSE operation excited, shots-to-lockout requested
113F	4415	Lockout Close w/ Event - OPEN Exec	FLT[MCU]	Normal	Lockout close complete w/ event after - OPEN executed
1140	4416	Persistent Phase Imbalance - OPEN Exec	FLT[MCU]	Normal	Persistent phase imbalance; OPEN executed
1141	4417	Phase Imbalance w/ Reclose Enabled	FLT[MCU]	Normal	Phase imbalance w/ reclose enabled; Waiting
1142	4418	Switch Closed; Reclose Cancelled	FLT[MCU]	Normal	Switch closed; Operator action; Reclose cancelled
1143	4419	Voltage Restored after Imbalance	FLT[MCU]	Normal	Voltage OK after imbalance; Voltage restored; Waiting
1144	4420	Switch Closed; Reclose Cancelled	FLT[MCU]	Normal	Switch closed; Operator action; Reclose cancelled (duplicate???)
1145	4421	Imbalance Corrected RECLOSE Exec	FLT[MCU]	Normal	Imbalance corrected w/ reclose enabled; CLOSE executed

Definitions of Historic Events

1146	4422	Shots-to-Lockout Latched On	FLT[MCU]	Normal	Shots-to-lockout latched on
1147	4423	Successful Reclose; Sequence Ended	FLT[MCU]	Normal	Successful reclose; Sequence ended; Count reset
1148	4424	LOV Sectionalizing Fail - Sync Error	FLT[MCU]	Normal	LOV Fail Sync Err
1149	4425	FI Breaker Tripped	FLT[MCU]	Normal	FI Breaker Tripped
114A	4426	FI Breaker Closed	FLT[MCU]	Normal	FI Breaker Closed
114B	4427	3P Volt Loss w/ Current Present	FLT[MCU]	Normal	No OC then VL; Current still present; Noted
114C	4428	Volt Loss Only Count Reached	FLT[MCU]	Normal	No OC before VL; Volt Loss Only count reached
114D	4429	OPEN Exec on Volt Loss Only	FLT[MCU]	Normal	Open operation executed on Voltage Loss Only
114E	4430	Sect Disabled for Voltage Loss Only	FLT[MCU]	Normal	Sectionalizing Disabled on Voltage Loss Only; None
114F	4431	Extended Volt Loss; OPEN	FLT[MCU]	Normal	Reclose memory time limit; Extended Volt Loss; OPEN
1150	4432	Instant reclose Qualification w/ OC	FLT[MCU]	Normal	O/C then VLoss; Qualify for instant reclose
1151	4433	Instant reclose Qualification No OC	FLT[MCU]	Normal	No O/C & VLoss; Qualify for instant reclose
1152	4434	Persistent VLoss; Reclose Qualified	FLT[MCU]	Normal	Persistent VLoss; Breaker Operation Qualified
1153	4435	Instant Reclose; Not Counted	FLT[MCU]	Normal	OC + Instant Reclose Qualification
1154	4436	Tripped on Phase Loss	FLT[MCU]	Normal	Tripped based on Phase Loss
1155	4437	SW1 Ph. Loss Prot. LOV Phase A	FLT[MCU]	Normal	SW1 Ph. Loss Prot. LOV Phase A
1156	4438	SW1 Ph. Loss Prot. LOV Phase B	FLT[MCU]	Normal	SW1 Ph. Loss Prot. LOV Phase B
1157	4439	SW1 Ph. Loss Prot. LOV Phase C	FLT[MCU]	Normal	SW1 Ph. Loss Prot. LOV Phase C
1158	4440	SW2 Ph. Loss Prot. LOV Phase A	FLT[MCU]	Normal	SW2 Ph. Loss Prot. LOV Phase A
1159	4441	SW2 Ph. Loss Prot. LOV Phase B	FLT[MCU]	Normal	SW2 Ph. Loss Prot. LOV Phase B
115a	4442	SW2 Ph. Loss Prot. LOV Phase C	FLT[MCU]	Normal	SW2 Ph. Loss Prot. LOV Phase C
1201	4609	Originating a SRC Runner	NET[MCU]	All	Data 1:Debug Data Data1 Type: ushort Data 2:Debug Data Data2 Type: ushort Data 3:Debug Data Data3 Type: ushort Data 4:Debug Data Data4 Type: ushort
1202	4610	Received Old Runner	NET[MCU]	All	Data 1:Debug Data Data1 Type: ushort Data 2:Debug Data Data2 Type: ushort Data 3:Debug Data Data3 Type: ushort
1203	4611	Received Duplicate Runner	NET[MCU]	All	Data 1:Debug Data Data1 Type: ushort Data 2:Debug Data Data2 Type: ushort
1204	4612	Received New Runner	NET[MCU]	All	Data 1:Debug Data Data1 Type: ushort Data 2:Debug Data Data2 Type: ushort
1205	4613	Forwarding a Received Runner	NET[MCU]	All	Data 1:Debug Data Data1 Type: ushort Data 2:Debug Data Data2 Type: ushort Data 3:Debug Data Data3 Type: ushort Data 4:Debug Data Data4 Type: ushort
1206	4614	Originating an Endload Runner	NET[MCU]	All	Data 1:Debug Data Data1 Type: ushort Data 2:Debug Data Data2 Type: ushort Data 3:Debug Data Data3 Type: ushort
1207	4615	COS Cleared	NET[MCU]	All	Data 1:Debug Data Data1 Type: ushort Data 2:Debug Data Data2 Type: ushort Data 3:Debug Data Data3 Type: ushort Data 4:Debug Data Data4 Type: ushort
1208	4616	Team Config Netlist Mismatch	NET[MCU]	All	Data 1:Debug Data Data1 Type: ushort Data 2:Debug Data Data2 Type: ushort

Definitions of Historic Events

					Data 3:Debug Data Data3 Type: ushort Data 4:Debug Data Data4 Type: ushort
1209	4617	COS Active	NET[MCU]	All	Data 1:Debug Data Data1 Type: ushort Data 2:Debug Data Data2 Type: ushort Data 3:Debug Data Data3 Type: ushort Data 4:Debug Data Data4 Type: ushort
120A	4618	Missing Runners	NET[MCU]	Normal	Data 1:Expected Count Data1 Type: ushort Data 2:Received Count Data2 Type: ushort
120B	4619	All Runners Received	NET[MCU]	Normal	Data 1:Expected Count Data1 Type: ushort Data 2:Received Count Data2 Type: ushort
120C	4620	NETLIST no alt source found	NET[MCU]	All	Data 1:Debug Data Data1 Type: ushort Data 2:Debug Data Data2 Type: ushort Data 3:Debug Data Data3 Type: ushort Data 4:Debug Data Data4 Type: ushort
120D	4621	NETLIST alt source result	NET[MCU]	All	Data 1:Debug Data Data1 Type: ushort Data 2:Debug Data Data2 Type: ushort Data 3:Debug Data Data3 Type: ushort Data 4:Debug Data Data4 Type: ushort
120E	4622	Building COS Runner	NET[MCU]	All	Data 1:Debug Data Data1 Type: ushort Data 2:Debug Data Data2 Type: ushort Data 3:Debug Data Data3 Type: ushort Data 4:Debug Data Data4 Type: ushort
120F	4623	COS Reported by IT	NET[MCU]	All	Data 1:Debug Data Data1 Type: ushort Data 2:Debug Data Data2 Type: ushort Data 3:Debug Data Data3 Type: ushort Data 4:Debug Data Data4 Type: ushort
1210	4624	COS Received in Runner	NET[MCU]	All	Data 1:Debug Data Data1 Type: ushort Data 2:Debug Data Data2 Type: ushort Data 3:Debug Data Data3 Type: ushort Data 4:Debug Data Data4 Type: ushort
1211	4625	Forwarding Dup. COS Runner	NET[MCU]	All	Data 1:Debug Data Data1 Type: ushort Data 2:Debug Data Data2 Type: ushort Data 3:Debug Data Data3 Type: ushort Data 4:Debug Data Data4 Type: ushort
1212	4626	Loc Netlist Old. Need it From RTU	NET[MCU]	All	Data 1:Debug Data Data1 Type: ushort Data 2:Debug Data Data2 Type: ushort Data 3:Debug Data Data3 Type: ushort Data 4:Debug Data Data4 Type: ushort
1213	4627	New Netlist Request From RTU	NET[MCU]	All	Data 1:Debug Data Data1 Type: ushort Data 2:Debug Data Data2 Type: ushort Data 3:Debug Data Data3 Type: ushort Data 4:Debug Data Data4 Type: ushort
1214	4628	Netlist Record Sent	NET[MCU]	All	Data 1:Debug Data Data1 Type: ushort

					Data 2:Debug Data Data2 Type: ushort Data 3:Debug Data Data3 Type: ushort Data 4:Debug Data Data4 Type: ushort
1215	4629	Netlist Record Received	NET[MCU]	All	Data 1:Debug Data Data1 Type: ushort Data 2:Debug Data Data2 Type: ushort Data 3:Debug Data Data3 Type: ushort Data 4:Debug Data Data4 Type: ushort
1216	4630	ITII Mode is Active	NET[MCU]	Normal	Data 1:Debug Data Data1 Type: Instance Data 2:Debug Data Data2 Type: ushort Data 3:Debug Data Data3 Type: ushort Data 4:Debug Data Data4 Type: ushort
1217	4631	ITII Mode is Inactive	NET[MCU]	Normal	Data 1:Debug Data Data1 Type: Instance Data 2:Debug Data Data2 Type: ushort Data 3:Debug Data Data3 Type: ushort Data 4:Debug Data Data4 Type: ushort
1218	4632	NET: Missing Runners in Adj Net Active	NET[MCU]	All	Data 1:Null Data1 Type: ushort Data 2:Null Data2 Type: ushort Data 3:Null Data3 Type: ushort Data 4:Null Data4 Type: ushort
1219	4633	NET: Missing Runners Adj Net Inactive	NET[MCU]	All	Data 1:Null Data1 Type: ushort Data 2:Null Data2 Type: ushort Data 3:Null Data3 Type: ushort Data 4:Null Data4 Type: ushort
1220	4640	NETX Adj data delivery runner timeout	NET[MCU]	Normal	Data 1:Null Data1 Type: ushort Data 2:Null Data2 Type: ushort Data 3:Null Data3 Type: ushort Data 4:Null Data4 Type: ushort
1221	4641	NETX Adj data delivery runner initiated	NET[MCU]	Normal	Data 1:Null Data1 Type: ushort Data 2:Null Data2 Type: ushort Data 3:Null Data3 Type: ushort Data 4:Null Data4 Type: ushort
1222	4642	NETX Indiv Adj Data Runner Path Timeout	NET[MCU]	Normal	Data 1:Null Data1 Type: ushort Data 2:Null Data2 Type: ushort Data 3:Null Data3 Type: ushort Data 4:Null Data4 Type: ushort
1223	4643	NETX Indiv Adj Data Runner Path Present	NET[MCU]	Normal	Data 1:Null Data1 Type: ushort Data 2:Null Data2 Type: ushort Data 3:Null Data3 Type: ushort Data 4:Null Data4 Type: ushort
1241	4673	NETV: Netlist Changed	NET[MCU]	Normal	Data 1: Netview number of devices/switches in DivisionNet Data1 Type: NumOfDevices Data 2: Number of entries in the D-W (Device-Wire) tables Data2 Type: NumOfWirePairs Data 3: Number of Teams Data3 Type: NumOfTeams Data 4:Debug Data Data4 Type: ushort
1242	4674	NETV: Network Config. Changed	NET[MCU]	Normal	

Definitions of Historic Events

					Data 1:Debug Data Data1 Type: ushort Data 2:Debug Data Data2 Type: ushort Data 3:Debug Data Data3 Type: ushort Data 4:Debug Data Data4 Type: ushort
1250	4688	NETX dispatch initiated	NET[MCU]	Normal	Data 1: Net Object Type Data1 Type: RunnerType Data 2: Source RTU Address Data2 Type: RTUAddress Data 3: Source Node ID Data3 Type: SrcNodeID Data 4: Destination Node ID Data4 Type: DestNodeID
1251	4689	NETX EPD netlist received	NET[MCU]	Normal	Data 1: Net Object ID Data1 Type: ObjID Data 2: Size of the arriving object in bytes, also a flag/signal of arrival to State machine A Data2 Type: SizeOfObject Data 3: Net Object Length Data3 Type: ObjectLength Data 4: Bufsiz Data4 Type: bufsiz
1252	4690	NETX Net list trouble	NET[MCU]	Normal	Data 1: Net Object ID Data1 Type: ObjID Data 2: Size of the arriving object in bytes, also a flag/signal of arrival to State machine A Data2 Type: SizeOfObject Data 3: Net Object Length Data3 Type: ObjectLength Data 4: Bufsiz Data4 Type: bufsiz
1253	4691	NETX bad runner index	NET[MCU]	Normal	Data 1: Runner Number Data1 Type: RunnerNumber Data 2: Feeder Net ID Data2 Type: FeederNetID Data 3: Feeder Net CRC Data3 Type: FeederNetCRC Data 4:Null Data4 Type: ushort
1254	4692	NETX node index not found	NET[MCU]	Normal	Data 1: Source RTU Address Data1 Type: RTUAddress Data 2: Destination Node ID Data2 Type: DestNodeID Data 3: Node Index Data3 Type: NodeIndex Data 4: Net Object Type Data4 Type: RunnerType
1255	4693	NETX bad object data length	NET[MCU]	Normal	Data 1: Source RTU Address Data1 Type: RTUAddress Data 2: Net Object Length Data2 Type: ObjectLength Data 3: Data Length Data3 Type: DataLength Data 4: Net Object Type Data4 Type: RunnerType
1256	4694	NETX new netlist delivery	NET[MCU]	Normal	Data 1: Source RTU Address Data1 Type: RTUAddress Data 2: Destination Node ID Data2 Type: DestNodeID Data 3: Runner Number Data3 Type: RunnerNumber Data 4: Size of runner in RTU addresses Data4 Type: RTUAddress
1257	4695	NETX chk for comm chk runner's passing	NET[MCU]	Normal	NETX check for communication check runner's passing Data 1: Source RTU Address Data1 Type: RTUAddress Data 2: Destination Node ID Data2 Type: DestNodeID Data 3: Runner Number Data3 Type: RunnerNumber Data 4: Feeder Net ID Data4 Type: FeederNetID
1258	4696	NETX chk for comm chk runner's return	NET[MCU]	Normal	NETX check for communication check runner's return Data 1: Source RTU Address Data1 Type: RTUAddress Data 2: Destination Node ID Data2 Type: DestNodeID Data 3: Runner Number Data3 Type: RunnerNumber Data 4: Feeder Net ID Data4 Type: FeederNetID
1259	4697	NETX intiate communication check runner	NET[MCU]	Normal	Data 1:Null Data1 Type: ushort Data 2:Null Data2 Type: ushort Data 3:Null Data3 Type: ushort Data 4:Null Data4 Type: ushort

125A	4698	NEX communication check runner's timeout	NET[MCU]	Normal	Data 1:Null Data1 Type: ushort Data 2:Null Data2 Type: ushort Data 3:Null Data3 Type: ushort Data 4:Null Data4 Type: ushort
125B	4699	NETX communication check runner complete	NET[MCU]	Normal	Data 1:Null Data1 Type: ushort Data 2:Null Data2 Type: ushort Data 3:Null Data3 Type: ushort Data 4:Null Data4 Type: ushort
125C	4700	NETX activation runner return	NET[MCU]	Normal	Data 1: Source RTU Address Data1 Type: RTUAddress Data 2: Destination Node ID Data2 Type: DestNodeID Data 3: Runner Number Data3 Type: RunnerNumber Data 4: Size of runner in RTU addresses Data4 Type: RTUAddress
125D	4701	NETX activation of the runner's passing	NET[MCU]	Normal	Data 1: Source RTU Address Data1 Type: RTUAddress Data 2: Destination Node ID Data2 Type: DestNodeID Data 3: Runner Number Data3 Type: RunnerNumber Data 4: Size of runner in RTU addresses Data4 Type: RTUAddress
125E	4702	NETX activation of runner's intiation	NET[MCU]	Normal	Data 1: RETV:AT EPD Launch all the Activation Runners to the next RTU in line Data1 Type: ushort Data 2:Null Data2 Type: ushort Data 3:Null Data3 Type: ushort Data 4:Null Data4 Type: ushort
125F	4703	NETX activation of runner is complete	NET[MCU]	Normal	Data 1:Null Data1 Type: ushort Data 2:Null Data2 Type: ushort Data 3:Null Data3 Type: ushort Data 4:Null Data4 Type: ushort
1260	4704	NETX activation of runner's timout	NET[MCU]	Normal	Data 1:Null Data1 Type: ushort Data 2:Null Data2 Type: ushort Data 3:Null Data3 Type: ushort Data 4:Null Data4 Type: ushort
1261	4705	NETX collection runner return	NET[MCU]	Normal	Data 1: Source RTU Address Data1 Type: RTUAddress Data 2: Destination Node ID Data2 Type: DestNodeID Data 3: Runner Number Data3 Type: RunnerNumber Data 4: FeederNetID Data4 Type: FeederNetID
1262	4706	NETX collection runner's passing	NET[MCU]	Normal	Data 1: Source RTU Address Data1 Type: RTUAddress Data 2: Destination Node ID Data2 Type: DestNodeID Data 3: Runner Number Data3 Type: RunnerNumber Data 4: FeederNetID Data4 Type: FeederNetID
1263	4707	NETX collection as the runner intiates	NET[MCU]	Normal	Data 1:Null Data1 Type: ushort Data 2:Null Data2 Type: ushort Data 3:Null Data3 Type: ushort Data 4:Null Data4 Type: ushort
1264	4708	NETX collection of runner's timeout	NET[MCU]	Normal	Data 1: RETV:AT EPD Launch all the Activation Runners to the next RTU in line Data1 Type: ushort

Definitions of Historic Events

					Data 2:Null Data2 Type: ushort Data 3:Null Data3 Type: ushort Data 4:Null Data4 Type: ushort
1265	4709	NETX data delivery runner's return	NET[MCU]	Normal	Data 1: Source RTU Address Data1 Type: RTUAddress Data 2: Destination Node ID Data2 Type: DestNodeID Data 3: Runner Number Data3 Type: RunnerNumber Data 4: FeederNetID Data4 Type: FeederNetID
1266	4710	NETX data delivery of runner's passing	NET[MCU]	Normal	Data 1: Source RTU Address Data1 Type: RTUAddress Data 2: Destination Node ID Data2 Type: DestNodeID Data 3: Runner Number Data3 Type: RunnerNumber Data 4: FeederNetID Data4 Type: FeederNetID
1267	4711	NETX data delivery runner is initiated	NET[MCU]	Normal	Data 1:Null Data1 Type: ushort Data 2:Null Data2 Type: ushort Data 3:Null Data3 Type: ushort Data 4:Null Data4 Type: ushort
1268	4712	NETX data delivery of runner's timeout	NET[MCU]	Normal	Data 1:Null Data1 Type: ushort Data 2:Null Data2 Type: ushort Data 3:Null Data3 Type: ushort Data 4:Null Data4 Type: ushort
1269	4713	NETX Feeder Net delivery to initiate rnr	NET[MCU]	Normal	NETX Feeder Net delivery to initiate runner Data 1:Null Data1 Type: ushort Data 2:Null Data2 Type: ushort Data 3:Null Data3 Type: ushort Data 4:Null Data4 Type: ushort
126A	4714	NETX Feeder Net runner delivery complete	NET[MCU]	Normal	>NETX Feeder Net delivery of runner is complete Data 1:Null Data1 Type: ushort Data 2:Null Data2 Type: ushort Data 3:Null Data3 Type: ushort Data 4:Null Data4 Type: ushort
126B	4715	NETX Feeder Net delivery rnr's timeout	NET[MCU]	Normal	NETX Feeder Net delivery runner's timeout Data 1:Null Data1 Type: ushort Data 2:Null Data2 Type: ushort Data 3:Null Data3 Type: ushort Data 4:Null Data4 Type: ushort
126C	4716	NETX data runner's cycle is complete	NET[MCU]	Normal	Data 1:Null Data1 Type: ushort Data 2:Null Data2 Type: ushort Data 3:Null Data3 Type: ushort Data 4:Null Data4 Type: ushort
126D	4717	NETX continue adjacent distributers	NET[MCU]	Normal	Data 1: Source RTU Address Data1 Type: RTUAddress Data 2: Destination Node ID Data2 Type: DestNodeID Data 3: Runner Number Data3 Type: RunnerNumber Data 4:Null Data4 Type: ushort
126E	4718	NETX inti adj Feeder Net distributers	NET[MCU]	Normal	NETX inti adjacent Feeder Net distributers Data 1: Source RTU Address Data1 Type: RTUAddress Data 2: Net Object ID Data2 Type: ObjID Data 3: Destination Node ID Data3 Type: DestNodeID Data 4: Net Object Length Data4 Type: ObjectLength
126F	4719	NETX init adjacent data block reporter	NET[MCU]	Normal	NETX inti adjacent data block reporter Data 1: Source RTU Address Data1 Type: RTUAddress Data 2: Net Object ID Data2 Type: ObjID

Definitions of Historic Events

					Data 3: Destination Node ID Data3 Type: DestNodeID Data 4: Net Object Length Data4 Type: ObjectLength
1270	4720	NETX fwd adjacent data block reporter	NET[MCU]	Normal	NETX forward adjacent data block reporter Data 1: Source RTU Address Data1 Type: RTUAddress Data 2: Net Object ID Data2 Type: ObjID Data 3: Destination Node ID Data3 Type: DestNodeID Data 4: Net Object Length Data4 Type: ObjectLength
1271	4721	NETX sync net list to DAT delayed	NET[MCU]	Normal	Data 1: SyncStat Data1 Type: syncstat Data 2:Null Data2 Type: ushort Data 3:Null Data3 Type: ushort Data 4:Null Data4 Type: ushort
1272	4722	NETX sync net list to DAT is not good	NET[MCU]	Normal	Data 1: SyncStat Data1 Type: syncstat Data 2:Null Data2 Type: ushort Data 3:Null Data3 Type: ushort Data 4:Null Data4 Type: ushort
1273	4723	NETX netlist copy request	NET[MCU]	Normal	Data 1: Source RTU Address Data1 Type: RTUAddress Data 2: Net object ID Data2 Type: ObjID Data 3: Feeder Net ID Data3 Type: FeederNetID Data 4: Feeder Net CRC Data4 Type: FeederNetCRC
1274	4724	NETX netlist copy response	NET[MCU]	Normal	Data 1: Source RTU Address Data1 Type: RTUAddress Data 2: Net Object ID Data2 Type: ObjID Data 3: Feeder Net ID Data3 Type: FeederNetID Data 4: Feeder Net CRC Data4 Type: FeederNetCRC
1275	4725	NETX Feeder Net ID and CRC mismatch	NET[MCU]	Normal	Data 1: Source RTU Address Data1 Type: RTUAddress Data 2: Feeder Net ID Data2 Type: FeederNetID Data 3: Feeder Net CRC Data3 Type: FeederNetCRC Data 4: Net Object Type Data4 Type: RunnerType
1276	4726	NETX netlist reporter returned	NET[MCU]	Normal	Data 1: Source RTU Address Data1 Type: RTUAddress Data 2: Net Object ID Data2 Type: ObjID Data 3: Destination Node ID Data3 Type: DestNodeID Data 4: Object Length Data4 Type: ObjectLength
1277	4727	NETX forward net list reporter	NET[MCU]	Normal	Data 1: Source RTU Address Data1 Type: RTUAddress Data 2: Net Object ID Data2 Type: ObjID Data 3: Destination Node ID Data3 Type: DestNodeID Data 4: Object Length Data4 Type: ObjectLength
1278	4728	NETX net list copy initiate	NET[MCU]	Normal	Data 1: Feeder Net ID Data1 Type: FeederNetID Data 2: Feeder Net CRC Data2 Type: FeederNetCRC Data 3:Null Data3 Type: ushort Data 4:Null Data4 Type: ushort
1279	4729	NETX report adj netlist distributers	NET[MCU]	Normal	NETX report adjacent netlist distributors Data 1:Null Data1 Type: ushort Data 2:Null Data2 Type: ushort Data 3:Null Data3 Type: ushort Data 4:Null Data4 Type: ushort
127A	4730	NETX report adjacent data block	NET[MCU]	Normal	Data 1:Null Data1 Type: ushort Data 2:Null Data2 Type: ushort

Definitions of Historic Events

					Data 3:Null Data3 Type: ushort Data 4:Null Data4 Type: ushort
1280	4736	Configuration is in progress	NET[MCU]	Normal	Data 1:Debug Data Data1 Type: Instance Data 2:Debug Data Data2 Type: ushort Data 3:Debug Data Data3 Type: ushort Data 4:Debug Data Data4 Type: ushort
1281	4737	Configuration is not in progress	NET[MCU]	Normal	Data 1:Debug Data Data1 Type: ushort Data 2:Debug Data Data2 Type: ushort Data 3:Debug Data Data3 Type: ushort Data 4:Debug Data Data4 Type: ushort
1282	4738	Invalid Request Config Request	NET[MCU]	Normal	Data 1:Debug Data Data1 Type: ushort Data 2:Debug Data Data2 Type: ushort Data 3:Debug Data Data3 Type: ushort Data 4:Debug Data Data4 Type: ushort
1283	4739	Settings Accepted	NET[MCU]	Normal	Data 1:Debug Data Data1 Type: ushort Data 2:Debug Data Data2 Type: ushort Data 3:Debug Data Data3 Type: ushort Data 4:Debug Data Data4 Type: ushort
1284	4740	Settings Received	NET[MCU]	Normal	If Data 4 reads 10 then Data 4 = Net Object State Revived Command Data 1: Net View number of devices in Division Data1 Type: ushort Data 2: Error Code 1 Data2 Type: Hexushort Data 3: Error Code 2 Data3 Type: Hexushort Data 4:Null Data4 Type: ushort
1285	4741	Propagation Enabled	NET[MCU]	Normal	Data 1:Debug Data Data1 Type: ushort Data 2:Debug Data Data2 Type: ushort Data 3:Debug Data Data3 Type: ushort Data 4:Debug Data Data4 Type: ushort
1286	4742	Propagation Disabled	NET[MCU]	Normal	Data 1:Debug Data Data1 Type: ushort Data 2:Debug Data Data2 Type: ushort Data 3:Debug Data Data3 Type: ushort Data 4:Debug Data Data4 Type: ushort
1287	4743	Netlist Rejected by IntelliTEAM	NET[MCU]	Normal	Data 1:Debug Data Data1 Type: ushort Data 2:Debug Data Data2 Type: ushort Data 3:Debug Data Data3 Type: ushort Data 4:Debug Data Data4 Type: ushort
1290	4752	Netlist Loaded From BMM	NET[MCU]	Normal	
1291	4753	Netlist BMM Load Issue	NET[MCU]	Normal	Data 1:Debug Data Data1 Type: ushort Data 2:Debug Data Data2 Type: ushort Data 3:Debug Data Data3 Type: ushort Data 4:Debug Data Data4 Type: ushort
1292	4754	Netlist Saved To BMM	NET[MCU]	Normal	
1293	4755	Netlist BMM Save Issue	NET[MCU]	Normal	Data 1:Debug Data Data1 Type: ushort Data 2:Debug Data Data2 Type: ushort Data 3:Debug Data Data3 Type: ushort Data 4:Debug Data Data4 Type: ushort

1294	4756	Netlist Was Erased	NET[MCU]	Normal	Data 1:Debug Data Data1 Type: ushort
12A0	4768	NETO buffer pool initialized	NET[MCU]	Normal	Data 1:Null Data1 Type: ushort Data 2:Null Data2 Type: ushort Data 3:Null Data3 Type: ushort Data 4:Null Data4 Type: ushort
12A1	4769	NETO combined buffers	NET[MCU]	Normal	Data 1: Loop Count Data1 Type: ushort Data 2: Def Count Data2 Type: ushort Data 3:Null Data3 Type: ushort Data 4:Null Data4 Type: ushort
12A2	4770	NETO buffer pool length is bad	NET[MCU]	Normal	Data 1: Total Length Data1 Type: totallen Data 2: Pool Size Data2 Type: ushort Data 3: Cumulative Free Buffer Space Data3 Type: netobuffFree Data 4: Loop Count Data4 Type: ushort
12A3	4771	NETO does not enough space to store obj	NET[MCU]	Normal	NETO does not have enough space to store object Data 1: Net Fragment ID Data1 Type: netfragID Data 2: Source Net ID Data2 Type: SrcNodeID Data 3: Cumulative Free Buffer Space Data3 Type: netobuffFree Data 4: Data Length Data4 Type: DataLength
12A4	4772	NETO object buffering is full	NET[MCU]	Normal	Data 1: Net Fragment ID Data1 Type: netfragID Data 2: Source Net ID Data2 Type: SrcNodeID Data 3:Null Data3 Type: ushort Data 4:Null Data4 Type: ushort
12A5	4773	NETO bad store request	NET[MCU]	Normal	Data 1: Net Fragment ID Data1 Type: netfragID Data 2: Source Net ID Data2 Type: SrcNodeID Data 3:Null Data3 Type: ushort Data 4:Null Data4 Type: ushort
12A6	4774	NETO data buffer is full	NET[MCU]	Normal	Data 1: Net Fragment ID Data1 Type: netfragID Data 2: Source Net ID Data2 Type: SrcNodeID Data 3:Null Data3 Type: ushort Data 4:Null Data4 Type: ushort
12A7	4775	NETO object handed up	NET[MCU]	Normal	Data 1: Net Object State Data1 Type: ObjState Data 2: Source RTU Address Data2 Type: RTUAddress Data 3: Net Object ID Data3 Type: ObjID Data 4:Null Data4 Type: ushort
12A8	4776	NETO deleted object FIR only	NET[MCU]	Normal	Data 1: Source RTU Address Data1 Type: RTUAddress Data 2: Net Object ID Data2 Type: ObjID Data 3: Net Fragment ID Data3 Type: netfragID Data 4:Null Data4 Type: ushort
12A9	4777	NETO bad fragment added	NET[MCU]	Normal	Data 1: Source RTU Address Data1 Type: RTUAddress Data 2: Net Object ID Data2 Type: ObjID Data 3: Net Fragment ID Data3 Type: netfragID Data 4: Net Fragment ID Data4 Type: netfragID
12AA	4778	NETO fragment not found	NET[MCU]	Normal	Data3 could equal the NetObject State if we are talking about the NETxVerboseLog Data 1: Source RTU Address Data1 Type: RTUAddress

Definitions of Historic Events

					Data 2: Net Object ID Data2 Type: ObjID Data 3: Net Fragment ID Data3 Type: netfragID Data 4:Null Data4 Type: ushort
12AB	4779	NETO object fragment sent	NET[MCU]	Normal	Data 1: Net Fragment ID Data1 Type: netfragID Data 2: Net object ID Data2 Type: ObjID Data 3: Net object type Data3 Type: RunnerType Data 4: Data Length Data4 Type: DataLength
12AC	4780	NETO object fragment was declined	NET[MCU]	Normal	Data 1: xmtresultcode Data1 Type: xmtresultcode Data 2: Destination RTU Address Data2 Type: RTUAddress Data 3: Net Fragment ID Data3 Type: netfragID Data 4: Data Length Data4 Type: DataLength
12AD	4781	NETO object list's timeout	NET[MCU]	Normal	Data 1: Source RTU Address Data1 Type: RTUAddress Data 2: Net Fragment ID Data2 Type: netfragID Data 3: Net Object ID Data3 Type: ObjID Data 4: Net Object State Data4 Type: ObjState
12B0	4784	NETD ACK has failed	NET[MCU]	Normal	Data 1: Destination RTU Address Data1 Type: RTUAddress Data 2: DataLength Data2 Type: DataLength Data 3: Result= (netdSendObject(DNPGetLocalAddress(DNPADDRGOLDEN), destAddr, DNPCIDNETOBJMGNT, datatosend, (NETOBJHEADDATALEN + 1)); Data3 Type: ushort Data 4:Null Data4 Type: ushort
12B1	4785	NETD sending object	NET[MCU]	Normal	Data 1: Destination RTU Address Data1 Type: RTUAddress Data 2: Data Length Data2 Type: DataLength Data 3: Result=DNPXmtMultiService Data3 Type: ushort Data 4: Connection ID Data4 Type: connectID
12B2	4786	NETD received object	NET[MCU]	Normal	Data 1: Source RTU Address Data1 Type: RTUAddress Data 2: Net Object ID Data2 Type: ObjID Data 3: Net Object Type Data3 Type: RunnerType Data 4: Data Length Data4 Type: DataLength
1300	4864	SW1 Phase A Overcurrent Start	ACW[MCU]	Normal	Current Over Threshold
1301	4865	SW1 Phase B Overcurrent Start	ACW[MCU]	Normal	Current Over Threshold
1302	4866	SW1 Phase C Overcurrent Start	ACW[MCU]	Normal	Current Over Threshold
1303	4867	SW1 Neutral Overcurrent Start	ACW[MCU]	Normal	Current Over Threshold
1304	4868	SW1 Phase A Overcurrent End	ACW[MCU]	Normal	Current Below Threshold
1305	4869	SW1 Phase B Overcurrent End	ACW[MCU]	Normal	Current Below Threshold
1306	4870	SW1 Phase C Overcurrent End	ACW[MCU]	Normal	Current Below Threshold
1307	4871	SW1 Neutral Overcurrent End	ACW[MCU]	Normal	Current Below Threshold
1308	4872	SW1 Phase A Fault Detected	ACW[MCU]	Normal	Current Over Threshold for Duration Threshold
1309	4873	SW1 Phase B Fault Detected	ACW[MCU]	Normal	Current Over Threshold for Duration Threshold
130A	4874	SW1 Phase C Fault Detected	ACW[MCU]	Normal	Current Over Threshold for Duration Threshold
130B	4875	SW1 Neutral Fault Detected	ACW[MCU]	Normal	Current Over Threshold for Duration THreshold
130C	4876	SW2 Phase A Overcurrent Start	ACW[MCU]	Normal	Current Over Threshold
130D	4877	SW2 Phase B Overcurrent Start	ACW[MCU]	Normal	Current Over Threshold
130E	4878	SW2 Phase C Overcurrent Start	ACW[MCU]	Normal	Current Over Threshold
130F	4879	SW2 Neutral Overcurrent Start	ACW[MCU]	Normal	Current Over Threshold
1310	4880	SW2 Phase A Overcurrent End	ACW[MCU]	Normal	Current Below Threshold
1311	4881	SW2 Phase B Overcurrent End	ACW[MCU]	Normal	Current Below Threshold
1312	4882	SW2 Phase C Overcurrent End	ACW[MCU]	Normal	Current Below Threshold
1313	4883	SW2 Neutral Overcurrent End	ACW[MCU]	Normal	Current Below Threshold

Definitions of Historic Events

1314	4884	SW2 Phase A Fault Detected	ACW[MCU]	Normal	Current Over Threshold for Duration Threshold
1315	4885	SW2 Phase B Fault Detected	ACW[MCU]	Normal	Current Over Threshold for Duration Threshold
1316	4886	SW2 Phase C Fault Detected	ACW[MCU]	Normal	Current Over Threshold for Duration Threshold
1317	4887	SW2 Neutral Fault Detected	ACW[MCU]	Normal	Current Over Threshold for Duration Threshold
1318	4888	SW1 Phase A Loss of Voltage	ACW[MCU]	Normal	Voltage below Threshold
1319	4889	SW1 Phase A Normal Voltage	ACW[MCU]	Normal	Voltage above Threshold
131A	4890	SW1 Phase B Loss of Voltage	ACW[MCU]	Normal	Voltage below Threshold
131B	4891	SW1 Phase B Normal Voltage	ACW[MCU]	Normal	Voltage above Threshold
131C	4892	SW1 Phase C Loss of Voltage	ACW[MCU]	Normal	Voltage below Threshold
131D	4893	SW1 Phase C Normal Voltage	ACW[MCU]	Normal	Voltage above Threshold
131E	4894	SW2 Phase A Loss of Voltage	ACW[MCU]	Normal	Voltage below Threshold
131F	4895	SW2 Phase A Normal Voltage	ACW[MCU]	Normal	Voltage above Threshold
1320	4896	SW2 Phase B Loss of Voltage	ACW[MCU]	Normal	Voltage below Threshold
1321	4897	SW2 Phase B Normal Voltage	ACW[MCU]	Normal	Voltage above Threshold
1322	4898	SW2 Phase C Loss of Voltage	ACW[MCU]	Normal	Voltage below Threshold
1323	4899	SW2 Phase C Normal Voltage	ACW[MCU]	Normal	Voltage above Threshold
1324	4900	SW1 Voltage Sensor Bad On	ACW[MCU]	Normal	SW1 Voltage Sensor Bad On
1325	4901	SW1 Voltage Sensor Bad Off	ACW[MCU]	Normal	SW1 Voltage Sensor Bad Off
1326	4902	SW2 Voltage Sensor Bad On	ACW[MCU]	Normal	SW2 Voltage Sensor Bad On
1327	4903	SW2 Voltage Sensor Bad Off	ACW[MCU]	Normal	SW2 Voltage Sensor Bad Off
1328	4904	SW1 Voltage Sensor Recovered to Normal	ACW[MCU]	Normal	SW1 V Sensor recovered to normal
1329	4905	SW2 Voltage Sensor Recovered to Normal	ACW[MCU]	Normal	SW2 V Sensor recovered to normal
132A	4906	SW1 Direction 1 Current Flow On	ACW[MCU]	Normal	
132B	4907	SW1 Direction 1 Current Flow Off	ACW[MCU]	Normal	
132C	4908	SW1 Direction 2 Current Flow On	ACW[MCU]	Normal	
132D	4909	SW1 Direction 2 Current Flow Off	ACW[MCU]	Normal	
132E	4910	SW2 Direction 1 Current Flow On	ACW[MCU]	Normal	
132F	4911	SW2 Direction 1 Current Flow Off	ACW[MCU]	Normal	
1330	4912	SW2 Direction 2 Current Flow On	ACW[MCU]	Normal	
1331	4913	SW2 Direction 2 Current Flow Off	ACW[MCU]	Normal	
1400	5120	Fail Override Active	CMD[MCU]	Normal	Fail Override is active
1401	5121	Fail Override OFF	CMD[MCU]	Normal	Fail Override Disabled
					Command Received
1402	5122	Command	CMD[MCU]	Normal	Data 1: Command Code Data1 Type: CommandCode Data 2: Command Code Data2 Type: CommandSource Data 4: SCADA Command Data4 Type: SCADACmd
1403	5123	External Command Rejected	CMD[MCU]	Normal	External Command Rejected
1404	5124	External Command Overridden	CMD[MCU]	Normal	Switch Op Allowed by Fail Ovewrride Data 1: Command Code Data1 Type: CommandCode
1405	5125	Hot Line Tag Active	CMD[MCU]	Normal	Hot Line Tag is active
1406	5126	Hot Line Tag OFF	CMD[MCU]	Normal	Hot Line Tag Disabled
1407	5127	SW1 Hot Line Tag Active	CMD[MCU]	Normal	SW1 Hot Line Tag is active
1408	5128	SW1 Hot Line Tag OFF	CMD[MCU]	Normal	SW1 Hot Line Tag Disabled
1409	5129	SW2 Hot Line Tag Active	CMD[MCU]	Normal	SW2 Hot Line Tag is active
140A	5130	SW2 Hot Line Tag OFF	CMD[MCU]	Normal	SW2 Hot Line Tag Disabled
140B	5131	SW3 Hot Line Tag Active	CMD[MCU]	Normal	SW3 Hot Line Tag is active
140C	5132	SW3 Hot Line Tag OFF	CMD[MCU]	Normal	SW3 Hot Line Tag Disabled
140D	5133	Hot Line Tag Set Local	CMD[MCU]	Normal	Hot Line Tag Set by FP or WiFi
140E	5134	Hot Line Tag Set Remote	CMD[MCU]	Normal	Hot Line Tag Set by SCADA
140F	5135	SCADA Command	CMD[MCU]	Normal	SCADA Command Received

Definitions of Historic Events

					Data 1: Command Code Data1 Type: SCADACode Data 3: SCADA Command Data3 Type: SCADACmd
1410	5136	SW1 S-T-L On	CMD[MCU]	Normal	SW1 S-T-L On
1411	5137	SW1 S-T-L Off	CMD[MCU]	Normal	SW1 S-T-L Off
1412	5138	SW2 S-T-L On	CMD[MCU]	Normal	SW2 S-T-L On
1413	5139	SW2 S-T-L Off	CMD[MCU]	Normal	SW2 S-T-L Off
1414	5140	Command Backup Issue	CMD[MCU]	Normal	Command Backup Issue Data 1: Reason Data1 Type: ushort Data 2: Step Data2 Type: ushort
1415	5141	Command Restore Issue	CMD[MCU]	Normal	Command Restore Issue Data 1: Reason Data1 Type: ushort Data 2: Step Data2 Type: ushort
1416	5142	Command Backup Success	CMD[MCU]	Normal	Command Backup Success
1417	5143	Command Restore Success	CMD[MCU]	Normal	Command Restore Success
1418	5144	SW Op in progress; cmd ignored	CMD[MCU]	Normal	SW Op in progress; cmd ignored Data 1: Data1 Type: CommandCode Data 2: Data2 Type: CommandSource
1500	5376	SW1 Open	SWX[MCU]	Normal	SW1 Open
1501	5377	SW1 Not Open	SWX[MCU]	Normal	SW1 Close
1502	5378	SW2 Open SWX	SWX[MCU]	Normal	SW2 Open
1503	5379	SW2 Not Open	SWX[MCU]	Normal	SW2 Close
1504	5380	SW3 Open	SWX[MCU]	Normal	SW3 Open
1505	5381	SW3 Not Open	SWX[MCU]	Normal	SW3 Close
1506	5382	SW1 Closed SWX	SWX[MCU]	Normal	SW1 Closed
1507	5383	SW1 Not Closed	SWX[MCU]	Normal	SW1 Not Closed
1508	5384	SW2 Closed SWX	SWX[MCU]	Normal	SW2 Closed
1509	5385	SW2 Not Closed	SWX[MCU]	Normal	SW2 Not Closed
150A	5386	SW3 Closed	SWX[MCU]	Normal	SW3 Closed
150B	5387	SW3 Not Closed	SWX[MCU]	Normal	SW3 Not Closed
150C	5388	Switch 1 Disabled/External Local	SWX[MCU]	Normal	SW1 Has Errors or Manually Disabled Data 1: Switch Data1 Type: SWnum Data 2: Disabled Code Data2 Type: SWDisabledType
150D	5389	SW1 OK	SWX[MCU]	Normal	SW1 OK
150E	5390	Switch 2 Disabled/External Local	SWX[MCU]	Normal	SW2 Has Errors or Manually Disabled Data 1: Switch Data1 Type: SWnum Data 2: Disabled Code Data2 Type: SWDisabledType
150F	5391	SW2 OK	SWX[MCU]	Normal	SW2 OK
1510	5392	Switch 3 Disabled/External Local	SWX[MCU]	Normal	SW3 Has Errors or Manually Disabled
1511	5393	SW3 OK	SWX[MCU]	Normal	SW3 OK
1512	5394	SW1 Visible Disconnect Open	SWX[MCU]	Normal	SW1 Visible Disconnect Open
1513	5395	SW1 Visible Disconnect Closed	SWX[MCU]	Normal	SW1 Visible Disconnect Closed
1514	5396	SW2 Visible Disconnect Open	SWX[MCU]	Normal	SW2 Visible Disconnect Open
1515	5397	SW2 Visible Disconnect Closed	SWX[MCU]	Normal	SW2 Visible Disconnect Closed
1516	5398	SW1 Grounded	SWX[MCU]	Normal	SW1 Grounded
1517	5399	SW1 Not Grounded	SWX[MCU]	Normal	SW1 Not Grounded
1518	5400	SW2 Grounded	SWX[MCU]	Normal	SW2 Grounded
1519	5401	SW2 Not Grounded	SWX[MCU]	Normal	SW2 Not Grounded
151A	5402	SW1 Position Problem	SWX[MCU]	Normal	opensense == closesense
151B	5403	SW1 Position Good	SWX[MCU]	Normal	opensense != closesense
151C	5404	SW2 Position Problem	SWX[MCU]	Normal	opensense == closesense
151D	5405	SW2 Position Good	SWX[MCU]	Normal	opensense != closesense
151E	5406	SW3 Position Problem	SWX[MCU]	Normal	opensense == closesense
151F	5407	SW3 Position Good	SWX[MCU]	Normal	opensense != closesense

1520	5408	Low Pressure	SWX[MCU]	Normal	Low Pressure
1521	5409	Good Pressure	SWX[MCU]	Normal	Low Pressure Vanishes
1522	5410	Global Disable	SWX[MCU]	Normal	Global Disable
1523	5411	Global Disable OFF	SWX[MCU]	Normal	Global Disable switched OFF
1524	5412	Fault Interrupter Active	SWX[MCU]	Normal	Fault Interrupter Active
1525	5413	Fault Interrupter Cleared	SWX[MCU]	Normal	Fault Interrupter Cleared
1526	5414	Could not Reg Double Binary Status Point	SWX[MCU]	Normal	Could not Register Double Binary Status Point
					Manual Operation Status Set
1527	5415	Manual Operation Status Set	SWX[MCU]	Normal	Data 1: Data1 Type: SWnum Data 2: Data2 Type: SWXCommandSource
1528	5416	ManOp Status Check and Cleared	SWX[MCU]	Normal	ManOp Status Check and Cleared Data 1: Data1 Type: SWnum
1529	5417	Switch Operation Failed	SWX[MCU]	Normal	Switch Operation Failed Data 1: Data1 Type: SWnum Data 2: Data2 Type: SWOp
152A	5418	Sw Op Started	SWX[MCU]	Normal	Sw Op Started Data 1: Data1 Type: SWnum Data 2: Data2 Type: SWSWOp
152B	5419	Set Switch Close Operation Count	SWX[MCU]	Normal	Set Switch Close Operation Count Data 1: Data1 Type: SWnum Data 2: Data2 Type: ushort
1538	5432	Error Registering Double Status Point	SWX[MCU]	Normal	Fault Interrupter Cleared Data 1: Data1 Type: SwitchNum
1701	5889	WiFi Intrusion Attempt	WFM[MCU]	Normal	Alarms reported from WiFi module for replay attack or authentication failure. Data 1:Debug Data Data1 Type: ushort
1704	5892	WiFi User Connected	WFM[MCU]	Normal	WiFi user connected.
1705	5893	WiFi User Disconnected	WFM[MCU]	Normal	WiFi user disconnected.
1707	5895	WiFi Intrusion Active	WFM[MCU]	Normal	WiFi intrusion active.
1708	5896	WiFi Intrusion Cleared	WFM[MCU]	Normal	WiFi intrusion cleared.
1709	5897	WiFi SCADA Disable	WFM[MCU]	Normal	WiFi disabled from SCADA.
170A	5898	WiFi SCADA Enable	WFM[MCU]	Normal	WiFi enabled from SCADA.
1751	5969	WiFi Test	WFM[MCU]	Normal	
1800	6144	GPS Enabled by IntelliLink	UTL[MCU]	Normal	Data 1:Debug Data Data1 Type: ushort
1801	6145	GPS Disabled by IntelliLink	UTL[MCU]	Normal	Data 1:Debug Data Data1 Type: ushort
1802	6146	GPS Not Active Time Source On	UTL[MCU]	Normal	GPS is not the active time source set. Data 1: Data1 Type: TimeSource Data 2: Data2 Type: GPSStatus Data 3: Data3 Type: FixQuality
1803	6147	GPS Not Active Time Source Off	UTL[MCU]	Normal	GPS is not the active time source cleared. Data 1: Data1 Type: TimeSource Data 2: Data2 Type: GPSStatus Data 3: Data3 Type: FixQuality
1804	6148	GPS Status Changed	UTL[MCU]	Normal	GPS Status Changed. Data 1: Data1 Type: TimeSource Data 2: Data2 Type: GPSStatus Data 3: Data3 Type: FixQuality Data 4: Data4 Type: OneHexByte

Definitions of Historic Events

190D	6413	Manual Lever Reenable Detected	EVT[MCU]	Normal	
1913	6419	Command Rejected by ATX or Line Faulted	EVT[MCU]	Normal	Data 1: Command Rejected by ATX Data1 Type: ushort Data 2: Blocked by Sync Check Data2 Type: ushort Data 3: PulseClosing Detected Fault Data3 Type: ushort Data 4: Fault Detected in Closing Profile Data4 Type: ushort
1914	6420	Closed Successfully and GP Active	EVT[MCU]	Normal	
1C00	7168	Unknown error	PGE[MCU]	Normal	Data 1: Data1 Type: ushort Data 2: Data2 Type: ushort Data 3: Data3 Type: ushort Data 4: Data4 Type: ushort
1C01	7169	Invalid func code or command received	PGE[MCU]	Normal	Data 1: Data1 Type: ushort Data 2: Data2 Type: ushort Data 3: Data3 Type: ushort Data 4: Data4 Type: ushort
1C02	7170	Control requested on invalid channel	PGE[MCU]	Normal	Data 1: Data1 Type: ushort Data 2: Data2 Type: ushort Data 3: Data3 Type: ushort Data 4: Data4 Type: ushort
1C03	7171	Channel not selected before operate	PGE[MCU]	Normal	Data 1: Data1 Type: ushort Data 2: Data2 Type: ushort Data 3: Data3 Type: ushort Data 4: Data4 Type: ushort
1C04	7172	Control selection timed out	PGE[MCU]	Normal	Data 1: Data1 Type: ushort Data 2: Data2 Type: ushort Data 3: Data3 Type: ushort Data 4: Data4 Type: ushort
1C05	7173	Control select followed by non-operate	PGE[MCU]	Normal	Data 1: Data1 Type: ushort Data 2: Data2 Type: ushort Data 3: Data3 Type: ushort Data 4: Data4 Type: ushort
1C06	7174	Packet CRC error	PGE[MCU]	Normal	Data 1: Data1 Type: ushort Data 2: Data2 Type: ushort Data 3: Data3 Type: ushort Data 4: Data4 Type: ushort
1C07	7175	Control requested while in LOCAL mode	PGE[MCU]	Normal	Data 1: Data1 Type: ushort Data 2: Data2 Type: ushort Data 3: Data3 Type: ushort Data 4: Data4 Type: ushort
1C08	7176	Packet size inconsistent with command	PGE[MCU]	Normal	Data 1: Data1 Type: ushort Data 2: Data2 Type: ushort Data 3: Data3 Type: ushort Data 4: Data4 Type: ushort
1C09	7177	Packet size illegal	PGE[MCU]	Normal	Data 1: Data1 Type: ushort Data 2: Data2 Type: ushort

Definitions of Historic Events

					Data 3: Data3 Type: ushort Data 4: Data4 Type: ushort
1C0A	7178	Packet size too small for this command	PGE[MCU]	Normal	Data 1: Data1 Type: ushort Data 2: Data2 Type: ushort Data 3: Data3 Type: ushort Data 4: Data4 Type: ushort
1C0B	7179	Unsupported request received	PGE[MCU]	Normal	Data 1: Data1 Type: ushort Data 2: Data2 Type: ushort Data 3: Data3 Type: ushort Data 4: Data4 Type: ushort
1C0C	7180	PGE Packet has bad characters or framing	PGE[MCU]	Normal	Data 1: Data1 Type: ushort Data 2: Data2 Type: ushort Data 3: Data3 Type: ushort Data 4: Data4 Type: ushort
1C0D	7181	Scan request has bad sequence number	PGE[MCU]	Normal	Data 1: Data1 Type: ushort Data 2: Data2 Type: ushort Data 3: Data3 Type: ushort Data 4: Data4 Type: ushort
1C0E	7182	Scan By Table req has bad table number	PGE[MCU]	Normal	Data 1: Data1 Type: ushort Data 2: Data2 Type: ushort Data 3: Data3 Type: ushort Data 4: Data4 Type: ushort
1C0F	7183	Switch not ready for shots-to-lockout	PGE[MCU]	Normal	Data 1: Data1 Type: ushort Data 2: Data2 Type: ushort Data 3: Data3 Type: ushort Data 4: Data4 Type: ushort
1C10	7184	Manual operation request received	PGE[MCU]	Normal	Data 1: Data1 Type: ushort Data 2: Data2 Type: ushort Data 3: Data3 Type: ushort Data 4: Data4 Type: ushort
1C11	7185	Invalid PGE RTU address received	PGE[MCU]	Normal	Data 1: Data1 Type: ushort Data 2: Data2 Type: ushort Data 3: Data3 Type: ushort Data 4: Data4 Type: ushort
1C12	7186	Rejected DNP message rcvd on PGE port	PGE[MCU]	Normal	Data 1: Data1 Type: ushort Data 2: Data2 Type: ushort Data 3: Data3 Type: ushort Data 4: Data4 Type: ushort
1CFF	7423	PGE Test event	PGE[MCU]	Normal	Data 1: Data1 Type: ushort Data 2: Data2 Type: ushort Data 3: Data3 Type: ushort Data 4: Data4 Type: ushort
1D00	7424	SER Packet has bad characters or framing	SER[MCU]	Extended	Data 1: Data1 Type: ushort Data 2: Data2 Type: ushort

Definitions of Historic Events

					Data 3: Data3 Type: ushort Data 4: Data4 Type: ushort
1F00	7936	Prohibit Rest. Xmit Status Active	RTL[MCU]	Normal	Data 1: Data1 Type: ushort Data 2: Data2 Type: ushort Data 3: Data3 Type: ushort Data 4: Data4 Type: ushort
1F01	7937	Enable Rest. Xmit Status Active	RTL[MCU]	Normal	Data 1: Data1 Type: ushort Data 2: Data2 Type: ushort Data 3: Data3 Type: ushort Data 4: Data4 Type: ushort
1F02	7938	Prohibit Rest. Xmit Status Clear	RTL[MCU]	Normal	Data 1: Data1 Type: ushort Data 2: Data2 Type: ushort Data 3: Data3 Type: ushort Data 4: Data4 Type: ushort
1F03	7939	Enable Rest. Xmit Status Clear	RTL[MCU]	Normal	Data 1: Data1 Type: ushort Data 2: Data2 Type: ushort Data 3: Data3 Type: ushort Data 4: Data4 Type: ushort
1F04	7940	Error Registering Team Peer	RTL[MCU]	Normal	Data 1: Data1 Type: ushort Data 2: Data2 Type: ushort Data 3: Data3 Type: ushort Data 4: Data4 Type: ushort
1F05	7941	P2P message response	RTL[MCU]	Normal	Data 1: Data1 Type: ushort Data 2: Data2 Type: ushort Data 3: Data3 Type: ushort Data 4: Data4 Type: ushort
1F06	7942	Clr PR Status Control Pt Rcvd	RTL[MCU]	Normal	Data 1: Data1 Type: ushort Data 2: Data2 Type: ushort Data 3: Data3 Type: ushort Data 4: Data4 Type: ushort
1F07	7943	Clr Rest. Enab Stat Ctrl Pt Rcvd	RTL[MCU]	Normal	Data 1: Data1 Type: ushort Data 2: Data2 Type: ushort Data 3: Data3 Type: ushort Data 4: Data4 Type: ushort
1F08	7944	Prohibit Rest. Sent to Remote Dev	RTL[MCU]	Normal	Data 1: Data1 Type: ushort Data 2: Data2 Type: ushort Data 3: Data3 Type: ushort Data 4: Data4 Type: ushort
1F09	7945	Transfer Trip Sent to Remote Dev	RTL[MCU]	Normal	Data 1: Data1 Type: ushort Data 2: Data2 Type: ushort Data 3: Data3 Type: ushort Data 4: Data4 Type: ushort
1F0A	7946	Error sending P.R. to Rmt Dev	RTL[MCU]	Normal	Data 1: Data1 Type: ushort Data 2: Data2 Type: ushort

Definitions of Historic Events

					Data 3: Data3 Type: ushort Data 4: Data4 Type: ushort
1F0B	7947	Error sending Xfer Trip to Rmt Dev	RTL[MCU]	Normal	Data 1: Data1 Type: ushort Data 2: Data2 Type: ushort Data 3: Data3 Type: ushort Data 4: Data4 Type: ushort
1F0C	7948	Transfer Trip Enabled	RTL[MCU]	Normal	Data 1: Data1 Type: ushort Data 2: Data2 Type: ushort Data 3: Data3 Type: ushort Data 4: Data4 Type: ushort
1F0D	7949	Transfer Trip Disabled	RTL[MCU]	Normal	Data 1: Data1 Type: ushort Data 2: Data2 Type: ushort Data 3: Data3 Type: ushort Data 4: Data4 Type: ushort
1F0E	7950	Clearing Prohib Rest Blocked	RTL[MCU]	All	Clearing Prohibit Rest. Blocked Data 1:Debug Data Data1 Type: ushort Data 2:Debug Data Data2 Type: ushort Data 3:Debug Data Data3 Type: ushort Data 4:Debug Data Data4 Type: ClearPRBlocker
1F0F	7951	DNP3 Response received	RTL[MCU]	Normal	Data 1: Data1 Type: ushort Data 2: Data2 Type: ushort Data 3: Data3 Type: ushort Data 4: Data4 Type: ushort
1F10	7952	P.R. sent from local conditions	RTL[MCU]	Normal	Data 1: Data1 Type: ushort Data 2: Data2 Type: ushort Data 3: Data3 Type: ushort Data 4: Data4 Type: ushort
1F11	7953	Enable Restoration sent to RTU	RTL[MCU]	Normal	Data 1: Data1 Type: ushort Data 2: Data2 Type: ushort Data 3: Data3 Type: ushort Data 4: Data4 Type: ushort
1F12	7954	RMT Xmit PR Enabd Local Conditions	RTL[MCU]	Normal	Data 1: Data1 Type: ushort Data 2: Data2 Type: ushort Data 3: Data3 Type: ushort Data 4: Data4 Type: ushort
1F13	7955	RMT Xmit PR Disabd Local Conditions	RTL[MCU]	Normal	Data 1: Data1 Type: ushort Data 2: Data2 Type: ushort Data 3: Data3 Type: ushort Data 4: Data4 Type: ushort
1F14	7956	RMT Xmit PR Enabd for SCADA	RTL[MCU]	Normal	Data 1: Data1 Type: ushort Data 2: Data2 Type: ushort Data 3: Data3 Type: ushort Data 4: Data4 Type: ushort
1F15	7957	RMT Xmit PR Disabd for SCADA	RTL[MCU]	Normal	Data 1: Data1 Type: ushort Data 2: Data2 Type: ushort

Definitions of Historic Events

					Data 3: Data3 Type: ushort Data 4: Data4 Type: ushort
1F16	7958	Clear PR on HLT removal disabled	RTL[MCU]	Normal	Data 1: Data1 Type: ushort Data 2: Data2 Type: ushort Data 3: Data3 Type: ushort Data 4: Data4 Type: ushort
7218	29208	NETX make runner source	NET[MCU]	Normal	Data 1: Size of runner in RTU addresses Data1 Type: RTUAddress Data 2: Runner RTU lists Data2 Type: RTUlists Data 3: Runner node lists Data3 Type: Nodelists Data 4:Null Data4 Type: ushort
7219	29209	NETX make runner RTUs	NET[MCU]	Normal	Data 1: Size of runner in RTU addresses Data1 Type: RTUAddress Data 2: Runner RTU lists Data2 Type: RTUlists Data 3: Runner node lists Data3 Type: Nodelists Data 4:Null Data4 Type: ushort
721A	29210	NETX make runner destination	NET[MCU]	Normal	Data 1: Size of runner in RTU addresses Data1 Type: RTUAddress Data 2: Runner RTU lists Data2 Type: RTUlists Data 3: Runner node lists Data3 Type: Nodelists Data 4:Null Data4 Type: ushort
721B	29211	NETX begin sendind activation runners	NET[MCU]	Normal	Data 1:Null Data1 Type: ushort Data 2:Null Data2 Type: ushort Data 3:Null Data3 Type: ushort Data 4:Null Data4 Type: ushort
721C	29212	NETX activation object runner sent	NET[MCU]	Normal	Data 1:Null Data1 Type: ushort Data 2: RTU Address Data2 Type: RTUAddress Data 3: Data Length Data3 Type: DataLength Data 4:Null Data4 Type: ushort
721D	29213	NETX forward activate runners	NET[MCU]	Normal	Data 1: Runner Number Data1 Type: RunnerNumber Data 2: Runner Index Number Data2 Type: RunnerIndex Data 3: Type of netlist distribution[RunnerIndex] Data3 Type: ushort Data 4:Null Data4 Type: ushort
721E	29214	NETX forward activation runner index	NET[MCU]	Normal	Data 1: Runner Index Number Data1 Type: RunnerIndex Data 2: Null Data2 Type: ushort Data 3: Null Data3 Type: ushort Data 4: Null Data4 Type: ushort
721F	29215	NETX forward activation runner source	NET[MCU]	Normal	Data 1: RTU Address Data1 Type: RTUAddress Data 2: Source Net Node ID Data2 Type: SrcNodeID Data 3: Destination Net Node ID Data3 Type: DestNodeID Data 4:Null Data4 Type: ushort
7220	29216	NETX forward activation runner sent ok	NET[MCU]	Normal	NETX forwarding activation runner sent ok Data 1: Runner Index Number Data1 Type: RunnerIndex Data 2: RTU Address Data2 Type: RTUAddress Data 3: Data Length Data3 Type: DataLength Data 4:Null Data4 Type: ushort

Definitions of Historic Events

7221	29217	NETX Feeder Net is activated	NET[MCU]	Normal	Data 1: Our position in the Node Index Table Data1 Type: NodeIndex Data 2: Feeder Net Ids in the array Data2 Type: FeederNetID Data 3: Runner Index Data3 Type: RunnerIndex Data 4:Null Data4 Type: ushort
7222	29218	NETX Feeder Net added to division list	NET[MCU]	Normal	Data 1: VM table Index Data1 Type: VMIndex Data 2: Feeder Net Ids in the array Data2 Type: FeederNetID Data 3: Feeder Net CRCs Data3 Type: FeederNetCRC Data 4:Null Data4 Type: ushort
7223	29219	NETX accept activation runner	NET[MCU]	Normal	Data 1: Runner Number Data1 Type: RunnerNumber Data 2: Runner index Data2 Type: RunnerIndex Data 3: Type of netlist distribution Data3 Type: FeederNetObjType Data 4: Null Data4 Type: ushort
7224	29220	NETX accept activation runner failed	NET[MCU]	Normal	Data 1: Runner Number Data1 Type: RunnerNumber Data 2: Identify Actual Runner Data2 Type: RunnerNumber Data 3: Null Data3 Type: ushort Data 4: Null Data4 Type: ushort
7225	29221	NETX accept activation runner result	NET[MCU]	Normal	Data 1: Runner Number Data1 Type: RunnerNumber Data 2: Identify Actual Runner Data2 Type: RunnerNumber Data 3: Null Data3 Type: ushort Data 4: Null Data4 Type: ushort
7226	29222	NETX Make Nodes start	NET[MCU]	Normal	Data 1: Runner Number Data1 Type: FeederNetID Data 2: Local RTU Address Data2 Type: RTUAddress Data 3: Number of associated payload elements Data3 Type: NumPayLoad Data 4:Null Data4 Type: ushort
7227	29223	NETX Make Nodes complete	NET[MCU]	Normal	Data 1: Number of associated payload elements Data1 Type: NumPayLoad Data 2: Number of Node IDs in the list Data2 Type: NumNodeID Data 3:Null Data3 Type: ushort Data 4:Null Data4 Type: ushort
7228	29224	NETX add nodes start	NET[MCU]	Normal	Data 1: Null Data1 Type: ushort Data 2: Team Member Number Data2 Type: TeamRecord Data 3: Feeder Net CRC Data3 Type: FeederNetCRC Data 4: Null Data4 Type: ushort
7229	29225	NETX add node id	NET[MCU]	Normal	Data 1: Node ID Data1 Type: SrcNodeID Data 2: Switch Data2 Type: SWnum Data 3: Side information related to the switch Data3 Type: SideInfo Data 4: Null Data4 Type: ushort
722A	29226	NETX add a new node	NET[MCU]	Normal	Data 1: Feeder Net ID Data1 Type: FeederNetID Data 2: Number of Node Index entries in the Node Table Data2 Type: NumNodeIndex Data 3: Number of Node IDs in list Data3 Type: NumNodeID Data 4:Null Data4 Type: ushort

Definitions of Historic Events

722B	29227	NETX report adjacent NetList start	NET[MCU]	Normal	Data 1: Left Node Index Data1 Type: NodeIndex Data 2:Null Data2 Type: ushort Data 3: Feeder Net CRC of the left Data3 Type: FeederNetCRC Data 4:Null Data4 Type: ushort
722C	29228	NETX report adjacent to runner side1	NET[MCU]	Normal	Data 1: Tie deliverers an adjacent NL to a Runner Source for delivery Data1 Type: RunnerType Data 2: Destination Feeder Net ID Data2 Type: FeederNetID Data 3: Destination Feeder Net CRC Data3 Type: FeederNetCRC Data 4:Null Data4 Type: ushort
722D	29229	NETX report adj netlist obj send to s1	NET[MCU]	Normal	NETX report adjacent netlist object send to side1 Data 1: Number of teams Data1 Type: NumOfTeams Data 2: Destination RTU Address Data2 Type: RTUAddress Data 3: Length of Feeder Net description method Data3 Type: dctsiz Data 4:Null Data4 Type: ushort
722E	29230	NETX Adj fdrnet netlist propagation done	NET[MCU]	Normal	NETX Adj feedernet netlist propagation done Data 1: Adjacent FeederNet's CRC Data1 Type: Hexushort Data 2: Returned netlist runners of the adj feedernet Data2 Type: NumRunners Data 3: Netlist runners in the adj feedernet Data3 Type: NumRunners Data 4: Sent netlist runners of adj feedernet Data4 Type: NumRunners
7230	29232	NETX send adj Feeder Net Runner's qty	NET[MCU]	Normal	NETX send adjacent Feeder Net Runner's qty Data 1: This is the runner's source device Data1 Type: DeviceNumber Data 2: Runner Source row number in nnet Data2 Type: NetViewRowNum Data 3: Number of runners Data3 Type: NumRunners Data 4:Null Data4 Type: ushort
7231	29233	NETX send adj FdrNet runner's FdrNet ID	NET[MCU]	Normal	NETX send adjacent Feeder Net runner's feedernetID Data 1: Runner Index Data1 Type: RunnerIndex Data 2: Feeder Net ID Data2 Type: FeederNetID Data 3: Feeder Net CRC Data3 Type: FeederNetCRC Data 4:Null Data4 Type: ushort
7232	29234	NETX send adj Feeder Net runner's type	NET[MCU]	Normal	NETX send adjacent Feeder Net runner's type Data 1: Runner Type Data1 Type: RunnerType Data 2: Feeder Net ID Data2 Type: FeederNetID Data 3: Feeder Net CRC Data3 Type: FeederNetCRC Data 4:Null Data4 Type: ushort
7233	29235	NETX send adj FNet runner's adj FNet ID	NET[MCU]	Normal	NETX send adjacent Feeder Net runner's adj FeederNetID Data 1: Adjeacent Feeder Net ID Data1 Type: FeederNetID Data 2: Adjeacent Feeder Net CRC Data2 Type: FeederNetCRC Data 3: Number of teams Data3 Type: NumOfTeams Data 4:Null Data4 Type: ushort
7234	29236	NETX send adj Feeder Net runner's rtu	NET[MCU]	Normal	NETX send adjacent Feeder Net runner's rtu Data 1: Runner Number Data1 Type: RunnerNumber Data 2: RTU Address Data2 Type: RTUAddress Data 3: Length of Feeder Net description method Data3 Type: dctsiz Data 4: Null Data4 Type: ushort
7235	29237	NETX request netlist ok	NET[MCU]	Normal	 Data 1: Runner Number Data1 Type: RunnerNumber Data 2: Net destination RTU Address Data2 Type: RTUAddress Data 3: Length of Feeder Net description method Data3 Type:

Definitions of Historic Events

					dctsiz Data 4: Null Data4 Type: ushort
7236	29238	NETX reply Feeder Net req: crc is bad	NET[MCU]	Normal	NETX reply Feeder Net request, crc is bad Data 1: Feeder Net ID Data1 Type: FeederNetID Data 2: Feeder Net CRC Data2 Type: FeederNetCRC Data 3: Feeder Net CRC Data3 Type: FeederNetCRC Data 4:Null Data4 Type: ushort
7237	29239	NETX reply request sent ok	NET[MCU]	Normal	Data 1: Feeder Net ID Data1 Type: FeederNetID Data 2: Destination RTU address Data2 Type: RTUAddress Data 3: Data Length Data3 Type: DataLength Data 4:Null Data4 Type: ushort
7238	29240	NETX reply Feeder Net request not found	NET[MCU]	Normal	Data 1: Feeder Net ID Data1 Type: FeederNetID Data 2: Feeder Net CRC Data2 Type: FeederNetCRC Data 3:Null Data3 Type: ushort Data 4:Null Data4 Type: ushort
7239	29241	NETX requested Feeder Net is a duplicate	NET[MCU]	Normal	Data 1: Feeder Net ID Data1 Type: FeederNetID Data 2: Incoming Feeder Net ID Data2 Type: FeederNetID Data 3:Null Data3 Type: ushort Data 4:Null Data4 Type: ushort
723A	29242	NETX requested Feeder Net good	NET[MCU]	Normal	Data 1: Netx is out of memory Data1 Type: ErrorCodeNETX Data 2: NetxFindspace(incoming number of teams) Data2 Type: NumOfTeams Data 3: Incoming number of teams Data3 Type: NumOfTeams Data 4:Null Data4 Type: ushort
723B	29243	NETX save requested Feeder Net ID	NET[MCU]	Normal	Data 1: Incoming Feeder Net ID Data1 Type: FeederNetID Data 2: Incoming Feeder Net CRC Data2 Type: FeederNetCRC Data 3: Incoming number of teams Data3 Type: NumOfTeams Data 4:Null Data4 Type: ushort
723C	29244	NETX requeued Feeder Net saved ok	NET[MCU]	Normal	Data 1: Size of team array Data1 Type: ushort Data 2: Size of teamsp data Data2 Type: ushort Data 3:Null Data3 Type: ushort Data 4:Null Data4 Type: ushort
723D	29245	NETX forward Feeder Net runner	NET[MCU]	Normal	Data 1: Identify Actual Runner Data1 Type: RunnerNumber Data 2: Runner Index Data2 Type: RunnerIndex Data 3: Type of netlist distribution[RunnerIndex] Data3 Type: FeederNetObjType Data 4:Null Data4 Type: ushort
723E	29246	NETX's forward runner's index	NET[MCU]	Normal	Data 1: Incoming Runner's index Data1 Type: RunnerIndex Data 2:Null Data2 Type: ushort Data 3:Null Data3 Type: ushort Data 4:Null Data4 Type: ushort
723F	29247	NETX forward Feeder Net destination rtu	NET[MCU]	Normal	Data 1: RTU Address Data1 Type: RTUAddress Data 2: Source Node ID Data2 Type: SrcNodeID Data 3: Destination Node ID Data3 Type: DestNodeID Data 4:Null Data4 Type: ushort
7240	29248	NETX forward Feeder Net rnr sent: OK	NET[MCU]	Normal	NETX forward FeederNet runner sent,ok Data 1: Runner Index Data1 Type: RunnerIndex

Definitions of Historic Events

					Data 2: RTU address Data2 Type: RTUAddress Data 3: Data Length Data3 Type: DataLength Data 4:Null Data4 Type: ushort
7243	29251	NETX forward adjacent Feeder Net sent ok	NET[MCU]	Normal	Data 1: Runner Number Data1 Type: RunnerNumber Data 2: Destination RTU Address Data2 Type: RTUAddress Data 3: Length of Feeder Net description method Data3 Type: detsiz Data 4:Null Data4 Type: ushort
7244	29252	NETX save adjacent Feeder Net runner cvd	NET[MCU]	Normal	Data 1: Feeder Net ID Data1 Type: FeederNetID Data 2: Feeder Net CRC Data2 Type: FeederNetCRC Data 3: Number of teams Data3 Type: NumOfTeams Data 4: Null Data4 Type: ushort
7245	29253	NETX save adjacent Feeder Net IDs	NET[MCU]	Normal	Data 1: Adjeacent Feeder Net ID Data1 Type: FeederNetID Data 2: Adjeacent Feeder Net CRC Data2 Type: FeederNetCRC Data 3: Number of teams Data3 Type: NumOfTeams Data 4:Null Data4 Type: ushort
7246	29254	NETX save adjacent Feeder Net node ID	NET[MCU]	Normal	Data 1: Feeder Net Node ID Data1 Type: SrcNodeID Data 2: Node Index Data2 Type: NodeIndex Data 3:Null Data3 Type: ushort Data 4:Null Data4 Type: ushort
7247	29255	NETX save adj FeederNet dup chk hit	NET[MCU]	Normal	NETX save adjacent Feeder Net duplicate check hit Data 1: Feeder Net ID in the array Data1 Type: FeederNetID Data 2: Adjeacent Feeder Net ID Data2 Type: FeederNetID Data 3:Null Data3 Type: ushort Data 4:Null Data4 Type: ushort
7249	29257	NETX save adj Feeder Net number of teams	NET[MCU]	Normal	NETX save adjacent Feeder Net number of teams Data 1: Adjeacent Number of Teams Data1 Type: NumOfTeams Data 2: Starting Index in the array Data2 Type: FeederNetIndex Data 3:Null Data3 Type: ushort Data 4:Null Data4 Type: ushort
724A	29258	NETX save adj FNet; our num of teams	NET[MCU]	Normal	NETX save adjacent Feeder Net, our num of teams Data 1: Our number of teams Data1 Type: NumOfTeams Data 2: Starting Index in the array Data2 Type: FeederNetIndex Data 3:Null Data3 Type: ushort Data 4:Null Data4 Type: ushort
724E	29262	NETX adjacent FNet added to division net	NET[MCU]	Normal	NETX adjacent Feeder Net added to division net Data 1: VM table index for this Feeder Net ID Data1 Type: VMIndex Data 2: Feeder Net ID Data2 Type: FeederNetID Data 3: Feeder Net CRC Data3 Type: FeederNetCRC Data 4:Null Data4 Type: ushort
724F	29263	NETX save adjacent Feeder Net conflict	NET[MCU]	Normal	Data 1: Feeder Net ID in the array Data1 Type: FeederNetID Data 2: Adjeacent Feeder Net ID Data2 Type: FeederNetID Data 3:Null Data3 Type: ushort Data 4:Null Data4 Type: ushort
7250	29264	NETX save adj FeederNet node indx failed	NET[MCU]	Normal	NETX save adjacent Feeder Net node index failed Data 1: Node Index Data1 Type: NodeIndex Data 2: Feeder Net ID Data2 Type: FeederNetID Data 3: Feeder Net CRC Data3 Type: FeederNetCRC Data 4:Null Data4 Type: ushort
7251	29265	NETX save Feeder Net runner received	NET[MCU]	Normal	

Definitions of Historic Events

					Data 1: Feeder Net ID Data1 Type: FeederNetID Data 2: Feeder Net CRC Data2 Type: FeederNetCRC Data 3: Number of teams Data3 Type: NumOfTeams Data 4:Null Data4 Type: ushort
7252	29266	NETX save Feeder Net runner's nodeindex	NET[MCU]	Normal	Data 1: Incoming Feeder Net ID Data1 Type: FeederNetID Data 2: Incoming Feeder Net CRC Data2 Type: FeederNetCRC Data 3: Node Index Data3 Type: NodeIndex Data 4:Null Data4 Type: ushort
7253	29267	NETX save Feeder Net's dup replaced	NET[MCU]	Normal	NETX save Feeder Net's duplicate replaced Data 1: Feeder Net ID in the array Data1 Type: FeederNetID Data 2: Incoming Feeder Net ID Data2 Type: FeederNetID Data 3:Null Data3 Type: ushort Data 4:Null Data4 Type: ushort
7254	29268	NETX save Feeder Net's present status	NET[MCU]	Normal	Data 1: Feeder Net ID in the array Data1 Type: FeederNetID Data 2: Incoming Feeder Net ID Data2 Type: FeederNetID Data 3:Null Data3 Type: ushort Data 4:Null Data4 Type: ushort
725A	29274	NETX save Feeder Net runner success	NET[MCU]	Normal	Data 1: Node Index Data1 Type: NodeIndex Data 2: Left Node/Right Node Index Data2 Type: NodeIndex Data 3: Incoming Feeder Net ID Data3 Type: FeederNetID Data 4:Null Data4 Type: ushort
725B	29275	NETX save Feeder Net's both sides check	NET[MCU]	Normal	Data 1: Incoming Node ID Data1 Type: SrcNodeID Data 2: Team Member Count Data2 Type: ushort Data 3: Node Index Data3 Type: NodeIndex Data 4:Null Data4 Type: ushort
725C	29276	NETX save Feeder Net to our side	NET[MCU]	Normal	Data 1: FeederNetID NodeIndex Data1 Type: FeederNetID Data 2: FeederNetID otherIndex Data2 Type: FeederNetID Data 3: Node Index Data3 Type: NodeIndex Data 4:Null Data4 Type: ushort
725D	29277	NETX saved Feeder Net added to the index	NET[MCU]	Normal	Data 1: Node Index Data1 Type: NodeIndex Data 2: Incoming Feeder Net ID Data2 Type: FeederNetID Data 3: Incoming Feeder Net CRC Data3 Type: FeederNetCRC Data 4:Null Data4 Type: ushort
725F	29279	NETX saved FNet's nodeindx has failed	NET[MCU]	Normal	NETX saved Feeder Net's node index has failed Data 1: Node Index Data1 Type: NodeIndex Data 2: Feeder Net ID Data2 Type: FeederNetID Data 3: Feeder Net CRC Data3 Type: FeederNetCRC Data 4: Null Data4 Type: ushort
7261	29281	NETX accept the Feeder Net runner	NET[MCU]	Normal	Data 1: Runner Number Data1 Type: RunnerNumber Data 2: Identify actual runner Data2 Type: RunnerNumber Data 3:Null Data3 Type: ushort Data 4:Null Data4 Type: ushort
7263	29283	NETX register DNP Address List Size	NET[MCU]	Normal	Data 1:Null Data1 Type: ushort Data 2:Null Data2 Type: ushort Data 3:Null Data3 Type: ushort Data 4:Null Data4 Type: ushort
7264	29284	NETX communication check runner sent ok	NET[MCU]	Normal	Data 1:Null Data1 Type: ushort

Definitions of Historic Events

					Data 2: RTU Address Data2 Type: RTUAddress Data 3: Size of received runner in Bytes Data3 Type: RunnerSize Data 4:Null Data4 Type: ushort
7265	29285	NETX get communication chk runner number	NET[MCU]	Normal	NETX get communication check runner number Data 1: Runner Number Data1 Type: RunnerNumber Data 2:Null Data2 Type: ushort Data 3: Number of associated payload elements Data3 Type: NumPayLoad Data 4:Null Data4 Type: ushort
7266	29286	NETX comm chk rnr's size is mismatched	NET[MCU]	Normal	NETX communication check runner's size is mismatched Data 1: Runner Number Data1 Type: RunnerNumber Data 2: Object Length Data2 Type: DataLength Data 3: Size of received runner in Bytes Data3 Type: RunnerSize Data 4:Null Data4 Type: ushort
7267	29287	NETX get communication chk runner index	NET[MCU]	Normal	NETX get communication check runner index Data 1: Size of received runner in Bytes Data1 Type: RunnerSize Data 2:Null Data2 Type: ushort Data 3: Runner Index Data3 Type: RunnerIndex Data 4:Null Data4 Type: ushort
7268	29288	NETX get communication chk rnr's rtu add	NET[MCU]	Normal	NETX get communication check runner's rtu address Data 1: RTU Address Data1 Type: RTUAddress Data 2: Our local RTU Address Data2 Type: RTUAddress Data 3: Runner Index Data3 Type: RunnerIndex Data 4:Null Data4 Type: ushort
7269	29289	NETX get comm chk rnr's dest rtu	NET[MCU]	Normal	NETX get communication check runner's destination rtu Data 1: RTU Address Data1 Type: RTUAddress Data 2: Our local RTU Address Data2 Type: RTUAddress Data 3: Runner Index Data3 Type: RunnerIndex Data 4:Null Data4 Type: ushort
726A	29290	NETX get comm chkrnr rnr internal node	NET[MCU]	Normal	NETX get communication checkrunner runner internal nodes Data 1: RTU Address Data1 Type: RTUAddress Data 2: Runner Index Data2 Type: RunnerIndex Data 3: Node Count Data3 Type: NodeCount Data 4:Null Data4 Type: ushort
726C	29292	NETX get comm chk runner rtu address	NET[MCU]	Normal	NETX get communication check runner rtu address Data 1: RTU Address Data1 Type: RTUAddress Data 2: Our local RTU Address Data2 Type: RTUAddress Data 3:Null Data3 Type: ushort Data 4:Null Data4 Type: ushort
726D	29293	NETX get comm chk rnr indx fault	NET[MCU]	Normal	NETX get communication check runner index fault Data 1: Size of the received runner in Bytes Data1 Type: RunnerSize Data 2:Null Data2 Type: ushort Data 3: Runner Index Data3 Type: RunnerIndex Data 4:Null Data4 Type: ushort
726E	29294	NETX begin forwarding comm chk rnr	NET[MCU]	Normal	NETX begin forwarding communication check runner Data 1: Identify Actual Runner Number Data1 Type: RunnerNumber Data 2:Null Data2 Type: ushort Data 3: Size of runner in RTU addresses Data3 Type: RTUAddress Data 4:Null Data4 Type: ushort
726F	29295	NETX forwarding comm check rnr sent ok	NET[MCU]	Normal	NETX forwarding communication check runner sent ok Data 1:Null Data1 Type: ushort Data 2: RTU Address Data2 Type: RTUAddress Data 3: Size of received runner in Bytes Data3 Type: RunnerSize Data 4:Null Data4 Type: ushort

7270	29296	NETX accept communication check runner	NET[MCU]	Normal	Data 1: Runner Number Data1 Type: RunnerNumber Data 2:Null Data2 Type: ushort Data 3: Size of runner in RTU Addresses Data3 Type: RTUAddress Data 4:Null Data4 Type: ushort
7271	29297	NETX comm chk rnr size is mismatched	NET[MCU]	Normal	NETX communication check runner size is mismatched Data 1: Runner Number Data1 Type: RunnerNumber Data 2: Data Length Data2 Type: DataLength Data 3: Size of received runner in Bytes Data3 Type: RunnerSize Data 4:Null Data4 Type: ushort
7272	29298	NETX communication check runner's index	NET[MCU]	Normal	Data 1: Size of received runner in Bytes Data1 Type: RunnerSize Data 2:Null Data2 Type: ushort Data 3: Null Data3 Type: RunnerIndex Data 4:Null Data4 Type: ushort
7273	29299	NETX get comm check runner's data	NET[MCU]	Normal	NETX get communication check runner's data Data 1: Runner Number Data1 Type: RunnerNumber Data 2: Object Length Data2 Type: DataLength Data 3: Size of runner in RTU Addresses Data3 Type: RTUAddress Data 4:Null Data4 Type: ushort
7274	29300	NETX done accepting comm check runners	NET[MCU]	Normal	NETX done accepting communication check runners Data 1: Claimed in dispatch Data1 Type: EntryPointDevice Data 2: RTU Address Data2 Type: RTUAddress Data 3: Actual runner number from header Data3 Type: RunnerNumber Data 4:Null Data4 Type: ushort
7275	29301	NETX make table of runner number	NET[MCU]	Normal	Data 1: Runner Number Data1 Type: RunnerNumber Data 2: Feeder Net ID Data2 Type: FeederNetID Data 3: Feeder Net CRC Data3 Type: FeederNetCRC Data 4:Null Data4 Type: ushort
7276	29302	NETX make runner table count	NET[MCU]	Normal	Data 1:Null Data1 Type: ushort Data 2:Null Data2 Type: ushort Data 3: Runner Index Data3 Type: RunnerIndex Data 4:Null Data4 Type: ushort
7277	29303	NETX acpt data collection rnr bad count	NET[MCU]	Normal	NETX accept data collection runner bad count Data 1: Net Destination Node ID Data1 Type: DestNodeID Data 2: Runner Number Data2 Type: RunnerNumber Data 3: Runner's quantity Data3 Type: RunnerQuantity Data 4:Null Data4 Type: ushort
7278	29304	NETX data delivery rnr node index failed	NET[MCU]	Normal	NETX data delivery Runner node index failed Data 1: Node ID Data1 Type: SrcNodeID Data 2:Null Data2 Type: ushort Data 3:Null Data3 Type: ushort Data 4:Null Data4 Type: ushort
7279	29305	NETX data runner information	NET[MCU]	Normal	Data 1:Null Data1 Type: ushort Data 2:Null Data2 Type: ushort Data 3:Null Data3 Type: ushort Data 4:Null Data4 Type: ushort
727A	29306	NETX data runner source rtu	NET[MCU]	Normal	Data 1: The Normal State NetView length Data1 Type: NETViewLength

Definitions of Historic Events

					Data 2: The local device number of the FN runner source device Data2 Type: DeviceIndex Data 3: RTU Address Data3 Type: RTUAddress Data 4:Null Data4 Type: ushort
727B	29307	NETX data runner selection	NET[MCU]	Normal	Data 1: Feeder Net ID Data1 Type: FeederNetID Data 2: Nnet row number Data2 Type: NetViewRowNum Data 3: The local device number of the FN runner source device Data3 Type: DeviceIndex Data 4:Null Data4 Type: ushort
727C	29308	NETX peer is registered already	NET[MCU]	Normal	Data 1: RTU Address Data1 Type: RTUAddress Data 2:Null Data2 Type: ushort Data 3: Registration Status Data3 Type: RegistrationStatus Data 4:Null Data4 Type: ushort
727D	29309	NETX peer is deregistered; reregistering	NET[MCU]	Normal	NETX peer is deregistered, re-registering Data 1: RTU Address Data1 Type: RTUAddress Data 2:Null Data2 Type: ushort Data 3: Registration Status Data3 Type: RegistrationStatus Data 4:Null Data4 Type: ushort
727E	29310	NETX dest device node indx failure	NET[MCU]	Normal	NETX destination device node index failure Data 1: Find this node in the NLTA arrays Data1 Type: IndexMngTable Data 2: VM table Index Data2 Type: VMIndex Data 3: Index into the substation list for Feeder Net "tree root"> Data3 Type: Substation Data 4:Null Data4 Type: ushort
7288	29320	NETX dispatch designer Feeder Net object	NET[MCU]	Normal	Data 1: Source RTU Address Data1 Type: RTUAddress Data 2: Destination RTU Address Data2 Type: RTUAddress Data 3: Destination Node ID Data3 Type: DestNodeID Data 4:Null Data4 Type: ushort
7289	29321	NETX dispatch FeederNet source and dest	NET[MCU]	Normal	NETX dispatch Feeder Net source and destination Data 1: Source RTU Address Data1 Type: RTUAddress Data 2: Destination RTU Address Data2 Type: RTUAddress Data 3: Destination Node ID Data3 Type: DestNodeID Data 4:Null Data4 Type: ushort
728A	29322	NETX dispatch Feeder Net dest Node ID	NET[MCU]	Normal	NETX dispatch Feeder Net destination Node ID Data 1: Runner Number Data1 Type: RunnerNumber Data 2: Incoming Feeder Net ID Data2 Type: FeederNetID Data 3: Incoming Feeder Net CRC Data3 Type: FeederNetCRC Data 4:Null Data4 Type: ushort
728B	29323	NETX dispatch Feeder Net delivery index	NET[MCU]	Normal	Data 1: Incoming Feeder Net ID Data1 Type: FeederNetID Data 2: Incoming Feeder Net CRC Data2 Type: FeederNetCRC Data 3: Runner Index Data3 Type: RunnerIndex Data 4:Null Data4 Type: ushort
728C	29324	NETX dispatch Feeder Net delivery save	NET[MCU]	Normal	Data 1: Destination Index Data1 Type: DestinationIndex Data 2: Runner Number Data2 Type: RunnerNumber Data 3: Size of runner in RTU Addresses Data3 Type: RTUAddress Data 4:Null Data4 Type: ushort
728E	29326	NETX dispatch comm chk source and dest	NET[MCU]	Normal	NETX dispatch communication check source and destination Data 1: Source RTU Adress Data1 Type: RTUAddress Data 2: Destination RTU Address Data2 Type: RTUAddress

Definitions of Historic Events

					Data 3: Destination Node ID Data3 Type: DestNodeID Data 4:Null Data4 Type: ushort
728F	29327	NETX dispatch comm check FeederNet ID	NET[MCU]	Normal	NETX dispatch communication check Feeder Net ID Data 1: Claimed in Dispatch Data1 Type: EntryPointDevice Data 2: Destination Index Data2 Type: DestinationIndex Data 3: Number of associated payload elements Data3 Type: NumPayLoad Data 4:Null Data4 Type: ushort
7295	29333	NETX dispatch comm check sent to	NET[MCU]	Normal	NETX dispatch communication check sent to Data 1: Runner Number Data1 Type: RunnerNumber Data 2: Feeder Net ID Data2 Type: FeederNetID Data 3: Feeder Net CRC Data3 Type: FeederNetCRC Data 4:Null Data4 Type: ushort
7296	29334	NETX dispatch comm check handled	NET[MCU]	Normal	NETX dispatch communication check handled Data 1: Runner Index Data1 Type: RunnerIndex Data 2: Null Data2 Type: ushort Data 3: Null Data3 Type: ushort Data 4: Null Data4 Type: ushort
7297	29335	NETX dispatch netlist rqst src and dest	NET[MCU]	Normal	NETX dispatch netlist request source and destination Data 1: Source RTU Address Data1 Type: RTUAddress Data 2: Destination RTU Address Data2 Type: RTUAddress Data 3: Destination Node ID Data3 Type: DestNodeID Data 4:Null Data4 Type: ushort
7298	29336	NETX dispatch netlist request FNet ID	NET[MCU]	Normal	NETX dispatch netlist request Feeder Net ID Data 1: Destination RTU Address Data1 Type: RTUAddress Data 2: FeederNetID Data2 Type: FeederNetID Data 3: FeederNetCRC Data3 Type: FeederNetCRC Data 4:Null Data4 Type: ushort
729A	29338	NETX dispatch primary rqst netlist resp	NET[MCU]	Normal	NETX dispatch primary request netlist response Data 1: Source RTU Address Data1 Type: RTUAddress Data 2: Destination RTU Address Data2 Type: RTUAddress Data 3: Destination Node ID Data3 Type: DestNodeID Data 4:Null Data4 Type: ushort
729B	29339	NETX dispatch prim netlist src and dest	NET[MCU]	Normal	NETX dispatch primary netlist source and destination Data 1: Source RTU Address Data1 Type: RTUAddress Data 2: Destination RTU Address Data2 Type: RTUAddress Data 3: Destination Node ID Data3 Type: DestNodeID Data 4:Null Data4 Type: ushort
729C	29340	NETX dispatch primary netlist source ID	NET[MCU]	Normal	Data 1: Source RTU Address Data1 Type: RTUAddress Data 2: Data Length Data2 Type: DataLength Data 3: Net source Node ID Data3 Type: SrcNodeID Data 4:Null Data4 Type: ushort
729D	29341	NETX dispatch primary netlist indx found	NET[MCU]	Normal	NETX dispatch primary netlist index found Data 1: Feeder Net ID Data1 Type: FeederNetID Data 2: Feeder Net CRC Data2 Type: FeederNetCRC Data 3: Runner Index Data3 Type: RunnerIndex Data 4:Null Data4 Type: ushort
729E	29342	NETX dispatch primary netlist indx nums	NET[MCU]	Normal	NETX dispatch primary netlist indexed numbers Data 1: Destination Index Data1 Type: DestinationIndex Data 2: Runner Number Data2 Type: RunnerNumber Data 3: Size of runner in RTU Addresses Data3 Type: RTUAddress Data 4:Null Data4 Type: ushort
72A0	29344	NETX dispatch newadj delivery rnr src ST	NET[MCU]	Normal	NETX dispatch new adjacent delivery runner source ST Data 1: Source RTU Address Data1 Type: RTUAddress

Definitions of Historic Events

					Data 2: Destination RTU Address Data2 Type: RTUAddress Data 3: Net Destination Node ID Data3 Type: DestNodeID Data 4:Null Data4 Type: ushort
72A1	29345	NETX dispatch new adj delivery rnr done	NET[MCU]	Normal	NETX dispatch new adjacent delivery runner done Data 1:Null Data1 Type: ushort Data 2:Null Data2 Type: ushort Data 3:Null Data3 Type: ushort Data 4:Null Data4 Type: ushort
72A4	29348	NETX dispatch adj netlist reporter src	NET[MCU]	Normal	NETX dispatch adjacent netlist reporter source Data 1: Source RTU Address Data1 Type: RTUAddress Data 2: Destination RTU Address Data2 Type: RTUAddress Data 3: Net destination Node ID Data3 Type: DestNodeID Data 4:Null Data4 Type: ushort
72A5	29349	NETX dispatch adj netlist report sending	NET[MCU]	Normal	NETX dispatch adjacent netlist reporter sending Data 1: Runner Number Data1 Type: RunnerNumber Data 2: Number of actual data elements in DLV Data2 Type: NumDataElements Data 3: Net destination Node ID Data3 Type: DestNodeID Data 4:Null Data4 Type: ushort
72A8	29352	NETX dispat act Netlist rep fail to frwd	NET[MCU]	Normal	NETX dispatch Active Netlist reporter failed to forward Data 1: Source RTU Address Data1 Type: RTUAddress Data 2: Destination RTU Address Data2 Type: RTUAddress Data 3: Net destination Node ID Data3 Type: DestNodeID Data 4:Null Data4 Type: ushort
72AA	29354	NETX state machine A state 01 arrival	NET[MCU]	Normal	Data 1:Null Data1 Type: ushort Data 2: Waiting for IT Designer Data2 Type: StatusFeedbackArea Data 3: Null Data3 Type: StatusFeedbackArea Data 4:Null Data4 Type: ushort
72AB	29355	NETX state machA state 01 depart FNet ID	NET[MCU]	Normal	NETX state machine A state 01 depart Feeder Net ID Data 1: Incoming Feeder Net ID from IntelliTeam Designer Data1 Type: FeederNetID Data 2: Incoming new Feeder Net CRC from IntelliTeam Designer Data2 Type: FeederNetCRC Data 3:Null Data3 Type: ushort Data 4:Null Data4 Type: ushort
72AC	29356	NETX state machA state01 num of teams	NET[MCU]	Normal	NETX state machine A state 01 number of teams Data 1: Feeder Net incoming team array number of teams Data1 Type: INCNUMTEAM Data 2: Number of Device-Wire pairs from prep function Data2 Type: DeviceWirepairs Data 3: Number of Incoming Feeder Net Flags from ITD Data3 Type: FeederNetObjectFlags Data 4:Null Data4 Type: ushort
72AD	29357	NETX state machine A state 02 arrival	NET[MCU]	Normal	Data 1:Null Data1 Type: ushort Data 2: Perform NETview Express analysis Data2 Type: StatusFeedbackArea Data 3: Waiting for IT Designer Data3 Type: StatusFeedbackArea Data 4:Null Data4 Type: ushort
72AE	29358	NETX statemachA state02 arriv net stat	NET[MCU]	Normal	NETX state machine A state 02 arrival net status Data 1: Number of devices in the Feeder Net Data1 Type: NumDevicesinFN Data 2: Number if entries in row,one for device,one for wire Data2 Type: ExpressNetViewRow Data 3: Number of paths in this Feeder Net Data3 Type: NumPaths Data 4:Null Data4 Type: ushort

72AF	29359	NETX state machine A state 03 arrival	NET[MCU]	Normal	<p>Data 1:Null Data1 Type: ushort Data 2: Create comm check runners and launch, then wait for return Data2 Type: StatusFeedbackArea Data 3: Perform NETview Express analysis Data3 Type: StatusFeedbackArea Data 4:Null Data4 Type: ushort</p>
72B0	29360	Register the peer RTU Address	NET[MCU]	Normal	<p>Data 1: Number of NETLIST runners in RunnerSource Data1 Type: NETLISTRNR Data 2: Size of runner in RTU addresses Data2 Type: RTUAddress Data 3: RTU address of the controls for each stop along the way Data3 Type: RTUAddress Data 4:Null Data4 Type: ushort</p>
72B1	29361	NetX statemachA state03 peer regs fail	NET[MCU]	Normal	<p>NetX state machine A state 03 peer registration has failed Data 1: Runner Number Data1 Type: RunnerNumber Data 2: RTU Address Data2 Type: RTUAddress Data 3: Registration Status Data3 Type: RegistrationStatus Data 4:Null Data4 Type: ushort</p>
72B2	29362	NetX statemachA state03 all peers regs	NET[MCU]	Normal	<p>NetX state machine A state 03 all peers registered Data 1: Common check runners timeout counter Data1 Type: ushort Data 2:Null Data2 Type: ushort Data 3: Number of NETLIST runners in RunnerSource Data3 Type: NETLISTRNR Data 4:Null Data4 Type: ushort</p>
72B3	29363	Netx state machA state 03 timeout failed	NET[MCU]	Normal	<p>Netx state machine A state 03 timeout failed Data 1: Common check of NETLIST runners in RunnerSource Data1 Type: ushort Data 2:Null Data2 Type: ushort Data 3: Number of NETLIST runners in RunnerSource Data3 Type: NETLISTRNR Data 4:Null Data4 Type: ushort</p>
72B4	29364	NETX statemachA state03 make rnrs failed	NET[MCU]	Normal	<p>NETX state machine A state 03 make runners failed Data 1: NETV source normal Data1 Type: NETVSRC Data 2:Null Data2 Type: ushort Data 3:Null Data3 Type: ushort Data 4:Null Data4 Type: ushort</p>
72B5	29365	NETX state machine A state 04 arrival	NET[MCU]	Normal	<p>Data 1:Null Data1 Type: ushort Data 2: go ahead and SEND the CCRs Data2 Type: StatusFeedbackArea Data 3: Create comm check runners and launch, then wait for return Data3 Type: StatusFeedbackArea Data 4:Null Data4 Type: ushort</p>
72B6	29366	NETX state machine A state 04 is done	NET[MCU]	Normal	<p>Data 1: Common check of NETLIST runners in RunnerSource Data1 Type: ushort Data 2:Null Data2 Type: ushort Data 3: Number of NETLIST runners in RunnerSource Data3 Type: NETLISTRNR Data 4:Null Data4 Type: ushort</p>
72B7	29367	NETX state machine A state 05 arrival	NET[MCU]	Normal	<p>Data 1:Null Data1 Type: ushort Data 2: Start FN delivery Runners Data2 Type: StatusFeedbackArea Data 3: go ahead and SEND the CCRs Data3 Type:</p>

Definitions of Historic Events

					StatusFeedbackArea Data 4:Null Data4 Type: ushort
72B8	29368	NETX statemachA state 05 arrival FNet ID	NET[MCU]	Normal	<p>NETX state machine A state 05 arrival FeederNET ID</p> <p>Data 1: Feeder Net incoming team array number of teams Data1 Type: INCNUMTEAM</p> <p>Data 2: Number of NETLIST runners in RunnerSource Data2 Type: NETLISTRNR</p> <p>Data 3: Incoming new Feeder Net ID from IntelliTeam Designer Data3 Type: FeederNetID</p> <p>Data 4:Null Data4 Type: ushort</p>
72B9	29369	NETX state machine A state 06 arrival	NET[MCU]	Normal	<p>Data 1:Null Data1 Type: ushort</p> <p>Data 2: Send activate runners Data2 Type: StatusFeedbackArea</p> <p>Data 3: Start FN delivery Runners Data3 Type: StatusFeedbackArea</p> <p>Data 4:Null Data4 Type: ushort</p>
72BA	29370	NETX state machine A state 07 arrival	NET[MCU]	Normal	<p>Data 1:Null Data1 Type: ushort</p> <p>Data 2: Dashboard Feedback at the end of the successful deployment Data2 Type: StatusFeedbackArea</p> <p>Data 3: Send activate runners Data3 Type: StatusFeedbackArea</p> <p>Data 4:Null Data4 Type: ushort</p>
72BB	29371	NETX state machine A state 11 arrival	NET[MCU]	Normal	<p>Data 1:Null Data1 Type: ushort</p> <p>Data 2: Error Reporting Data2 Type: StatusFeedbackArea</p> <p>Data 3: Dashboard Feedback at the end of the successful deployment Data3 Type: StatusFeedbackArea</p> <p>Data 4:Null Data4 Type: ushort</p>
72BF	29375	NETX state machine C state 2 arrival	NET[MCU]	Normal	<p>Data 1:Null Data1 Type: ushort</p> <p>Data 2: Checks Registrations of the Destination RTU Addresses for the CCRs to be sent Data2 Type: StatusFeedbackArea</p> <p>Data 3: Error Reporting Data3 Type: StatusFeedbackArea</p> <p>Data 4:Null Data4 Type: ushort</p>
72C0	29376	NETX statemachC state2 regs is good	NET[MCU]	Normal	<p>NETX state machine C state 2 registration is good</p> <p>Data 1: Runner Number Data1 Type: RunnerNumber</p> <p>Data 2: RTU Address Data2 Type: RTUAddress</p> <p>Data 3: Registration Status Data3 Type: RegistrationStatus</p> <p>Data 4:Null Data4 Type: ushort</p>
72C1	29377	NETX state machC state 2 regs failed	NET[MCU]	Normal	<p>NETX state machine C state 2 registration failed</p> <p>Data 1: Runner Number Data1 Type: RunnerNumber</p> <p>Data 2: RTU Address Data2 Type: RTUAddress</p> <p>Data 3: Registration Status Data3 Type: RegistrationStatus</p> <p>Data 4:Null Data4 Type: ushort</p>
72C2	29378	NETX state machine C state 02 is done	NET[MCU]	Normal	<p>Data 1:Null Data1 Type: ushort</p> <p>Data 2: Current state of machine C State 2 Data2 Type: StatusFeedbackArea</p> <p>Data 3: Previous state of machine C State 2 Data3 Type: StatusFeedbackArea</p> <p>Data 4:Null Data4 Type: ushort</p>
72C3	29379	NETX state machine D state 01 Arrival	NET[MCU]	Normal	<p>Data 1:Null Data1 Type: ushort</p> <p>Data 2: Idle state waiting for management Sequence to be initiated upon need Data2 Type: StatusFeedbackArea</p> <p>Data 3: Null Data3 Type: StatusFeedbackArea</p> <p>Data 4:Null Data4 Type: ushort</p>

72C4	29380	NETX state machine D state 02 Arrival	NET[MCU]	Normal	<p>Data 1:Null Data1 Type: ushort Data 2: Registers the RTU of the control that sent the Netlist Reporter Runner to us Data2 Type: StatusFeedbackArea Data 3: Idle state waiting for management Sequence to be initiated upon need Data3 Type: StatusFeedbackArea Data 4:Null Data4 Type: ushort</p>
72C5	29381	NETX state machD state 2 registered DNP	NET[MCU]	Normal	<p>NETX state machine D state 2 registered DNP Data 1: RTU Address Data1 Type: RTUAddress Data 2:Null Data2 Type: ushort Data 3:Null Data3 Type: ushort Data 4:Null Data4 Type: ushort</p>
72C6	29382	NETX state machine D state 3 arrival	NET[MCU]	Normal	<p>Data 1:Null Data1 Type: ushort Data 2: Checks on and waits for successful registration of the DNP Address from D0 Data2 Type: StatusFeedbackArea Data 3: Registers the RTU of the control that sent the Netlist Reporter Runner to us Data3 Type: StatusFeedbackArea Data 4:Null Data4 Type: ushort</p>
72C7	29383	NETX state machD state 03 regs failed	NET[MCU]	Normal	<p>NETX state machine D state 03 registration failed Data 1: RTU Address Data1 Type: RTUAddress Data 2:Null Data2 Type: ushort Data 3: Registration Status Data3 Type: RegistrationStatus Data 4:Null Data4 Type: ushort</p>
72C8	29384	NETX statemachD state 03 regs is good	NET[MCU]	Normal	<p>NETX state machine D state 03 registration is good Data 1: RTU Address Data1 Type: RTUAddress Data 2:Null Data2 Type: ushort Data 3: Registration Status Data3 Type: RegistrationStatus Data 4:Null Data4 Type: ushort</p>
72C9	29385	NETX state machine D state 04 arrival	NET[MCU]	Normal	<p>Data 1:Null Data1 Type: ushort Data 2: Scans the list of reported Primary FeederNets and requests each one with delay between each request provided by next state waiting on the reply. Data2 Type: StatusFeedbackArea Data 3: Checks on and waits for successful registration of the DNP Address from D0 Data3 Type: StatusFeedbackArea Data 4:Null Data4 Type: ushort</p>
72CA	29386	NETX state machine D state 05 arrival	NET[MCU]	Normal	<p>Data 1:Null Data1 Type: ushort Data 2: Waits until the requested Feeder Net has been returned then goes back to previous state Data2 Type: StatusFeedbackArea Data 3: Scans the list of reported Primary FeederNets and requests each one with delay between each request provided by next state waiting on the reply. Data3 Type: StatusFeedbackArea Data 4:Null Data4 Type: ushort</p>
72CB	29387	NETX state machine D state 06 arrival	NET[MCU]	Normal	<p>Data 1:Null Data1 Type: ushort Data 2: the list of reported Adjacent FeederNets and requests each one with delay between each request provided by next state waiting on the reply Data2 Type: StatusFeedbackArea Data 3: Waits until the requested Feeder Net has been returned then goes back to previous state Data3 Type: StatusFeedbackArea Data 4:Null Data4 Type: ushort</p>
72CC	29388	NETX state machine D state 07 arrival	NET[MCU]	Normal	<p>Data 1:Null Data1 Type: ushort Data 2: Waits until the requested Feeder Net has been returned then goes back to previous state Data2 Type: StatusFeedbackArea Data 3: The list of reported Adjacent FeederNets and requests each one with delay between each request provided by next state waiting on the reply Data3 Type: StatusFeedbackArea Data 4:Null Data4 Type: ushort</p>

Definitions of Historic Events

					state waiting on the reply Data3 Type: StatusFeedbackArea Data 4:Null Data4 Type: ushort
72CD	29389	NETX state machine D state 08 arrival	NET[MCU]	Normal	Data 1:Null Data1 Type: ushort Data 2: All Delivered now, proceed to apply Data2 Type: StatusFeedbackArea Data 3: Waits until the requested Feeder Net has been returned then goes back to previous state Data3 Type: StatusFeedbackArea Data 4:Null Data4 Type: ushort
72CE	29390	NETX state machD state8 make div net	NET[MCU]	Normal	NETX state machine D state 8 make division net Data 1: Record Where in VM find array this net list is in Data1 Type: ushort Data 2: Feeder Net ID Data2 Type: FeederNetID Data 3: Feeder Net CRC Data3 Type: FeederNetCRC Data 4: Null Data4 Type: ushort
72CF	29391	NETX state machine D state 9 arrival	NET[MCU]	Normal	Data 1:Null Data1 Type: ushort Data 2: Registers New RTUs and copies our DivisionNet information to appropriate tables Data2 Type: StatusFeedbackArea Data 3: All Delivered now, proceed to apply Data3 Type: StatusFeedbackArea Data 4:Null Data4 Type: ushort
72D0	29392	NETX state machine D state 09 Make Nodes	NET[MCU]	Normal	Data 1: Index into the substation list for Feeder Net "tree root" Data1 Type: Substation Data 2: Power Source Data-Starting Row in Present NetView for this Power Source Data2 Type: ushort Data 3:Null Data3 Type: ushort Data 4:Null Data4 Type: ushort
72D1	29393	NETX state machD state9 make nodes fail	NET[MCU]	Normal	NETX state machine D state 9 make nodes fail Data 1:Null Data1 Type: ushort Data 2:Null Data2 Type: ushort Data 3:Null Data3 Type: ushort Data 4:Null Data4 Type: ushort
72D2	29394	NETX state machine D state 10 arrival	NET[MCU]	Normal	Data 1:Null Data1 Type: ushort Data 2: Cleanup and return to Idle state Data2 Type: StatusFeedbackArea Data 3: All Delivered now, proceed to apply Data3 Type: StatusFeedbackArea Data 4: Null Data4 Type: ushort
72D3	29395	NETX state machine E state 01 arrival	NET[MCU]	Normal	Data 1:Null Data1 Type: ushort Data 2: Runner Source Device Data Collection and Data Distribution manager IDLEStarts Runners on signal from State Machine F State 4 when it finds we are a runner source Data2 Type: StatusFeedbackArea Data 3: Cleanup and return to Idle state Data3 Type: StatusFeedbackArea Data 4:Null Data4 Type: ushort
72D4	29396	NETX state machine F state 01 Arrival	NET[MCU]	Normal	Data 1: Runner Number for non-runner source devices Data1 Type: RunnerNumber Data 2: State Machine F Manages sequences of operations in support of multiple simultaneous, Netlist Distributions Data2 Type: StatusFeedbackArea Data 3: Null Data3 Type: StatusFeedbackArea Data 4: Null Data4 Type: ushort

Definitions of Historic Events

72D5	29397	NETX state machine F state 02 Arrival	NET[MCU]	Normal	<p>Data 1: Runner Number for non-runner source devices Data1 Type: RunnerNumber</p> <p>Data 2: This state waits for the arrival of all required Activation Runners then applies the new Feeder Net to NETV and DAT Data2 Type: StatusFeedbackArea</p> <p>Data 3: State Machine F Manages sequences of operations in support of multiple simultaneous, Netlist Distributions Data3 Type: StatusFeedbackArea</p> <p>Data 4: Null Data4 Type: ushort</p>	
72D6	29398	NETX state machine F state 03 Arrival	NET[MCU]	Normal	<p>Data 1: Runner Number for non-runner source devices Data1 Type: RunnerNumber</p> <p>Data 2: This state waits for the arrival of all required Activation Runners then applies the new Feeder Net to NETV and DAT Data2 Type: StatusFeedbackArea</p> <p>Data 3: State Machine F Manages sequences of operations in support of multiple simultaneous, Netlist Distributions Data3 Type: StatusFeedbackArea</p> <p>Data 4: Null Data4 Type: ushort</p>	
72D7	29399	NETX state machine F state 04 Arrival	NET[MCU]	Normal	<p>Data 1: Runner Number for non-runner source devices Data1 Type: RunnerNumber</p> <p>Data 2: Releases our claim on PushingHoldoff, then waits for all appropriate runners to have returned,then Analyzes to see if this is a runner source, lists Runners if yes, checks RSD Registration Data2 Type: StatusFeedbackArea</p> <p>Data 3: State Machine F Manages sequences of operations in support of multiple simultaneous, Netlist Distributions Data3 Type: StatusFeedbackArea</p> <p>Data 4: Null Data4 Type: ushort</p>	
72D8	29400	NETX state machF state 04 runner source	NET[MCU]	Normal	<p>NETX state machine F state 04 runner source</p> <p>Data 1: Runner Source Device Data1 Type: RSD</p> <p>Data 2: Null Data2 Type: ushort</p> <p>Data 3: Null Data3 Type: ushort</p> <p>Data 4: Null Data4 Type: ushort</p>	
72DA	29402	NETX state machine G state 01 Arrival	NET[MCU]	Normal	<p>Data 1: Null Data1 Type: ushort</p> <p>Data 2: State Machine G Manages sequences of operations in support of Sending of Feeder Net Deployment Runner Objects. State 1 is the IdleState Data2 Type: StatusFeedbackArea</p> <p>Data 3: Null Data3 Type: StatusFeedbackArea</p> <p>Data 4: Null Data4 Type: ushort</p>	
72DB	29403	NETx state machine G state 01 deployment	NET[MCU]	Normal	<p>Data 1: Incoming number of teams Data1 Type: INCNUMTEAM</p> <p>Data 2: Number of netlist runners Data2 Type: NETLISTRNR</p> <p>Data 3: Feeder Net ID from IntelliTeam Designer Data3 Type: FeederNetID</p> <p>Data 4: Null Data4 Type: ushort</p>	
72DC	29404	NETX state machine G state 02 Arrival	NET[MCU]	Normal	<p>Data 1: Null Data1 Type: ushort</p> <p>Data 2: G State 2 Creates and sends (store object) until the runner-list required number of runners has been sent Data2 Type: StatusFeedbackArea</p> <p>Data 3: State Machine G Manages sequences of operations in support of Sending of Feeder Net Deployment Runner Objects Data3 Type: StatusFeedbackArea</p> <p>Data 4: Null Data4 Type: ushort</p>	
72DD	29405	NETX state machG state02 store object	NET[MCU]	Normal	<p>NETX state machine G state 02 store object</p> <p>Data 1: Runner Number Data1 Type: RunnerNumber</p>	

Definitions of Historic Events

					Data 2: RTU Address Data2 Type: RTUAddress Data 3: Data Length Data3 Type: DataLength Data 4:Null Data4 Type: ushort
72E1	29409	NETX state machH state02 storage ok	NET[MCU]	Normal	NETX state machine H state 02 storeage ok Data 1: Runner Number Data1 Type: RunnerNumber Data 2: Destination RTU Address Data2 Type: RTUAddress Data 3: Null Data3 Type: ushort Data 4: Null Data4 Type: ushort
72E6	29414	NETX too many in Netview row	NET[MCU]	Normal	NETX too many in Netview row (would overflow) Data 1: Current row number Data1 Type: ushort Data 2:Null Data2 Type: ushort Data 3:Null Data3 Type: ushort Data 4:Null Data4 Type: ushort
72E7	29415	NETX too many Netview columns	NET[MCU]	Normal	Data 1: Current row number Data1 Type: ushort Data 2:Null Data2 Type: ushort Data 3:Null Data3 Type: ushort Data 4:Null Data4 Type: ushort
72E8	29416	Overflow the device instance table	NET[MCU]	Normal	Data 1: Device Type Data1 Type: dev Data 2:Null Data2 Type: ushort Data 3:Null Data3 Type: ushort Data 4:Null Data4 Type: ushort
72E9	29417	NETX too many substations in Feeder Net	NET[MCU]	Normal	Would overflow Data 1: Number of team record Data1 Type: nt Data 2:Null Data2 Type: ushort Data 3:Null Data3 Type: ushort Data 4:Null Data4 Type: ushort
72EA	29418	NETX too many netx devices	NET[MCU]	Normal	Data 1:Null Data1 Type: ushort Data 2: Number of device connection present,counter,list length Data2 Type: nsngl Data 3:Null Data3 Type: ushort Data 4:Null Data4 Type: ushort
72EB	29419	NETX too many netx columns	NET[MCU]	Normal	If Data4 is 4 then data 1 would be the deviceCountTotal Data 1:Null Data1 Type: ushort Data 2: Number of device connection present,counter,list length Data2 Type: nsngl Data 3:Null Data3 Type: ushort Data 4:Null Data4 Type: ushort
72EC	29420	NETX too many netx rows	NET[MCU]	Normal	If Data4 is 10 then data 1 would be the deviceCountTotal Data 1:Null Data1 Type: ushort Data 2: Number of device connection present,counter,list length Data2 Type: nsngl Data 3:Null Data3 Type: ushort Data 4:Null Data4 Type: ushort
72ED	29421	NETX too many NETV rows	NET[MCU]	Normal	Data 1: Current row number Data1 Type: ushort Data 2:Null Data2 Type: ushort Data 3:Null Data3 Type: ushort Data 4:Null Data4 Type: ushort
72EE	29422	NETX too many DGs in Feeder Net	NET[MCU]	Normal	Data 1: Current row number Data1 Type: ushort Data 2:Null Data2 Type: ushort Data 3:Null Data3 Type: ushort Data 4:Null Data4 Type: ushort

72EF	29423	NETX found DG in Feeder Net	NET[MCU]	Normal	Data 1: Current row number Data1 Type: ushort Data 2:Null Data2 Type: ushort Data 3:Null Data3 Type: ushort Data 4:Null Data4 Type: ushort
------	-------	-----------------------------	----------	--------	--